

1 Release Description

The i.MX Android™ automotive-11.0.0_1.1.0 release is an Android Automotive GA (RFP) release on NXP's i.MX 8QuadXPlus/8QuadMax MEK board and platform, which is based on Android 11. It supports the device type In-vehicle infotainment defined in <https://source.android.com/devices/automotive/>.

i.MX Android automotive-11.0.0_1.1.0 release includes all necessary code, documents, and tools to assist users in building and running Android Automotive on the i.MX 8QuadXPlus/8QuadMax MEK board from scratch. Pre-built images are also included for a quick trial on the following platforms:

- i.MX 8QuadXPlus/8QuadMax MEK Board and Platform

This release includes all porting and enhancements based on the Android open source code.

Most of the deliveries in this release are provided in source code with the exception of some proprietary modules/libraries from third parties.

2 Supported Hardware SoC/Boards

The supported hardware system-on-chip (SoCs)/boards are listed as follows:

- i.MX 8QuadMax (Silicon Revision B0) MEK Board and Platform
- i.MX 8QuadXPlus (Silicon Revision B0, C0) MEK Board and Platform

3 Release Package Contents

The automotive-11.0.0_1.1.0 release package includes the following software and documents.

Table 1. Release package contents

i.MX Android proprietary source code package	<ul style="list-style-type: none"> • imx-automotive-11.0.0_1.1.0.tar.gz: i.MX Android Automotive proprietary source code package to enable Android Automotive on i.MX boards. For example, Hardware Abstraction Layer implementation, hardware codec acceleration, etc.
Documents	<p>The following documents are included in android_automotive-11.0.0_1.1.0_docs.zip:</p> <ul style="list-style-type: none"> • <i>Android™ Quick Start Guide (AQSUG)</i>: A document that explains how to run Android Automotive on an i.MX board using prebuilt images. • <i>Android™ User's Guide (AUG)</i>: A document describing procedures for configuring and building this release package. • <i>Android™ Release Notes (ARN)</i>: A document that introduces key updates and known issues in this release.

Table continues on the next page...

Contents

1	Release Description.....	1
2	Supported Hardware SoC/Boards	1
3	Release Package Contents.....	1
4	Features	2
5	Multimedia Codecs.....	4
6	Change Log.....	4
7	Known Issues and Limitations.....	4
8	Revision History.....	5



Table 1. Release package contents (continued)

	<ul style="list-style-type: none"> • <i>i.MX Android™ Extended Codec Release Notes (IMXACRN)</i>: A document that provides the extended codec information. • <i>i.MX Android™ Security User's Guide (ASUG)</i>: A document that describes how to do customization work on security features supported by i.MX Android software. • <i>i.MX TensorFlow Lite on Android User's Guide (IMXTFLUG)</i>: A document that describes the TensorFlow Lite on Android platform. • <i>i.MX Graphics User's Guide (IMXGRAPHICUG)</i>: A document that describes GPU 2D API, Tools, Memory, and Application programming guidelines.
Prebuilt images	<p>You can test Android Automotive with a prebuilt image on i.MX reference board before building any code:</p> <ul style="list-style-type: none"> • <i>automotive-11.0.0_1.1.0_image_8qmek.tar.gz</i>: Prebuilt images with NXP extended features with the EVS function enabled in the Cortex-M4 CPU core for the i.MX 8QuadMax/8QuadXPlus MEK board. The extended features include more multimedia format support. • <i>automotive-11.0.0_1.1.0_image_8qmek2.tar.gz</i>: Prebuilt images with NXP extended features without EVS function enabled in the Cortex-M4 CPU core for the i.MX 8QuadMax/8QuadXPlus MEK board. <p>All prebuilt images are in a separate package. See the <i>Android™ Quick Start Guide (AQSUG)</i> and <i>Android™ User's Guide (AUG)</i> to choose the appropriate image.</p>

4 Features

Table 2. Features

Feature	i.MX 8QuadXPlus/ 8QuadMax MEK	Remarks
Google Android 11 release	Y	Based on android-11.0.0_r17 release.
Linux 5.4.47 kernel (merged with the AOSP kernel)	Y	Based on Linux® OS BSP L5.4.47 GA release.
U-Boot	Y	v2020.04
Trusty OS	Y	-
Graphics-HW	Y	VeriSilicon GC7000L GPU for i.MX 8QuadXPlus, GC7000XSVX GPU for i.MX 8QuadMax with 6.4.0.p2 driver
Graphics-HW 3D acceleration	Y	OpenGL ES 1.1/2.0/3.1 through GC7000L for i.MX 8QuadXPlus, OpenGL ES 1.1/2.0/3.1/3.2 through GC7000XSVX for i.MX 8QuadMax.
Graphics-HW accelerated UI surface composition	Y	OpenGL ES 3.1 through GC7000L for i.MX 8QuadXPlus, OpenGL ES 3.2 through GC7000XSVX for i.MX 8QuadMax.
SCFW	Y	Version 1.6.0

Table continues on the next page...

Table 2. Features (continued)

Feature	i.MX 8QuadXPlus/ 8QuadMax MEK	Remarks
SECO firmware	Y	Version 3.7.0 for i.MX 8QuadMax B0 and i.MX 8QuadXPlus B0, Version 3.7.1 for i.MX 8QuadXPlus C0.
Boot source	eMMC	-
Splash Screen	Y	Supports USB mouse.
UI (input)	Y	-
UI (display)	HDMI display	Supports LVDS-to-HDMI display.
UI (brightness control)	N	-
Storage - External Media	Y	-
Connectivity - Ethernet	N	-
Connectivity - Bluetooth [®] wireless technology	Y	NXP 88W8997. Profiles: A2DP Sink, AVRCP, BLE Host, HFP, PBAPClient, MAPMCE, PAN, MMAPMCE, PAN, HID Device.
Connectivity - Wi-Fi	Y	NXP 88W8997. Features: STA mode, AP mode, AP/STA Concurrency, Wi-Fi Direct.
Connectivity - USB Tethering	Y	Supports Wi-Fi as upstream.
Power - CPU Freq	Y	-
Power - Bus Freq	Y	-
Media - Music Play	Y	ESAI+CS42888 (no support for multichannel).
Media - HDMI audio output	N	-
Misc - ADB over USB	Y	-
Misc - Fastboot utility	Y	-
Misc - SW update and factory reset	Y	-
File-based Encryption	Y	-
Ethernet APK	Y	-
webGL	Y	-
Vulkan	Y	-
USB TYPEC PD	Y	-

Table continues on the next page...

Table 2. Features (continued)

Feature	i.MX 8QuadXPlus/ 8QuadMax MEK	Remarks
OTA for A/B	Y	-
TEE backed Keymaster HAL	Y	This is based on i.MX Trusty OS TEE firmware.
TEE backed AVB	Y	This is based on i.MX Trusty OS TEE firmware and secure storage of eMMC chip. In this release, the RPMB part needs to be initialized manually.
Media rearview camera	Y	MAX9286 camera.
Car Audio Policy	Y	Alarm, notification, and system sounds are played from the audio jack on the CPU board. Other sounds such as music are played from the extended audio board.

5 Multimedia Codecs

For multimedia codecs and features, see the *i.MX Android™ Extended Codec Release Notes (IMXACRN)*.

6 Change Log

Compared to the automotive-10.0.0_2.4.0 release, this release has the following major changes:

- Upgraded the Android code base from android-10.0.0_r32 to android-11.0.0_r17.
- Upgraded the kernel from v5.4.24 to v5.4.47.

7 Known Issues and Limitations

The known issues about the hardware and hardware rework instructions are not included in this document. Read all hardware-related reference material and ensure the necessary hardware modifications have been made before using the software.

Table 3. Known issues and limitations

Issue description	Remarks
The Google USB driver must be installed multiple times for the MTP, PTP, MTP&ADB, PTP&ADB, and ADB function settings.	Some Windows XP environments may display MTP and PTP windows even with only PTP enabled in the device.
For i.MX 8QuadXPlus silicon revision B0 chip, it fails to boot from some types of eMMC.	<p>In the default settings, the UUU script burns the boot image into eMMC Boot Partition with 32KB offset. Although it works properly on the MEK board, it fails to read the boot image on some types of eMMC.</p> <p>There are two possible solutions:</p> <ul style="list-style-type: none"> • Download flash.bin in the eMMC Boot Partition + 0KB offset + eMMC fastboot enabled in fuse. • Download flash.bin in the eMMC User Partition + 32KB offset (eMMC fastboot can be either enabled or disabled in fuse). <p>For more information, see https://community.nxp.com/docs/DOC-342877.</p>

8 Revision History

Table 4. Revision history

Revision number	Date	Substantive changes
O8.1.0_1.1.0_AUTO-EAR	02/2018	Initial release
O8.1.0_1.1.0_AUTO-beta	05/2018	i.MX 8QuadXPlus/8QuadMax Beta release
P9.0.0_1.0.2-AUTO-alpha	11/2018	i.MX 8QuadXPlus/8QuadMax Automotive Alpha release
P9.0.0_1.0.2-AUTO-beta	01/2019	i.MX 8QuadXPlus/8QuadMax Automotive Beta release
P9.0.0_2.1.0-AUTO-ga	04/2019	i.MX 8QuadXPlus/8QuadMax Automotive GA release
P9.0.0_2.1.0-AUTO-ga	08/2019	Updated the location of the SCFW porting kit
automotive-10.0.0_1.1.0	03/2020	i.MX 8QuadXPlus/8QuadMax MEK (Silicon Revision B0) GA release
android-10.0.0_2.2.0-AUTO	06/2020	i.MX 8QuadXPlus/8QuadMax MEK GA release
android-10.0.0_2.4.0	07/2020	i.MX 8QuadMax MEK GA release
android-11.0.0_1.1.0-AUTO	01/2021	i.MX 8QuadXPlus/8QuadMax MEK GA release

How To Reach Us

Home Page:

nxp.com

Web Support:

nxp.com/support

Information in this document is provided solely to enable system and software implementers to use NXP products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits based on the information in this document. NXP reserves the right to make changes without further notice to any products herein.

NXP makes no warranty, representation, or guarantee regarding the suitability of its products for any particular purpose, nor does NXP assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters that may be provided in NXP data sheets and/or specifications can and do vary in different applications, and actual performance may vary over time. All operating parameters, including "typicals," must be validated for each customer application by customer's technical experts. NXP does not convey any license under its patent rights nor the rights of others. NXP sells products pursuant to standard terms and conditions of sale, which can be found at the following address: nxp.com/SalesTermsandConditions.

Right to make changes - NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Security — Customer understands that all NXP products may be subject to unidentified or documented vulnerabilities. Customer is responsible for the design and operation of its applications and products throughout their lifecycles to reduce the effect of these vulnerabilities on customer's applications and products. Customer's responsibility also extends to other open and/or proprietary technologies supported by NXP products for use in customer's applications. NXP accepts no liability for any vulnerability. Customer should regularly check security updates from NXP and follow up appropriately. Customer shall select products with security features that best meet rules, regulations, and standards of the intended application and make the ultimate design decisions regarding its products and is solely responsible for compliance with all legal, regulatory, and security related requirements concerning its products, regardless of any information or support that may be provided by NXP. NXP has a Product Security Incident Response Team (PSIRT) (reachable at PSIRT@nxp.com) that manages the investigation, reporting, and solution release to security vulnerabilities of NXP products.

NXP, the NXP logo, NXP SECURE CONNECTIONS FOR A SMARTER WORLD, COOLFLUX, EMBRACE, GREENCHIP, HITAG, ICODE, JCOP, LIFE, VIBES, MIFARE, MIFARE CLASSIC, MIFARE DESFire, MIFARE PLUS, MIFARE FLEX, MANTIS, MIFARE ULTRALIGHT, MIFARE4MOBILE, MIGLO, NTAG, ROADLINK, SMARTLX, SMARTMX, STARPLUG, TOPFET, TRENCHMOS, UCODE, Freescale, the Freescale logo, Altivec, CodeWarrior, ColdFire, ColdFire+, the Energy Efficient Solutions logo, Kinetis, Layerscape, MagniV, mobileGT, PEG, PowerQUICC, Processor Expert, QorIQ, QorIQ Qonverge, SafeAssure, the SafeAssure logo, StarCore, Symphony, VortiQa, Vybrid, Airfast, BeeKit, BeeStack, CoreNet, Flexis, MXC, Platform in a Package, QUICC Engine, Tower, TurboLink, EdgeScale, EdgeLock, eIQ, and Immersive3D are trademarks of NXP B.V. All other product or service names are the property of their respective owners. AMBA, Arm, Arm7, Arm7TDMI, Arm9, Arm11, Artisan, big.LITTLE, Cordio, CoreLink, CoreSight, Cortex, DesignStart, DynamIQ, Jazelle, Keil, Mali, Mbed, Mbed Enabled, NEON, POP, RealView, SecurCore, Socrates, Thumb, TrustZone, ULINK, ULINK2, ULINK-ME, ULINK-PLUS, ULINKpro, μ Vision, Versatile are trademarks or registered trademarks of Arm Limited (or its subsidiaries) in the US and/or elsewhere. The related technology may be protected by any or all of patents, copyrights, designs and trade secrets. All rights reserved. Oracle and Java are registered trademarks of Oracle and/or its affiliates. The Power Architecture and Power.org word marks and the Power and Power.org logos and related marks are trademarks and service marks licensed by Power.org.

© NXP B.V. 2018-2021.

All rights reserved.

For more information, please visit: <http://www.nxp.com>

For sales office addresses, please send an email to: salesaddresses@nxp.com

Date of release: 25 January 2021

Document identifier: ARN

