

1 General description

The PF5103 integrates multiple high performance buck regulators, and LDO regulators. It can operate as a stand-alone point-of-load regulator IC, or as a companion chip to a larger PMIC.

Built-in one-time programmable (OTP) memory stores key startup configurations drastically reducing external components typically used to set output voltage and sequence of regulators. Regulator parameters are adjustable through high-speed I2C after startup offering flexibility for different system states.

Functional safety features, developed according to ISO26262 specifications, enables the device to reach up to ASIL B safety level.

Note: Electrical characteristics for the PF5103 are maintained in the datasheet.

2 Features and benefits

- Three high efficiency buck regulators
- Two LDO regulators
- Functional safety circuits to fit up to ASIL B safety level
 - Voltage monitoring with independent reference
 - Watchdog monitor – Simple
 - Independent Clock monitor
 - Overvoltage monitoring of V1P6 internal regulators
 - ABIST on monitoring circuits at startup
- External clock synchronization and Frequency spread spectrum
- Standby mode – controlled by dual function Sync/Standby pin
- One-time programmable device configuration
- 3.4 MHz I2C communication interface
- 28-pin flip chip QFN package with wettable flank

3 Applications

- Automotive – RADAR, Infotainment, Domain controllers
- High-end consumer and industrial



4 Ordering information


Table 1. Ordering information

Type number ^[1]	Package		
	Name	Description	Version
MPF5103AMMA6ES ^[2]	QFN28	QFN28, plastic thermal enhanced very thin quad flat pack; no leads, wettable flank, 28 terminals, 0.5 mm pitch, 4.5 mm x 4.5 mm x 0.53 mm body	SOT2089-1(SC)

[1] To order parts in tape and reel, add the R2 suffix to the part number.


[2] Safety grade: PF5103-QM, non-programmed device.

5 Power-up sequence summary



The signals depicted above are enable signals for each regulator. They don't represent the actual ramp voltage.

6 Hardware configuration diagram



7 OTP configuration

See PF5103 datasheet for parametric details. The OTP configuration summary for A6 sequence ID is provided in Tables below.

Table 2. Device OTP configuration

Functional block	Feature	OTP selection
System Configuration	I2C Address	0x0B
	I2C CRC	Disabled
	VIN_OVLO Enable	Disabled
	VIN_OVLO Mode	Interruption only on VIN_OVLO
	VIN_OVLO Debounce	10 us
	VIN_OV Threshold	103.25 %
	VIN_UV Threshold	96.75 %
	Maximum Fault Counter	15
	Standby Mode Enable	Standby function Disabled
	Low Power STANDBY	Disabled
I/O Configuration	XFAIL Operation	Disabled
	Standby Polarity	STANDBY Active High
	INTB Dual Function	INTB function enabled
Watchdog Monitoring	WD Timer	WD Disabled
	WD Window Duration	1 ms
	WD Clear Window	Cleared within 100 % timer
	Watchdog Error Maximum Value	8
	WD Standby Mode	Disabled

Configuration report for PF5103-QM OTP program ID: A6 rev A

Clock Management	Nominal Switching Frequency	20 MHz
	SYNC Mode	SYNC function Disabled
	SW Mode	PWM
	Frequency Spread Spectrum Mode	Disabled
	Spread Spectrum Type	Pseudo-random modulation
	FSYNC Frequency Range	Between 2.2 MHz and 2.8 MHz
	FSS Mode	23.5 kHz
	Clock DIV1	Divider 9 and frequency = 2.22 MHz
	Clock DIV2	Divider 9 and frequency = 2.22 MHz

Table 3. Power Sequencer configuration

Functional block	Feature	OTP selection
Power Up Sequence	Sequence Time Base	100 us
	SW1 Sequence Slot	Slot 0
	SW2 Sequence Slot	Slot 1
	SW3 Sequence Slot	Slot 4
	LDO1 Sequence Slot	OFF
	LDO2 Sequence Slot	Slot 2
	PGOOD Power Up Sequence	Slot 5
	GPO Sequence Slot	OFF
Power-Down Sequence	Phase Sequence Delay	No delay

Configuration report for PF5103-QM OTP program ID: A6 rev A

Table 4. SW Regulator configuration

Functional block	Feature	OTP selection
SW1	Output Voltage	0.70000 V
	UV Detection Threshold	96 %
	OV Detection Threshold	104 %
	ILIM Detection Threshold	5.0 A
	Output Inductor	0.47 uH
	Switching Phase	No phase shift
	SW1 Standby	Disabled
	PGOOD Mode	Enabled
	SW1 Clock	CLK_DIV1
	SW1 OV Bypass	OV Protection Enabled
	SW1 UV Bypass	UV Protection Enabled
	SW1 ILIM Bypass	ILIM Fault bypassed
	SW1 DVS Ramp	7.8 mV/us at fsw = 2.5 MHz
	SW1 Gain Margin	70 uS
	SW1 Compensation Resistor	40 kOhm
	SW1 Compensation Capacitor	100 pF
SW2	Output Voltage	1.00000 V
	UV Detection Threshold	96 %
	OV Detection Threshold	104 %
	ILIM Detection Threshold	5.0 A
	Output Inductor	0.47 uH

Configuration report for PF5103-QM OTP program ID: A6 rev A

	Switching Phase	Shifted by 1 CLK
	SW2 Standby	Disabled
	PGOOD Mode	Enabled
	SW2 Clock	CLK_DIV1
	SW2 OV Bypass	OV Protection Enabled
	SW2 UV Bypass	UV Protection Enabled
	SW2 ILIM Bypass	ILIM Fault bypassed
	SW2 DVS Ramp	7.8 mV/us at fsw = 2.5 MHz
	SW2 Gain Margin	70 uS
	SW2 Compensation Resistor	40 kOhm
	SW2 Compensation Capacitor	100 pF
SW3	Output Voltage	2.00000 V
	UV Detection Threshold	96 %
	OV Detection Threshold	104 %
	ILIM Detection Threshold	5.0 A
	Output Inductor	0.47 uH
	Switching Phase	Shifted by 2 CLK
	SW3 Standby	Disabled
	PGOOD Mode	Enabled
	SW3 Clock	CLK_DIV1
	SW3 OV Bypass	OV Protection Enabled
	SW3 UV Bypass	UV Protection Enabled

Configuration report for PF5103-QM OTP program ID: A6 rev A

	SW3 ILIM Bypass	ILIM Fault bypassed
	SW3 DVS Ramp	7.8 mV/us at fsw = 2.5 MHz
	SW3 Gain Margin	35 uS
	SW3 Compensation Resistor	80 kOhm
	SW3 Compensation Capacitor	100 pF
Multi Phase selection	SW1 Multi-phase Selector	SW1,SW2 and SW3 operate in single phase mode

Table 5. LDO Regulator configuration

Functional block	Feature	OTP selection
LDO1	Output Voltage	0.75 V
	UV Detection Threshold	96.5 %
	OV Detection Threshold	103.5 %
	LDO1 STANDBY	Disabled
	PGOOD Mode	Disabled
	LDO1 DVS Ramp	180 us
	LDO1 Regulator Mode	Normal Mode
	LDO1 OV Bypass	OV Protection Enabled
	LDO1 UV Bypass	UV Protection Enabled
	LDO1 ILIM Bypass	ILIM Protection Enabled
LDO2	Output Voltage	1.8 V
	UV Detection Threshold	96 %
	OV Detection Threshold	104 %

Configuration report for PF5103-QM OTP program ID: A6 rev A

	LDO2 STANDBY	Disabled
	PGOOD Mode	Enabled
	LDO2 DVS Ramp	390 us
	LDO2 Regulator Mode	Normal Mode
	LDO2 OV Bypass	OV Protection Enabled
	LDO2 UV Bypass	UV Protection Enabled
	LDO2 ILIM Bypass	ILIM Fault bypassed
LDO Common	LDOx Out Open	Disabled

Table 6. Program ID

Functional block	Feature	OTP selection
Program ID	Program ID High	A
	Program ID Low	6
	Program ID Rev	A

8 Legal information

8.1 Definitions

Draft - The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Limited warranty and liability - Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. NXP Semiconductors takes no responsibility for the content in this document if provided by an information source outside of NXP Semiconductors. In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory. Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of NXP Semiconductors.

Right to make changes - NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use - NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors and its suppliers accept no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications - Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification. Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products. NXP Semiconductors does not accept any liability related to any default, damage, costs or problem

which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

Limiting values - Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale - NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at <http://www.nxp.com/profile/terms>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

No offer to sell or license - Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Suitability for use in automotive applications - This NXP Semiconductors product has been qualified for use in automotive applications. Unless otherwise agreed in writing, the product is not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors and its suppliers accept no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Export control - This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Translations - A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

8.2 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

NXP - is a trademark of NXP B.V.

Contents

1 General description	1
2 Features and benefits	1
3 Applications	1
4 Ordering information	2
5 Power up sequence summary	2
6 Hardware configuration diagram	3
7 OTP configuration	4
8 Legal information	10

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

© NXP B.V. 2025 .

All rights reserved.

For more information, please visit: <http://www.nxp.com>

For sales office addresses, please send an email to: salesaddresses@nxp.com

Date of release: 12/8/2025

Document identifier: R_MPF5103AMMA6ES