

PART INFORMATION		
Mfg Item Number		AFT20P140-4WNR3
Mfg Item Name		OM780-4 straight Cu
SUPPLIER		
Company Name		Freescale Semiconductor Inc
Company Unique ID		14-141-7928
Response Date		2018-05-16
Response Document ID		00E2K02572D014A1.28
Contact Name		Freescale Semiconductor Inc
Contact Title		Product Technical Support
Contact Phone		1-800-521-6274
Contact Email		support@freescale.com
Authorized Representative		Daniel Binyon
Representative Title		EPP Customer Response
Representative Phone		512-895-3406
Representative Email		eppanlst@freescale.com
URL for Additional Information		www.freescale.com
DECLARATION		
EU RoHS		Yes
Pb Free		Yes
HalogenFree		Yes
Plating Indicator		e3
EU RoHS Exemption(s)		
MANUFACTURING		
Mfg Item Number		AFT20P140-4WNR3
Mfg Item Name		OM780-4 straight Cu
Version		ALL
Weight		3.191900
UoM		g
Unit Volume		EACH
J-STD-020 MSL Rating		3
Peak Processing Temperature		260 C
Max Time at Peak Temperature		40 seconds
Number of Processing Cycles		3

RoHS	
RoHS Directive	2011/65/EU
RoHS Definition	RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) of homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material of Cadmium
RoHS Legal Definition	Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part(s) identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a RoHS restricted substance) in excess of the applicable quantity limit identified below. If a homogeneous material within the part(s) contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Suppliers Standard Terms and Conditions of Sale applicable to such part(s) shall apply.
RoHS Declaration	1 - Item(s) do not contain RoHS restricted substances per the definition above
Supplier Acceptance	Accepted
Signature	Daniel Binyon
Exemption List Version	2012/51/EU
List of Freescale Accepted Exemptions	6(a) : Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight 6(b) : Lead as an alloying element in aluminium containing up to 0.4% lead by weight 6(c) : Copper alloy containing up to 4% lead by weight 7(a) : Lead in high melting temperature type solders (i.e. lead-based alloys containing 85% by weight or more lead) 7(b) : Lead in solders for servers, storage and storage array systems, network infrastructure equipment for switching, signaling, transmission, and network management for telecommunications 7(c)-I : Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound 7(c)-II : Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher 7(c)-III : Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC 7(c)-IV : Lead in PZT based dielectric ceramic materials for capacitors being part of integrated circuits or discrete semiconductors 15 : Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit flip chip packages

MATERIAL COMPOSITION

Homogeneous Material	Weight	SubstanceClass	Substance	CAS	Exemption	SubstanceWeight	UoM	SubPart PPM	SubPart%	ARTICLEPPM	ARTICLE%
Die Encapsulant	0.4849						g				
Die Encapsulant		Solvents, additives, and other materials	Benzophenonetetracarboxylic Acid Dianhydride	2421-28-5		0.03628895	g	74838	7.4838	11369	1.1369
Die Encapsulant		Plastics/polymers	Poly[o-(cresyl glycidyl ether)-co-formaldehyde]	29690-82-2		0.01451548	g	29935	2.9935	4547	0.4547
Die Encapsulant		Plastics/polymers	Other Epoxy resins	-		0.01451548	g	29935	2.9935	4547	0.4547
Die Encapsulant		Plastics/polymers	Proprietary Material-Other Epoxy resins	-		0.01451548	g	29935	2.9935	4547	0.4547
Die Encapsulant		Metals	Magnesium, metal	7439-95-4		0.00086555	g	1785	0.1785	271	0.0271
Die Encapsulant		Solvents, additives, and other materials	Proprietary Material-Other organic silicon compounds	-		0.00259955	g	5361	0.5361	814	0.0814
Die Encapsulant		Glass	Silica, crystalline - quartz (SiO2)	14808-60-7		0.01451548	g	29935	2.9935	4547	0.4547
Die Encapsulant		Glass	Silica, vitreous	60876-86-0		0.38708403	g	798276	79.8276	121270	12.127
Bonding Wire, Aluminum	0.0539						g				
Bonding Wire, Aluminum		Metals	Aluminum, metal	7429-90-5		0.0539	g	1000000	100	16886	1.6886
Lead Frame Plating	0.0668						g				
Lead Frame Plating		Lead/Lead Compounds	Lead	7439-92-1		0.00001336	g	200	0.02	4	0.0004
Lead Frame Plating		Metals	Tin, metal	7440-31-5		0.06678664	g	999800	99.98	20923	2.0923
Copper Lead Frame	0.6008						g				
Copper Lead Frame		Metals	Copper, metal	7440-50-8		0.57914416	g	963955	96.3955	181441	18.1441
Copper Lead Frame		Solvents, additives, and other materials	Phosphorus, elemental (not containing red allotrope)	7723-14-0		0.00049566	g	825	0.0825	155	0.0155
Copper Lead Frame		Metals	Iron, metal	7439-89-6		0.0141188	g	23500	2.35	4423	0.4423
Copper Lead Frame		Lead/Lead Compounds	Lead	7439-92-1		0.00010214	g	170	0.017	31	0.0031
Copper Lead Frame		Metals	Silver, metal	7440-22-4		0.006008	g	10000	1	1882	0.1882
Copper Lead Frame		Metals	Tin, metal	7440-31-5		0.00018024	g	300	0.03	56	0.0056
Copper Lead Frame		Metals	Zinc, metal	7440-66-6		0.000751	g	1250	0.125	235	0.0235
Silicon Semiconductor Die	0.0097						g				
Silicon Semiconductor Die		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%).	-		0.000194	g	20000	2	60	0.006
Silicon Semiconductor Die		Glass	Silicon, doped	-		0.009506	g	980000	98	2978	0.2978
Silicon Semiconductor Die	0.0097						g				
Silicon Semiconductor Die		Metals	Gold, metal	7440-57-5		0.00009894	g	10200	1.02	30	0.003
Silicon Semiconductor Die		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%).	-		0.00019202	g	19796	1.9796	60	0.006
Silicon Semiconductor Die		Glass	Silicon, doped	-		0.00940904	g	970004	97.0004	2947	0.2947
Silicon Semiconductor Die	0.0097						g				
Silicon Semiconductor Die		Metals	Gold, metal	7440-57-5		0.00009894	g	10200	1.02	30	0.003
Silicon Semiconductor Die		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%).	-		0.00019202	g	19796	1.9796	60	0.006
Silicon Semiconductor Die		Glass	Silicon, doped	-		0.00940904	g	970004	97.0004	2947	0.2947
Silicon Semiconductor Die	0.0097						g				
Silicon Semiconductor Die		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%).	-		0.000194	g	20000	2	60	0.006
Silicon Semiconductor Die		Glass	Silicon, doped	-		0.009506	g	980000	98	2978	0.2978
Heat Sink	1.9467						g				
Heat Sink		Metals	Cobalt, metal	7440-48-4		0.00661099	g	3396	0.3396	2071	0.2071
Heat Sink		Metals	Copper, metal	7440-50-8		1.91784602	g	985178	98.5178	600865	60.0865
Heat Sink		Metals	Gold, metal	7440-57-5		0.00170336	g	875	0.0875	533	0.0533
Heat Sink		Nickel (external applications only)	Nickel	7440-02-0		0.01553077	g	7978	0.7978	4865	0.4865
Heat Sink		Metals	Palladium, metal	7440-05-3		0.00310693	g	1596	0.1596	973	0.0973
Heat Sink		Metals	Zirconium, metal	7440-67-7		0.00190193	g	977	0.0977	595	0.0595

LINKS	
MCD LINK	
NXP website	http://www.nxp.com
GENERAL ENVIRONMENTAL COMPLIANCE LINKS	
RoHS signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-ROHS-DECLARATION.pdf
China RoHS	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/china-rohs:ENV_CHINA_ROHS_STRATEGY
REACH signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-REACH-STATEMENT.pdf
ELV signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-ELV-STATEMENT.pdf
Conflict Minerals statement	http://www.nxp.com/files/corporate/doc/support_info/NXP-STATEMENT-CONFLICT-MINERALS.pdf
NXP ENVIRONMENTAL INFORMATION	
Environmental Compliance website	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization:ABUENVPRFPRDX
FAQ	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/eco-product-faqs:ENVIRON_FAQ
Technical Service Request	http://www.nxp.com/support/sales-and-support:SUPPORTHOME
LINKS TO BLANK IPC1752 FORMS	
Blank IPC1752 v1.1 Form	http://www.NXP.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf

IPC1752 XML LINKS

http://www.freescale.com/mcds/AFT20P140-4WNR3_IPC1752_v11.xml

http://www.freescale.com/mcds/AFT20P140-4WNR3_IPC1752A.xml