



Table of Contents	
1	Title
2	Notes
3	Sensors

BRKT-STBC-SA9500

		RF, Analog & Sensor Group 6501 William Cannon Drive West Austin, TX 78735-8599	
<small>This document contains information proprietary to Freescale Semiconductor and shall not be used for engineering design, procurement or manufacture in whole or in part without the express written permission of Freescale Semiconductor.</small>			
Designer: Krithi S		ICAP Classification: FCP: FUK2: X PUB:	
Drawing Title:		BRKT-STBC-SA9500	
Drawn by: Krithi S		Page Title: CONTENT	
Approved: Team		Size C	Document Number SCH-28966 PDF: SPF-28966
Date: Sunday, October 11, 2015		Sheet 1	of 3
		Rev A1	

- 54321
- D
- C
- B
- A
- 54321
1. Unless Otherwise Specified:
All resistors are in ohms, 5%, 1/8 Watt
All capacitors are in uF, 20%, 50V
All voltages are DC
All polarized capacitors are aluminum electrolytic
2. Interrupted lines coded with the same letter or letter combinations are electrically connected.
3. Device type number is for reference only. The number varies with the manufacturer.
4. Special signal usage:
_B Denotes - Active-Low Signal
<> or [] Denotes - Vectored Signals
5. Interpret diagram in accordance with American National Standards Institute specifications, current revision, with the exception of logic block symbology.



ICAP Classification: FCP: FIUO: X PUBI:

Drawing Title: **BRKT-STBC-SA9500**

Page Title: **NOTES**

Size C	Document Number SCH-28966 PDF: SPF-28966	Rev A1
-----------	---	-----------

Date: Sunday, October 11, 2015	Sheet 2 of 3
--------------------------------	--------------

EDGE OF BRKOUT BOARD

