

PART INFORMATION		
Mfg Item Number		GC33931VWR2
Mfg Item Name		HSOP 44 16*11.1*3.1P0.65
SUPPLIER		
Company Name		Freescale Semiconductor Inc
Company Unique ID		14-141-7928
Response Date		2018-04-09
Response Document ID		6140A1.1
Contact Name		Freescale Semiconductor Inc
Contact Title		Product Technical Support
Contact Phone		1-800-521-6274
Contact Email		support@freescale.com
Authorized Representative		Daniel Binyon
Representative Title		EPP Customer Response
Representative Phone		512-895-3406
Representative Email		eppanlst@freescale.com
URL for Additional Information		www.freescale.com
DECLARATION		
EU RoHS		Yes
Pb Free		No
HalogenFree		No
Plating Indicator		e4
EU RoHS Exemption(s)		7a
MANUFACTURING		
Mfg Item Number		GC33931VWR2
Mfg Item Name		HSOP 44 16*11.1*3.1P0.65
Version		ALL
Weight		1.899100
UoM		g
Unit Volume		EACH
J-STD-020 MSL Rating		3
Peak Processing Temperature		245 C
Max Time at Peak Temperature		30 seconds
Number of Processing Cycles		3

RoHS	
RoHS Directive	2011/65/EU
RoHS Definition	RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) of homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material of Cadmium
RoHS Legal Definition	Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part(s) identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a RoHS restricted substance) in excess of the applicable quantity limit identified below. If a homogeneous material within the part(s) contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Suppliers Standard Terms and Conditions of Sale applicable to such part(s) shall apply.
RoHS Declaration	4 - Item(s) does not contain RoHS restricted substances per the definition above except for selected exemptions
Supplier Acceptance	Accepted
Signature	Daniel Binyon
Exemption List Version	2012/51/EU
Exemptions in this part	7a:Lead in high melting temperature type solders (i.e. lead-based alloys containing 85 % by weight or more lead)
List of Freescale Accepted Exemptions	6(a) : Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight 6(b) : Lead as an alloying element in aluminium containing up to 0.4% lead by weight 6(c) : Copper alloy containing up to 4% lead by weight 7(a) : Lead in high melting temperature type solders (i.e. lead-based alloys containing 85% by weight or more lead) 7(b) : Lead in solders for servers, storage and storage array systems, network infrastructure equipment for switching, signaling, transmission, and network management for telecommunications 7(c)-I : Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound 7(c)-II : Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher 7(c)-III : Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC 7(c)-IV : Lead in PZT based dielectric ceramic materials for capacitors being part of integrated circuits or discrete semiconductors 15 : Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit flip chip packages

MATERIAL COMPOSITION

Homogeneous Material	Weight	SubstanceClass	Substance	CAS	Exemption	SubstanceWeight	UoM	SubPart PPM	SubPart%		ARTICLEPPM	ARTICLE%
Bonding Wire	0.0026						g					
Bonding Wire		Metals	Gold, metal	7440-57-5		0.0026	g	1000000	100		1369	0.1369
Solder Die Attach	0.0149				7a		g					
Solder Die Attach		Cadmium/Cadmium Compounds	Cadmium	7440-43-9		0.00000003	g	2	0.0002		0	0
Solder Die Attach		Metals	Chromium(VI)	18540-29-9		0.000000003	g	2	0.0002		0	0
Solder Die Attach		Lead/Lead Compounds	Lead	7439-92-1		0.0142285	g	954933	95.4933		7492	0.7492
Solder Die Attach		Mercury/Mercury Compounds	Mercury	7439-97-6		0.000000003	g	2	0.0002		0	0
Solder Die Attach		Metals	Silver, metal	7440-22-4		0.00027301	g	25034	2.5034		196	0.0196
Solder Die Attach		Metals	Tin, metal	7440-31-5		0.0002984	g	20027	2.0027		157	0.0157
Die Encapsulant	0.73865						g					
Die Encapsulant		Antimony/Antimony Compounds	Antimony trioxide	1309-64-4		0.01069491	g	14479	1.4479		5631	0.5631
Die Encapsulant		Bismuth/Bismuth Compounds	Bismuth	7440-69-9		0.00737542	g	9985	0.9985		3883	0.3883
Die Encapsulant		Brominated Flame Retardants (other than PBBs or PBDEs)	TBBA-epichlorhydrin oligomer	40039-93-8		0.00442525	g	5991	0.5991		2330	0.233
Die Encapsulant		Plastics/polymers	Proprietary Material-Other Epoxy resins	-		0.04351609	g	58913	5.8913		22914	2.2914
Die Encapsulant		Solvents, additives, and other materials	Carbon Black	1333-86-4		0.002213	g	2996	0.2996		1165	0.1165
Die Encapsulant		Solvents, additives, and other materials	Other organic phosphorous compounds	-		0.00737542	g	9985	0.9985		3883	0.3883
Die Encapsulant		Solvents, additives, and other materials	Other organic Silicon Compounds	-		0.00737542	g	9985	0.9985		3883	0.3883
Die Encapsulant		Plastics/polymers	Phenol, polymer with formaldehyde	9003-35-4		0.02876451	g	38942	3.8942		15146	1.5146
Die Encapsulant		Plastics/polymers	Proprietary Material-Other phenolic resins	-		0.01069491	g	14479	1.4479		5631	0.5631
Die Encapsulant		Glass	Silica, vitreous	60876-96-0		0.60882965	g	824260	82.426		320593	32.0593
Die Encapsulant		Metals	Zinc, metal	7440-66-6		0.00737542	g	9985	0.9985		3883	0.3883
Copper Lead Frame	1.1182						g					
Copper Lead Frame		Metals	Copper, metal	7440-50-8		1.09354928	g	977955	97.7955		575835	57.5835
Copper Lead Frame		Metals	Gold, metal	7440-57-5		0.00038354	g	343	0.0343		201	0.0201
Copper Lead Frame		Metals	Iron, metal	7439-89-6		0.01339827	g	11982	1.1982		7055	0.7055
Copper Lead Frame		Lead/Lead Compounds	Lead	7439-92-1		0.00023035	g	206	0.0206		121	0.0121
Copper Lead Frame		Nickel (external applications only)	Nickel	7440-02-0		0.00980326	g	8767	0.8767		5162	0.5162
Copper Lead Frame		Metals	Palladium, metal	7440-05-3		0.0008353	g	747	0.0747		439	0.0439
Silicon Semiconductor Die	0.02475						g					
Silicon Semiconductor Die		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%)	-		0.000495	g	20000	2		260	0.026
Silicon Semiconductor Die		Glass	Silicon, doped	-		0.024255	g	980000	98		12771	1.2771

LINKS	
MCD LINK	
NXP website	http://www.nxp.com
GENERAL ENVIRONMENTAL COMPLIANCE LINKS	
RoHS signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-ROHS-DECLARATION.pdf
China RoHS	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/china-rohs:ENV_CHINA_ROHS_STRATEGY
REACH signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-REACH-STATEMENT.pdf
ELV signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-ELV-STATEMENT.pdf
Conflict Minerals statement	http://www.nxp.com/files/corporate/doc/support_info/NXP-STATEMENT-CONFLICT-MINERALS.pdf
NXP ENVIRONMENTAL INFORMATION	
Environmental Compliance website	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization:ABUENVPRFPRDX
FAQ	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/eco-product-faqs:ENVIRON_FAQ
Technical Service Request	http://www.nxp.com/support/sales-and-support:SUPPORTHOME
LINKS TO BLANK IPC1752 FORMS	
Blank IPC1752 v1.1 Form	http://www.NXP.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf

IPC1752 XML LINKS

http://www.freescale.com/mcds/GC33931VWR2_IPC1752_v11.xml

http://www.freescale.com/mcds/GC33931VWR2_IPC1752A.xml