

PART INFORMATION	
Mfg Item Number	AFT26P100-4WGSR3
Mfg Item Name	NI-780S-4 Gull Wing
SUPPLIER	
Company Name	Freescale Semiconductor Inc
Company Unique ID	14-141-7928
Response Date	2018-05-21
Response Document ID	00GZK11239D016A1.14
Contact Name	Freescale Semiconductor Inc
Contact Title	Product Technical Support
Contact Phone	1-800-521-6274
Contact Email	support@freescale.com
Authorized Representative	Daniel Binyon
Representative Title	EPP Customer Response
Representative Phone	512-895-3406
Representative Email	eppanlst@freescale.com
URL for Additional Information	www.freescale.com
DECLARATION	
EU RoHS	Yes
Pb Free	Yes
HalogenFree	Yes
Plating Indicator	e4
EU RoHS Exemption(s)	
MANUFACTURING	
Mfg Item Number	AFT26P100-4WGSR3
Mfg Item Name	NI-780S-4 Gull Wing
Version	ALL
Weight	3.256900
UoM	g
Unit Volume	EACH
J-STD-020 MSL Rating	
Peak Processing Temperature	260 C
Max Time at Peak Temperature	40 seconds
Number of Processing Cycles	3

RoHS	
RoHS Directive	2011/65/EU
RoHS Definition	RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) of homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material of Cadmium
RoHS Legal Definition	Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part(s) identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a RoHS restricted substance) in excess of the applicable quantity limit identified below. If a homogeneous material within the part(s) contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Suppliers Standard Terms and Conditions of Sale applicable to such part(s) shall apply.
RoHS Declaration	1 - Item(s) do not contain RoHS restricted substances per the definition above
Supplier Acceptance	Accepted
Signature	Daniel Binyon
Exemption List Version	2012/51/EU
List of Freescale Accepted Exemptions	6(a) : Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight 6(b) : Lead as an alloying element in aluminium containing up to 0.4% lead by weight 6(c) : Copper alloy containing up to 4% lead by weight 7(a) : Lead in high melting temperature type solders (i.e. lead-based alloys containing 85% by weight or more lead) 7(b) : Lead in solders for servers, storage and storage array systems, network infrastructure equipment for switching, signaling, transmission, and network management for telecommunications 7(c)-I : Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound 7(c)-II : Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher 7(c)-III : Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC 7(c)-IV : Lead in PZT based dielectric ceramic materials for capacitors being part of integrated circuits or discrete semiconductors 15 : Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit flip chip packages

MATERIAL COMPOSITION

Homogeneous Material	Weight	SubstanceClass	Substance	CAS	Exemption	SubstanceWeight	UoM	SubPart PPM	SubPart%		ARTICLEPPM	ARTICLE%
Cap/Cover	0.6864						g					
Cap/Cover		Metals	Aluminum Oxides (Al2O3)	1344-28-1		0.64683728	g	942362	94.2362		198605	19.8605
Cap/Cover		Plastics/polymers	Proprietary Material-Other Epoxy resins	-		0.01505824	g	21938	2.1938		4623	0.4623
Cap/Cover		Metals	Magnesium-oxide	1309-48-4		0.00671368	g	9781	0.9781		2061	0.2061
Cap/Cover		Glass	Silica, crystalline - quartz (SiO2)	14808-60-7		0.0164482	g	23963	2.3963		5050	0.505
Cap/Cover		Solvents, additives, and other materials	Proprietary Material-Other miscellaneous substances.	-		0.0013426	g	1956	0.1956		412	0.0412
Bonding Wire, Aluminum	0.0058						g					
Bonding Wire, Aluminum		Metals	Aluminum, metal	7429-90-5		0.0058	g	1000000	100		1780	0.178
Silicon Semiconductor Die	0.0211						g					
Silicon Semiconductor Die		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%).	-		0.000422	g	20000	2		129	0.0129
Silicon Semiconductor Die		Glass	Silicon, doped	-		0.020678	g	980000	98		6348	0.6348
Header Assembly	2.4963						g					
Header Assembly		Metals	Aluminum Oxides (Al2O3)	1344-28-1		0.16646077	g	66683	6.6683		51110	5.111
Header Assembly		Metals	Cobalt, metal	7440-48-4		0.0292142	g	11703	1.1703		8969	0.8969
Header Assembly		Metals	Copper, metal	7440-50-8		1.05108458	g	421057	42.1057		322741	32.2741
Header Assembly		Metals	Gold, metal	7440-57-5		0.00259366	g	1039	0.1039		796	0.0796
Header Assembly		Metals	Iron, metal	7439-89-6		0.0442594	g	17730	1.773		13589	1.3589
Header Assembly		Metals	Molybdenum, metal	7439-98-7		1.04258219	g	417651	41.7651		320114	32.0114
Header Assembly		Nickel (external applications only)	Nickel	7440-02-0		0.0748915	g	30001	3.0001		22994	2.2994
Header Assembly		Metals	Palladium, metal	7440-05-3		0.00201701	g	808	0.0808		619	0.0619
Header Assembly		Glass	Silica, crystalline - quartz (SiO2)	14808-60-7		0.00555926	g	2227	0.2227		1706	0.1706
Header Assembly		Metals	Silver, metal	7440-22-4		0.02594405	g	10393	1.0393		7965	0.7965
Header Assembly		Metals	Tungsten, metal	7440-33-7		0.04785657	g	19171	1.9171		14693	1.4693
Header Assembly		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%).	-		0.0028333	g	1135	0.1135		869	0.0869
Header Assembly		Metals	Titanium (III) oxide (Ti2O3)	1344-54-3		0.00100351	g	402	0.0402		308	0.0308
Silicon Semiconductor Die	0.0211						g					
Silicon Semiconductor Die		Metals	Gold, metal	7440-57-5		0.00021522	g	10200	1.02		66	0.0066
Silicon Semiconductor Die		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%).	-		0.0004177	g	19796	1.9796		128	0.0128
Silicon Semiconductor Die		Glass	Silicon, doped	-		0.02046708	g	970004	97.0004		6284	0.6284
Capacitor, 0201	0.0051						g					
Capacitor, 0201		Metals	Aluminum Oxides (Al2O3)	1344-28-1		0.00015842	g	31063	3.1063		48	0.0048
Capacitor, 0201		Metals	Copper, metal	7440-50-8		0.00031457	g	61680	6.168		96	0.0096
Capacitor, 0201		Metals	Gold, metal	7440-57-5		0.00032715	g	64148	6.4148		100	0.01
Capacitor, 0201		Metals	Manganese dioxide	1313-13-9		0.00000516	g	1011	0.1011		1	0.0001
Capacitor, 0201		Nickel (external applications only)	Nickel	7440-02-0		0.00016987	g	33308	3.3308		52	0.0052
Capacitor, 0201		Metals	Tin, metal	7440-31-5		0.00005033	g	9869	0.9869		15	0.0015
Capacitor, 0201		Metals	Barium titanate	12047-27-7		0.0040745	g	798921	79.8921		1251	0.1251
Silicon Semiconductor Die	0.0211						g					
Silicon Semiconductor Die		Metals	Gold, metal	7440-57-5		0.00021522	g	10200	1.02		66	0.0066
Silicon Semiconductor Die		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%).	-		0.0004177	g	19796	1.9796		128	0.0128
Silicon Semiconductor Die		Glass	Silicon, doped	-		0.02046708	g	970004	97.0004		6284	0.6284

LINKS	
MCD LINK	
NXP website	http://www.nxp.com
GENERAL ENVIRONMENTAL COMPLIANCE LINKS	
RoHS signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-ROHS-DECLARATION.pdf
China RoHS	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/china-rohs:ENV_CHINA_ROHS_STRATEGY
REACH signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-REACH-STATEMENT.pdf
ELV signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-ELV-STATEMENT.pdf
Conflict Minerals statement	http://www.nxp.com/files/corporate/doc/support_info/NXP-STATEMENT-CONFLICT-MINERALS.pdf
NXP ENVIRONMENTAL INFORMATION	
Environmental Compliance website	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization:ABUENVPRFPRDX
FAQ	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/eco-product-faqs:ENVIRON_FAQ
Technical Service Request	http://www.nxp.com/support/sales-and-support:SUPPORTHOME
LINKS TO BLANK IPC1752 FORMS	
Blank IPC1752 v1.1 Form	http://www.NXP.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf

IPC1752 XML LINKS

http://www.freescale.com/mcds/AFT26P100-4WGSR3_IPC1752_v11.xml

http://www.freescale.com/mcds/AFT26P100-4WGSR3_IPC1752A.xml