

PART INFORMATION

Mfg Item Number	MC33886VW
Mfg Item Name	HSOP20 11*16*3.2P1.3

SUPPLIER

Company Name	Freescale Semiconductor Inc
Company Unique ID	14-141-7928
Response Date	2013-06-25
Response Document ID	6051A1.16
Contact Name	Freescale Semiconductor Inc
Contact Title	Product Technical Support
Contact Phone	1-800-521-6274
Contact Email	support@freescale.com
Authorized Representative	Daniel Binyon
Representative Title	EPP Customer Response
Representative Phone	512-895-3406
Representative Email	eppanlst@freescale.com
URL for Additional Information	www.freescale.com

DECLARATION

EU RoHS	Yes
Pb Free	No
HalogenFree	No
Plating Indicator	e4
EU RoHS Exemption(s)	7a

MANUFACTURING

Mfg Item Number	MC33886VW
Mfg Item Name	HSOP20 11*16*3.2P1.3
Version	ALL
Weight	2.215100
UoM	g
Unit Volume	EACH
J-STD-020 MSL Rating	3
Peak Processing Temperature	245 C
Max Time at Peak Temperature	30 seconds
Number of Processing Cycles	3

RoHS	
RoHS Directive	2011/65/EU
RoHS Definition	RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) of homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material of Cadmium
RoHS Legal Definition	Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part(s) identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a RoHS restricted substance) in excess of the applicable quantity limit identified below. If a homogeneous material within the part(s) contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Suppliers Standard Terms and Conditions of Sale applicable to such part(s) shall apply.
RoHS Declaration	4 - Item(s) does not contain RoHS restricted substances per the definition above except for selected exemptions
Supplier Acceptance	Accepted
Signature	Daniel Binyon
Exemptions in this part	7a:Lead in high melting temperature type solders (i.e. lead-based alloys containing 85 % by weight or more lead)
List of Freescale Accepted Exemptions	<p>6(a) : Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight</p> <p>6(b) : Lead as an alloying element in aluminium containing up to 0.4% lead by weight</p> <p>6(c) : Copper alloy containing up to 4% lead by weight</p> <p>7(a) : Lead in high melting temperature type solders (i.e. lead-based alloys containing 85% by weight or more lead)</p> <p>7(b) : Lead in solders for servers, storage and storage array systems, network infrastructure equipment for switching, signaling, transmission, and network management for telecommunications</p> <p>7(c)-I : Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound</p> <p>7(c)-II : Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher</p> <p>7(c)-III : Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC</p> <p>7(c)-IV : Lead in PZT based dielectric ceramic materials for capacitors being part of integrated circuits or discrete semiconductors</p> <p>15 : Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit flip chip packages</p>

MATERIAL COMPOSITION

SubPart	Weight	SubstanceClass	Substance	CAS	Exemption	SubstanceWeight	UoM	SubPart PPM	SubPart%	REACHPPM	REACH%
Copper Lead Frame	1.9167						g				
Copper Lead Frame		Metals	Copper, metal	7440-50-8		1.807222	g	942881	94.2881	815877	81.5877
Copper Lead Frame		Metals	Gold, metal	7440-57-5		0.00022	g	115	0.0115	99	0.0099
Copper Lead Frame		Solvents, additives, and other materials	Phosphorus	7723-14-0		0.00045	g	235	0.0235	203	0.0203
Copper Lead Frame		Metals	Iron, metal	7439-89-6		0.012815	g	6686	0.6686	5785	0.5785
Copper Lead Frame		Metals	Lead, metallic lead and lead alloys	7439-92-1		0.000025	g	13	0.0013	11	0.0011
Copper Lead Frame		Metals	Nickel, metal	7440-02-0		0.087474	g	45638	4.5638	39489	3.9489
Copper Lead Frame		Metals	Palladium, metal	7440-05-3		0.007814	g	4077	0.4077	3527	0.3527
Copper Lead Frame		Metals	Zinc, metal	7440-66-6		0.00068	g	355	0.0355	306	0.0306
Silicon Semiconductor Die	0.0066						g				
Silicon Semiconductor Die		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%)	-		0.000132	g	20000	2	59	0.0059
Silicon Semiconductor Die		Glass	Silicon, doped	-		0.006468	g	980000	98	2919	0.2919
Die Encapsulant	0.2876						g				
Die Encapsulant		Flame Retardants	Antimony trioxide	1309-64-4		0.004201	g	14606	1.4606	1896	0.1896
Die Encapsulant		Metals	Bismuth, metal	7440-69-9		0.00266	g	9250	0.925	1200	0.12
Die Encapsulant		Flame Retardants	Bisphenol A diglycidyl ether, brominated	40039-93-8		0.00168	g	5842	0.5842	758	0.0758
Die Encapsulant		Solvents, additives, and other materials	Carbon Black	1333-86-4		0.00084	g	2921	0.2921	379	0.0379
Die Encapsulant		Solvents, additives, and other materials	Other organic phosphorous compounds	-		0.00266	g	9250	0.925	1200	0.12
Die Encapsulant		Solvents, additives, and other materials	Other organic Silicon Compounds	-		0.00266	g	9250	0.925	1200	0.12
Die Encapsulant		Plastics/polymers	Phenol, polymer with formaldehyde	9003-35-4		0.011201	g	38948	3.8948	5056	0.5056
Die Encapsulant		Glass	Silica, vitreous	80676-86-0		0.238035	g	827654	82.7654	107461	10.7461
Die Encapsulant		Metals	Zinc, metal	7440-66-6		0.00266	g	9250	0.925	1200	0.12
Die Encapsulant		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%)	-		0.004201	g	14606	1.4606	1896	0.1896
Die Encapsulant		Solvents, additives, and other materials	Proprietary Material-Other miscellaneous substances.	-		0.016802	g	58423	5.8423	7585	0.7585
Bonding Wire, Copper	0.0035						g				
Bonding Wire, Copper		Metals	Copper, metal	7440-50-8		0.003395	g	970000	97	1532	0.1532
Bonding Wire, Copper		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%)	-		0.000105	g	30000	3	47	0.0047
Solder Die Attach	0.0007				7a		g				
Solder Die Attach		Metals	Cadmium, metal	7440-43-9		0	g	2	0.0002	0	0
Solder Die Attach		Metals	Chromium(VI)	18540-29-9		0	g	2	0.0002	0	0
Solder Die Attach		Metals	Lead, metallic lead and lead alloys	7439-92-1		0.000668	g	954933	95.4933	301	0.0301
Solder Die Attach		Metals	Mercury	7439-97-6		0	g	2	0.0002	0	0
Solder Die Attach		Metals	Silver, metal	7440-22-4		0.000018	g	25034	2.5034	8	0.0008
Solder Die Attach		Metals	Ti, metal	7440-31-5		0.000014	g	20027	2.0027	6	0.0006

LINKS

MCD LINK

Freescale website <http://www.freescale.com>

GENERAL ENVIRONMENTAL COMPLIANCE LINKS

RoHS signed letter http://www.freescale.com/files/abstract/corporate/ehs_epp/ENV_ROHS_Freescale_Response.pdf

China RoHS <http://www.freescale.com/chinarohs>

REACH signed letter http://www.freescale.com/files/abstract/corporate/ehs_epp/ENV_REACH_Freescale_Response.pdf

ELV signed letter http://www.freescale.com/files/abstract/corporate/ehs_epp/ENV_ELV_Freescale_Reponse.pdf

Conflict Minerals statement http://www.freescale.com/files/abstract/corporate/ehs_epp/ENV_CONFLICT_METAL_Freescale_Response.pdf

FREESCALE ENVIRONMENTAL INFORMATION

EPP website <http://www.freescale.com/epp>

FAQ http://www.freescale.com/webapp/sps/site/overview.jsp?code=ENVIRON_FAQ

Technical Service Request https://www.freescale.com/webapp/servicerequest.create_SR.framework?defaultCategory=Hardware Product Support&defaultTopic=Environmentally Preferred Prod

LINKS TO BLANK IPC1752 FORMS

Blank IPC1752 v0.9 Form http://www.freescale.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v0.9_MCD_Template.pdf

Blank IPC1752 v1.1 Form http://www.freescale.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf

IPC1752 XML LINKS

http://www.freescale.com/mcds/MC33886VW_IPC1752_v09.xml

http://www.freescale.com/mcds/MC33886VW_IPC1752_v11.xml

http://www.freescale.com/mcds/MC33886VW_IPC1752A.xml