

**PART INFORMATION**

Mfg Item Number	MC68HC908QT4CPE
Mfg Item Name	PDIP 8 9.78*6.35*7.36

**SUPPLIER**

Company Name	Freescale Semiconductor Inc
Company Unique ID	14-141-7928
Response Date	2015-07-07
Response Document ID	0003K11060D024A1.7
Contact Name	Freescale Semiconductor Inc
Contact Title	Product Technical Support
Contact Phone	1-800-521-6274
Contact Email	support@freescale.com
Authorized Representative	Daniel Binyon
Representative Title	EPP Customer Response
Representative Phone	512-895-3406
Representative Email	eppanlst@freescale.com
URL for Additional Information	www.freescale.com

**DECLARATION**

EU RoHS	Yes
Pb Free	Yes
HalogenFree	Yes
Plating Indicator	e3
EU RoHS Exemption(s)	

**MANUFACTURING**

Mfg Item Number	MC68HC908QT4CPE
Mfg Item Name	PDIP 8 9.78*6.35*7.36
Version	ALL
Weight	0.422100
UoM	g
Unit Volume	EACH
J-STD-020 MSL Rating	
Peak Processing Temperature	
Max Time at Peak Temperature	
Number of Processing Cycles	3

RoHS	
RoHS Directive	2011/65/EU
RoHS Definition	RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) of homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material of Cadmium
RoHS Legal Definition	Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part(s) identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a RoHS restricted substance) in excess of the applicable quantity limit identified below. If a homogeneous material within the part(s) contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Suppliers Standard Terms and Conditions of Sale applicable to such part(s) shall apply.
RoHS Declaration	1 - Item(s) do not contain RoHS restricted substances per the definition above
Supplier Acceptance	Accepted
Signature	Daniel Binyon
Exemption List Version	2012/51/EU
List of Freescale Accepted Exemptions	<p>6(a) : Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight</p> <p>6(b) : Lead as an alloying element in aluminium containing up to 0.4% lead by weight</p> <p>6(c) : Copper alloy containing up to 4% lead by weight</p> <p>7(a) : Lead in high melting temperature type solders (i.e. lead-based alloys containing 85% by weight or more lead)</p> <p>7(b) : Lead in solders for servers, storage and storage array systems, network infrastructure equipment for switching, signaling, transmission, and network management for telecommunications</p> <p>7(c)-I : Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound</p> <p>7(c)-II : Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher</p> <p>7(c)-III : Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC</p> <p>7(c)-IV : Lead in PZT based dielectric ceramic materials for capacitors being part of integrated circuits or discrete semiconductors</p> <p>15 : Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit flip chip packages</p>

MATERIAL COMPOSITION

Homogeneous Material	Weight	SubstanceClass	Substance	CAS	Exemption	SubstanceWeight	UoM	SubPart PPM	SubPart%	ARTICLEPPM	ARTICLE%
Lead Frame Plating	0.0081						g				
Lead Frame Plating		Lead/Lead Compounds	Lead	7439-92-1		0.0000162	g	200	0.02	3	0.0003
Lead Frame Plating		Metals	Tin, metal	7440-31-5		0.0080838	g	999800	99.98	19185	1.9185
Bonding Wire	0.0003						g				
Bonding Wire		Metals	Gold, metal	7440-57-5		0.0003	g	1000000	100	710	0.071
Copper Lead Frame	0.0812						g				
Copper Lead Frame		Metals	Copper, metal	7440-50-8		0.07827315	g	963955	96.3955	185437	18.5437
Copper Lead Frame		Solvents, additives, and other materials	Phosphorus, elemental (not containing red allotrope)	7723-14-0		0.00006699	g	825	0.0825	158	0.0158
Copper Lead Frame		Metals	Iron, metal	7439-89-6		0.0019082	g	23500	2.35	4520	0.452
Copper Lead Frame		Lead/Lead Compounds	Lead	7439-92-1		0.0000138	g	170	0.017	32	0.0032
Copper Lead Frame		Metals	Silver, metal	7440-22-4		0.000812	g	10000	1	1923	0.1923
Copper Lead Frame		Metals	Tin, metal	7440-31-5		0.0002436	g	300	0.03	57	0.0057
Copper Lead Frame		Metals	Zinc, metal	7440-66-6		0.0001015	g	1250	0.125	240	0.024
Epoxy Die Attach	0.0027						g				
Epoxy Die Attach		Plastics/polymers	Epikote 862	28064-14-4		0.000405	g	150000	15	959	0.0959
Epoxy Die Attach		Metals	Silver, metal	7440-22-4		0.00216	g	800000	80	5117	0.5117
Epoxy Die Attach		Solvents, additives, and other materials	2-ethylhexyl glycidyl ether	2461-15-6		0.000135	g	50000	5	319	0.0319
Die Encapsulant	0.3286						g				
Die Encapsulant		Plastics/polymers	Poly(o-cresyl glycidyl ether)-co-formaldehyde	29690-82-2		0.03286	g	100000	10	7784	0.7784
Die Encapsulant		Plastics/polymers	Other Epoxy resins	-		0.003286	g	10000	1	7784	0.7784
Die Encapsulant		Solvents, additives, and other materials	Carbon Black	1333-86-4		0.00131473	g	4001	0.4001	3114	0.3114
Die Encapsulant		Solvents, additives, and other materials	Other organic Silicon Compounds	-		0.00821434	g	24998	2.4998	19460	1.946
Die Encapsulant		Plastics/polymers	Phenol, polymer with formaldehyde	9003-35-4		0.01643	g	50000	5	38924	3.8924
Die Encapsulant		Plastics/polymers	Other phenolic resins	-		0.003286	g	10000	1	7784	0.7784
Die Encapsulant		Glass	Silica, vitreous	80676-86-0		0.26320893	g	801001	80.1001	623584	62.3584
Silicon Semiconductor Die	0.0012						g				
Silicon Semiconductor Die		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%)	-		0.000024	g	20000	2	56	0.0056
Silicon Semiconductor Die		Glass	Silicon, doped	-		0.001176	g	980000	98	2786	0.2786

## LINKS

### MCD LINK

Freescale website <http://www.freescale.com>

### GENERAL ENVIRONMENTAL COMPLIANCE LINKS

RoHS signed letter [http://www.freescale.com/files/abstract/corporate/ehs\\_epp/ENV\\_ROHS\\_Freescale\\_Response.pdf](http://www.freescale.com/files/abstract/corporate/ehs_epp/ENV_ROHS_Freescale_Response.pdf)

China RoHS <http://www.freescale.com/chinarohs>

REACH signed letter [http://www.freescale.com/files/abstract/corporate/ehs\\_epp/ENV\\_REACH\\_Freescale\\_Response.pdf](http://www.freescale.com/files/abstract/corporate/ehs_epp/ENV_REACH_Freescale_Response.pdf)

ELV signed letter [http://www.freescale.com/files/abstract/corporate/ehs\\_epp/ENV\\_ELV\\_Freescale\\_Reponse.pdf](http://www.freescale.com/files/abstract/corporate/ehs_epp/ENV_ELV_Freescale_Reponse.pdf)

Conflict Minerals statement [http://www.freescale.com/files/abstract/corporate/ehs\\_epp/ENV\\_CONFLICT\\_METAL\\_Freescale\\_Response.pdf](http://www.freescale.com/files/abstract/corporate/ehs_epp/ENV_CONFLICT_METAL_Freescale_Response.pdf)

### FREESCALE ENVIRONMENTAL INFORMATION

EPP website <http://www.freescale.com/epp>

FAQ [http://www.freescale.com/webapp/sps/site/overview.jsp?code=ENVIRON\\_FAQ](http://www.freescale.com/webapp/sps/site/overview.jsp?code=ENVIRON_FAQ)

Technical Service Request [https://www.freescale.com/webapp/servicerequest.create\\_SR.framework?defaultCategory=Hardware Product Support&defaultTopic=Environmentally Preferred Prod](https://www.freescale.com/webapp/servicerequest.create_SR.framework?defaultCategory=Hardware+Product+Support&defaultTopic=Environmentally+Preferred+Prod)

### LINKS TO BLANK IPC1752 FORMS

Blank IPC1752 v1.1 Form [http://www.freescale.com/files/abstract/corporate/ehs\\_epp/IPC-1752-2\\_v1.1\\_MCD\\_Template.pdf](http://www.freescale.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf)

IPC1752 XML LINKS

[http://www.freescale.com/mcdfs/MC68HC908QT4CPE\\_IPC1752\\_v11.xml](http://www.freescale.com/mcdfs/MC68HC908QT4CPE_IPC1752_v11.xml)

[http://www.freescale.com/mcdfs/MC68HC908QT4CPE\\_IPC1752A.xml](http://www.freescale.com/mcdfs/MC68HC908QT4CPE_IPC1752A.xml)