

PART INFORMATION		
Mfg Item Number		MC7448VU1600LD
Mfg Item Name		FCCBGA 360 25SQ*2.2P1.27
SUPPLIER		
Company Name		Freescale Semiconductor Inc
Company Unique ID		14-141-7928
Response Date		2017-06-07
Response Document ID		8429K11079D005A1.34
Contact Name		Freescale Semiconductor Inc
Contact Title		Product Technical Support
Contact Phone		1-800-521-6274
Contact Email		support@freescale.com
Authorized Representative		Daniel Binyon
Representative Title		EPP Customer Response
Representative Phone		512-895-3406
Representative Email		eppanlst@freescale.com
URL for Additional Information		www.freescale.com
DECLARATION		
EU RoHS		Yes
Pb Free		No
HalogenFree		Yes
Plating Indicator		e2
EU RoHS Exemption(s)		15
MANUFACTURING		
Mfg Item Number		MC7448VU1600LD
Mfg Item Name		FCCBGA 360 25SQ*2.2P1.27
Version		ALL
Weight		3.109600
UoM		g
Unit Volume		EACH
J-STD-020 MSL Rating		1
Peak Processing Temperature		260 C
Max Time at Peak Temperature		40 seconds
Number of Processing Cycles		3

RoHS	
RoHS Directive	2011/65/EU
RoHS Definition	RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) of homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material of Cadmium
RoHS Legal Definition	Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part(s) identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a RoHS restricted substance) in excess of the applicable quantity limit identified below. If a homogeneous material within the part(s) contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Suppliers Standard Terms and Conditions of Sale applicable to such part(s) shall apply.
RoHS Declaration	4 - Item(s) does not contain RoHS restricted substances per the definition above except for selected exemptions
Supplier Acceptance	Accepted
Signature	Daniel Binyon
Exemption List Version	2012/51/EU
Exemptions in this part	15:Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit flip chip packages
List of Freescale Accepted Exemptions	6(a) : Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight 6(b) : Lead as an alloying element in aluminium containing up to 0.4% lead by weight 6(c) : Copper alloy containing up to 4% lead by weight 7(a) : Lead in high melting temperature type solders (i.e. lead-based alloys containing 85% by weight or more lead) 7(b) : Lead in solders for servers, storage and storage array systems, network infrastructure equipment for switching, signaling, transmission, and network management for telecommunications 7(c)-I : Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound 7(c)-II : Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher 7(c)-III : Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC 7(c)-IV : Lead in PZT based dielectric ceramic materials for capacitors being part of integrated circuits or discrete semiconductors 15 : Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit flip chip packages

MATERIAL COMPOSITION

Homogeneous Material	Weight	SubstanceClass	Substance	CAS	Exemption	SubstanceWeight	UoM	SubPart PPM	SubPart%		ARTICLEPPM	ARTICLE%
Underfill	0.0336						g					
Underfill		Solvents, additives, and other materials	Methylhexahydrophthalic anhydride	25550-51-0		0.00507578	g	151065	15.1065		1632	0.1632
Underfill		Plastics/polymers	1,3-bis(2,3-epoxypropoxy)-2,2-dimethylpropane	17557-23-2		0.00187135	g	55695	5.5695		601	0.0601
Underfill		Plastics/polymers	1,6-Bis(2,3-epoxypropoxy) naphthalene	27610-48-6		0.00187135	g	55695	5.5695		601	0.0601
Underfill		Plastics/polymers	Elastomer Modified Diglycidyl Ether	68909-14-8		0.00187135	g	55695	5.5695		601	0.0601
Underfill		Glass	Silica, crystalline - quartz (SiO2)	14808-60-7		0.02193345	g	652781	65.2781		7053	0.7053
Underfill		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%).	-		0.00097672	g	29069	2.9069		314	0.0314
Capactor, 0306	0.0816						g					
Capactor, 0306		Metals	Copper, metal	7440-50-8		0.0112608	g	138000	13.8		3621	0.3621
Capactor, 0306		Nickel (external applications only)	Nickel	7440-02-0		0.015912	g	195000	19.5		5117	0.5117
Capactor, 0306		Metals	Tin, metal	7440-31-5		0.0010608	g	13000	1.3		341	0.0341
Capactor, 0306		Metals	Barium titanate	12047-27-7		0.0533664	g	654000	65.4		17161	1.7161
Capactor Solder Paste	0.0503						g					
Capactor Solder Paste		Metals	Copper, metal	7440-50-8		0.0002515	g	5000	0.5		80	0.008
Capactor Solder Paste		Lead/Lead Compounds	Lead	7439-92-1		0.00000417	g	83	0.0083		1	0.0001
Capactor Solder Paste		Metals	Silver, metal	7440-22-4		0.001509	g	30000	3		485	0.0485
Capactor Solder Paste		Metals	Tin, metal	7440-31-5		0.04853533	g	964917	96.4917		15608	1.5608
Organic Substrate, Halogen-free	2.1793						g					
Organic Substrate, Halogen-free		Metals	Aluminum Oxides (Al2O3)	1344-28-1		0.05309647	g	24364	2.4364		17075	1.7075
Organic Substrate, Halogen-free		Metals	Barium oxide	1304-28-5		0.31647141	g	145217	14.5217		101772	10.1772
Organic Substrate, Halogen-free		Metals	Boron oxide	1303-86-2		0.06972888	g	31996	3.1996		22423	2.2423
Organic Substrate, Halogen-free		Solvents, additives, and other materials	Calcium monoxide	1305-78-8		0.03856925	g	17698	1.7698		12403	1.2403
Organic Substrate, Halogen-free		Metals	Chromium oxide	1308-38-9		0.00673622	g	3091	0.3091		2166	0.2166
Organic Substrate, Halogen-free		Metals	Copper, metal	7440-50-8		0.31101662	g	142714	14.2714		100018	10.0018
Organic Substrate, Halogen-free		Metals	Cuprous oxide	1317-39-1		0.0016846	g	773	0.0773		541	0.0541
Organic Substrate, Halogen-free		Metals	Gold, metal	7440-57-5		0.00198316	g	910	0.091		637	0.0637
Organic Substrate, Halogen-free		Solvents, additives, and other materials	Phosphorus, elemental (not containing red allotrope)	7723-14-0		0.00136424	g	626	0.0626		438	0.0438
Organic Substrate, Halogen-free		Lead/Lead Compounds	Lead	7439-92-1		0.00001526	g	7	0.0007		4	0.0004
Organic Substrate, Halogen-free		Nickel (external applications only)	Nickel	7440-02-0		0.02684026	g	12316	1.2316		8631	0.8631
Organic Substrate, Halogen-free		Metals	Palladium, metal	7440-05-3		0.00017216	g	79	0.0079		55	0.0055
Organic Substrate, Halogen-free		Glass	Silicon dioxide	7631-86-9		1.1761682	g	539700	53.97		378261	37.8261
Organic Substrate, Halogen-free		Metals	Silver, metal	7440-22-4		0.00056226	g	258	0.0258		180	0.018
Organic Substrate, Halogen-free		Metals	Strontium Oxide	1314-11-0		0.00421041	g	1932	0.1932		1354	0.1354
Organic Substrate, Halogen-free		Metals	Tin, metal	7440-31-5		0.0203089	g	9319	0.9319		6531	0.6531
Organic Substrate, Halogen-free		Metals	Zirconium oxide	1314-23-4		0.03351763	g	15380	1.538		10778	1.0778
Organic Substrate, Halogen-free		Metals	Barium titanate	12047-27-7		0.11685407	g	53620	5.362		37578	3.7578
Solder Balls - Pb Free, Sn/Ag	0.6123						g					
Solder Balls - Pb Free, Sn/Ag		Metals	Aluminum, metal	7429-90-5		0.00001959	g	32	0.0032		6	0.0006
Solder Balls - Pb Free, Sn/Ag		Antimony/Antimony Compounds	Antimony (metallic)	7440-36-0		0.00007654	g	125	0.0125		24	0.0024
Solder Balls - Pb Free, Sn/Ag		Arsenic/Arsenic Compounds	Arsenic	7440-38-2		0.00004592	g	75	0.0075		14	0.0014
Solder Balls - Pb Free, Sn/Ag		Bismuth/Bismuth Compounds	Bismuth	7440-69-9		0.00011511	g	188	0.0188		37	0.0037
Solder Balls - Pb Free, Sn/Ag		Cadmium/Cadmium Compounds	Cadmium	7440-43-9		0.00000796	g	13	0.0013		2	0.0002
Solder Balls - Pb Free, Sn/Ag		Metals	Copper, metal	7440-50-8		0.00003857	g	63	0.0063		12	0.0012
Solder Balls - Pb Free, Sn/Ag		Metals	Gold, metal	7440-57-5		0.00003857	g	63	0.0063		12	0.0012
Solder Balls - Pb Free, Sn/Ag		Metals	Iridium, metal	7440-74-6		0.00003857	g	63	0.0063		12	0.0012
Solder Balls - Pb Free, Sn/Ag		Solvents, additives, and other materials	Sulfur	7704-34-9		0.00000429	g	7	0.0007		1	0.0001
Solder Balls - Pb Free, Sn/Ag		Solvents, additives, and other materials	Phosphorus, elemental (not containing red allotrope)	7723-14-0		0.00003857	g	63	0.0063		12	0.0012
Solder Balls - Pb Free, Sn/Ag		Metals	Iron, metal	7439-89-6		0.00007654	g	125	0.0125		24	0.0024
Solder Balls - Pb Free, Sn/Ag		Lead/Lead Compounds	Lead	7439-92-1		0.00019165	g	313	0.0313		61	0.0061
Solder Balls - Pb Free, Sn/Ag		Nickel (external applications only)	Nickel	7440-02-0		0.00001959	g	32	0.0032		6	0.0006
Solder Balls - Pb Free, Sn/Ag		Metals	Silver, metal	7440-22-4		0.02143172	g	35002	3.5002		6892	0.6892
Solder Balls - Pb Free, Sn/Ag		Metals	Tin, metal	7440-31-5		0.59014518	g	963617	96.3617		189781	18.9781
Solder Balls - Pb Free, Sn/Ag		Metals	Zinc, metal	7440-66-6		0.00001163	g	19	0.0019		3	0.0003
High Pb Bumped Semiconductor D	0.1525				15		g					
High Pb Bumped Semiconductor D		Lead/Lead Compounds	Lead	7439-92-1		0.01436199	g	94177	9.4177		4618	0.4618
High Pb Bumped Semiconductor D		Nickel (external applications only)	Nickel	7440-02-0		0.00012581	g	825	0.0825		40	0.004
High Pb Bumped Semiconductor D		Metals	Tin, metal	7440-31-5		0.00079579	g	4956	0.4956		243	0.0243
High Pb Bumped Semiconductor D		Metals	Titanium, metal	7440-32-6		0.00000641	g	42	0.0042		2	0.0002
High Pb Bumped Semiconductor D		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%).	-		0.0013725	g	9000	0.9		441	0.0441
High Pb Bumped Semiconductor D		Glass	Silicon, doped	-		0.1358775	g	891000	89.1		43696	4.3696

LINKS	
MCD LINK	
NXP website	http://www.nxp.com
GENERAL ENVIRONMENTAL COMPLIANCE LINKS	
RoHS signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-ROHS-DECLARATION.pdf
China RoHS	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/china-rohs:ENV_CHINA_ROHS_STRATEGY
REACH signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-REACH-STATEMENT.pdf
ELV signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-ELV-STATEMENT.pdf
Conflict Minerals statement	http://www.nxp.com/files/corporate/doc/support_info/NXP-STATEMENT-CONFLICT-MINERALS.pdf
NXP ENVIRONMENTAL INFORMATION	
Environmental Compliance website	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization:ABUENVPRFPRDX
FAQ	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/eco-product-faqs:ENVIRON_FAQ
Technical Service Request	http://www.nxp.com/support/sales-and-support:SUPPORTHOME
LINKS TO BLANK IPC1752 FORMS	
Blank IPC1752 v1.1 Form	http://www.NXP.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf

IPC1752 XML LINKS

http://www.freescale.com/mcds/MC7448VU1600LD_IPC1752_v11.xml

http://www.freescale.com/mcds/MC7448VU1600LD_IPC1752A.xml