

**PART INFORMATION**

Mfg Item Number	MC68040RC25A
Mfg Item Name	PGA 179 FG

**SUPPLIER**

Company Name	Freescale Semiconductor Inc
Company Unique ID	14-141-7928
Response Date	2017-06-22
Response Document ID	5018A1.14
Contact Name	Freescale Semiconductor Inc
Contact Title	Product Technical Support
Contact Phone	1-800-521-6274
Contact Email	support@freescale.com
Authorized Representative	Daniel Binyon
Representative Title	EPP Customer Response
Representative Phone	512-895-3406
Representative Email	eppanlst@freescale.com
URL for Additional Information	www.freescale.com

**DECLARATION**

EU RoHS	Yes
Pb Free	No
HalogenFree	Yes
Plating Indicator	e4
EU RoHS Exemption(s)	7c-I

**MANUFACTURING**

Mfg Item Number	MC68040RC25A
Mfg Item Name	PGA 179 FG
Version	ALL
Weight	24.933500
UoM	g
Unit Volume	EACH
J-STD-020 MSL Rating	
Peak Processing Temperature	
Max Time at Peak Temperature	
Number of Processing Cycles	3

RoHS	
RoHS Directive	2011/65/EU
RoHS Definition	RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) of homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material of Cadmium
RoHS Legal Definition	Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part(s) identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a RoHS restricted substance) in excess of the applicable quantity limit identified below. If a homogeneous material within the part(s) contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Suppliers Standard Terms and Conditions of Sale applicable to such part(s) shall apply.
RoHS Declaration	4 - Item(s) does not contain RoHS restricted substances per the definition above except for selected exemptions
Supplier Acceptance	Accepted
Signature	Daniel Binyon
Exemption List Version	2012/51/EU
Exemptions in this part	7c-I:Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound
List of Freescale Accepted Exemptions	<p>6(a) : Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight</p> <p>6(b) : Lead as an alloying element in aluminium containing up to 0.4% lead by weight</p> <p>6(c) : Copper alloy containing up to 4% lead by weight</p> <p>7(a) : Lead in high melting temperature type solders (i.e. lead-based alloys containing 85% by weight or more lead)</p> <p>7(b) : Lead in solders for servers, storage and storage array systems, network infrastructure equipment for switching, signaling, transmission, and network management for telecommunications</p> <p>7(c)-I : Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound</p> <p>7(c)-II : Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher</p> <p>7(c)-III : Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC</p> <p>7(c)-IV : Lead in PZT based dielectric ceramic materials for capacitors being part of integrated circuits or discrete semiconductors</p> <p>15 : Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit flip chip packages</p>

MATERIAL COMPOSITION

Homogeneous Material	Weight	SubstanceClass	Substance	CAS	Exemption	SubstanceWeight	UoM	SubPart PPM	SubPart%	ARTICLEPPM	ARTICLE%
Cap/Cover	1.7291						g				
Cap/Cover		Metals	Cobalt, metal	7440-48-4		0.259365	g	150000	15	10402	1.0402
Cap/Cover		Metals	Gold, metal	7440-57-5		0.069164	g	40000	4	2773	0.2773
Cap/Cover		Metals	Iron, metal	7439-89-6		0.86455	g	500000	50	34674	3.4674
Cap/Cover		Nickel (external applications only)	Nickel	7440-02-0		0.51873	g	300000	30	20804	2.0804
Cap/Cover		Metals	Tin, metal	7440-31-5		0.017291	g	10000	1	693	0.0693
Epoxy Die Attach	0.075				7c-1		g				
Epoxy Die Attach		Lead/Lead Compounds	Lead (II) oxide	1317-36-8		0.00154958	g	20661	2.0661	62	0.0062
Epoxy Die Attach		Solvents, additives, and other materials	Other organic Silicon Compounds	-		0.00619838	g	82645	8.2645	248	0.0248
Epoxy Die Attach		Metals	Silver, metal	7440-22-4		0.06198351	g	826447	82.6447	2485	0.2485
Epoxy Die Attach		Metals	Silver (I) oxide	20667-12-3		0.00309915	g	41322	4.1322	124	0.0124
Epoxy Die Attach		Metals	Tellurium in Glass frit	7446-07-3		0.0006198	g	8264	0.8264	24	0.0024
Epoxy Die Attach		Metals	Vanadium (V) oxide	1314-62-1		0.00154958	g	20661	2.0661	62	0.0062
Header Assembly	22.9893						g				
Header Assembly		Metals	Aluminum Oxides (Al2O3)	1344-28-1		19.343867	g	841430	84.143	775831	77.5831
Header Assembly		Metals	Chromium, metal	7440-47-3		0.21386946	g	9303	0.9303	8577	0.8577
Header Assembly		Metals	Cobalt, metal	7440-48-4		0.04515099	g	1964	0.1964	1810	0.181
Header Assembly		Metals	Copper, metal	7440-50-8		0.02257549	g	982	0.0982	905	0.0905
Header Assembly		Metals	Gold, metal	7440-57-5		0.08080739	g	3515	0.3515	3240	0.324
Header Assembly		Metals	Iron, metal	7439-89-6		0.07128982	g	3101	0.3101	2859	0.2859
Header Assembly		Nickel (external applications only)	Nickel	7440-02-0		0.08317529	g	3618	0.3618	3335	0.3335
Header Assembly		Glass	Silica, crystalline - quartz (SiO2)	14808-60-7		1.04562333	g	45483	4.5483	41936	4.1936
Header Assembly		Metals	Silver, metal	7440-22-4		0.12239503	g	5324	0.5324	4908	0.4908
Header Assembly		Metals	Tungsten, metal	7440-33-7		1.9605275	g	85280	8.528	78630	7.863
Bonding Wire, Aluminum	0.001						g				
Bonding Wire, Aluminum		Metals	Aluminum, metal	7429-90-5		0.001	g	1000000	100	40	0.004
Silicon Semiconductor Die	0.1391						g				
Silicon Semiconductor Die		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%)	-		0.002782	g	20000	2	111	0.0111
Silicon Semiconductor Die		Glass	Silicon, doped	-		0.136318	g	980000	98	5467	0.5467

## LINKS

MCD LINK	
NXP website	<a href="http://www.nxp.com">http://www.nxp.com</a>
GENERAL ENVIRONMENTAL COMPLIANCE LINKS	
RoHS signed letter	<a href="http://www.nxp.com/files/corporate/doc/support_info/NXP-ROHS-DECLARATION.pdf">http://www.nxp.com/files/corporate/doc/support_info/NXP-ROHS-DECLARATION.pdf</a>
China RoHS	<a href="http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/china-rohs:ENV_CHINA_ROHS_STRATEGY">http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/china-rohs:ENV_CHINA_ROHS_STRATEGY</a>
REACH signed letter	<a href="http://www.nxp.com/files/corporate/doc/support_info/NXP-REACH-STATEMENT.pdf">http://www.nxp.com/files/corporate/doc/support_info/NXP-REACH-STATEMENT.pdf</a>
ELV signed letter	<a href="http://www.nxp.com/files/corporate/doc/support_info/NXP-ELV-STATEMENT.pdf">http://www.nxp.com/files/corporate/doc/support_info/NXP-ELV-STATEMENT.pdf</a>
Conflict Minerals statement	<a href="http://www.nxp.com/files/corporate/doc/support_info/NXP-STATEMENT-CONFLICT-MINERALS.pdf">http://www.nxp.com/files/corporate/doc/support_info/NXP-STATEMENT-CONFLICT-MINERALS.pdf</a>
NXP ENVIRONMENTAL INFORMATION	
Environmental Compliance website	<a href="http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization:ABUENVPRFPRDX">http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization:ABUENVPRFPRDX</a>
FAQ	<a href="http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/eco-product-faqs:ENVIRON_FAQ">http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/eco-product-faqs:ENVIRON_FAQ</a>
Technical Service Request	<a href="http://www.nxp.com/support/sales-and-support:SUPPORTHOME">http://www.nxp.com/support/sales-and-support:SUPPORTHOME</a>
LINKS TO BLANK IPC1752 FORMS	
Blank IPC1752 v1.1 Form	<a href="http://www.NXP.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf">http://www.NXP.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf</a>

IPC1752 XML LINKS

[http://www.freescale.com/mcdfs/MC68040RC25A\\_IPC1752\\_v11.xml](http://www.freescale.com/mcdfs/MC68040RC25A_IPC1752_v11.xml)

[http://www.freescale.com/mcdfs/MC68040RC25A\\_IPC1752A.xml](http://www.freescale.com/mcdfs/MC68040RC25A_IPC1752A.xml)