

**PART INFORMATION**

Mfg Item Number	MC68332AVEH20
Mfg Item Name	PQFP 132 0.950*.950P.025

**SUPPLIER**

Company Name	Freescale Semiconductor Inc
Company Unique ID	14-141-7928
Response Date	2014-12-31
Response Document ID	8023K00071D026A1.18
Contact Name	Freescale Semiconductor Inc
Contact Title	Product Technical Support
Contact Phone	1-800-521-6274
Contact Email	support@freescale.com
Authorized Representative	Daniel Binyon
Representative Title	EPP Customer Response
Representative Phone	512-895-3406
Representative Email	eppanlst@freescale.com
URL for Additional Information	www.freescale.com

**DECLARATION**

EU RoHS	Yes
Pb Free	Yes
HalogenFree	No
Plating Indicator	e3
EU RoHS Exemption(s)	

**MANUFACTURING**

Mfg Item Number	MC68332AVEH20
Mfg Item Name	PQFP 132 0.950*.950P.025
Version	ALL
Weight	4.724500
UoM	g
Unit Volume	EACH
J-STD-020 MSL Rating	3
Peak Processing Temperature	245 C
Max Time at Peak Temperature	30 seconds
Number of Processing Cycles	3

RoHS	
RoHS Directive	2011/65/EU
RoHS Definition	RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) of homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material of Cadmium
RoHS Legal Definition	Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part(s) identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a RoHS restricted substance) in excess of the applicable quantity limit identified below. If a homogeneous material within the part(s) contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Suppliers Standard Terms and Conditions of Sale applicable to such part(s) shall apply.
RoHS Declaration	1 - Item(s) do not contain RoHS restricted substances per the definition above
Supplier Acceptance	Accepted
Signature	Daniel Binyon
Exemption List Version	2012/51/EU
List of Freescale Accepted Exemptions	<p>6(a) : Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight</p> <p>6(b) : Lead as an alloying element in aluminium containing up to 0.4% lead by weight</p> <p>6(c) : Copper alloy containing up to 4% lead by weight</p> <p>7(a) : Lead in high melting temperature type solders (i.e. lead-based alloys containing 85% by weight or more lead)</p> <p>7(b) : Lead in solders for servers, storage and storage array systems, network infrastructure equipment for switching, signaling, transmission, and network management for telecommunications</p> <p>7(c)-I : Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound</p> <p>7(c)-II : Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher</p> <p>7(c)-III : Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC</p> <p>7(c)-IV : Lead in PZT based dielectric ceramic materials for capacitors being part of integrated circuits or discrete semiconductors</p> <p>15 : Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit flip chip packages</p>

MATERIAL COMPOSITION

Homogeneous Material	Weight	SubstanceClass	Substance	CAS	Exemption	SubstanceWeight	UoM	SubPart PPM	SubPart%	ARTICLEPPM	ARTICLE%
Die Encapsulant	2.7905						g				
Die Encapsulant		Antimony/Antimony Compounds	Antimony trioxide	1309-64-4		0.03946604	g	14143	1.4143	8353	0.8353
Die Encapsulant		Solvents, additives, and other materials	Proprietary Material-Other aromatic amines	-		0.00394577	g	1414	0.1414	835	0.0835
Die Encapsulant		Brominated Flame Retardants (other than PBBs or PBDEs)	TBBA-epichlorohydrin oligomer	40039-93-8		0.03946604	g	14143	1.4143	8353	0.8353
Die Encapsulant		Plastics/polymers	Poly(o-cresyl glycidyl ether)-co-formaldehyde	23690-82-2		0.21706183	g	77786	7.7786	45943	4.5943
Die Encapsulant		Solvents, additives, and other materials	Proprietary Material-Other organic silicon compounds	-		0.00523843	g	12628	1.2628	7458	0.7458
Die Encapsulant		Plastics/polymers	Phenol, polymer with formaldehyde	9003-35-4		0.09640958	g	34549	3.4549	20406	2.0406
Die Encapsulant		Plastics/polymers	Phenol, p-xylylene dimethyl ether copolymer	20834-02-6		0.06427359	g	23033	2.3033	13004	1.3004
Die Encapsulant		Glass	Silica, crystalline - quartz (SiO2)	14808-60-7		0.7729499	g	277117	27.7117	163677	16.3677
Die Encapsulant		Glass	Silica, vitreous	80676-86-0		1.52134433	g	545187	54.5187	322011	32.2011
Epoxy Die Attach	0.0056						g				
Epoxy Die Attach		Cadmium/Cadmium Compounds	Cadmium	7440-43-9		0.00000002	g	3	0.0003	0	0
Epoxy Die Attach		Plastics/polymers	Phenolic Polymer Resin, Epikote 155	9003-35-5		0.00771734	g	137740	13.774	163	0.163
Epoxy Die Attach		Lead/Lead Compounds	Lead	7439-92-1		0.00000004	g	7	0.0007	0	0
Epoxy Die Attach		Plastics/polymers	Phenol, polymer with formaldehyde	9003-35-4		0.0011697	g	30303	3.0303	35	0.0035
Epoxy Die Attach		Metals	Silver, metal	7440-22-4		0.0046589	g	831947	83.1947	986	0.986
Bonding Wire	0.0031						g				
Bonding Wire		Metals	Gold, metal	7440-57-5		0.0031	g	1000000	100	656	0.656
Copper Lead Frame	1.8782						g				
Copper Lead Frame		Metals	Copper, metal	7440-50-8		1.81050028	g	963955	96.3955	383228	38.3228
Copper Lead Frame		Solvents, additives, and other materials	Phosphorus	7723-14-0		0.00154952	g	825	0.0825	327	0.0327
Copper Lead Frame		Metals	Iron, metal	7439-89-6		0.0441377	g	23500	2.35	9342	0.9342
Copper Lead Frame		Lead/Lead Compounds	Lead	7439-92-1		0.00031929	g	170	0.017	67	0.0067
Copper Lead Frame		Metals	Silver, metal	7440-22-4		0.018782	g	10000	1	3975	0.3975
Copper Lead Frame		Metals	Tin, metal	7440-31-5		0.00056346	g	300	0.03	119	0.0119
Copper Lead Frame		Metals	Zinc, metal	7440-66-6		0.00234775	g	1250	0.125	496	0.0496
Silicon Semiconductor Die	0.0262						g				
Silicon Semiconductor Die		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%)	-		0.000524	g	20000	2	110	0.011
Silicon Semiconductor Die		Glass	Silicon, doped	-		0.025676	g	980000	98	5434	0.5434
Lead Frame Plating	0.0209						g				
Lead Frame Plating		Lead/Lead Compounds	Lead	7439-92-1		0.00000418	g	200	0.02	0	0
Lead Frame Plating		Metals	Tin, metal	7440-31-5		0.02089582	g	99800	99.98	4422	0.4422

## LINKS

### MCD LINK

Freescale website <http://www.freescale.com>

### GENERAL ENVIRONMENTAL COMPLIANCE LINKS

RoHS signed letter [http://www.freescale.com/files/abstract/corporate/ehs\\_epp/ENV\\_ROHS\\_Freescale\\_Response.pdf](http://www.freescale.com/files/abstract/corporate/ehs_epp/ENV_ROHS_Freescale_Response.pdf)

China RoHS <http://www.freescale.com/chinarohs>

REACH signed letter [http://www.freescale.com/files/abstract/corporate/ehs\\_epp/ENV\\_REACH\\_Freescale\\_Response.pdf](http://www.freescale.com/files/abstract/corporate/ehs_epp/ENV_REACH_Freescale_Response.pdf)

ELV signed letter [http://www.freescale.com/files/abstract/corporate/ehs\\_epp/ENV\\_ELV\\_Freescale\\_Reponse.pdf](http://www.freescale.com/files/abstract/corporate/ehs_epp/ENV_ELV_Freescale_Reponse.pdf)

Conflict Minerals statement [http://www.freescale.com/files/abstract/corporate/ehs\\_epp/ENV\\_CONFLICT\\_METAL\\_Freescale\\_Response.pdf](http://www.freescale.com/files/abstract/corporate/ehs_epp/ENV_CONFLICT_METAL_Freescale_Response.pdf)

### FREESCALE ENVIRONMENTAL INFORMATION

EPP website <http://www.freescale.com/epp>

FAQ [http://www.freescale.com/webapp/sps/site/overview.jsp?code=ENVIRON\\_FAQ](http://www.freescale.com/webapp/sps/site/overview.jsp?code=ENVIRON_FAQ)

Technical Service Request [https://www.freescale.com/webapp/servicerequest.create\\_SR.framework?defaultCategory=Hardware Product Support&defaultTopic=Environmentally Preferred Prod](https://www.freescale.com/webapp/servicerequest.create_SR.framework?defaultCategory=Hardware Product Support&defaultTopic=Environmentally Preferred Prod)

### LINKS TO BLANK IPC1752 FORMS

Blank IPC1752 v1.1 Form [http://www.freescale.com/files/abstract/corporate/ehs\\_epp/IPC-1752-2\\_v1.1\\_MCD\\_Template.pdf](http://www.freescale.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf)

IPC1752 XML LINKS

[http://www.freescale.com/mcdfs/MC68332AVEH20\\_IPC1752\\_v11.xml](http://www.freescale.com/mcdfs/MC68332AVEH20_IPC1752_v11.xml)

[http://www.freescale.com/mcdfs/MC68332AVEH20\\_IPC1752A.xml](http://www.freescale.com/mcdfs/MC68332AVEH20_IPC1752A.xml)