

**PART INFORMATION**

Mfg Item Number	MC68MH360ZQ33L
Mfg Item Name	PBGA 357 25*25*1.2P1.27

**SUPPLIER**

Company Name	Freescale Semiconductor Inc
Company Unique ID	14-141-7928
Response Date	2014-12-29
Response Document ID	5058K10790D048A1.26
Contact Name	Freescale Semiconductor Inc
Contact Title	Product Technical Support
Contact Phone	1-800-521-6274
Contact Email	support@freescale.com
Authorized Representative	Daniel Binyon
Representative Title	EPP Customer Response
Representative Phone	512-895-3406
Representative Email	eppanlst@freescale.com
URL for Additional Information	www.freescale.com

**DECLARATION**

EU RoHS	No
Pb Free	No
HalogenFree	No
Plating Indicator	e0
EU RoHS Exemption(s)	

**MANUFACTURING**

Mfg Item Number	MC68MH360ZQ33L
Mfg Item Name	PBGA 357 25*25*1.2P1.27
Version	ALL
Weight	2.173700
UoM	g
Unit Volume	EACH
J-STD-020 MSL Rating	3
Peak Processing Temperature	260 C
Max Time at Peak Temperature	40 seconds
Number of Processing Cycles	3

RoHS	
RoHS Directive	2011/65/EU
RoHS Definition	RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) of homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material of Cadmium
RoHS Legal Definition	Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part(s) identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a RoHS restricted substance) in excess of the applicable quantity limit identified below. If a homogeneous material within the part(s) contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Suppliers Standard Terms and Conditions of Sale applicable to such part(s) shall apply.
RoHS Declaration	3 - Item(s) does not contain RoHS restricted substances per the definition above except for lead in solders and selected exemptions, if any
Supplier Acceptance	Accepted
Signature	Daniel Binyon
Exemption List Version	2012/51/EU
List of Freescale Accepted Exemptions	<p>6(a) : Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight</p> <p>6(b) : Lead as an alloying element in aluminium containing up to 0.4% lead by weight</p> <p>6(c) : Copper alloy containing up to 4% lead by weight</p> <p>7(a) : Lead in high melting temperature type solders (i.e. lead-based alloys containing 85% by weight or more lead)</p> <p>7(b) : Lead in solders for servers, storage and storage array systems, network infrastructure equipment for switching, signaling, transmission, and network management for telecommunications</p> <p>7(c)-I : Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound</p> <p>7(c)-II : Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher</p> <p>7(c)-III : Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC</p> <p>7(c)-IV : Lead in PZT based dielectric ceramic materials for capacitors being part of integrated circuits or discrete semiconductors</p> <p>15 : Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit flip chip packages</p>

MATERIAL COMPOSITION

Homogeneous Material	Weight	SubstanceClass	Substance	CAS	Exemption	SubstanceWeight	UoM	SubPart PPM	SubPart%	ARTICLEPPM	ARTICLE%
Die Encapsulant	0.76435						g				
Die Encapsulant		Metals	Aluminum, metal	7429-90-5		0.02361536	g	30896	3.0896	10864	1.0864
Die Encapsulant		Arsenic/Arsenic Compounds	Arsenic	7440-38-2		0.00000076	g	1	0.0001	0	0
Die Encapsulant		Cadmium/Cadmium Compounds	Cadmium	7440-43-9		0.00000076	g	1	0.0001	0	0
Die Encapsulant		Plastics/polymers	Proprietary Material-Other Epoxy resins	-		0.02361536	g	30896	3.0896	10864	1.0864
Die Encapsulant		Solvents, additives, and other materials	Carbon Black	1333-86-4		0.00236184	g	3090	0.309	1086	0.1086
Die Encapsulant		Lead/Lead Compounds	Lead	7439-92-1		0.00000076	g	1	0.0001	0	0
Die Encapsulant		Solvents, additives, and other materials	Other organic phosphorous compounds	-		0.00236184	g	3090	0.309	1086	0.1086
Die Encapsulant		Plastics/polymers	Proprietary Material-Other phenolic resins	-		0.04329431	g	56642	5.6642	19917	1.9917
Die Encapsulant		Glass	Silica, vitreous	60676-86-0		0.66809901	g	875383	87.5383	307833	30.7833
Epoxy Die Attach	0.0066						g				
Epoxy Die Attach		Solvents, additives, and other materials	1,3,5-Triazine-2,4-diamine, 6-[2-(2-methyl-1H-imidazol-1-yl)ethyl]	38668-46-1		0.00005578	g	8451	0.8451	25	0.0025
Epoxy Die Attach		Plastics/polymers	Phenolic Polymer Resin, Epikote 155	9003-36-5		0.00085522	g	129579	12.9579	393	0.0393
Epoxy Die Attach		Plastics/polymers	4,4'-Dihydroxydiphenyl	92-88-6		0.00005578	g	8451	0.8451	25	0.0025
Epoxy Die Attach		Metals	Silver, metal	7440-22-4		0.00563322	g	853519	85.3519	2591	0.2591
Bonding Wire	0.0143						g				
Bonding Wire		Metals	Gold, metal	7440-57-5		0.0143	g	1000000	100	6578	0.6578
Solder Balls - Low Lead	0.6825						g				
Solder Balls - Low Lead		Metals	Aluminum, metal	7429-90-5		0.00005546	g	8	0.0008	2	0.0002
Solder Balls - Low Lead		Antimony/Antimony Compounds	Antimony (metallic)	7440-38-0		0.00000478	g	7	0.0007	2	0.0002
Solder Balls - Low Lead		Arsenic/Arsenic Compounds	Arsenic	7440-38-2		0.00001365	g	20	0.002	6	0.0006
Solder Balls - Low Lead		Bismuth/Bismuth Compounds	Bismuth	7440-69-9		0.00000751	g	11	0.0011	3	0.0003
Solder Balls - Low Lead		Metals	Copper, metal	7440-50-8		0.00000683	g	10	0.001	3	0.0003
Solder Balls - Low Lead		Metals	Iron, metal	7439-89-6		0.0000116	g	17	0.0017	5	0.0005
Solder Balls - Low Lead		Lead/Lead Compounds	Lead	7439-92-1		0.24571229	g	360018	36.0018	113038	11.3038
Solder Balls - Low Lead		Nickel (external applications only)	Nickel	7440-02-0		0.00002525	g	37	0.0037	11	0.0011
Solder Balls - Low Lead		Metals	Silver, metal	7440-22-4		0.01359404	g	19918	1.9918	6253	0.6253
Solder Balls - Low Lead		Metals	Tin, metal	7440-31-5		0.42311381	g	619947	61.9947	194651	19.4651
Solder Balls - Low Lead		Metals	Zinc, metal	7440-66-6		0.00000478	g	7	0.0007	2	0.0002
Silicon Semiconductor Die	0.04245						g				
Silicon Semiconductor Die		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%)	-		0.000849	g	20000	2	390	0.039
Silicon Semiconductor Die		Glass	Silicon, doped	-		0.041601	g	980000	98	19138	1.9138
Organic Substrate	0.6635						g				
Organic Substrate		Solvents, additives, and other materials	Acrylonitrile/Butadiene copolymer, carboxyl terminated (26/74)	68891-46-3		0.01297939	g	19562	1.9562	5971	0.5971
Organic Substrate		Metals	Barium sulfate	7727-43-7		0.05871444	g	88492	8.8492	27011	2.7011
Organic Substrate		Flame Retardants	Bromine	7726-95-6		0.02695535	g	40626	4.0626	12400	1.24
Organic Substrate		Metals	Copper, metal	7440-50-8		0.04142496	g	62434	6.2434	19057	1.9057
Organic Substrate		Plastics/polymers	4,4'-dihydroxy-3,3',5,5'-tetramethylbiphenyl diglycidyl ether	85954-11-6		0.08598628	g	129595	12.9595	39557	3.9557
Organic Substrate		Plastics/polymers	Phenolic Polymer Resin, Epikote 155	9003-36-5		0.21600441	g	32553	32.553	99371	9.9371
Organic Substrate		Metals	Gold, metal	7440-57-5		0.01430551	g	2156	0.2156	658	0.0658
Organic Substrate		Solvents, additives, and other materials	Silicon	7440-21-3		0.01545159	g	23288	2.3288	7108	0.7108
Organic Substrate		Nickel (external applications only)	Nickel	7440-02-0		0.0145134	g	21874	2.1874	6676	0.6676
Organic Substrate		Glass	Fibrous-glass-wool	65997-17-3		0.17821942	g	268605	26.8605	81988	8.1988
Organic Substrate		Plastics/polymers	Other acrylic resins	-		0.00709215	g	10689	1.0689	3262	0.3262
Organic Substrate		Plastics/polymers	Other acrylic/epoxy resin mixture	-		0.0047281	g	7126	0.7126	2175	0.2175

## LINKS

### MCD LINK

Freescale website <http://www.freescale.com>

### GENERAL ENVIRONMENTAL COMPLIANCE LINKS

RoHS signed letter [http://www.freescale.com/files/abstract/corporate/ehs\\_epp/ENV\\_ROHS\\_Freescale\\_Response.pdf](http://www.freescale.com/files/abstract/corporate/ehs_epp/ENV_ROHS_Freescale_Response.pdf)

China RoHS <http://www.freescale.com/chinarohs>

REACH signed letter [http://www.freescale.com/files/abstract/corporate/ehs\\_epp/ENV\\_REACH\\_Freescale\\_Response.pdf](http://www.freescale.com/files/abstract/corporate/ehs_epp/ENV_REACH_Freescale_Response.pdf)

ELV signed letter [http://www.freescale.com/files/abstract/corporate/ehs\\_epp/ENV\\_ELV\\_Freescale\\_Reponse.pdf](http://www.freescale.com/files/abstract/corporate/ehs_epp/ENV_ELV_Freescale_Reponse.pdf)

Conflict Minerals statement [http://www.freescale.com/files/abstract/corporate/ehs\\_epp/ENV\\_CONFLICT\\_METAL\\_Freescale\\_Response.pdf](http://www.freescale.com/files/abstract/corporate/ehs_epp/ENV_CONFLICT_METAL_Freescale_Response.pdf)

### FREESCALE ENVIRONMENTAL INFORMATION

EPP website <http://www.freescale.com/epp>

FAQ [http://www.freescale.com/webapp/sps/site/overview.jsp?code=ENVIRON\\_FAQ](http://www.freescale.com/webapp/sps/site/overview.jsp?code=ENVIRON_FAQ)

Technical Service Request [https://www.freescale.com/webapp/servicerequest.create\\_SR.framework?defaultCategory=Hardware Product Support&defaultTopic=Environmentally Preferred Prod](https://www.freescale.com/webapp/servicerequest.create_SR.framework?defaultCategory=Hardware Product Support&defaultTopic=Environmentally Preferred Prod)

### LINKS TO BLANK IPC1752 FORMS

Blank IPC1752 v1.1 Form [http://www.freescale.com/files/abstract/corporate/ehs\\_epp/IPC-1752-2\\_v1.1\\_MCD\\_Template.pdf](http://www.freescale.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf)

IPC1752 XML LINKS

[http://www.freescale.com/mcdfs/MC68MH360ZQ33L\\_IPC1752\\_v11.xml](http://www.freescale.com/mcdfs/MC68MH360ZQ33L_IPC1752_v11.xml)

[http://www.freescale.com/mcdfs/MC68MH360ZQ33L\\_IPC1752A.xml](http://www.freescale.com/mcdfs/MC68MH360ZQ33L_IPC1752A.xml)