

PART INFORMATION

Mfg Item Number	MK26FN2M0VMD18
Mfg Item Name	MAPBGA 144 13*13*1.7 P1

SUPPLIER

Company Name	Freescale Semiconductor Inc
Company Unique ID	14-141-7928
Response Date	2017-08-01
Response Document ID	007BK00169D014A1.8
Contact Name	Freescale Semiconductor Inc
Contact Title	Product Technical Support
Contact Phone	1-800-521-6274
Contact Email	support@freescale.com
Authorized Representative	Daniel Binyon
Representative Title	EPP Customer Response
Representative Phone	512-895-3406
Representative Email	eppanlst@freescale.com
URL for Additional Information	www.freescale.com

DECLARATION

EU RoHS	Yes
Pb Free	Yes
HalogenFree	Yes
Plating Indicator	e1
EU RoHS Exemption(s)	

MANUFACTURING

Mfg Item Number	MK26FN2M0VMD18
Mfg Item Name	MAPBGA 144 13*13*1.7 P1
Version	ALL
Weight	0.441000
UoM	g
Unit Volume	EACH
J-STD-020 MSL Rating	3
Peak Processing Temperature	260 C
Max Time at Peak Temperature	40 seconds
Number of Processing Cycles	3

RoHS	
RoHS Directive	2011/65/EU
RoHS Definition	RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) of homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material of Cadmium
RoHS Legal Definition	Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part(s) identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a RoHS restricted substance) in excess of the applicable quantity limit identified below. If a homogeneous material within the part(s) contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Suppliers Standard Terms and Conditions of Sale applicable to such part(s) shall apply.
RoHS Declaration	1 - Item(s) do not contain RoHS restricted substances per the definition above
Supplier Acceptance	Accepted
Signature	Daniel Binyon
Exemption List Version	2012/51/EU
List of Freescale Accepted Exemptions	<p>6(a) : Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight</p> <p>6(b) : Lead as an alloying element in aluminium containing up to 0.4% lead by weight</p> <p>6(c) : Copper alloy containing up to 4% lead by weight</p> <p>7(a) : Lead in high melting temperature type solders (i.e. lead-based alloys containing 85% by weight or more lead)</p> <p>7(b) : Lead in solders for servers, storage and storage array systems, network infrastructure equipment for switching, signaling, transmission, and network management for telecommunications</p> <p>7(c)-I : Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound</p> <p>7(c)-II : Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher</p> <p>7(c)-III : Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC</p> <p>7(c)-IV : Lead in PZT based dielectric ceramic materials for capacitors being part of integrated circuits or discrete semiconductors</p> <p>15 : Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit flip chip packages</p>

MATERIAL COMPOSITION

Homogeneous Material	Weight	SubstanceClass	Substance	CAS	Exemption	SubstanceWeight	UoM	SubPart PPM	SubPart%	ARTICLEPPM	ARTICLE%
Solder Balls - Lead Free	0.0734						g				
Solder Balls - Lead Free		Metals	Aluminum, metal	7429-90-5		0.0000228	g	31	0.0031	5	0.0005
Solder Balls - Lead Free		Antimony/Antimony Compounds	Antimony (metallic)	7440-36-0		0.00000918	g	125	0.0125	20	0.002
Solder Balls - Lead Free		Arsenic/Arsenic Compounds	Arsenic	7440-38-2		0.00000543	g	74	0.0074	12	0.0012
Solder Balls - Lead Free		Bismuth/Bismuth Compounds	Bismuth	7440-69-9		0.00001373	g	187	0.0187	31	0.0031
Solder Balls - Lead Free		Cadmium/Cadmium Compounds	Cadmium	7440-43-8		0.00000088	g	12	0.0012	1	0.0001
Solder Balls - Lead Free		Metals	Copper, metal	7440-50-8		0.00036556	g	4994	0.4994	831	0.0831
Solder Balls - Lead Free		Metals	Gold, metal	7440-57-5		0.00000455	g	62	0.0062	10	0.001
Solder Balls - Lead Free		Metals	Indium, metal	7440-74-6		0.00000455	g	62	0.0062	10	0.001
Solder Balls - Lead Free		Solvents, additives, and other materials	Sulfur	7704-34-9		0.00000044	g	6	0.0006	0	0
Solder Balls - Lead Free		Solvents, additives, and other materials	Phosphorus, elemental (not containing red allotrope)	7723-14-0		0.00000455	g	62	0.0062	10	0.001
Solder Balls - Lead Free		Metals	Iron, metal	7439-89-6		0.00000918	g	125	0.0125	20	0.002
Solder Balls - Lead Free		Lead/Lead Compounds	Lead	7439-92-1		0.00002753	g	375	0.0375	62	0.0062
Solder Balls - Lead Free		Nickel (external applications only)	Nickel	7440-02-0		0.00000228	g	31	0.0031	5	0.0005
Solder Balls - Lead Free		Metals	Silver, metal	7440-22-4		0.00293255	g	3953	3.953	6649	0.6649
Solder Balls - Lead Free		Metals	Tin, metal	7440-31-5		0.07001492	g	953882	95.3882	158763	15.8763
Solder Balls - Lead Free		Metals	Zinc, metal	7440-66-6		0.00000139	g	19	0.0019	3	0.0003
Non-Conductive Epoxy/Adhesive	0.0015						g				
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Proprietary Material-Other Epoxy resins	-		0.0001125	g	75000	7.5	255	0.0255
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Crosslinked acrylate polymer	25767-43-5		0.0003	g	200000	20	680	0.068
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Other polymers	-		0.0001125	g	75000	7.5	255	0.0255
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Proprietary Material-Other polymers	-		0.0003	g	200000	20	680	0.068
Non-Conductive Epoxy/Adhesive		Glass	Silica, vitreous	80676-86-0		0.000675	g	450000	45	1530	0.153
Bonding Wire, Copper	0.0037						g				
Bonding Wire, Copper		Metals	Copper, metal	7440-50-8		0.003589	g	970000	97	8138	0.8138
Bonding Wire, Copper		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%)	-		0.000111	g	30000	3	251	0.0251
Die Encapsulant, Halogen-free	0.2362						g				
Die Encapsulant, Halogen-free		Metals	Other aluminum compounds	-		0.007086	g	30000	3	16068	1.6068
Die Encapsulant, Halogen-free		Solvents, additives, and other materials	Carbon Black	1333-86-4		0.002362	g	10000	1	5356	0.5356
Die Encapsulant, Halogen-free		Plastics/polymers	Phenol, polymer with formaldehyde	9003-35-4		0.007086	g	30000	3	16068	1.6068
Die Encapsulant, Halogen-free		Plastics/polymers	Other phenolic resins	-		0.007086	g	30000	3	16068	1.6068
Die Encapsulant, Halogen-free		Glass	Silica, vitreous	80676-86-0		0.20077	g	850000	85	455284	45.5284
Die Encapsulant, Halogen-free		Plastics/polymers	Other Non-halogenated Epoxy resins	-		0.01181	g	50000	5	26780	2.678
Organic Substrate	0.112						g				
Organic Substrate		Solvents, additives, and other materials	Other aromatic amines and their salts	-		0.00001848	g	165	0.0165	41	0.0041
Organic Substrate		Metals	Barium sulfate	7727-43-7		0.00062339	g	5566	0.5566	1413	0.1413
Organic Substrate		Metals	Copper, metal	7440-50-8		0.05082737	g	453816	45.3816	115254	11.5254
Organic Substrate		Plastics/polymers	Phenolic Polymer Resin, Epikote 155	9003-36-5		0.00186178	g	16623	1.6623	4221	0.4221
Organic Substrate		Plastics/polymers	Other Epoxy resins	-		0.0046359	g	41392	4.1392	10512	1.0512
Organic Substrate		Metals	Gold, metal	7440-57-5		0.00147594	g	13178	1.3178	3346	0.3346
Organic Substrate		Metals	Talc	14807-96-6		0.00031405	g	2804	0.2804	712	0.0712
Organic Substrate		Nickel (external applications only)	Nickel	7440-02-0		0.01151707	g	102831	10.2831	26115	2.6115
Organic Substrate		Glass	Fibrous-glass-wool	65997-17-3		0.02615715	g	233546	23.3546	58313	5.8313
Organic Substrate		Glass	Silicon dioxide	7631-86-9		0.00340446	g	30397	3.0397	7719	0.7719
Organic Substrate		Solvents, additives, and other materials	Other Aromatic carbonyl compounds	-		0.0011682	g	1043	0.1043	264	0.0264
Organic Substrate		Plastics/polymers	Triazine	25722-86-1		0.00186178	g	16623	1.6623	4221	0.4221
Organic Substrate		Metals	Aluminum Hydroxide	21645-51-2		0.00463848	g	41415	4.1415	10518	1.0518
Organic Substrate		Metals	Copper phthalocyanine	147-14-8		0.00000549	g	49	0.0049	12	0.0012
Organic Substrate		Solvents, additives, and other materials	Quinacridone pigment	1047-16-1		0.00000549	g	49	0.0049	12	0.0012
Organic Substrate		Solvents, additives, and other materials	3-methoxy-3-methyl-1-butyl acetate	103429-90-9		0.00068354	g	6103	0.6103	1549	0.1549
Organic Substrate		Solvents, additives, and other materials	Bis(3-ethyl-5-methyl-4-maleimidophenyl)methane	105391-33-1		0.00186178	g	16623	1.6623	4221	0.4221
Organic Substrate		Plastics/polymers	Epoxy Resin	115254-47-2		0.0198554	g	17728	1.7728	4502	0.4502
Organic Substrate		Solvents, additives, and other materials	1,2,4-Trimethylbenzene	95-63-6		0.00000549	g	49	0.0049	12	0.0012
Silicon Semiconductor Die	0.0142						g				
Silicon Semiconductor Die		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%)	-		0.000284	g	20000	2	643	0.0643
Silicon Semiconductor Die		Glass	Silicon, doped	-		0.013916	g	980000	98	31555	3.1555

LINKS

MCD LINK	
NXP website	http://www.nxp.com
GENERAL ENVIRONMENTAL COMPLIANCE LINKS	
RoHS signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-ROHS-DECLARATION.pdf
China RoHS	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/china-rohs:ENV_CHINA_ROHS_STRATEGY
REACH signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-REACH-STATEMENT.pdf
ELV signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-ELV-STATEMENT.pdf
Conflict Minerals statement	http://www.nxp.com/files/corporate/doc/support_info/NXP-STATEMENT-CONFLICT-MINERALS.pdf
NXP ENVIRONMENTAL INFORMATION	
Environmental Compliance website	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization:ABUENVPRFPRDX
FAQ	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/eco-product-faqs:ENVIRON_FAQ
Technical Service Request	http://www.nxp.com/support/sales-and-support:SUPPORTHOME
LINKS TO BLANK IPC1752 FORMS	
Blank IPC1752 v1.1 Form	http://www.NXP.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf

IPC1752 XML LINKS

http://www.freescale.com/mcdfs/MK26FN2M0VMD18_IPC1752_v11.xml

http://www.freescale.com/mcdfs/MK26FN2M0VMD18_IPC1752A.xml