

**PART INFORMATION**

Mfg Item Number	MPC850SRZQ50BU
Mfg Item Name	PBGA 256 23*23*1.22P1.27

**SUPPLIER**

Company Name	Freescale Semiconductor Inc
Company Unique ID	14-141-7928
Response Date	2016-07-28
Response Document ID	5061K10792D036A1.28
Contact Name	Freescale Semiconductor Inc
Contact Title	Product Technical Support
Contact Phone	1-800-521-6274
Contact Email	support@freescale.com
Authorized Representative	Daniel Binyon
Representative Title	EPP Customer Response
Representative Phone	512-895-3406
Representative Email	eppanlst@freescale.com
URL for Additional Information	www.freescale.com

**DECLARATION**

EU RoHS	No
Pb Free	No
HalogenFree	Yes
Plating Indicator	e0
EU RoHS Exemption(s)	

**MANUFACTURING**

Mfg Item Number	MPC850SRZQ50BU
Mfg Item Name	PBGA 256 23*23*1.22P1.27
Version	ALL
Weight	1.724050
UoM	g
Unit Volume	EACH
J-STD-020 MSL Rating	3
Peak Processing Temperature	260 C
Max Time at Peak Temperature	40 seconds
Number of Processing Cycles	3

RoHS	
RoHS Directive	2011/65/EU
RoHS Definition	RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) of homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material of Cadmium
RoHS Legal Definition	Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part(s) identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a RoHS restricted substance) in excess of the applicable quantity limit identified below. If a homogeneous material within the part(s) contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Suppliers Standard Terms and Conditions of Sale applicable to such part(s) shall apply.
RoHS Declaration	3 - Item(s) does not contain RoHS restricted substances per the definition above except for lead in solders and selected exemptions, if any
Supplier Acceptance	Accepted
Signature	Daniel Binyon
Exemption List Version	2012/51/EU
List of Freescale Accepted Exemptions	<p>6(a) : Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight</p> <p>6(b) : Lead as an alloying element in aluminium containing up to 0.4% lead by weight</p> <p>6(c) : Copper alloy containing up to 4% lead by weight</p> <p>7(a) : Lead in high melting temperature type solders (i.e. lead-based alloys containing 85% by weight or more lead)</p> <p>7(b) : Lead in solders for servers, storage and storage array systems, network infrastructure equipment for switching, signaling, transmission, and network management for telecommunications</p> <p>7(c)-I : Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound</p> <p>7(c)-II : Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher</p> <p>7(c)-III : Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC</p> <p>7(c)-IV : Lead in PZT based dielectric ceramic materials for capacitors being part of integrated circuits or discrete semiconductors</p> <p>15 : Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit flip chip packages</p>

MATERIAL COMPOSITION

Homogeneous Material	Weight	SubstanceClass	Substance	CAS	Exemption	SubstanceWeight	UoM	SubPart PPM	SubPart%	ARTICLEPPM	ARTICLE%
Die Encapsulant	0.76215						g				
Die Encapsulant		Metals	Aluminum, metal	7429-90-5		0.02354739	g	30896	3.0896	13658	1.3658
Die Encapsulant		Arsenic/Arsenic Compounds	Arsenic	7440-38-2		0.00000076	g	1	0.0001	0	0
Die Encapsulant		Cadmium/Cadmium Compounds	Cadmium	7440-43-9		0.00000076	g	1	0.0001	0	0
Die Encapsulant		Plastics/polymers	Proprietary Material-Other Epoxy resins	-		0.02354739	g	30896	3.0896	13658	1.3658
Die Encapsulant		Solvents, additives, and other materials	Carbon Black	1333-86-4		0.00235504	g	3090	0.309	1365	0.1365
Die Encapsulant		Lead/Lead Compounds	Lead	7439-92-1		0.00000076	g	1	0.0001	0	0
Die Encapsulant		Solvents, additives, and other materials	Other organic phosphorous compounds	-		0.00235504	g	3090	0.309	1365	0.1365
Die Encapsulant		Plastics/polymers	Proprietary Material-Other phenolic resins	-		0.0431697	g	56642	5.6642	25039	2.5039
Die Encapsulant		Glass	Silica, vitreous	60676-86-0		0.66717316	g	875383	87.5383	386999	38.6999
Epoxy Die Attach	0.0171						g				
Epoxy Die Attach		Solvents, additives, and other materials	1,3,5-Triazine-2,4-diamine, 6-[2-(2-methyl-1H-imidazol-1-yl)ethyl]	38668-46-1		0.00014451	g	8451	0.8451	83	0.0083
Epoxy Die Attach		Plastics/polymers	Phenolic Polymer Resin, Epikote 155	9003-36-5		0.0022158	g	129579	12.9579	1285	0.1285
Epoxy Die Attach		Plastics/polymers	4,4'-Dihydroxydiphenyl	92-88-6		0.00014451	g	8451	0.8451	83	0.0083
Epoxy Die Attach		Metals	Silver, metal	7440-22-4		0.01459518	g	853519	85.3519	8465	0.8465
Solder Balls - Low Lead	0.4952						g				
Solder Balls - Low Lead		Metals	Aluminum, metal	7429-90-5		0.00003296	g	8	0.0008	2	0.0002
Solder Balls - Low Lead		Antimony/Antimony Compounds	Antimony (metallic)	7440-36-0		0.00003047	g	7	0.0007	2	0.0002
Solder Balls - Low Lead		Arsenic/Arsenic Compounds	Arsenic	7440-38-2		0.0000099	g	20	0.002	5	0.0005
Solder Balls - Low Lead		Bismuth/Bismuth Compounds	Bismuth	7440-69-9		0.00002046	g	11	0.0011	3	0.0003
Solder Balls - Low Lead		Metals	Copper, metal	7440-50-8		0.00000495	g	10	0.001	2	0.0002
Solder Balls - Low Lead		Metals	Iron, metal	7439-89-6		0.00000942	g	17	0.0017	4	0.0004
Solder Balls - Low Lead		Lead/Lead Compounds	Lead	7439-92-1		0.1782891	g	360018	36.0018	103408	10.3408
Solder Balls - Low Lead		Nickel (external applications only)	Nickel	7440-02-0		0.00001932	g	37	0.0037	10	0.001
Solder Balls - Low Lead		Metals	Silver, metal	7440-22-4		0.0098339	g	19918	1.9918	5721	0.5721
Solder Balls - Low Lead		Metals	Tin, metal	7440-31-5		0.3969776	g	619947	61.9947	178067	17.8067
Solder Balls - Low Lead		Metals	Zinc, metal	7440-66-6		0.00003047	g	7	0.0007	2	0.0002
Organic Substrate	0.3714						g				
Organic Substrate		Solvents, additives, and other materials	Acrylonitrile/Butadiene copolymer, carboxyl terminated (26/74)	68891-46-3		0.00256897	g	6917	0.6917	1400	0.14
Organic Substrate		Metals	Barium sulfate	7727-43-7		0.02383979	g	64189	6.4189	13827	1.3827
Organic Substrate		Metals	Copper, metal	7440-50-8		0.06592461	g	177503	17.7503	38238	3.8238
Organic Substrate		Metals	Gold, metal	7440-57-5		0.00350824	g	9446	0.9446	2034	0.2034
Organic Substrate		Solvents, additives, and other materials	Silicon	7440-21-3		0.00000826	g	830	0.083	178	0.0178
Organic Substrate		Nickel (external applications only)	Nickel	7440-02-0		0.00083008	g	2235	0.2235	481	0.0481
Organic Substrate		Glass	Fibrous-glass-wool	65997-17-3		0.11230727	g	302389	30.2389	65141	6.5141
Organic Substrate		Plastics/polymers	Other acrylic resins	-		0.0021042	g	81342	8.1342	17522	1.7522
Organic Substrate		Plastics/polymers	Proprietary Material-Other Non-halogenated Epoxy resins	-		0.13190236	g	355149	35.5149	76507	7.6507
Bonding Wire, PtCu	0.0143						g				
Bonding Wire, PtCu		Metals	Copper, metal	7440-50-8		0.0140283	g	981000	98.1	8136	0.8136
Bonding Wire, PtCu		Metals	Gold, metal	7440-57-5		0.0000143	g	1000	0.1	8	0.0008
Bonding Wire, PtCu		Metals	Palladium, metal	7440-05-3		0.0000254	g	18000	1.8	149	0.0149
Silicon Semiconductor Die	0.0639						g				
Silicon Semiconductor Die		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%)	-		0.001278	g	20000	2	741	0.0741
Silicon Semiconductor Die		Glass	Silicon, doped	-		0.062622	g	980000	98	36322	3.6322

## LINKS

MCD LINK	
NXP website	<a href="http://www.nxp.com">http://www.nxp.com</a>
GENERAL ENVIRONMENTAL COMPLIANCE LINKS	
RoHS signed letter	<a href="http://www.nxp.com/files/corporate/doc/support_info/NXP-ROHS-DECLARATION.pdf">http://www.nxp.com/files/corporate/doc/support_info/NXP-ROHS-DECLARATION.pdf</a>
China RoHS	<a href="http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/china-rohs:ENV_CHINA_ROHS_STRATEGY">http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/china-rohs:ENV_CHINA_ROHS_STRATEGY</a>
REACH signed letter	<a href="http://www.nxp.com/files/corporate/doc/support_info/NXP-REACH-STATEMENT.pdf">http://www.nxp.com/files/corporate/doc/support_info/NXP-REACH-STATEMENT.pdf</a>
ELV signed letter	<a href="http://www.nxp.com/files/corporate/doc/support_info/NXP-ELV-STATEMENT.pdf">http://www.nxp.com/files/corporate/doc/support_info/NXP-ELV-STATEMENT.pdf</a>
Conflict Minerals statement	<a href="http://www.nxp.com/files/corporate/doc/support_info/NXP-STATEMENT-CONFLICT-MINERALS.pdf">http://www.nxp.com/files/corporate/doc/support_info/NXP-STATEMENT-CONFLICT-MINERALS.pdf</a>
NXP ENVIRONMENTAL INFORMATION	
Environmental Compliance website	<a href="http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization:ABUENVPRFPRDX">http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization:ABUENVPRFPRDX</a>
FAQ	<a href="http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/eco-product-faqs:ENVIRON_FAQ">http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/eco-product-faqs:ENVIRON_FAQ</a>
Technical Service Request	<a href="http://www.nxp.com/support/sales-and-support:SUPPORTHOME">http://www.nxp.com/support/sales-and-support:SUPPORTHOME</a>
LINKS TO BLANK IPC1752 FORMS	
Blank IPC1752 v1.1 Form	<a href="http://www.NXP.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf">http://www.NXP.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf</a>

IPC1752 XML LINKS

[http://www.freescale.com/mcdfs/MPC850SRZQ50BU\\_IPC1752\\_v11.xml](http://www.freescale.com/mcdfs/MPC850SRZQ50BU_IPC1752_v11.xml)

[http://www.freescale.com/mcdfs/MPC850SRZQ50BU\\_IPC1752A.xml](http://www.freescale.com/mcdfs/MPC850SRZQ50BU_IPC1752A.xml)