

PART INFORMATION	
Mfg Item Number	MMPF0100F0EP
Mfg Item Name	QFN-56 EP 8SQ*0.9 P0.5
SUPPLIER	
Company Name	Freescale Semiconductor Inc
Company Unique ID	14-141-7928
Response Date	2015-10-23
Response Document ID	00BAA1.13
Contact Name	Freescale Semiconductor Inc
Contact Title	Product Technical Support
Contact Phone	1-800-521-6274
Contact Email	support@freescale.com
Authorized Representative	Daniel Binyon
Representative Title	EPP Customer Response
Representative Phone	512-895-3406
Representative Email	eppanlst@freescale.com
URL for Additional Information	www.freescale.com
DECLARATION	
EU RoHS	Yes
Pb Free	Yes
HalogenFree	Yes
Plating Indicator	e3
EU RoHS Exemption(s)	
MANUFACTURING	
Mfg Item Number	MMPF0100F0EP
Mfg Item Name	QFN-56 EP 8SQ*0.9 P0.5
Version	ALL
Weight	0.147800
UoM	g
Unit Volume	EACH
J-STD-020 MSL Rating	3
Peak Processing Temperature	260 C
Max Time at Peak Temperature	40 seconds
Number of Processing Cycles	3

RoHS	
RoHS Directive	2011/65/EU
RoHS Definition	RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) of homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material of Cadmium
RoHS Legal Definition	Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part(s) identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a RoHS restricted substance) in excess of the applicable quantity limit identified below. If a homogeneous material within the part(s) contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Suppliers Standard Terms and Conditions of Sale applicable to such part(s) shall apply.
RoHS Declaration	1 - Item(s) do not contain RoHS restricted substances per the definition above
Supplier Acceptance	Accepted
Signature	Daniel Binyon
Exemption List Version	2012/51/EU
List of Freescale Accepted Exemptions	6(a) : Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight 6(b) : Lead as an alloying element in aluminium containing up to 0.4% lead by weight 6(c) : Copper alloy containing up to 4% lead by weight 7(a) : Lead in high melting temperature type solders (i.e. lead-based alloys containing 85% by weight or more lead) 7(b) : Lead in solders for servers, storage and storage array systems, network infrastructure equipment for switching, signaling, transmission, and network management for telecommunications 7(c)-I : Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound 7(c)-II : Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher 7(c)-III : Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC 7(c)-IV : Lead in PZT based dielectric ceramic materials for capacitors being part of integrated circuits or discrete semiconductors 15 : Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit flip chip packages

MATERIAL COMPOSITION

Homogeneous Material	Weight	SubstanceClass	Substance	CAS	Exemption	SubstanceWeight	UoM	SubPart PPM	SubPart%		ARTICLEPPM	ARTICLE%
Lead Frame Plating	0.0012						g					
Lead Frame Plating		Lead/Lead Compounds	Lead	7439-92-1		0.00000024	g	200	0.02		1	0.0001
Lead Frame Plating		Metals	Tin, metal	7440-31-5		0.00119976	g	999800	99.98		8117	0.8117
Epoxy Die Attach	0.0018						g					
Epoxy Die Attach		Solvents, additives, and other materials	Other acrylates	-		0.00012606	g	70035	7.0035		852	0.0852
Epoxy Die Attach		Solvents, additives, and other materials	Proprietary Material-Other acrylates	-		0.00009905	g	55028	5.5028		670	0.067
Epoxy Die Attach		Solvents, additives, and other materials	Other acrylonitrile compounds	-		0.00002251	g	12506	1.2506		152	0.0152
Epoxy Die Attach		Solvents, additives, and other materials	Other organic Silicon Compounds	-		0.00002251	g	12506	1.2506		152	0.0152
Epoxy Die Attach		Plastics/polymers	Phenol, polymer with formaldehyde	9003-35-4		0.00004502	g	25013	2.5013		304	0.0304
Epoxy Die Attach		Plastics/polymers	Other polymers	-		0.00009905	g	55028	5.5028		670	0.067
Epoxy Die Attach		Metals	Silver, metal	7440-22-4		0.0013858	g	769884	76.9884		9376	0.9376
Bonding Wire, PdCu	0.0031						g					
Bonding Wire, PdCu		Metals	Copper, metal	7440-50-8		0.00301621	g	972970	97.297		20407	2.0407
Bonding Wire, PdCu		Metals	Palladium, metal	7440-05-3		0.00008379	g	27030	2.703		566	0.0566
Copper Lead Frame	0.0434						g					
Copper Lead Frame		Metals	Copper, metal	7440-50-8		0.04183564	g	963955	96.3955		283055	28.3055
Copper Lead Frame		Solvents, additives, and other materials	Phosphorus, elemental (not containing red allotrope)	7723-14-0		0.00003581	g	825	0.0825		242	0.0242
Copper Lead Frame		Metals	Iron, metal	7439-89-6		0.00101199	g	23500	2.35		6900	0.69
Copper Lead Frame		Lead/Lead Compounds	Lead	7439-92-1		0.00000738	g	170	0.017		49	0.0049
Copper Lead Frame		Metals	Silver, metal	7440-22-4		0.000434	g	10000	1		2936	0.2936
Copper Lead Frame		Metals	Tin, metal	7440-31-5		0.00001302	g	300	0.03		88	0.0088
Copper Lead Frame		Metals	Zinc, metal	7440-66-6		0.00005425	g	1250	0.125		367	0.0367
Silicon Semiconductor Die	0.0048						g					
Silicon Semiconductor Die		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%)	-		0.0000096	g	20000	2		649	0.0649
Silicon Semiconductor Die		Glass	Silicon, doped	-		0.004704	g	980000	98		31826	3.1826
Die Encapsulant, Halogen-free	0.0935						g					
Die Encapsulant, Halogen-free		Plastics/polymers	Other Epoxy resins	-		0.00468201	g	50075	5.0075		31678	3.1678
Die Encapsulant, Halogen-free		Solvents, additives, and other materials	Carbon Black	1333-86-4		0.00046825	g	5008	0.5008		3168	0.3168
Die Encapsulant, Halogen-free		Plastics/polymers	Other phenolic resins	-		0.00468201	g	50075	5.0075		31678	3.1678
Die Encapsulant, Halogen-free		Glass	Silicon dioxide	7631-86-9		0.00421386	g	45068	4.5068		28510	2.851
Die Encapsulant, Halogen-free		Glass	Silica, vitreous	60676-86-0		0.07945387	g	849774	84.9774		537587	53.7587

LINKS	
MCD LINK	
Freescal website	http://www.freescal.com
GENERAL ENVIRONMENTAL COMPLIANCE LINKS	
RoHS signed letter	http://www.freescal.com/files/abstract/corporate/ehs_epp/ENV_ROHS_Freescal_Response.pdf
China RoHS	http://www.freescal.com/chinarohs
REACH signed letter	http://www.freescal.com/files/abstract/corporate/ehs_epp/ENV_REACH_Freescal_Response.pdf
ELV signed letter	http://www.freescal.com/files/abstract/corporate/ehs_epp/ENV_ELV_Freescal_Reponse.pdf
Conflict Minerals statement	http://www.freescal.com/files/abstract/corporate/ehs_epp/ENV_CONFLICT_METAL_Freescal_Response.pdf
FREESCALE ENVIRONMENTAL INFORMATION	
EPP website	http://www.freescal.com/epp
FAQ	http://www.freescal.com/webapp/sps/site/overview.jsp?code=ENVIRON_FAQ
Technical Service Request	https://www.freescal.com/webapp/servicerequest.create_SR.framework?defaultCategory=Hardware Product Support&defaultTopic=Environmentally Preferred Prod
LINKS TO BLANK IPC1752 FORMS	
Blank IPC1752 v1.1 Form	http://www.freescal.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf

IPC1752 XML LINKS

http://www.freescale.com/mcds/MMPF0100F0EP_IPC1752_v11.xml

http://www.freescale.com/mcds/MMPF0100F0EP_IPC1752A.xml