

PART INFORMATION		
Mfg Item Number	MSC8256ESAG1000B	
Mfg Item Name	FCPBGA 783 29SQ3.55P1.0	
SUPPLIER		
Company Name	Freescale Semiconductor Inc	
Company Unique ID	14-141-7928	
Response Date	2014-02-10	
Response Document ID	8448K50008S294A1.5	
Contact Name	Freescale Semiconductor Inc	
Contact Title	Product Technical Support	
Contact Phone	1-800-521-6274	
Contact Email	support@freescale.com	
Authorized Representative	Daniel Binyon	
Representative Title	EPP Customer Response	
Representative Phone	512-895-3406	
Representative Email	eppanlst@freescale.com	
URL for Additional Information	www.freescale.com	
DECLARATION		
EU RoHS	Yes	
Pb Free	Yes	
HalogenFree	Yes	
Plating Indicator	e1	
EU RoHS Exemption(s)		
MANUFACTURING		
Mfg Item Number	MSC8256ESAG1000B	
Mfg Item Name	FCPBGA 783 29SQ3.55P1.0	
Version	ALL	
Weight	11.142700	
UoM	g	
Unit Volume	EACH	
J-STD-020 MSL Rating	3	
Peak Processing Temperature	245 C	
Max Time at Peak Temperature	30 seconds	
Number of Processing Cycles	3	

RoHS	
RoHS Directive	2011/65/EU
RoHS Definition	RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) of homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material of Cadmium
RoHS Legal Definition	Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part(s) identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a RoHS restricted substance) in excess of the applicable quantity limit identified below. If a homogeneous material within the part(s) contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Suppliers Standard Terms and Conditions of Sale applicable to such part(s) shall apply.
RoHS Declaration	1 - Item(s) do not contain RoHS restricted substances per the definition above
Supplier Acceptance	Accepted
Signature	Daniel Binyon
Exemption List Version	2012/51/EU
List of Freescale Accepted Exemptions	6(a) : Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight 6(b) : Lead as an alloying element in aluminium containing up to 0.4% lead by weight 6(c) : Copper alloy containing up to 4% lead by weight 7(a) : Lead in high melting temperature type solders (i.e. lead-based alloys containing 85% by weight or more lead) 7(b) : Lead in solders for servers, storage and storage array systems, network infrastructure equipment for switching, signaling, transmission, and network management for telecommunications 7(c)-I : Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound 7(c)-II : Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher 7(c)-III : Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC 7(c)-IV : Lead in PZT based dielectric ceramic materials for capacitors being part of integrated circuits or discrete semiconductors 15 : Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit flip chip packages

MATERIAL COMPOSITION

Homogeneous Material	Weight	SubstanceClass	Substance	CAS	Exemption	SubstanceWeight	UoM	SubPart PPM	SubPart%		ARTICLEPPM	ARTICLE%
Bonding Agent	0.0852						g					
Bonding Agent		Solvents, additives, and other materials	Siloxanes and silicones, di-Me, vinyl group-terminated	68083-19-2		0.03834	g	450000	45		3440	0.344
Bonding Agent		Glass	Silica, crystalline - quartz (SiO2)	14808-60-7		0.03408	g	400000	40		3058	0.3058
Bonding Agent		Solvents, additives, and other materials	Dimethyvinylated and trimethylated silica	68988-89-6		0.01278	g	150000	15		1146	0.1146
Die Encapsulant, Filler	0.0281						g					
Die Encapsulant, Filler		Metals	Aluminum, metal	7429-90-5		0.020232	g	720000	72		1815	0.1815
Die Encapsulant, Filler		Solvents, additives, and other materials	Proprietary Material-Other siloxanes and silicones	-		0.002529	g	90000	9		226	0.0226
Die Encapsulant, Filler		Metals	Zinc oxide	1314-13-2		0.005058	g	180000	18		453	0.0453
Die Encapsulant, Filler		Solvents, additives, and other materials	Proprietary Material-Other miscellaneous substances.	-		0.000281	g	10000	1		25	0.0025
Solder Balls - Lead Free	0.7763						g					
Solder Balls - Lead Free		Metals	Copper, metal	7440-50-8		0.00388849	g	5009	0.5009		348	0.0348
Solder Balls - Lead Free		Metals	Silver, metal	7440-22-4		0.02333092	g	30054	3.0054		2093	0.2093
Solder Balls - Lead Free		Metals	Tin, metal	7440-31-5		0.74908059	g	964937	96.4937		67226	6.7226
Underfill	0.0424						g					
Underfill		Bismuth/Bismuth Compounds	Bismuth nitrate	10361-44-1		0.000212	g	5000	0.5		19	0.0019
Underfill		Bismuth/Bismuth Compounds	Bismuth trioxide	1304-76-3		0.000212	g	5000	0.5		19	0.0019
Underfill		Plastics/polymers	1,6-Bis(2,3-epoxypropoxy) naphthalene	27610-48-6		0.00636	g	150000	15		570	0.057
Underfill		Plastics/polymers	Phenolic Polymer Resin, Epkote 155	9003-36-5		0.00424	g	100000	10		380	0.038
Underfill		Solvents, additives, and other materials	Carbon Black	1333-86-4		0.000212	g	5000	0.5		19	0.0019
Underfill		Plastics/polymers	4,4'-Isopropylidenediphenol-1-chloro-2,3-epoxypropane Concentrate	25068-38-6		0.001272	g	30000	3		114	0.0114
Underfill		Glass	Silica, vitreous	60676-86-0		0.02544	g	600000	60		2282	0.2282
Underfill		Solvents, additives, and other materials	Proprietary Material-Other miscellaneous substances.	-		0.000212	g	5000	0.5		19	0.0019
Underfill		Solvents, additives, and other materials	Proprietary Material-Other aliphatic amine compounds	-		0.00424	g	100000	10		380	0.038
Organic Substrate, Halogen-free	2.5						g					
Organic Substrate, Halogen-free		Solvents, additives, and other materials	Proprietary Material-Other acrylonitrile compounds	-		0.22885	g	91420	9.142		20511	2.0511
Organic Substrate, Halogen-free		Arsenic/Arsenic Compounds	Arsenic	7440-39-2		0.000015	g	6	0.0006		1	0.0001
Organic Substrate, Halogen-free		Metals	Barium sulfate	7727-43-7		0.01155	g	4620	0.462		1036	0.1036
Organic Substrate, Halogen-free		Metals	Copper, metal	7440-50-8		1.14129	g	456516	45.6516		102424	10.2424
Organic Substrate, Halogen-free		Lead/Lead Compounds	Lead	7439-92-1		0.0000075	g	3	0.0003		0	0
Organic Substrate, Halogen-free		Glass	Fibrous-glass-wool	65997-17-3		1.02292	g	409168	40.9168		91801	9.1801
Organic Substrate, Halogen-free		Glass	Silicon dioxide	7631-86-9		0.073235	g	29294	2.9294		6572	0.6572
Organic Substrate, Halogen-free		Metals	Silver, metal	7440-22-4		0.0005375	g	215	0.0215		48	0.0048
Organic Substrate, Halogen-free		Metals	Tin, metal	7440-31-5		0.021895	g	8758	0.8758		1964	0.1964
Heat Spreader	7.435						g					
Heat Spreader		Metals	Copper, metal	7440-50-8		6.99043161	g	940206	94.0206		627384	62.7384
Heat Spreader		Nickel (external applications only)	Nickel	7440-02-0		0.44456839	g	59794	5.9794		39897	3.9897
Capacitor_0402	0.0116						g					
Capacitor_0402		Solvents, additives, and other materials	Calcium monoxide	1305-78-8		0.00020866	g	17988	1.7988		18	0.0018
Capacitor_0402		Metals	Cuprous oxide	1317-39-1		0.00054098	g	46636	4.6636		48	0.0048
Capacitor_0402		Nickel (external applications only)	Nickel	7440-02-0		0.00072645	g	62625	6.2625		65	0.0065
Capacitor_0402		Metals	Tin, metal	7440-31-5		0.0001623	g	13991	1.3991		14	0.0014
Capacitor_0402		Metals	Barium titanate	12047-27-7		0.00996161	g	858760	85.876		894	0.0894
Capacitor_0402	0.0116						g					
Capacitor_0402		Solvents, additives, and other materials	Calcium monoxide	1305-78-8		0.00020866	g	17988	1.7988		18	0.0018
Capacitor_0402		Metals	Cuprous oxide	1317-39-1		0.00054098	g	46636	4.6636		48	0.0048
Capacitor_0402		Nickel (external applications only)	Nickel	7440-02-0		0.00072645	g	62625	6.2625		65	0.0065
Capacitor_0402		Metals	Tin, metal	7440-31-5		0.0001623	g	13991	1.3991		14	0.0014
Capacitor_0402		Metals	Barium titanate	12047-27-7		0.00996161	g	858760	85.876		894	0.0894
Capacitor_0402	0.0116						g					
Capacitor_0402		Solvents, additives, and other materials	Calcium monoxide	1305-78-8		0.00020866	g	17988	1.7988		18	0.0018
Capacitor_0402		Metals	Cuprous oxide	1317-39-1		0.00054098	g	46636	4.6636		48	0.0048
Capacitor_0402		Nickel (external applications only)	Nickel	7440-02-0		0.00072645	g	62625	6.2625		65	0.0065
Capacitor_0402		Metals	Tin, metal	7440-31-5		0.0001623	g	13991	1.3991		14	0.0014
Capacitor_0402		Metals	Barium titanate	12047-27-7		0.00996161	g	858760	85.876		894	0.0894
Capacitor_0402	0.0116						g					
Capacitor_0402		Solvents, additives, and other materials	Calcium monoxide	1305-78-8		0.00020866	g	17988	1.7988		18	0.0018
Capacitor_0402		Metals	Cuprous oxide	1317-39-1		0.00054098	g	46636	4.6636		48	0.0048
Capacitor_0402		Nickel (external applications only)	Nickel	7440-02-0		0.00072645	g	62625	6.2625		65	0.0065
Capacitor_0402		Metals	Tin, metal	7440-31-5		0.0001623	g	13991	1.3991		14	0.0014
Capacitor_0402		Metals	Barium titanate	12047-27-7		0.00996161	g	858760	85.876		894	0.0894
Pb-free Bumped Semiconductor D	0.2177						g					
Pb-free Bumped Semiconductor D		Nickel (external applications only)	Nickel	7440-02-0		0.0010885	g	5000	0.5		97	0.0097
Pb-free Bumped Semiconductor D		Metals	Silver, metal	7440-22-4		0.00068576	g	3150	0.315		61	0.0061
Pb-free Bumped Semiconductor D		Metals	Tin, metal	7440-31-5		0.01890725	g	86850	8.685		1696	0.1696
Pb-free Bumped Semiconductor D		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%).	-		0.0019593	g	9000	0.9		175	0.0175
Pb-free Bumped Semiconductor D		Glass	Silicon, doped	-		0.19505919	g	896000	89.6		17506	1.7505

LINKS	
MCD LINK	
Freescal website	http://www.freescal.com
GENERAL ENVIRONMENTAL COMPLIANCE LINKS	
RoHS signed letter	http://www.freescal.com/files/abstract/corporate/ehs_epp/ENV_ROHS_Freescal_Response.pdf
China RoHS	http://www.freescal.com/chinarohs
REACH signed letter	http://www.freescal.com/files/abstract/corporate/ehs_epp/ENV_REACH_Freescal_Response.pdf
ELV signed letter	http://www.freescal.com/files/abstract/corporate/ehs_epp/ENV_ELV_Freescal_Reponse.pdf
Conflict Minerals statement	http://www.freescal.com/files/abstract/corporate/ehs_epp/ENV_CONFLICT_METAL_Freescal_Response.pdf
FREESCALE ENVIRONMENTAL INFORMATION	
EPP website	http://www.freescal.com/epp
FAQ	http://www.freescal.com/webapp/sps/site/overview.jsp?code=ENVIRON_FAQ
Technical Service Request	https://www.freescal.com/webapp/servicerequest.create_SR.framework?defaultCategory=Hardware Product Support&defaultTopic=Environmentally Preferred Prod
LINKS TO BLANK IPC1752 FORMS	
Blank IPC1752 v1.1 Form	http://www.freescal.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf

IPC1752 XML LINKS

http://www.freescale.com/mcds/MS8256ESAG1000B_IPC1752_v11.xml

http://www.freescale.com/mcds/MS8256ESAG1000B_IPC1752A.xml