

**PART INFORMATION**

Mfg Item Number	MPC8306SVMABDCA
Mfg Item Name	MAP 369 19*19*1.61 P0.8

**SUPPLIER**

Company Name	Freescale Semiconductor Inc
Company Unique ID	14-141-7928
Response Date	2017-06-08
Response Document ID	0073K00171D009A1.22
Contact Name	Freescale Semiconductor Inc
Contact Title	Product Technical Support
Contact Phone	1-800-521-6274
Contact Email	support@freescale.com
Authorized Representative	Daniel Binyon
Representative Title	EPP Customer Response
Representative Phone	512-895-3406
Representative Email	eppanlst@freescale.com
URL for Additional Information	www.freescale.com

**DECLARATION**

EU RoHS	Yes
Pb Free	Yes
HalogenFree	Yes
Plating Indicator	e2
EU RoHS Exemption(s)	

**MANUFACTURING**

Mfg Item Number	MPC8306SVMABDCA
Mfg Item Name	MAP 369 19*19*1.61 P0.8
Version	ALL
Weight	1.035200
UoM	g
Unit Volume	EACH
J-STD-020 MSL Rating	3
Peak Processing Temperature	260 C
Max Time at Peak Temperature	40 seconds
Number of Processing Cycles	3

RoHS	
RoHS Directive	2011/65/EU
RoHS Definition	RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) of homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material of Cadmium
RoHS Legal Definition	Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part(s) identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a RoHS restricted substance) in excess of the applicable quantity limit identified below. If a homogeneous material within the part(s) contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Suppliers Standard Terms and Conditions of Sale applicable to such part(s) shall apply.
RoHS Declaration	1 - Item(s) do not contain RoHS restricted substances per the definition above
Supplier Acceptance	Accepted
Signature	Daniel Binyon
Exemption List Version	2012/51/EU
List of Freescale Accepted Exemptions	<p>6(a) : Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight</p> <p>6(b) : Lead as an alloying element in aluminium containing up to 0.4% lead by weight</p> <p>6(c) : Copper alloy containing up to 4% lead by weight</p> <p>7(a) : Lead in high melting temperature type solders (i.e. lead-based alloys containing 85% by weight or more lead)</p> <p>7(b) : Lead in solders for servers, storage and storage array systems, network infrastructure equipment for switching, signaling, transmission, and network management for telecommunications</p> <p>7(c)-I : Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound</p> <p>7(c)-II : Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher</p> <p>7(c)-III : Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC</p> <p>7(c)-IV : Lead in PZT based dielectric ceramic materials for capacitors being part of integrated circuits or discrete semiconductors</p> <p>15 : Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit flip chip packages</p>

MATERIAL COMPOSITION

Homogeneous Material	Weight	SubstanceClass	Substance	CAS	Exemption	SubstanceWeight	UoM	SubPart PPM	SubPart%	ARTICLEPPM	ARTICLE%
Non-Conductive Epoxy/Adhesive	0.0126						g				
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Proprietary Material-Other Epoxy resins	-		0.000945	g	75000	7.5	912	0.0912
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Crosslinked acrylate polymer	25767-43-5		0.00252	g	200000	20	2434	0.2434
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Other polymers	-		0.000945	g	75000	7.5	912	0.0912
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Proprietary Material-Other polymers	-		0.00252	g	200000	20	2434	0.2434
Non-Conductive Epoxy/Adhesive		Glass	Silica, vitreous	60676-86-0		0.00567	g	450000	45	5477	0.5477
Solder Balls - Pb Free, Sn/Ag	0.0529						g				
Solder Balls - Pb Free, Sn/Ag		Metals	Aluminum, metal	7429-90-5		0.00000297	g	32	0.0032	2	0.0002
Solder Balls - Pb Free, Sn/Ag		Antimony/Antimony Compounds	Antimony (metallic)	7440-36-0		0.00001161	g	125	0.0125	11	0.0011
Solder Balls - Pb Free, Sn/Ag		Arsenic/Arsenic Compounds	Arsenic	7440-38-2		0.00000697	g	75	0.0075	6	0.0006
Solder Balls - Pb Free, Sn/Ag		Bismuth/Bismuth Compounds	Bismuth	7440-69-9		0.00001747	g	188	0.0188	16	0.0016
Solder Balls - Pb Free, Sn/Ag		Cadmium/Cadmium Compounds	Cadmium	7440-43-9		0.00000121	g	13	0.0013	1	0.0001
Solder Balls - Pb Free, Sn/Ag		Metals	Copper, metal	7440-50-8		0.00000585	g	63	0.0063	5	0.0005
Solder Balls - Pb Free, Sn/Ag		Metals	Gold, metal	7440-57-5		0.00000585	g	63	0.0063	5	0.0005
Solder Balls - Pb Free, Sn/Ag		Metals	Indium, metal	7440-74-6		0.00000585	g	63	0.0063	5	0.0005
Solder Balls - Pb Free, Sn/Ag		Solvents, additives, and other materials	Sulfur	7704-34-9		0.00000065	g	7	0.0007	0	0
Solder Balls - Pb Free, Sn/Ag		Solvents, additives, and other materials	Phosphorus, elemental (not containing red allotrope)	7723-14-0		0.00000585	g	63	0.0063	5	0.0005
Solder Balls - Pb Free, Sn/Ag		Metals	Iron, metal	7439-89-6		0.00001161	g	125	0.0125	11	0.0011
Solder Balls - Pb Free, Sn/Ag		Lead/Lead Compounds	Lead	7439-92-1		0.00002908	g	313	0.0313	28	0.0028
Solder Balls - Pb Free, Sn/Ag		Nickel (external applications only)	Nickel	7440-02-0		0.00000297	g	32	0.0032	2	0.0002
Solder Balls - Pb Free, Sn/Ag		Metals	Silver, metal	7440-22-4		0.00325169	g	35002	3.5002	3141	0.3141
Solder Balls - Pb Free, Sn/Ag		Metals	Tin, metal	7440-31-5		0.0895386	g	963817	96.3817	86494	8.6494
Solder Balls - Pb Free, Sn/Ag		Metals	Zinc, metal	7440-66-6		0.00000177	g	19	0.0019	1	0.0001
Silicon Semiconductor Die	0.019						g				
Silicon Semiconductor Die		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%)	-		0.00038	g	20000	2	367	0.0367
Silicon Semiconductor Die		Glass	Silicon, doped	-		0.01862	g	980000	98	17986	1.7986
Die Encapsulant, Halogen-free	0.2741						g				
Die Encapsulant, Halogen-free		Plastics/polymers	Other Epoxy resins	-		0.016446	g	60000	6	15886	1.5886
Die Encapsulant, Halogen-free		Solvents, additives, and other materials	Carbon Black	1333-86-4		0.002741	g	10000	1	2647	0.2647
Die Encapsulant, Halogen-free		Solvents, additives, and other materials	Other inorganic compounds	-		0.005482	g	20000	2	5295	0.5295
Die Encapsulant, Halogen-free		Plastics/polymers	Other phenolic resins	-		0.013705	g	50000	5	13238	1.3238
Die Encapsulant, Halogen-free		Glass	Silica, vitreous	60676-86-0		0.235726	g	860000	86	227710	22.771
Bonding Wire, PdCu	0.0102						g				
Bonding Wire, PdCu		Metals	Copper, metal	7440-50-8		0.01007758	g	987998	98.7998	9734	0.9734
Bonding Wire, PdCu		Metals	Palladium, metal	7440-05-3		0.00012242	g	12002	1.2002	118	0.0118
Organic Substrate	0.6264						g				
Organic Substrate		Solvents, additives, and other materials	Acrylonitrile/Butadiene copolymer, carboxyl terminated (2974)	68891-46-3		0.0034997	g	5587	0.5587	3380	0.338
Organic Substrate		Metals	Barium sulfate	7727-43-7		0.0324826	g	51856	5.1856	31378	3.1378
Organic Substrate		Metals	Copper, metal	7440-50-8		0.29654886	g	425525	42.5525	257506	25.7506
Organic Substrate		Plastics/polymers	4,4'-dihydroxy-3,3',5,5'-tetramethylbiphenyl diglycidyl ether	85954-11-6		0.01862162	g	29728	2.9728	17988	1.7988
Organic Substrate		Plastics/polymers	Phenolic Polymer Resin, Epikote 155	9003-36-5		0.14239638	g	227325	22.7325	137554	13.7554
Organic Substrate		Metals	Gold, metal	7440-57-5		0.00123213	g	1967	0.1967	1190	0.119
Organic Substrate		Solvents, additives, and other materials	Silicon	7440-21-3		0.00042031	g	671	0.0671	406	0.0406
Organic Substrate		Nickel (external applications only)	Nickel	7440-02-0		0.01249981	g	19955	1.9955	12074	1.2074
Organic Substrate		Glass	Fibrous-glass-wool	65997-17-3		0.10753597	g	171673	17.1673	103879	10.3879
Organic Substrate		Plastics/polymers	Other acrylic resins	-		0.0246977	g	39428	3.9428	23857	2.3857
Organic Substrate		Plastics/polymers	Other acrylic/epoxy resin mixture	-		0.01646492	g	26285	2.6285	15905	1.5905

## LINKS

MCD LINK	
NXP website	<a href="http://www.nxp.com">http://www.nxp.com</a>
GENERAL ENVIRONMENTAL COMPLIANCE LINKS	
RoHS signed letter	<a href="http://www.nxp.com/files/corporate/doc/support_info/NXP-ROHS-DECLARATION.pdf">http://www.nxp.com/files/corporate/doc/support_info/NXP-ROHS-DECLARATION.pdf</a>
China RoHS	<a href="http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/china-rohs:ENV_CHINA_ROHS_STRATEGY">http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/china-rohs:ENV_CHINA_ROHS_STRATEGY</a>
REACH signed letter	<a href="http://www.nxp.com/files/corporate/doc/support_info/NXP-REACH-STATEMENT.pdf">http://www.nxp.com/files/corporate/doc/support_info/NXP-REACH-STATEMENT.pdf</a>
ELV signed letter	<a href="http://www.nxp.com/files/corporate/doc/support_info/NXP-ELV-STATEMENT.pdf">http://www.nxp.com/files/corporate/doc/support_info/NXP-ELV-STATEMENT.pdf</a>
Conflict Minerals statement	<a href="http://www.nxp.com/files/corporate/doc/support_info/NXP-STATEMENT-CONFLICT-MINERALS.pdf">http://www.nxp.com/files/corporate/doc/support_info/NXP-STATEMENT-CONFLICT-MINERALS.pdf</a>
NXP ENVIRONMENTAL INFORMATION	
Environmental Compliance website	<a href="http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization:ABUENVPRFPRDX">http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization:ABUENVPRFPRDX</a>
FAQ	<a href="http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/eco-product-faqs:ENVIRON_FAQ">http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/eco-product-faqs:ENVIRON_FAQ</a>
Technical Service Request	<a href="http://www.nxp.com/support/sales-and-support:SUPPORTHOME">http://www.nxp.com/support/sales-and-support:SUPPORTHOME</a>
LINKS TO BLANK IPC1752 FORMS	
Blank IPC1752 v1.1 Form	<a href="http://www.NXP.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf">http://www.NXP.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf</a>

IPC1752 XML LINKS

[http://www.freescale.com/mcdfs/MPC8306SVMABDCA\\_IPC1752\\_v11.xml](http://www.freescale.com/mcdfs/MPC8306SVMABDCA_IPC1752_v11.xml)

[http://www.freescale.com/mcdfs/MPC8306SVMABDCA\\_IPC1752A.xml](http://www.freescale.com/mcdfs/MPC8306SVMABDCA_IPC1752A.xml)