

<b>PART INFORMATION</b>	
Mfg Item Number	MPC8360ECVVAGDGA
Mfg Item Name	TBGA740 37.5*37.5*1.69P1
<b>SUPPLIER</b>	
Company Name	Freescale Semiconductor Inc
Company Unique ID	14-141-7928
Response Date	2017-04-10
Response Document ID	5101K11210D005A1.33
Contact Name	Freescale Semiconductor Inc
Contact Title	Product Technical Support
Contact Phone	1-800-521-6274
Contact Email	support@freescale.com
Authorized Representative	Daniel Binyon
Representative Title	EPP Customer Response
Representative Phone	512-895-3406
Representative Email	eppanlst@freescale.com
URL for Additional Information	www.freescale.com
<b>DECLARATION</b>	
EU RoHS	Yes
Pb Free	Yes
HalogenFree	Yes
Plating Indicator	e2
EU RoHS Exemption(s)	
<b>MANUFACTURING</b>	
Mfg Item Number	MPC8360ECVVAGDGA
Mfg Item Name	TBGA740 37.5*37.5*1.69P1
Version	ALL
Weight	10.796300
UoM	g
Unit Volume	EACH
J-STD-020 MSL Rating	3
Peak Processing Temperature	260 C
Max Time at Peak Temperature	40 seconds
Number of Processing Cycles	3

RoHS	
RoHS Directive	2011/65/EU
RoHS Definition	RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) of homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material of Cadmium
RoHS Legal Definition	<p>Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part(s) identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a RoHS restricted substance) in excess of the applicable quantity limit identified below. If a homogeneous material within the part(s) contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Suppliers Standard Terms and Conditions of Sale applicable to such part(s) shall apply.</p>
RoHS Declaration	1 - Item(s) do not contain RoHS restricted substances per the definition above
Supplier Acceptance	Accepted
Signature	Daniel Binyon
Exemption List Version	2012/51/EU
<p>List of Freescale Accepted Exemptions</p> <p>6(a) : Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight</p> <p>6(b) : Lead as an alloying element in aluminium containing up to 0.4% lead by weight</p> <p>6(c) : Copper alloy containing up to 4% lead by weight</p> <p>7(a) : Lead in high melting temperature type solders (i.e. lead-based alloys containing 85% by weight or more lead)</p> <p>7(b) : Lead in solders for servers, storage and storage array systems, network infrastructure equipment for switching, signaling, transmission, and network management for telecommunications</p> <p>7(c)-I : Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectric devices, or in a glass or ceramic matrix compound</p> <p>7(c)-II : Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher</p> <p>7(c)-III : Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC</p> <p>7(c)-IV : Lead in PZT based dielectric ceramic materials for capacitors being part of integrated circuits or discrete semiconductors</p> <p>15 : Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit flip chip packages</p>	

## MATERIAL COMPOSITION

Homogeneous Material	Weight	SubstanceClass	Substance	CAS	Exemption	SubstanceWeight	UoM	SubPart PPM	SubPart%	ARTICLEPPM	ARTICLE%
Epoxy Die Attach	0.0417	Solvents, additives, and other materials	1,3,5-Triazine-2,4-diamine, 6-(2-(2-methyl-1H-imidazol-1-yl)ethyl)	38668-46-1		g	8451	0.8451		32	0.0032
Epoxy Die Attach		Plastics/polymers	Phenolic Polymer Resin, Epikote 155	9003-36-5		g	129579	12.9579		500	0.05
Epoxy Die Attach		Plastics/polymers	4,4'-Dihydroxydiphenyl	92-88-6		g	8451	0.8451		32	0.0032
Epoxy Die Attach		Metals	Silver, metal	7440-22-4		g	853519	85.3519		3296	0.3296
Bonding Wire	0.025	Metals	Gold, metal	7440-57-5		g	1000000	100		2315	0.2315
Bonding Wire		Metals	Gold, metal	7440-57-5	0.025	g	1000000	100			
Solder Balls - Pb Free, Sn/Ag	0.8196	Metals	Aluminum, metal	7429-90-5		g	32	0.0032		2	0.0002
Solder Balls - Pb Free, Sn/Ag		Metals	Antimony (metallic)	7440-36-0		g	125	0.0125		9	0.0009
Solder Balls - Pb Free, Sn/Ag		Metals	Arsenic/Arsenic Compounds	7440-38-2		g	75	0.0075		5	0.0005
Solder Balls - Pb Free, Sn/Ag		Metals	Bismuth/Bismuth Compounds	7440-69-9		g	188	0.0188		14	0.0014
Solder Balls - Pb Free, Sn/Ag		Metals	Cadmium/Cadmium Compounds	7440-43-9		g	13	0.0013		0	0
Solder Balls - Pb Free, Sn/Ag		Metals	Copper, metal	7440-50-8		g	63	0.0063		4	0.0004
Solder Balls - Pb Free, Sn/Ag		Metals	Gold, metal	7440-57-5		g	63	0.0063		4	0.0004
Solder Balls - Pb Free, Sn/Ag		Metals	Indium, metal	7440-74-6		g	63	0.0063		4	0.0004
Solder Balls - Pb Free, Sn/Ag		Solvents, additives, and other materials	Sulfur	7704-34-9		g	7	0.0007		0	0
Solder Balls - Pb Free, Sn/Ag		Solvents, additives, and other materials	Phosphorus, elemental (not containing red allotrope)	7723-14-0		g	63	0.0063		4	0.0004
Solder Balls - Pb Free, Sn/Ag		Metals	Iron, metal	7439-89-6		g	110	0.011		8	0.0008
Solder Balls - Pb Free, Sn/Ag		Metals	Lead/lead Compounds	7439-92-1		g	313	0.0313		23	0.0023
Solder Balls - Pb Free, Sn/Ag		Nickel (external applications only)	Nickel	7440-02-0		g	32	0.0032		2	0.0002
Solder Balls - Pb Free, Sn/Ag		Metals	Silver, metal	7440-22-4		g	35002	3.5002		2657	0.2657
Solder Balls - Pb Free, Sn/Ag		Metals	Tin, metal	7440-31-5		g	963832	95.3532		73169	7.3169
Solder Balls - Pb Free, Sn/Ag		Metals	Zinc, metal	7440-66-6		g	19	0.0019		1	0.0001
Die Encapsulant, Halogen-free	0.4517	Plastics/polymers	Other Epoxy resins	-		g	80000	6		2510	0.251
Die Encapsulant, Halogen-free		Solvents, additives, and other materials	Carbon Black	1333-86-4		g	10000	1		418	0.0418
Die Encapsulant, Halogen-free		Solvents, additives, and other materials	Other inorganic compounds	-		g	20000	2		836	0.0836
Die Encapsulant, Halogen-free		Plastics/polymers	Other phenolic resins	-		g	50000	5		2091	0.2091
Die Encapsulant, Halogen-free		Glass	Silica, vitreous	60676-86-0		g	860000	86		35981	3.5981
Organic Substrate	9.4083	Metals	Aluminum, metal	7429-90-5		g	48	0.0048		41	0.0041
Organic Substrate		Metals	Barium sulfate	7727-43-7		g	333	0.0333		290	0.029
Organic Substrate		Metals	Copper, metal	7440-50-8		g	970424	97.0424		845685	84.5685
Organic Substrate		Metals	Cupric oxide	1317-38-0		g	6040	0.604		5263	0.5263
Organic Substrate		Metals	Gold, metal	7440-57-5		g	298	0.0298		259	0.0259
Organic Substrate		Metals	Manganese, metal	7439-96-5		g	48	0.0048		41	0.0041
Organic Substrate		Nickel (external applications only)	Nickel	7440-02-0		g	1572	0.1572		1369	0.1369
Organic Substrate		Solvents, additives, and other materials	Other organic compounds	-		g	3852	0.3852		3356	0.3356
Organic Substrate		Solvents, additives, and other materials	Other organic Silicon Compounds	-		g	22	0.0022		19	0.0019
Organic Substrate		Metals	Zirconium, metal	7440-67-7		g	962	0.0962		838	0.0838
Organic Substrate		Plastics/polymers	Other Non-halogenated Epoxy resins	-		g	3280	0.328		2858	0.2858
Silicon Semiconductor Die	0.05	Plastics/polymers	Other non-halogenated polymers	-		g	13121	1.3121		11434	1.1434
Silicon Semiconductor Die		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%)	-		g	20000	2		92	0.0092
Silicon Semiconductor Die		Glass	Silicon, doped	-		g	980000	98		4538	0.4538

**LINKS**

MCD LINK	
NXP website	<a href="http://www.nxp.com">http://www.nxp.com</a>
<b>GENERAL ENVIRONMENTAL COMPLIANCE LINKS</b>	
RoHS signed letter	<a href="http://www.nxp.com/files/corporate/doc/support_info/NXP-ROHS-DECLARATION.pdf">http://www.nxp.com/files/corporate/doc/support_info/NXP-ROHS-DECLARATION.pdf</a>
China RoHS	<a href="http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/china-rohs:ENV_CHINA_ROHS_STRATEGY">http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/china-rohs:ENV_CHINA_ROHS_STRATEGY</a>
REACH signed letter	<a href="http://www.nxp.com/files/corporate/doc/support_info/NXP-REACH-STATEMENT.pdf">http://www.nxp.com/files/corporate/doc/support_info/NXP-REACH-STATEMENT.pdf</a>
ELV signed letter	<a href="http://www.nxp.com/files/corporate/doc/support_info/NXP-ELV-STATEMENT.pdf">http://www.nxp.com/files/corporate/doc/support_info/NXP-ELV-STATEMENT.pdf</a>
Conflict Minerals statement	<a href="http://www.nxp.com/files/corporate/doc/support_info/NXP-STATEMENT-CONFLICT-MINERALS.pdf">http://www.nxp.com/files/corporate/doc/support_info/NXP-STATEMENT-CONFLICT-MINERALS.pdf</a>
<b>NXP ENVIRONMENTAL INFORMATION</b>	
Environmental Compliance website	<a href="http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization:ABUENVPRFPRDX">http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization:ABUENVPRFPRDX</a>
FAQ	<a href="http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/eco-product-faqs:ENVIRON_FAQ">http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/eco-product-faqs:ENVIRON_FAQ</a>
Technical Service Request	<a href="http://www.nxp.com/support/sales-and-support:SUPPORTHOME">http://www.nxp.com/support/sales-and-support:SUPPORTHOME</a>
LINKS TO BLANK IPC1752 FORMS	
Blank IPC1752 v1.1 Form	<a href="http://www.NXP.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf">http://www.NXP.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf</a>

IPC1752 XML LINKS

[http://www.freescale.com/mcds/MPC8360ECVVAGDGA\\_IPC1752\\_v11.xml](http://www.freescale.com/mcds/MPC8360ECVVAGDGA_IPC1752_v11.xml)

[http://www.freescale.com/mcds/MPC8360ECVVAGDGA\\_IPC1752A.xml](http://www.freescale.com/mcds/MPC8360ECVVAGDGA_IPC1752A.xml)