

PART INFORMATION		
Mfg Item Number		P1017NSE5CFB
Mfg Item Name		TEPBGA 457 19SQ 1.9 0.8
SUPPLIER		
Company Name		Freescale Semiconductor Inc
Company Unique ID		14-141-7928
Response Date		2017-10-10
Response Document ID		007MA1.18
Contact Name		Freescale Semiconductor Inc
Contact Title		Product Technical Support
Contact Phone		1-800-521-6274
Contact Email		support@freescale.com
Authorized Representative		Daniel Binyon
Representative Title		EPP Customer Response
Representative Phone		512-895-3406
Representative Email		eppanlst@freescale.com
URL for Additional Information		www.freescale.com
DECLARATION		
EU RoHS		Yes
Pb Free		Yes
HalogenFree		Yes
Plating Indicator		e2
EU RoHS Exemption(s)		
MANUFACTURING		
Mfg Item Number		P1017NSE5CFB
Mfg Item Name		TEPBGA 457 19SQ 1.9 0.8
Version		ALL
Weight		0.997500
UoM		g
Unit Volume		EACH
J-STD-020 MSL Rating		3
Peak Processing Temperature		260 C
Max Time at Peak Temperature		40 seconds
Number of Processing Cycles		3

RoHS	
RoHS Directive	2011/65/EU
RoHS Definition	RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) of homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material of Cadmium
RoHS Legal Definition	Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part(s) identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a RoHS restricted substance) in excess of the applicable quantity limit identified below. If a homogeneous material within the part(s) contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Suppliers Standard Terms and Conditions of Sale applicable to such part(s) shall apply.
RoHS Declaration	1 - Item(s) do not contain RoHS restricted substances per the definition above
Supplier Acceptance	Accepted
Signature	Daniel Binyon
Exemption List Version	2012/51/EU
List of Freescale Accepted Exemptions	6(a) : Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight 6(b) : Lead as an alloying element in aluminium containing up to 0.4% lead by weight 6(c) : Copper alloy containing up to 4% lead by weight 7(a) : Lead in high melting temperature type solders (i.e. lead-based alloys containing 85% by weight or more lead) 7(b) : Lead in solders for servers, storage and storage array systems, network infrastructure equipment for switching, signaling, transmission, and network management for telecommunications 7(c)-I : Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound 7(c)-II : Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher 7(c)-III : Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC 7(c)-IV : Lead in PZT based dielectric ceramic materials for capacitors being part of integrated circuits or discrete semiconductors 15 : Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit flip chip packages

MATERIAL COMPOSITION

Homogeneous Material	Weight	SubstanceClass	Substance	CAS	Exemption	SubstanceWeight	UoM	SubPart PPM	SubPart%	ARTICLEPPM	ARTICLE%
Epoxy Die Attach	0.0023						g				
Epoxy Die Attach		Solvents, additives, and other materials	1,3,5-Triazine-2,4-diamine, 6-[2-(2-methyl-1H-imidazol-1-yl)ethyl]	38668-46-1		0.00001944	g	8451	0.8451	19	0.0019
Epoxy Die Attach		Plastics/polymers	Phenolic Polymer Resin, Epikote 155	9003-36-5		0.00029803	g	129579	12.9579	298	0.0298
Epoxy Die Attach		Plastics/polymers	4,4'-Dihydroxydiphenyl	92-88-6		0.00001944	g	8451	0.8451	19	0.0019
Epoxy Die Attach		Metals	Silver, metal	7440-22-4		0.00196309	g	853519	85.3519	1968	0.1968
Solder Balls - Pb Free, Sn/Ag	0.1176						g				
Solder Balls - Pb Free, Sn/Ag		Metals	Aluminum, metal	7429-90-5		0.00000376	g	32	0.0032	3	0.0003
Solder Balls - Pb Free, Sn/Ag		Antimony/Antimony Compounds	Antimony (metallic)	7440-36-0		0.0000147	g	125	0.0125	14	0.0014
Solder Balls - Pb Free, Sn/Ag		Arsenic/Arsenic Compounds	Arsenic	7440-39-2		0.00000682	g	75	0.0075	8	0.0008
Solder Balls - Pb Free, Sn/Ag		Bismuth/Bismuth Compounds	Bismuth	7440-69-9		0.00002211	g	188	0.0188	22	0.0022
Solder Balls - Pb Free, Sn/Ag		Cadmium/Cadmium Compounds	Cadmium	7440-43-9		0.00000153	g	13	0.0013	1	0.0001
Solder Balls - Pb Free, Sn/Ag		Metals	Copper, metal	7440-50-8		0.00000741	g	63	0.0063	7	0.0007
Solder Balls - Pb Free, Sn/Ag		Metals	Gold, metal	7440-57-5		0.00000741	g	63	0.0063	7	0.0007
Solder Balls - Pb Free, Sn/Ag		Metals	Indium, metal	7440-74-6		0.00000741	g	63	0.0063	7	0.0007
Solder Balls - Pb Free, Sn/Ag		Sulfur	Sulfur	7704-34-9		0.00000082	g	7	0.0007	0	0
Solder Balls - Pb Free, Sn/Ag		Solvents, additives, and other materials	Phosphorus, elemental (not containing red allotrope)	7723-14-0		0.00000741	g	63	0.0063	7	0.0007
Solder Balls - Pb Free, Sn/Ag		Metals	Iron, metal	7439-89-6		0.0000147	g	125	0.0125	14	0.0014
Solder Balls - Pb Free, Sn/Ag		Lead/Lead Compounds	Lead	7439-92-1		0.00003691	g	313	0.0313	36	0.0036
Solder Balls - Pb Free, Sn/Ag		Nickel (external applications only)	Nickel	7440-02-0		0.00000376	g	32	0.0032	3	0.0003
Solder Balls - Pb Free, Sn/Ag		Metals	Silver, metal	7440-22-4		0.00411624	g	35002	3.5002	4126	0.4126
Solder Balls - Pb Free, Sn/Ag		Metals	Tin, metal	7440-31-5		0.11334488	g	963817	96.3817	113628	11.3628
Solder Balls - Pb Free, Sn/Ag		Metals	Zinc, metal	7440-66-6		0.00000223	g	19	0.0019	2	0.0002
Bonding Wire	0.0064						g				
Bonding Wire		Metals	Gold, metal	7440-57-5		0.0064	g	1000000	100	6416	0.6416
Organic Substrate, Halogen-free	0.3605						g				
Organic Substrate, Halogen-free		Solvents, additives, and other materials	Other acrylates	-		0.00447813	g	12422	1.2422	4489	0.4489
Organic Substrate, Halogen-free		Metals	Aluminum Oxides (Al2O3)	1344-28-1		0.01891832	g	52478	5.2478	18965	1.8965
Organic Substrate, Halogen-free		Metals	Barium	7440-39-3		0.00402534	g	11166	1.1166	4035	0.4035
Organic Substrate, Halogen-free		Metals	Copper, metal	7440-50-8		0.24088033	g	668184	66.8184	241484	24.1484
Organic Substrate, Halogen-free		Plastics/polymers	2,2'-(1-methylethylene)bis[4,1-phenyleneoxymethylene]bisoxirane	1675-54-3		0.00081617	g	2264	0.2264	818	0.0818
Organic Substrate, Halogen-free		Metals	Gold, metal	7440-57-5		0.00057392	g	1592	0.1592	575	0.0575
Organic Substrate, Halogen-free		Nickel (external applications only)	Nickel	7440-02-0		0.00475932	g	13202	1.3202	4771	0.4771
Organic Substrate, Halogen-free		Solvents, additives, and other materials	Other organic Silicon Compounds	-		0.00012221	g	339	0.0339	122	0.0122
Organic Substrate, Halogen-free		Glass	Fibrous-glass-wool	65997-17-3		0.0407657	g	113081	11.3081	40867	4.0867
Organic Substrate, Halogen-free		Glass	Silicon dioxide	7631-86-9		0.02327208	g	64555	6.4555	23330	2.333
Organic Substrate, Halogen-free		Solvents, additives, and other materials	Proprietary Material-Other miscellaneous substances.	-		0.00443127	g	12292	1.2292	4442	0.4442
Organic Substrate, Halogen-free		Plastics/polymers	Other Non-halogenated Epoxy resins	-		0.01745721	g	48425	4.8425	17500	1.75
Die Encapsulant	0.4857						g				
Die Encapsulant		Plastics/polymers	Other Epoxy resins	-		0.029142	g	60000	6	29215	2.9215
Die Encapsulant		Solvents, additives, and other materials	Carbon Black	1333-86-4		0.004857	g	10000	1	4869	0.4869
Die Encapsulant		Solvents, additives, and other materials	Other inorganic compounds.	-		0.009714	g	20000	2	9738	0.9738
Die Encapsulant		Plastics/polymers	Other phenolic resins	-		0.024285	g	50000	5	24345	2.4345
Die Encapsulant		Glass	Silica, vitreous	60676-86-0		0.417702	g	860000	86	418768	41.8768
Silicon Semiconductor Die	0.025						g				
Silicon Semiconductor Die		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%).	-		0.0005	g	20000	2	501	0.0501
Silicon Semiconductor Die		Glass	Silicon, doped	-		0.0245	g	980000	98	24561	2.4561

LINKS	
MCD LINK	
NXP website	http://www.nxp.com
GENERAL ENVIRONMENTAL COMPLIANCE LINKS	
RoHS signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-ROHS-DECLARATION.pdf
China RoHS	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/china-rohs:ENV_CHINA_ROHS_STRATEGY
REACH signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-REACH-STATEMENT.pdf
ELV signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-ELV-STATEMENT.pdf
Conflict Minerals statement	http://www.nxp.com/files/corporate/doc/support_info/NXP-STATEMENT-CONFLICT-MINERALS.pdf
NXP ENVIRONMENTAL INFORMATION	
Environmental Compliance website	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization:ABUENVPRFPRDX
FAQ	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/eco-product-faqs:ENVIRON_FAQ
Technical Service Request	http://www.nxp.com/support/sales-and-support:SUPPORTHOME
LINKS TO BLANK IPC1752 FORMS	
Blank IPC1752 v1.1 Form	http://www.NXP.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf

IPC1752 XML LINKS

http://www.freescale.com/mcds/P1017NSE5CFB_IPC1752_v11.xml

http://www.freescale.com/mcds/P1017NSE5CFB_IPC1752A.xml