

**PART INFORMATION**

Mfg Item Number	SAC7136J1VVF50R
Mfg Item Name	MAPBGA 208 17*17*0.8P1.0

**SUPPLIER**

Company Name	Freescale Semiconductor Inc
Company Unique ID	14-141-7928
Response Date	2017-06-08
Response Document ID	5253K00090D194A1.23
Contact Name	Freescale Semiconductor Inc
Contact Title	Product Technical Support
Contact Phone	1-800-521-6274
Contact Email	support@freescale.com
Authorized Representative	Daniel Binyon
Representative Title	EPP Customer Response
Representative Phone	512-895-3406
Representative Email	eppanlst@freescale.com
URL for Additional Information	www.freescale.com

**DECLARATION**

EU RoHS	No
Pb Free	No
HalogenFree	Yes
Plating Indicator	e0
EU RoHS Exemption(s)	

**MANUFACTURING**

Mfg Item Number	SAC7136J1VVF50R
Mfg Item Name	MAPBGA 208 17*17*0.8P1.0
Version	ALL
Weight	0.861400
UoM	g
Unit Volume	EACH
J-STD-020 MSL Rating	3
Peak Processing Temperature	240 C
Max Time at Peak Temperature	30 seconds
Number of Processing Cycles	3

RoHS	
RoHS Directive	2011/65/EU
RoHS Definition	RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) of homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material of Cadmium
RoHS Legal Definition	Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part(s) identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a RoHS restricted substance) in excess of the applicable quantity limit identified below. If a homogeneous material within the part(s) contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Suppliers Standard Terms and Conditions of Sale applicable to such part(s) shall apply.
RoHS Declaration	3 - Item(s) does not contain RoHS restricted substances per the definition above except for lead in solders and selected exemptions, if any
Supplier Acceptance	Accepted
Signature	Daniel Binyon
Exemption List Version	2012/51/EU
List of Freescale Accepted Exemptions	<p>6(a) : Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight</p> <p>6(b) : Lead as an alloying element in aluminium containing up to 0.4% lead by weight</p> <p>6(c) : Copper alloy containing up to 4% lead by weight</p> <p>7(a) : Lead in high melting temperature type solders (i.e. lead-based alloys containing 85% by weight or more lead)</p> <p>7(b) : Lead in solders for servers, storage and storage array systems, network infrastructure equipment for switching, signaling, transmission, and network management for telecommunications</p> <p>7(c)-I : Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound</p> <p>7(c)-II : Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher</p> <p>7(c)-III : Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC</p> <p>7(c)-IV : Lead in PZT based dielectric ceramic materials for capacitors being part of integrated circuits or discrete semiconductors</p> <p>15 : Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit flip chip packages</p>

MATERIAL COMPOSITION

Homogeneous Material	Weight	SubstanceClass	Substance	CAS	Exemption	SubstanceWeight	UoM	SubPart PPM	SubPart%	ARTICLEPPM	ARTICLE%
Non-Conductive Epoxy/Adhesive	0.0027						g				
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Proprietary Material-Other Epoxy resins	-		0.0002025	g	75000	7.5	235	0.0235
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Crosslinked acrylate polymer	25767-43-5		0.00054	g	200000	20	626	0.0626
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Other polymers	-		0.0002025	g	75000	7.5	235	0.0235
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Proprietary Material-Other polymers	-		0.00054	g	200000	20	626	0.0626
Non-Conductive Epoxy/Adhesive		Glass	Silica, vitreous	60676-86-0		0.001215	g	450000	45	1410	0.141
Solder Balls - Low Lead	0.2028						g				
Solder Balls - Low Lead		Lead/Lead Compounds	Lead	7439-92-1		0.073008	g	360000	36	84755	8.4755
Solder Balls - Low Lead		Metals	Silver, metal	7440-22-4		0.004056	g	20000	2	4708	0.4708
Solder Balls - Low Lead		Metals	Tin, metal	7440-31-5		0.125736	g	620000	62	145967	14.5967
Bonding Wire	0.0062						g				
Bonding Wire		Metals	Gold, metal	7440-57-5		0.0062	g	1000000	100	7197	0.7197
Silicon Semiconductor Die	0.04						g				
Silicon Semiconductor Die		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%)	-		0.0008	g	20000	2	928	0.0928
Silicon Semiconductor Die		Glass	Silicon, doped	-		0.0392	g	980000	98	45507	4.5507
Die Encapsulant, Halogen-free	0.4784						g				
Die Encapsulant, Halogen-free		Metals	Other aluminum compounds	-		0.014352	g	30000	3	16661	1.6661
Die Encapsulant, Halogen-free		Solvents, additives, and other materials	Carbon Black	1333-86-4		0.004784	g	10000	1	5553	0.5553
Die Encapsulant, Halogen-free		Plastics/polymers	Phenol, polymer with formaldehyde	9003-35-4		0.014352	g	30000	3	16661	1.6661
Die Encapsulant, Halogen-free		Plastics/polymers	Other phenolic resins	-		0.014352	g	30000	3	16661	1.6661
Die Encapsulant, Halogen-free		Glass	Silica, vitreous	60676-86-0		0.0664	g	850000	85	472081	47.2081
Die Encapsulant, Halogen-free		Plastics/polymers	Other Non-halogenated Epoxy resins	-		0.02392	g	50000	5	27768	2.7768
Organic Substrate	0.1313						g				
Organic Substrate		Solvents, additives, and other materials	Acrylonitrile/Butadiene copolymer, carboxyl terminated (2974)	68891-46-3		0.00115872	g	8825	0.8825	1345	0.1345
Organic Substrate		Metals	Barium sulfate	7727-43-7		0.01075334	g	81899	8.1899	12483	1.2483
Organic Substrate		Metals	Copper, metal	7440-50-8		0.01690829	g	128776	12.8776	19628	1.9628
Organic Substrate		Plastics/polymers	4,4'-dihydroxy-3,3',5,5'-tetramethylbiphenyl diglycidyl ether	85954-11-6		0.00889032	g	67710	6.771	10320	1.032
Organic Substrate		Plastics/polymers	Phenolic Polymer Resin, Epikote 155	9003-36-5		0.03983642	g	303400	30.34	46246	4.6246
Organic Substrate		Metals	Gold, metal	7440-57-5		0.00043697	g	3328	0.3328	507	0.0507
Organic Substrate		Solvents, additives, and other materials	Silicon	7440-21-3		0.00013905	g	1059	0.1059	161	0.0161
Organic Substrate		Nickel (external applications only)	Nickel	7440-02-0		0.00443558	g	33782	3.3782	5149	0.5149
Organic Substrate		Glass	Fibrous-glass-wool	65997-17-3		0.03783895	g	288187	28.8187	43927	4.3927
Organic Substrate		Plastics/polymers	Other acrylic resins	-		0.00654123	g	49819	4.9819	7593	0.7593
Organic Substrate		Plastics/polymers	Other acrylic/epoxy resin mixture	-		0.00436113	g	33215	3.3215	5062	0.5062

## LINKS

MCD LINK	
NXP website	<a href="http://www.nxp.com">http://www.nxp.com</a>
GENERAL ENVIRONMENTAL COMPLIANCE LINKS	
RoHS signed letter	<a href="http://www.nxp.com/files/corporate/doc/support_info/NXP-ROHS-DECLARATION.pdf">http://www.nxp.com/files/corporate/doc/support_info/NXP-ROHS-DECLARATION.pdf</a>
China RoHS	<a href="http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/china-rohs:ENV_CHINA_ROHS_STRATEGY">http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/china-rohs:ENV_CHINA_ROHS_STRATEGY</a>
REACH signed letter	<a href="http://www.nxp.com/files/corporate/doc/support_info/NXP-REACH-STATEMENT.pdf">http://www.nxp.com/files/corporate/doc/support_info/NXP-REACH-STATEMENT.pdf</a>
ELV signed letter	<a href="http://www.nxp.com/files/corporate/doc/support_info/NXP-ELV-STATEMENT.pdf">http://www.nxp.com/files/corporate/doc/support_info/NXP-ELV-STATEMENT.pdf</a>
Conflict Minerals statement	<a href="http://www.nxp.com/files/corporate/doc/support_info/NXP-STATEMENT-CONFLICT-MINERALS.pdf">http://www.nxp.com/files/corporate/doc/support_info/NXP-STATEMENT-CONFLICT-MINERALS.pdf</a>
NXP ENVIRONMENTAL INFORMATION	
Environmental Compliance website	<a href="http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization:ABUENVPRFPRDX">http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization:ABUENVPRFPRDX</a>
FAQ	<a href="http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/eco-product-faqs:ENVIRON_FAQ">http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/eco-product-faqs:ENVIRON_FAQ</a>
Technical Service Request	<a href="http://www.nxp.com/support/sales-and-support:SUPPORTHOME">http://www.nxp.com/support/sales-and-support:SUPPORTHOME</a>
LINKS TO BLANK IPC1752 FORMS	
Blank IPC1752 v1.1 Form	<a href="http://www.NXP.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf">http://www.NXP.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf</a>

IPC1752 XML LINKS

[http://www.freescale.com/mcdfs/SAC7136J1VVF50R\\_IPC1752\\_v11.xml](http://www.freescale.com/mcdfs/SAC7136J1VVF50R_IPC1752_v11.xml)

[http://www.freescale.com/mcdfs/SAC7136J1VVF50R\\_IPC1752A.xml](http://www.freescale.com/mcdfs/SAC7136J1VVF50R_IPC1752A.xml)