

PART INFORMATION	
Mfg Item Number	SPC5746CSK1MMH6
Mfg Item Name	MAPBGA 100 11*11*0.9P1.0
SUPPLIER	
Company Name	Freescale Semiconductor Inc
Company Unique ID	14-141-7928
Response Date	2018-01-02
Response Document ID	00LMK00149D010A1.7
Contact Name	Freescale Semiconductor Inc
Contact Title	Product Technical Support
Contact Phone	1-800-521-6274
Contact Email	support@freescale.com
Authorized Representative	Daniel Binyon
Representative Title	EPP Customer Response
Representative Phone	512-895-3406
Representative Email	eppanlst@freescale.com
URL for Additional Information	www.freescale.com
DECLARATION	
EU RoHS	Yes
Pb Free	Yes
HalogenFree	Yes
Plating Indicator	e2
EU RoHS Exemption(s)	
MANUFACTURING	
Mfg Item Number	SPC5746CSK1MMH6
Mfg Item Name	MAPBGA 100 11*11*0.9P1.0
Version	ALL
Weight	0.280200
UoM	g
Unit Volume	EACH
J-STD-020 MSL Rating	3
Peak Processing Temperature	260 C
Max Time at Peak Temperature	40 seconds
Number of Processing Cycles	3

RoHS	
RoHS Directive	2011/65/EU
RoHS Definition	RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) of homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material of Cadmium
RoHS Legal Definition	<p>Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part(s) identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a RoHS restricted substance) in excess of the applicable quantity limit identified below. If a homogeneous material within the part(s) contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Suppliers Standard Terms and Conditions of Sale applicable to such part(s) shall apply.</p>
RoHS Declaration	1 - Item(s) do not contain RoHS restricted substances per the definition above
Supplier Acceptance	Accepted
Signature	Daniel Binyon
Exemption List Version	2012/51/EU
<p>List of Freescale Accepted Exemptions</p> <p>6(a) : Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight</p> <p>6(b) : Lead as an alloying element in aluminium containing up to 0.4% lead by weight</p> <p>6(c) : Copper alloy containing up to 4% lead by weight</p> <p>7(a) : Lead in high melting temperature type solders (i.e. lead-based alloys containing 85% by weight or more lead)</p> <p>7(b) : Lead in solders for servers, storage and storage array systems, network infrastructure equipment for switching, signaling, transmission, and network management for telecommunications</p> <p>7(c)-I : Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectric devices, or in a glass or ceramic matrix compound</p> <p>7(c)-II : Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher</p> <p>7(c)-III : Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC</p> <p>7(c)-IV : Lead in PZT based dielectric ceramic materials for capacitors being part of integrated circuits or discrete semiconductors</p> <p>15 : Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit flip chip packages</p>	

MATERIAL COMPOSITION

Homogeneous Material	Weight	SubstanceClass	Substance	CAS	Exemption	SubstanceWeight	UoM	SubPart PPM	SubPart%	ARTICLEPPM	ARTICLE%
Non-Conductive Epoxy/Adhesive	0.0018	Plastics/polymers	Proprietary Material-Other Epoxy resins	-	0.000135	g	75000	7.5		481	0.0481
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Crosslinked acrylate polymer	25767-43-5	0.00036	g	200000	20		1284	0.1284
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Other polymers	-	0.000135	g	75000	7.5		481	0.0481
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Proprietary Material-Other polymers	-	0.00036	g	200000	20		1284	0.1284
Non-Conductive Epoxy/Adhesive		Glass	Silica, vitreous	60676-86-0	0.00081	g	450000	45		2890	0.289
Solder Balls - Pb Free, Sn/Ag	0.0536					g					
Solder Balls - Pb Free, Sn/Ag		Metals	Aluminum, metal	7429-90-5	0.00000172	g	32	0.0032		6	0.0006
Solder Balls - Pb Free, Sn/Ag		Antimony/Antimony Compounds	Antimony (metallic)	7440-36-0	0.000067	g	125	0.0125		23	0.0023
Solder Balls - Pb Free, Sn/Ag		Arsenic/Arsenic Compounds	Arsenic	7440-39-2	0.00000402	g	75	0.0075		14	0.0014
Solder Balls - Pb Free, Sn/Ag		Bismuth/Bismuth Compounds	Bismuth	7440-69-9	0.00001008	g	188	0.0168		35	0.0035
Solder Balls - Pb Free, Sn/Ag		Cadmium/Cadmium Compounds	Cadmium	7440-43-9	0.0000007	g	13	0.0013		2	0.0002
Solder Balls - Pb Free, Sn/Ag		Metals	Copper, metal	7440-50-8	0.00000338	g	63	0.0063		12	0.0012
Solder Balls - Pb Free, Sn/Ag		Metals	Gold, metal	7440-57-5	0.00000338	g	63	0.0063		12	0.0012
Solder Balls - Pb Free, Sn/Ag		Metals	Iridium, metal	7440-74-6	0.00000338	g	63	0.0063		12	0.0012
Solder Balls - Pb Free, Sn/Ag		Solvents, additives, and other materials	Sulfur	7704-34-9	0.00000038	g	7	0.0007		1	0.0001
Solder Balls - Pb Free, Sn/Ag		Solvents, additives, and other materials	Phosphorus, elemental (not containing red allotrope)	7723-14-0	0.00000338	g	63	0.0063		12	0.0012
Solder Balls - Pb Free, Sn/Ag		Metals	Iron, metal	7439-89-6	0.0000067	g	125	0.0125		23	0.0023
Solder Balls - Pb Free, Sn/Ag		Lead/Lead Compounds	Lead	7439-92-1	0.00001678	g	313	0.0313		59	0.059
Solder Balls - Pb Free, Sn/Ag		Nickel (external applications only)	Nickel	7440-02-0	0.00000172	g	32	0.0032		6	0.0006
Solder Balls - Pb Free, Sn/Ag		Metals	Silver, metal	7440-22-4	0.00187611	g	35002	3.5002		6695	0.6695
Solder Balls - Pb Free, Sn/Ag		Metals	Tin, metal	7440-31-5	0.0516055	g	963817	96.3817		184370	18.437
Solder Balls - Pb Free, Sn/Ag		Metals	Zinc, metal	7440-66-6	0.00000102	g	19	0.0019		3	0.0003
Die Encapsulant, Halogen-free	0.1372					g					
Die Encapsulant, Halogen-free		Plastics/polymers	Other Epoxy resins	-	0.008232	g	60000	6		29379	2.9379
Die Encapsulant, Halogen-free		Solvents, additives, and other materials	Carbon Black	1333-86-4	0.001372	g	10000	1		4896	0.4896
Die Encapsulant, Halogen-free		Solvents, additives, and other materials	Other inorganic compounds.	-	0.002744	g	20000	2		9793	0.9793
Die Encapsulant, Halogen-free		Plastics/polymers	Other phenolic resins	-	0.00686	g	50000	6		24482	2.4482
Die Encapsulant, Halogen-free		Glass	Silica, vitreous	60676-86-0	0.117992	g	860000	86		42123	42.1123
Organic Substrate	0.0593					g					
Organic Substrate		Solvents, additives, and other materials	Other aromatic amines and their salts	-	0.00001755	g	296	0.0296		62	0.0062
Organic Substrate		Metals	Barium sulfate	7727-43-7	0.00059229	g	9988	0.9988		2113	0.2113
Organic Substrate		Metals	Copper, metal	7440-50-8	0.02768734	g	466903	46.6903		98812	9.8812
Organic Substrate		Plastics/polymers	Other Epoxy resins	-	0.00251995	g	42495	4.2495		8993	0.8993
Organic Substrate		Metals	Gold, metal	7440-57-5	0.00140209	g	23644	2.3644		5003	0.5003
Organic Substrate		Metals	Talc	14807-96-6	0.00009834	g	5031	0.5031		1064	0.1064
Organic Substrate		Nickel (external applications only)	Nickel	7440-02-0	0.0109418	g	184516	18.4516		39049	3.9049
Organic Substrate		Glass	Fibrous-glass-wool	65997-17-3	0.01119933	g	188869	18.8869		39971	3.9971
Organic Substrate		Glass	Silicon dioxide	7631-86-9	0.00197831	g	33361	3.3361		7050	0.706
Organic Substrate		Solvents, additives, and other materials	Other Aromatic carbonyl compounds	-	0.00011095	g	1871	0.1871		395	0.0395
Organic Substrate		Metals	Copper (phthalocyanine	147-14-8	0.00000528	g	89	0.0089		18	0.0018
Organic Substrate		Solvents, additives, and other materials	Quinacridone pigment	1047-16-1	0.00000528	g	89	0.0089		18	0.0018
Organic Substrate		Solvents, additives, and other materials	3-methoxy-3-methyl-1-butyl acetate	103429-90-9	0.00004928	g	10949	1.0949		2317	0.2317
Organic Substrate		Plastics/polymers	Epoxy Resin	115254-47-2	0.0018633	g	31810	3.181		6732	0.6732
Organic Substrate		Solvents, additives, and other materials	1,2,4-Trimethylbenzene	95-63-6	0.00000528	g	89	0.0089		18	0.0018
Bonding Wire, PtCu	0.006					g					
Bonding Wire, PtCu		Metals	Copper, metal	7440-50-8	0.005886	g	981000	98.1		21006	2.1006
Bonding Wire, PtCu		Metals	Gold, metal	7440-57-5	0.000006	g	1000	0.1		21	0.0021
Bonding Wire, PtCu		Metals	Palladium, metal	7440-05-3	0.000108	g	18000	1.8		385	0.0385
Silicon Semiconductor Die	0.0223					g					
Silicon Semiconductor Die		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%)	-	0.000446	g	20000	2		1591	0.1591
Silicon Semiconductor Die		Glass	Silicon, doped	-	0.021854	g	980000	98		77994	7.7994

LINKS

MCD LINK	
NXP website	http://www.nxp.com
GENERAL ENVIRONMENTAL COMPLIANCE LINKS	
RoHS signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-ROHS-DECLARATION.pdf
China RoHS	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/china-rohs:ENV_CHINA_ROHS_STRATEGY
REACH signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-REACH-STATEMENT.pdf
ELV signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-ELV-STATEMENT.pdf
Conflict Minerals statement	http://www.nxp.com/files/corporate/doc/support_info/NXP-STATEMENT-CONFLICT-MINERALS.pdf
NXP ENVIRONMENTAL INFORMATION	
Environmental Compliance website	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization:ABUENVPRFPRDX
FAQ	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/eco-product-faqs:ENVIRON_FAQ
Technical Service Request	http://www.nxp.com/support/sales-and-support:SUPPORTHOME
LINKS TO BLANK IPC1752 FORMS	
Blank IPC1752 v1.1 Form	http://www.NXP.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf

IPC1752 XML LINKS

http://www.freescale.com/mcds/SPC5746CSK1MMH6_IPC1752_v11.xml

http://www.freescale.com/mcds/SPC5746CSK1MMH6_IPC1752A.xml