

Test Report Page: 1 of 9 No.: CE/2020/62794 Date: 2020/06/20

HENKEL CORPORATION 14000 JAMBOREE ROAD, IRVINE, CALIFORNIA, 92606 U.S.A.

The following sample(s) was/were submitted and identified by/on behalf of the applicant as:

Sample Submitted By : HENKEL CORPORATION

Sample Description : ADHESIVE Style/Item No. : 2033SC Sample Receiving Date: 2020/06/16

Testing Period 2020/06/16 TO 2020/06/20

Test Requested

(1) As specified by client, with reference to RoHS 2011/65/EU Annex II and amending Directive (EU) 2015/863 to determine Cadmium, Lead, Mercury, Cr(VI), PBBs, PBDEs, DBP, BBP, DEHP, DIBP contents in the submitted

(2) Please refer to next pages for the other item(s).

: Please refer to following pages. Test Result(s)

(1) Based on the performed tests on submitted sample(s), the test results of Cadmium, Lead, Conclusion

Mercury, Cr(VI), PBBs, PBDEs, DBP, BBP, DEHP, DIBP comply with the limits as set by

RoHS and amending Directive (EU) 2015/863.

Troy Chang / Manager -Signed for and behalf of SGS TAIWAN LTD. Chemical Laboratory - Taipei



PIN CODE: AB7F0FD4

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at https://twap.sgs.com/Terms-and-Conditions.html and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at https://twap.sgs.com/Terms-and-Conditions.html. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction form exercising all their rights and obligations under the transaction documents. This document cannot be reproduced, except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.



Test Report No.: CE/2020/62794 Page: 2 of 9 Date: 2020/06/20

HENKEL CORPORATION 14000 JAMBOREE ROAD, IRVINE, CALIFORNIA, 92606 U.S.A.

Test Result(s)

PART NAME No.1 : RED PASTE

Test Item(s)	Unit	Method	MDL	Result No.1	Limit
Cadmium (Cd)	mg/kg	With reference to IEC 62321-5 (2013) and performed by ICP-OES.	2	n.d.	100
Lead (Pb)	mg/kg	With reference to IEC 62321-5 (2013) and performed by ICP-OES.	2	n.d.	1000
Mercury (Hg)	mg/kg	With reference to IEC 62321-4:2013+ AMD1:2017 and performed by ICP-OES.	2	n.d.	1000
Hexavalent Chromium Cr(VI)	mg/kg	With reference to IEC 62321-7-2 (2017) and performed by UV-VIS.	8	n.d.	1000
Sum of PBBs	mg/kg		-	n.d.	1000
Monobromobiphenyl	mg/kg		5	n.d.	-
Dibromobiphenyl	mg/kg		5	n.d.	-
Tribromobiphenyl	mg/kg		5	n.d.	-
Tetrabromobiphenyl	mg/kg	With reference to IEC 62321-6 (2015) and performed by GC/MS.	5	n.d.	-
Pentabromobiphenyl	mg/kg		5	n.d.	-
Hexabromobiphenyl	mg/kg		5	n.d.	-
Heptabromobiphenyl	mg/kg		5	n.d.	-
Octabromobiphenyl	mg/kg		5	n.d.	-
Nonabromobiphenyl	mg/kg		5	n.d.	-
Decabromobiphenyl	mg/kg		5	n.d.	-
Sum of PBDEs	mg/kg		-	n.d.	1000
Monobromodiphenyl ether	mg/kg		5	n.d.	-
Dibromodiphenyl ether	mg/kg		5	n.d.	-
Tribromodiphenyl ether	mg/kg		5	n.d.	-
Tetrabromodiphenyl ether	mg/kg		5	n.d.	-
Pentabromodiphenyl ether	mg/kg		5	n.d.	
Hexabromodiphenyl ether	mg/kg		5	n.d.	-
Heptabromodiphenyl ether	mg/kg		5	n.d.	-
Octabromodiphenyl ether	mg/kg		5	n.d.	-
Nonabromodiphenyl ether	mg/kg		5	n.d.	-
Decabromodiphenyl ether	mg/kg		5	n.d.	-

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at https://twap.sgs.com/Terms-and-Conditions.html and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at https://twap.sgs.com/Terms-and-Conditions.html. Attention is drawn to the limits of initiality, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced, except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.



Test Report No.: CE/2020/62794 Page: 3 of 9 Date: 2020/06/20

HENKEL CORPORATION 14000 JAMBOREE ROAD, IRVINE, CALIFORNIA, 92606 U.S.A.

Test Item(s)	Unit	Method	MDL	Result	Limit
				No.1	
DBP (Dibutyl phthalate) (CAS No.: 84-74-2)	mg/kg	With reference to IEC 62321-8 (2017). Analysis was performed by GC/MS.	50	n.d.	1000
BBP (Butyl Benzyl phthalate) (CAS No.: 85-68-7)	mg/kg	With reference to IEC 62321-8 (2017). Analysis was performed by GC/MS.	50	n.d.	1000
DEHP (Di- (2-ethylhexyl) phthalate) (CAS No.: 117-81-7)	mg/kg	With reference to IEC 62321-8 (2017). Analysis was performed by GC/MS.	50	n.d.	1000
DIDP (Di-isodecyl phthalate) (CAS No.: 26761-40-0; 68515-49-1)	mg/kg	With reference to IEC 62321-8 (2017). Analysis was performed by GC/MS.	50	n.d.	-
DINP (Di-isononyl phthalate) (CAS No.: 28553-12-0; 68515-48-0)	mg/kg	With reference to IEC 62321-8 (2017). Analysis was performed by GC/MS.	50	n.d.	-
DNOP (Di-n-octyl phthalate) (CAS No.: 117-84-0)	mg/kg	With reference to IEC 62321-8 (2017). Analysis was performed by GC/MS.	50	n.d.	-
DIBP (Di-isobutyl phthalate) (CAS No.: 84-69-5)	mg/kg	With reference to IEC 62321-8 (2017). Analysis was performed by GC/MS.	50	n.d.	1000
Hexabromocyclododecane (HBCDD) and all major diastereoisomers identified (α- HBCDD, β- HBCDD, γ- HBCDD) (CAS No.: 25637-99-4 and 3194-55-6 (134237-51-7, 134237-50-6, 134237-52-8))	mg/kg	With reference to IEC 62321 (2008). Analysis was performed by GC/MS.	5	n.d.	-
Beryllium (Be)	mg/kg	With reference to US EPA 3050B (1996). Analysis was performed by ICP-OES.	2	n.d.	-

Note:

- 1. mg/kg = ppm; 0.1wt% = 1000ppm2. MDL = Method Detection Limit
- 3. n.d. = Not Detected
- 4. " " = Not Regulated
- 5. The statement of compliance conformity is based on comparison of testing results and limits.




Test Report No.: CE/2020/62794 Page: 4 of 9 Date: 2020/06/20

HENKEL CORPORATION 14000 JAMBOREE ROAD, IRVINE, CALIFORNIA, 92606 U.S.A.

Analytical flow chart of Heavy Metal

These samples were dissolved totally by pre-conditioning method according to below flow chart. (Cr⁶⁺ test method excluded)






Test Report No.: CE/2020/62794 Page: 5 of 9 Date: 2020/06/20

HENKEL CORPORATION 14000 JAMBOREE ROAD, IRVINE, CALIFORNIA, 92606 U.S.A.

Flow Chart of digestion for the elements analysis performed by ICP-OES

These samples were dissolved totally by pre-conditioning method according to below flow chart.




Steel, copper, aluminum, solder	Aqua regia, HNO ₃ , HCI, HF, H ₂ O ₂		
Glass	HNO ₃ /HF		
Gold, platinum, palladium, ceramic	Aqua regia		
Silver	HNO ₃		
Plastic	H ₂ SO ₄ , H ₂ O ₂ , HNO ₃ , HCI		
Others	Added appropriate reagent to total digestion		



Test Report Page: 6 of 9 No.: CE/2020/62794 Date: 2020/06/20

HENKEL CORPORATION 14000 JAMBOREE ROAD, IRVINE, CALIFORNIA, 92606 U.S.A.

Analytical flow chart - PBB/PBDE



This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at https://twap.sgs.com/Terms-and-Conditions.html and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at https://twap.sgs.com/Terms-and-Conditions.html. Attention is drawn to the limits of initiality, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced, except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.




Test Report Page: 7 of 9 No.: CE/2020/62794 Date: 2020/06/20

HENKEL CORPORATION 14000 JAMBOREE ROAD, IRVINE, CALIFORNIA, 92606 U.S.A.

Analytical flow chart - Phthalate

[Test method: IEC 62321-8]





Test Report Page: 8 of 9 No.: CE/2020/62794 Date: 2020/06/20

HENKEL CORPORATION 14000 JAMBOREE ROAD, IRVINE, CALIFORNIA, 92606 U.S.A.

Analytical flow chart - HBCDD Sample pretreatment Sample extraction by organic solvent Concentrate/Dilute the extracted solution Analysis was performed by GC/MS Data



Test Report No.: CE/2020/62794 Page: 9 of 9 Date: 2020/06/20

HENKEL CORPORATION 14000 JAMBOREE ROAD, IRVINE, CALIFORNIA, 92606 U.S.A.

* The tested sample / part is marked by an arrow if it's shown on the photo. *

CE/2020/62794



** End of Report **