



Report No. A2230163012101001

Company Name shown on Report	MITSUI HIGH-TEC INC.		
Address	10-1, KOMINE2-CHOME, YAHATANISHIKU KITAKYUSHU, 807-8588, JAPAN		
The following sampl applicant	e(s) and sample information was/were submitted and identified by/on the behalf of the		
Sample Name Sample Received Date	Au plating e Apr. 13, 2023		
Testing Period	Apr. 13, 2023 to Apr. 19, 2023		
Test Requested	As specified by client, to test Lead (Pb), Cadmium (Cd), Mercury (Hg), Hexavalent Chromium (Cr(VI)), Polybrominated Biphenyls (PBBs), Polybrominated Diphenyl Ethers (PBDEs), Phthalates (DBP, BBP, DEHP, DIBP), Fluorine (F), Chlorine (Cl), Bromine (Br) Iodine (I), Phthalates, Organotin compounds, Antimony(Sb), Hexabromocyclododecane (HBCDD), Perfluorooctane Sulfonates(PFOS), Perfluorooctanoic Acid(PFOA), Polychlorinated Biphenyls(PCBs), Polychlorinated Naphthalenes (PCNs), Polychlorinated terphenyls (PCTs), Polyvinyl Chloride (PVC), Short Chain Chlorinated Paraffins (SCCPs)		

Test Method	Please refer to the following page(s).
Test Result(s)	Please refer to the following page(s).

in the submitted sample(s).



Date

Apr. 19, 2023

No. R392331204

5F-6, No.9, Sec.2, Nankan Rd, Luzhu Dist., Taoyuan, Taiwan

Hotline:400-6788-333 www.cti-cert.com E-mail:info@cti-cert.com Complaint call:0755-33681700 Complaint E-mail:complaint@cti-cert.com



Report No. A2230163012101001

Test Method

Page 2 of 11

Test Item(s)	Test Method	Measured Equipment(s)
Lead (Pb)	Refer to IEC 62321-5:2013	ICP-OES
Cadmium (Cd)	Refer to IEC 62321-5:2013	ICP-OES
Mercury (Hg)	Refer to IEC 62321-4:2013+AMD1:2017 CSV	ICP-OES
Hexavalent Chromium (Cr(VI))	IEC 62321-7-1:2015	UV-Vis
Polybrominated Biphenyls (PBBs)	IEC 62321-6:2015	GC-MS
Polybrominated Diphenyl Ethers (PBDEs)	IEC 62321-6:2015	GC-MS
Phthalates (DBP, BBP, DEHP, DIBP)	IEC 62321-8:2017	GC-MS
Fluorine (F)	Refer to EN 14582:2016	IC
Chlorine (Cl)	Refer to EN 14582:2016	IC
Bromine (Br)	Refer to EN 14582:2016	IC
Iodine (I)	Refer to EN 14582:2016	IC
Phthalates	IEC 62321-8:2017	GC-MS
Organotin compounds	Refer to US EPA 3550C:2007 & ISO 17353:2004	GC-MS
Short Chain Chlorinated Paraffins (SCCPs)	Refer to US EPA 3550C:2007 & US EPA 8270E:2018	GC-MS(NCI)
Polychlorinated Naphthalenes (PCNs)	Refer to US EPA 3550C:2007 & US EPA 8270E:2018	GC-MS
Polychlorinated Biphenyls(PCBs)	Refer to US EPA 3550C:2007 & US EPA 8270E:2018	GC-MS
Polychlorinated terphenyls (PCTs)	Refer to US EPA 3550C:2007 & US EPA 8270E:2018	GC-MS
Polyvinyl Chloride (PVC)	Refer to JY/T 001-1996	FT-IR
Hexabromocyclododecane (HBCDD)	IEC 62321-9:2021	GC-MS
Perfluorooctanoic Acid(PFOA)	Refer to DIN CEN/TS 15968:2010	LC-MS-MS
Perfluorooctane Sulfonates(PFOS)	Refer to DIN CEN/TS 15968:2010	LC-MS-MS
Antimony(Sb)	Refer to US EPA 3050B:1996 & US EPA 6010D:2018	ICP-OES



Report No. A2230163012101001

Test Result(s)

Tested Herr(s)	Result	MDI	
Tested Item(s)	001	MDL	
Lead (Pb)	N.D.	2 mg/kg	
Cadmium (Cd)	N.D.	2 mg/kg	
Mercury (Hg)	N.D.	2 mg/kg	
Hexavalent Chromium (Cr(VI))	N.D. *	0.10 μg/cm ² (LOQ)	
Tested Item(s)	Result 001	MDL	
	001		
Polybrominated Biphenyls (PBBs)			
Monobromobiphenyl	N.D.	5 mg/kg	
Dibromobiphenyl	N.D.	5 mg/kg	
Tribromobiphenyl	N.D.	5 mg/kg	
Tetrabromobiphenyl	N.D.	5 mg/kg	
Pentabromobiphenyl	N.D.	5 mg/kg	
Hexabromobiphenyl	N.D.	5 mg/kg	
Heptabromobiphenyl	N.D.	5 mg/kg	
Octabromobiphenyl	N.D.	5 mg/kg	
Nonabromobiphenyl	N.D.	5 mg/kg	
Decabromobiphenyl	N.D.	5 mg/kg	
Tested Item(s)	Result	MDI	
Tested Item(s)	001	MDL	
Polybrominated Diphenyl Ethers (PBDEs)			
Monobromodiphenyl ether	N.D.	5 mg/kg	
Dibromodiphenyl ether	N.D.	5 mg/kg	
Tribromodiphenyl ether	N.D.	5 mg/kg	
Tetrabromodiphenyl ether	N.D.	5 mg/kg	
Pentabromodiphenyl ether	N.D.	5 mg/kg	
Hexabromodiphenyl ether	N.D.	5 mg/kg	
Heptabromodiphenyl ether	N.D.	5 mg/kg	
Octabromodiphenyl ether	N.D.	5 mg/kg	
Nonabromodiphenyl ether	N.D.	5 mg/kg	
Decabromodiphenyl ether	N.D.	5 mg/kg	



Report No. A2230163012101001

Test Result(s)

	Result	
Tested Item(s)	001	MDL
Phthalates (DBP, BBP, DEHP, DIBP)		
Butyl benzyl phthalate (BBP) CAS#:85-68-7	N.D.	50 mg/kg
Di-(2-ethylhexyl) phthalate (DEHP) CAS#:117-81-7	N.D.	50 mg/kg
Dibutyl phthalate (DBP) CAS#:84-74-2	N.D.	50 mg/kg
Diisobutyl phthalate (DIBP) CAS#:84-69-5	N.D.	50 mg/kg
	Result	
Tested Item(s)	001	MDL
Fluorine (F)	N.D.	50 mg/kg
Chlorine (Cl)	N.D.	50 mg/kg
Bromine (Br)	N.D.	50 mg/kg
Iodine (I)	N.D.	50 mg/kg
Tested Item(s)	Result	MDL
Testeu item(s)	001	WIDL
Phthalates		
Bis(2-methoxyethyl) phthalate (DMEP) CAS#:117-82-8	N.D.	50 mg/kg
Di-n-hexyl phthalate (DNHP/DHEXP) CAS#:84-75-3	N.D.	50 mg/kg
Di-iso-decyl phthalate (DIDP) CAS#:26761-40-0,68515-49-1	N.D.	50 mg/kg
Di-isononyl phthalate (DINP) CAS#:28553-12-0,68515-48-0	N.D.	50 mg/kg
Di-n-octyl phthalate (DNOP) CAS#:117-84-0	N.D.	50 mg/kg
1,2-Benzenedicarboxylic acid, di-C6-8-branched alkyl esters, C7-rich (DIHP) CAS#:71888-89-6	N.D.	50 mg/kg
1,2-Benzenedicarboxylic acid, di-(C7-11)-branched and linear alkyl esters (DHNUP) CAS#:68515-42-4	N.D.	50 mg/kg

Page 4 of 11



Report No. A2230163012101001

Test Result(s)

Tooted Item(e)	Result	
Tested Item(s)	001	MDL
Organotin compounds		·
Dibutyltin (DBT)	N.D.	5 mg/kg
Dioctyltin (DOT)	N.D.	5 mg/kg
Tributyltin (TBT)	N.D.	5 mg/kg
Triphenyltin (TPHT)	N.D.	5 mg/kg
Tributyltin oxide (TBTO)*	N.D.	5 mg/kg
	Result	
Tested Item(s)	001	MDL
Antimony (Sb)	N.D.	10 mg/kg
	Result	
Tested Item(s)	001	MDL
Polychlorinated Biphenyls(PCBs)		ł
Monochlorobiphenyl	N.D.	5 mg/kg
Dichlorobiphenyl	N.D.	5 mg/kg
Trichlorobiphenyl	N.D.	5 mg/kg
Tetrachlorobiphenyl	N.D.	5 mg/kg
Pentachlorobiphenyl	N.D.	5 mg/kg
Hexachlorobiphenyl	N.D.	5 mg/kg
Heptachlorobiphenyl	N.D.	5 mg/kg
Octachlorobiphenyl	N.D.	5 mg/kg
Nonachlorobiphenyl	N.D.	5 mg/kg
Decachlorobiphenyl	N.D.	5 mg/kg
Tested Item(s)	Result	MDI
Tested Item(s)	001	MDL
Short Chain Chlorinated Paraffins (SCCPs)	N.D.	50 mg/kg
Tested Item(s)	Result	MDL
	001	
Polyvinyl Chloride (PVC)	Negative	/
Tested Item(s)	Result 001	MDL
Perfluorooctanoic Acid (PFOA)	N.D.	0.01 mg/kg
	Result	
Tested Item(s)	001	MDL
Perfluorooctane Sulfonates (PFOS)	N.D.	0.01 mg/kg



Report No. A2230163012101001

Test Result(s)

	Result	
Tested Item(s)	001	MDL
Polychlorinated Triphenyls (PCTs)	N.D.	5 mg/kg
Tested Here(s)	Result	MDI
Tested Item(s)	001	MDL
Hexabromocyclododecane (HBCDD)	N.D.	20 mg/kg
Tested Item(s)	Result	MDI
Tested Item(s)	001	MDL
Polychlorinated Naphthalenes (PCNs)	N.D.	5 mg/kg

Sample/Part Description


No.	CTI Sample ID	Description
1	001	Golden plating

Remark:The sample(s) had been dissolved totally tested for Lead, Cadmium, Mercury, Antimony.-MDL = Method Detection Limit-N.D. = Not Detected (<MDL or LOQ)</td>-mg/kg = ppm = parts per million-LOQ = Limit of Quantification, The LOQ of Hexavalent chromium is 0.10 µg/cm²-▼The sample is negative for Cr(VI) – The Cr(VI) concentration is below 0.10 µg/cm².The coating is considered a non-Cr(VI) based coating.-Negative = Not contained Polyvinyl Chloride(PVC)-*=Concentration value of Tributyltin oxide by the conversion from the test results of Tributyl Tins.


Note: The testing data and result(s) in this report is(are) just for scientific research, education, internal quality control and product development etc.

Page 6 of 11












Report No. A2230163012101001

Page 9 of 11

9. Polychlorinated Biphenyls(PCBs), Polychlorinated Naphthalenes (PCNs), Polychlorinated terphenyls (PCTs)










Report No. A2230163012101001

Photo(s) of the sample(s)



Statement:

- 1. This report is considered invalid without approved signature, special seal and the seal on the perforation;
- 2. The Company Name shown on Report and Address, the sample(s) and sample information was/were provided by the applicant who should be responsible for the authenticity which CTI hasn't verified;
- 3. The result(s) shown in this report refer(s) only to the sample(s) tested;
- 4. Without written approval of CTI, this report can't be reproduced except in full;
- 5. In case of any discrepancy between the English version and Chinese version of the testing reports (if generated), the Chinese version shall prevail.

*** End of report ***

~ Eu

Page 11 of 11