

Test Report



Report No. A2210152964101001

Company Name MITSUI HIGH-TEC INC
shown on Report

Address 2-01,KOMINE,YAHATANISHI-KU KITAKYUSHU 807-8588,JAPAN

The following sample(s) and sample information was/were submitted and identified by/on the behalf of the applicant

Sample Name Au plating
Sample Received Date Apr. 25, 2021
Testing Period Apr. 25, 2021 to May 10, 2021

Test Requested As specified by client, to test Lead (Pb), Cadmium (Cd), Mercury (Hg), Hexavalent Chromium (Cr(VI)), Polybrominated Biphenyls (PBBs), Polybrominated Diphenyl Ethers (PBDEs), Beryllium(Be), Antimony(Sb), Hexabromocyclododecane (HBCDD), Fluorine (F), Chlorine (Cl), Bromine (Br), Iodine (I), Polychlorinated Naphthalenes (PCNs), Polychlorinated terphenyls (PCTs), Polychlorinated Biphenyls(PCBs), Phthalates, Short Chain Chlorinated Paraffins (SCCPs), Organotin compounds, Polyvinyl Chloride (PVC), Perfluorooctane Sulfonates(PFOS), Perfluorooctanoic Acid(PFOA) in the submitted sample(s).

Test Method Please refer to the following page(s).

Test Result(s) Please refer to the following page(s).

Conclusion

Tested Sample	According to standard/directive	Result
Submitted Sample	RoHS Directive 2011/65/EU with amendment (EU) 2015/863	PASS

PASS means that the results shown on the report comply with the limits set by RoHS Directive 2011/65/EU with amendment (EU) 2015/863.



Tested by Li zheng su

Approved by Chen kaimin

Chen kaimin
Lab Manager

Reviewed by Wendy Gong

Date May 10, 2021

No. R201805803

No.1351, Wanfang Road, Minhang District, Shanghai, China

Test Report

Report No. A2210152964101001

Page 2 of 11

Test Method

Test Item(s)	Test Method	Measured Equipment(s)
Lead (Pb)	Refer to IEC 62321-5:2013	ICP-OES
Cadmium (Cd)	Refer to IEC 62321-5:2013	ICP-OES
Mercury (Hg)	Refer to IEC 62321-4:2013+AMD1:2017 CSV	ICP-OES
Hexavalent Chromium (Cr(VI))	IEC 62321-7-1:2015	UV-Vis
Polybrominated Biphenyls (PBBs)	IEC 62321-6:2015	GC-MS
Polybrominated Diphenyl Ethers (PBDEs)	IEC 62321-6:2015	GC-MS
Phthalates (DBP, BBP, DEHP, DIBP)	IEC 62321-8:2017	GC-MS
Beryllium(Be)	Refer to US EPA 3050B:1996 & US EPA 6010D:2018*	ICP-OES
Antimony(Sb)	Refer to US EPA 3050B:1996 & US EPA 6010D:2018*	ICP-OES
Hexabromocyclododecane (HBCDD)	Refer to US EPA 3550C:2007 & US EPA 8270E:2018*	GC-MS
Fluorine (F)	Refer to EN 14582:2016*	IC
Chlorine (Cl)	Refer to EN 14582:2016*	IC
Bromine (Br)	Refer to EN 14582:2016*	IC
Iodine (I)	Refer to EN 14582:2016*	IC
Polychlorinated Naphthalenes (PCNs)	Refer to US EPA 3550C:2007 & US EPA 8270E:2018*	GC-MS
Polychlorinated terphenyls (PCTs)	Refer to US EPA 3550C:2007 & US EPA 8270D:2014*	GC-MS
Polychlorinated Biphenyls(PCBs)	Refer to US EPA 3540C:1996 & US EPA 8270E:2017*	GC-MS
Perfluorooctane Sulfonates(PFOS)	Refer to CEN/TS 15968:2010*	LC-MS-MS/LC-MS
Short Chain Chlorinated Paraffins (SCCPs)	Refer to US EPA 3550C:2007 & US EPA 8270E:2018*	GC-MS(NCI)
Organotin compounds	Refer to ISO 17353:2004(E)*	GC-MS
Polyvinyl Chloride (PVC)	Refer to JY/T 001-1996*	FT-IR
Perfluorooctanoic Acid(PFOA)	Refer to CEN/TS 15968:2010*	LC-MS-MS/LC-MS
Phthalates(DMEP, DNHP, DIDP, DINP, DNOP, DIHP, DHNUP)	Refer to EN 14372:2004(E)*	GC-MS

Test Report

Report No. A2210152964101001

Page 3 of 11

Test Result(s)

Tested Item(s)	Result	MDL	Limit
Lead(Pb)	N.D.	2 mg/kg	1000 mg/kg
Cadmium(Cd)	N.D.	2 mg/kg	100 mg/kg
Mercury(Hg)	N.D.	2 mg/kg	1000 mg/kg
Hexavalent Chromium(Cr(VI))	N.D. ▼	0.10 µg/cm ² (LOQ)	1000 mg/kg
Tested Item(s)	Result	MDL	Limit
Polybrominated Biphenyls (PBBs)			
Monobromobiphenyl	N.D.	5 mg/kg	1000 mg/kg
Dibromobiphenyl	N.D.	5 mg/kg	
Tribromobiphenyl	N.D.	5 mg/kg	
Tetrabromobiphenyl	N.D.	5 mg/kg	
Pentabromobiphenyl	N.D.	5 mg/kg	
Hexabromobiphenyl	N.D.	5 mg/kg	
Heptabromobiphenyl	N.D.	5 mg/kg	
Octabromobiphenyl	N.D.	5 mg/kg	
Nonabromobiphenyl	N.D.	5 mg/kg	
Decabromobiphenyl	N.D.	5 mg/kg	
Tested Item(s)	Result	MDL	Limit
Polybrominated Diphenyl Ethers (PBDEs)			
Monobromodiphenyl ether	N.D.	5 mg/kg	1000 mg/kg
Dibromodiphenyl ether	N.D.	5 mg/kg	
Tribromodiphenyl ether	N.D.	5 mg/kg	
Tetrabromodiphenyl ether	N.D.	5 mg/kg	
Pentabromodiphenyl ether	N.D.	5 mg/kg	
Hexabromodiphenyl ether	N.D.	5 mg/kg	
Heptabromodiphenyl ether	N.D.	5 mg/kg	
Octabromodiphenyl ether	N.D.	5 mg/kg	
Nonabromodiphenyl ether	N.D.	5 mg/kg	
Decabromodiphenyl ether	N.D.	5 mg/kg	

Test Report

Report No. A2210152964101001

Page 4 of 11

Test Result(s)

Tested Item(s)	Result	MDL	Limit
Phthalates (DBP, BBP, DEHP, DIBP)			
Dibutyl phthalate(DBP) CAS#:84-74-2	N.D.	50 mg/kg	1000 mg/kg
Butyl benzyl phthalate(BBP) CAS#:85-68-7	N.D.	50 mg/kg	1000 mg/kg
Di-(2-ethylhexyl) phthalate(DEHP) CAS#:117-81-7	N.D.	50 mg/kg	1000 mg/kg
Diisobutyl phthalate(DIBP) CAS#:84-69-5	N.D.	50 mg/kg	1000 mg/kg
Tested Item(s)	Result	MDL	
Beryllium(Be)	N.D.	10 mg/kg	
Antimony(Sb)	N.D.	10 mg/kg	
Tested Item(s)	Result	MDL	
Hexabromocyclododecane(HBCDD)	N.D.	5 mg/kg	
Tested Item(s)	Result	MDL	
Fluorine(F)	N.D.	1 µg/cm ²	
Chlorine(Cl)	N.D.	1 µg/cm ²	
Bromine(Br)	N.D.	1 µg/cm ²	
Iodine(I)	N.D.	1 µg/cm ²	
Tested Item(s)	Result	MDL	
Polychlorinated Naphthalenes(PCNs)	N.D.	5 mg/kg	
Tested Item(s)	Result	MDL	
Polychlorinated Triphenyls(PCTs)	N.D.	5 mg/kg	

Test Report

Report No. A2210152964101001

Page 5 of 11

Test Result(s)

Tested Item(s)	Result	MDL
Phthalates		
Di-n-octyl phthalate(DNOP) CAS#:117-84-0	N.D.	50 mg/kg
Di-isononyl phthalate(DINP) CAS#:28553-12-0,68515-48-0	N.D.	50 mg/kg
Di-iso-decyl phthalate(DIDP) CAS#:26761-40-0,68515-49-1	N.D.	50 mg/kg
Di-n-hexyl phthalate(DNHP) CAS#:84-75-3	N.D.	50 mg/kg
Bis(2-methoxyethyl) phthalate(DMEP) CAS#:117-82-8	N.D.	50 mg/kg
* ¹ 1,2-Benzenedicarboxylic acid, di-(C7-11)-branched and linear alkyl esters(DHNUP) CAS#:68515-42-4	N.D.	100 mg/kg
* ¹ 1,2-Benzenedicarboxylic acid, di-C6-8-branched alkyl esters, C7-rich(DIHP) CAS#:71888-89-6	N.D.	100 mg/kg
Tested Item(s)		
Result		
MDL		
Polychlorinated Biphenyls(PCBs)		
Monochlorobiphenyl	N.D.	5 mg/kg
Dichlorobiphenyl	N.D.	5 mg/kg
Trichlorobiphenyl	N.D.	5 mg/kg
Tetrachlorobiphenyl	N.D.	5 mg/kg
Pentachlorobiphenyl	N.D.	5 mg/kg
Hexachlorobiphenyl	N.D.	5 mg/kg
Heptachlorobiphenyl	N.D.	5 mg/kg
Octachlorobiphenyl	N.D.	5 mg/kg
Nonachlorobiphenyl	N.D.	5 mg/kg
Decachlorobiphenyl	N.D.	5 mg/kg
Tested Item(s)		
Result		
MDL		
Short Chain Chlorinated Paraffins(SCCPs)	N.D.	100 mg/kg

Test Report

Report No. A2210152964101001

Page 6 of 11

Test Result(s)

Tested Item(s)	Result	MDL
Organotin compounds		
Dibutyltin(DBT)	N.D.	5 mg/kg
Tributyltin(TBT)	N.D.	5 mg/kg
Tributyltin oxide(TBTO) * ²	N.D.	5 mg/kg
Diocetyl tin(DOT)	N.D.	5 mg/kg
Triphenyltin(TPHT)	N.D.	5 mg/kg
Tested Item(s)		
Polyvinyl Chloride(PVC)	Negative	/
Tested Item(s)		
Perfluorooctanoic Acid(PFOA)	N.D.	0.5 µg/m ²
Tested Item(s)		
Perfluorooctane Sulfonates(PFOS)	N.D.	0.5 µg/m ²

Sample/Part Description Golden plating

Remark: The sample(s) had been dissolved totally tested for Lead, Cadmium, Mercury, Beryllium, Antimony.

-MDL = Method Detection Limit

-N.D. = Not Detected (<MDL or LOQ)

-mg/kg = ppm = parts per million

-1000 mg/kg = 0.1%

-LOQ = Limit of Quantification, The LOQ of Hexavalent chromium is 0.10 µg/cm²

-The sample is negative for Cr(VI) – The Cr(VI) concentration is below 0.10 µg/cm². The coating is considered a non-Cr(VI) based coating.

-Negative = Not contained Polyvinyl Chloride(PVC)

-*¹= In view of the substances are established as UVCB substances (substances of unknown or variable composition, complex reaction products or biological materials) consisting of different and variable constituents, the test results are calculated based on the main constituents of the representative compounds for substances.

-*²= concentration value of Tributyltin oxide by the conversion from the test results of Tributyl Tins.

Note: “*” indicates the method(s) is (are) not in CNAS accreditation scope.


Test Report

Report No. A2210152964101001


Page 7 of 11

Test Process


1. Lead (Pb), Cadmium (Cd)




2. Mercury (Hg)



3. Hexavalent Chromium (Cr(VI))



4. Polybrominated Biphenyls (PBBs), Polybrominated Diphenyl Ethers (PBDEs)




Test Report


Report No. A2210152964101001

Page 8 of 11


5. Phthalates




6. Beryllium(Be), Antimony(Sb)



7. Hexabromocyclododecane (HBCDD)



8. Fluorine (F), Chlorine (Cl), Bromine (Br), Iodine (I)




Test Report


Report No. A2210152964101001

Page 9 of 11


9. Polychlorinated Naphthalenes (PCNs)



10. Polychlorinated terphenyls (PCTs)



11. Polychlorinated Biphenyls (PCBs)




Test Report


Report No. A2210152964101001

Page 10 of 11


12. Short Chain Chlorinated Paraffins (SCCPs)




13. Organotin compounds



14. Polyvinyl Chloride (PVC)



15. Perfluorooctanoic Acid(PFOA), Perfluorooctane Sulfonates(PFOS)




Test Report

Report No. A2210152964101001

Page 11 of 11

Photo(s) of the sample(s)



Statement:

1. This report is considered invalid without approved signature, special seal and the seal on the perforation;
2. The Company Name shown on Report and Address, the sample(s) and sample information was/were provided by the applicant who should be responsible for the authenticity which CTI hasn't verified;
3. The result(s) shown in this report refer(s) only to the sample(s) tested;
4. Without written approval of CTI, this report can't be reproduced except in full;
5. In case of any discrepancy between the English version and Chinese version of the testing reports (if generated), the Chinese version shall prevail.

*** End of report ***