

REPORT NO. JP/2023/031552

DATE: April 13,2023

PAGE: 1 OF 9

MITSUBISHI MATERIALS CORPORATION

12-6 TECHNOPARK SANDA-SHI HYOGO JAPAN

SAMPLE NAME Ti-W target (Lot:TWH43-38/MMC)

CLIENT REF.NO MATZ23C032

THE ABOVE SAMPLE(S) AND INFORMATION WERE PROVIDED BY THE APPLICANT.

上記のサンプル並びに情報は顧客により提供されました。

SAMPLE RECEIVED サンプル受領日

2023/03/31

TESTING DATE

分析期間

: 2023/03/31 TO 2023/04/12

TEST REQUESTED

分析項目

SELECTED TEST(S) AS REQUESTED BY CLIENT.

分析項目は顧客の要求によります。

TEST METHOD(S)

分析方法

WITH REFERENCE TO LATEST EDITION OF IEC62321 FOR RoHS 10 SUBSTANCES.

OTHER CHEMICALS WERE TESTED BY EACH APPROPRIATE METHOD.

RoHS10物質の分析は最新版のIEC62321を参照しました。

それ以外の化学物質についてはそれぞれに最適な方法で分析を行いました。

TEST RESULT(S)

分析結果

PLEASE REFER TO THE NEXT PAGE(S).

以下のページをご参照願います。



Fumitaka Maruyama / Quality Officer Central Chemical Laboratory SGS Japan Inc.

This Test Report is issued by the Company under its General Conditions of Service printed overleaf or available on request and accessible at http://www.sgs.com. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Unless otherwise stated the results shown in this Test Report refer only to the samples(s) tested.

to the immitation of liability, independing understand and jurisoticion issues delined unlerein. Unless otherwise stated the results shown in this test Report cannot be reproduced except, in full, without prior approval of the Company, Any unauthorized alteration, forgery or falsification of the content or appearance of this test report is unlawful and offenders may be prosecuted to the fullest extent of the law.

この検査報告書は裏面に記載された、もしくはhttp://www.sgs.comで入手が可能なサービスに関する一般的条件に則して発行されます。そうらに明記されている弊社の負うべき債務・補償の範囲及び同法言葉の改訂している事業にあることに関記されている弊社の負うべき債務・補償の範囲及び同法言葉の改訂している。他に特に明記のない限り、この検査報告書に記載された結果は、検査した試料のみに属します。この書面全体の複製以外には、弊社からの事前の許可を得ること無く複製することを禁じます。この検査報告書を無断で変更、偽造、改ざんすることは違法であり、違反者に対しては法的手段を講じることとなります。

SGS Japan Inc.

YBP East Tower 12F, 134 Godo-cho Hodogaya-ku Yokohama 240-0005, Japan URL: www.sgsgroup.jp



REPORT NO. JP/2023/031552

DATE: April 13,2023

PAGE: 2 OF 9

MITSUBISHI MATERIALS CORPORATION

12-6 TECHNOPARK SANDA-SHI HYOGO JAPAN

TEST RESULT(S)

ITEM(S)	UNIT	RESULT	METHOD	INST./PLACE	MDL
CADMIUM(Cd)	mg/kg	N.D.	IEC62321-5: 2013	ICP-OES	2
LEAD(Pb)	mg/kg	N.D.	IEC62321-5: 2013	ICP-OES	2
MERCURY(Hg)	mg/kg	N.D.	IEC62321-4: 2013+AMD1: 2017	ICP-OES	2
CHROMIUM VI(Cr(VI))	mg/kg	N.D.	IEC62321-7-1: 2015	UV/VIS	2
Polybrominated biphenyls(PBBs)					
Monobromobiphenyl	mg/kg	N.D.	IEC62321-6: 2015	GC/MS*	5
Dibromobiphenyl	mg/kg	N.D.			5
Tribromobiphenyl	mg/kg	N.D.			5
Tetrabromobiphenyl	mg/kg	N.D.			5
Pentabromobiphenyl	mg/kg	N.D.			5
Hexabromobiphenyl	mg/kg	N.D.	IEC02321-0. 2013		5
Heptabromobiphenyl	mg/kg	N.D.			5
Octabromobiphenyl	mg/kg	N.D.			5
Nonabromobiphenyl	mg/kg	N.D.			5
Decabromobiphenyl	mg/kg	N.D.			5
Polybrominated diphenyl ethers(PBDEs)					
Monobromodiphenyl ether	mg/kg	N.D.		GC/MS*	5
Dibromodiphenyl ether	mg/kg	N.D.	IEC62321-6: 2015		5
Tribromodiphenyl ether	mg/kg	N.D.			5
Tetrabromodiphenyl ether	mg/kg	N.D.			5
Pentabromodiphenyl ether	mg/kg	N.D.			5
Hexabromodiphenyl ether	mg/kg	N.D.			5
Heptabromodiphenyl ether	mg/kg	N.D.			5
Octabromodiphenyl ether	mg/kg	N.D.			5
Nonabromodiphenyl ether	mg/kg	N.D.			5
Decabromodiphenyl ether	mg/kg	N.D.			5
POLYCHLORINATED BIPHENYLS(PCBs)	mg/kg	N.D.	EPA3550C	GC/MS*	0.5
ANTIMONY(Sb)	mg/kg	N.D.	EPA3052	ICP-OES	2
ARSENIC(As)	mg/kg	N.D.	EPA3052	ICP-OES	10
BARIUM(Ba)	mg/kg	N.D.	EPA3052	ICP-OES	2
BERYLLIUM(Be)	mg/kg	N.D.	EPA3052	ICP-OES	10
PHOSPHORUS(P)	mg/kg	N.D.	EPA3052	ICP-OES	2
SELENIUM(Se)	mg/kg	N.D.	EPA3052	ICP-OES	5
SULFUR(S)	mg/kg	N.D.	EPA3052	ICP-OES	50
HALOGEN					
FLUORINE(F)	mg/kg	N.D.	BS EN14582(2016)/ Combustion	IC	50
CHLORINE(CI)	mg/kg	N.D.	BS EN14582(2016)/ Combustion	IC	50

NOTES: mg/kg = ppm, N.D. = Not Detected, INST. = INSTRUMENT, MDL = Method Detection Limit

REMARK: The content of Cr() has been calculated with regard to the sample weight as specified by client.

This Test Report is issued by the Company under its General Conditions of Service printed overleaf or available on request and accessible at http://www.sgs.com. Attention is drawn This Test Report is issued by use Company union its General Conditions of Service printed overlead or available on request and accessible at nupr/www.sgs.com. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Unless otherwise stated the results shown in this Test Report refer only to the samples(s) tested. This Test Report cannot be reproduced except, in full, without prior approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this test report is unlawful and offenders may be prosecuted to the fullest extent of the law.

この検査報告書は裏面に記載された、もしくはhttp://www.sgs.comで入手が可能なサービスに関する一般的条件に則して発行されます。そちらに明記されている弊社の負うべき債務・補償の範囲及び司法管轄の項目をご注意ください。他に特に明記のない限り、この検査報告書に記載された結果は、検査した試料のみに属します。この書面全体の複製以外には、弊社からの事前の許可を得ること無く複製することを禁じます。この検査報告書を無断で変更、偽造、改ざんすることは違法であり、違反者に対しては法的手段を講じることとなります。

^{* =} The test has been conducted in association with SGS Taiwan Ltd.



REPORT NO. JP/2023/031552

DATE: April 13,2023

PAGE: 3 OF 9

MITSUBISHI MATERIALS CORPORATION

12-6 TECHNOPARK SANDA-SHI HYOGO JAPAN

TEST RESULT(S)

ITEM(S)	UNIT	RESULT	METHOD	INST./PLACE	MDL
BROMINE(Br)	mg/kg	N.D.	BS EN14582(2016)/ Combustion	IC	50
IODINE(I)	mg/kg	N.D.	BS EN14582(2016)/ Combustion	IC	50
HEXABROMOCYCLODODECANE(HBCDD)	mg/kg	N.D.	IEC62321-9: 2021	GC/MS*	20
PHTHALATES					
DIISOBUTYL PHTHALATE(DIBP)	mg/kg	N.D.	IEC62321-8: 2017	GC/MS*	50
DIBUTYL PHTHALATE(DBP)	mg/kg	N.D.	IEC62321-8: 2017	GC/MS*	50
BUTYLBENZYL PHTHALATE(BBP)	mg/kg	N.D.	IEC62321-8: 2017	GC/MS*	50
DI(2-ETHYLHEXYL) PHTHALATE(DEHP)	mg/kg	N.D.	IEC62321-8: 2017	GC/MS*	50
DIOCTYL PHTHALATE(DNOP)	mg/kg	N.D.	IEC62321-8: 2017	GC/MS*	50
DIISONONYL PHTHALATE(DINP)	mg/kg	N.D.	IEC62321-8: 2017	GC/MS*	50
DIISODECYL PHTHALATE(DIDP)	mg/kg	N.D.	IEC62321-8: 2017	GC/MS*	50
PERFLUOROHEXANE SULFONATE(PFHxS)	mg/kg	N.D.	CEN/TS15968	LC/MS/MS*	0.01
PERFLUOROOCTANE SULFONATES(PFOS)	mg/kg	N.D.	CEN/TS15968	LC/MS/MS*	0.01
PERFLUOROHEXANOIC ACID(PFHxA)	mg/kg	N.D.	CEN/TS15968	LC/MS/MS*	0.01
PERFLUOROOCTANOIC ACID(PFOA)	mg/kg	N.D.	CEN/TS15968	LC/MS/MS*	0.01
PERFLUORONONANOIC ACID(PFNA)	mg/kg	N.D.	CEN/TS15968	LC/MS/MS*	0.01
PERFLUORODECANOIC ACID(PFDA)	mg/kg	N.D.	CEN/TS15968	LC/MS/MS*	0.01
PERFLUOROUNDECANOIC ACID(PFUnDA)	mg/kg	N.D.	CEN/TS15968	LC/MS/MS*	0.01
PERFLUORODODECANOIC ACID(PFDoDA)	mg/kg	N.D.	CEN/TS15968	LC/MS/MS*	0.01
PERFLUOROTRIDECANOIC ACID(PFTrDA)	mg/kg	N.D.	CEN/TS15968	LC/MS/MS*	0.01
PERFLUOROTETRADECANOIC ACID(PFTDA)	mg/kg	N.D.	CEN/TS15968	LC/MS/MS*	0.01

NOTES: mg/kg = ppm, N.D. = Not Detected, INST. = INSTRUMENT, MDL = Method Detection Limit

REMARK: The content of Cr() has been calculated with regard to the sample weight as specified by client.

^{* =} The test has been conducted in association with SGS Taiwan Ltd.



REPORT NO. JP/2023/031552

DATE: April 13,2023

PAGE: 4 OF 9


MITSUBISHI MATERIALS CORPORATION

12-6 TECHNOPARK SANDA-SHI HYOGO JAPAN

分析フローチャート MEASUREMENT FLOW CHART

酸分解前処理において試料を完全分解しています。

The sample was dissolved/ decomposed totally by acid pre-conditioning method according to below flow chart.



This Test Report is issued by the Company under its General Conditions of Service printed overleaf or available on request and accessible at http://www.sgs.com. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Unless otherwise stated the results shown in this Test Report refer only to the samples(s) tested.

to the immitation of liability, independing understand and jurisoticion issues delined unlerein. Unless otherwise stated the results shown in this test Report cannot be reproduced except, in full, without prior approval of the Company, Any unauthorized alteration, forgery or falsification of the content or appearance of this test report is unlawful and offenders may be prosecuted to the fullest extent of the law.

この検査報告書は裏面に記載された、もしくはhttp://www.sgs.comで入手が可能なサービスに関する一般的条件に則して発行されます。そうらに明記されている弊社の負うべき債務・補償の範囲及び同法言葉の改訂している事業にあることに関記されている弊社の負うべき債務・補償の範囲及び同法言葉の改訂している。他に特に明記のない限り、この検査報告書に記載された結果は、検査した試料のみに属します。この書面全体の複製以外には、弊社からの事前の許可を得ること無く複製することを禁じます。この検査報告書を無断で変更、偽造、改ざんすることは違法であり、違反者に対しては法的手段を講じることとなります。



REPORT NO. JP/2023/031552

DATE: April 13,2023

PAGE: 5 OF 9

MITSUBISHI MATERIALS CORPORATION


12-6 TECHNOPARK SANDA-SHI HYOGO JAPAN

分析フローチャート MEASUREMENT FLOW CHART

酸分解前処理において試料を完全分解しています。

The sample was dissolved/ decomposed totally by acid pre-conditioning method according to below flow chart.

<u>無機分析</u> **INORGANIC ANALYSIS**



This Test Report is issued by the Company under its General Conditions of Service printed overleaf or available on request and accessible at http://www.sgs.com. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Unless otherwise stated the results shown in this Test Report refer only to the samples(s) tested.

This Test Report cannot be reproduced except, in full, without prior approval of the Company, Any unauthorized alteration, forgery or falsification of the content or appearance of this test report is unlawful and offenders may be prosecuted to the fullest extent of the law.

この検査報告書は裏面に記載された、もしくはhttp://www.sgs.comで入手が可能なサービスに関する一般的条件に関して発行されます。そちらに明記されている弊社の負うべき債務・補償の範囲及び同談音報の項目をご注意された。もしくはhttp://www.sgs.comで入手が可能なサービスに関する一般的条件に関して発行されます。そちらに明記されている弊社の負うべき債務・補償の範囲及び同談音報の項目をご注意された。他に特に明記のない限り、この検査報告書に記載された結果は、検査した試料のみに属します。この書面全体の複製以外には、弊社からの事前の許可を得ること無く複製することを禁じます。この検査報告書を無断で変更、偽造、改ざんすることは違法であり、違反者に対しては法的手段を講じることとなります。



REPORT NO. JP/2023/031552


DATE: April 13,2023

PAGE: 6 OF 9

MITSUBISHI MATERIALS CORPORATION

12-6 TECHNOPARK SANDA-SHI HYOGO JAPAN

分析フローチャート MEASUREMENT FLOW CHART



This Test Report is issued by the Company under its General Conditions of Service printed overleaf or available on request and accessible at http://www.sgs.com. Attention is drawn Inis lest Heport is issued by the Company under its General Conditions of Service printed overleaf or available on request and accessible at nttp://www.sgs.com. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Unless otherwise stated the results shown in this Test Report refer only to the samples(s) tested. This Test Report cannot be reproduced except, in full, without prior approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this test report is unlawful and offenders may be prosecuted to the fullest extent of the law. この検査報告書は認された、もしくはhttp://www.sgs.comで入手が可能なサービスに関する一般的条件に則して発行されます。そちらに明記されている弊社の負うべき債務・補償の範囲及び司法音輪の項目をご注意ください。他に特に明記のない限り、この検査報告書に記載された結果は、検査した試料のみに属します。この書面全体の複製以外には、弊社からの事前の許可を得ること無く複製することを禁じます。この検査報告書を無断で変更、偽造、改ざんすることは違法であり、違反者に対しては法的手段を講じることとなります。



REPORT NO. JP/2023/031552

DATE: April 13,2023


PAGE: 7 OF 9

MITSUBISHI MATERIALS CORPORATION

12-6 TECHNOPARK SANDA-SHI HYOGO JAPAN

分析フローチャート MEASUREMENT FLOW CHART

PERFLUORINATED COMPOUNDs(PFCs)



This Test Report is issued by the Company under its General Conditions of Service printed overleaf or available on request and accessible at http://www.sgs.com. Attention is drawn Inis lest Heport is issued by the Company under its General Conditions of Service printed overleaf or available on request and accessible at nttp://www.sgs.com. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Unless otherwise stated the results shown in this Test Report refer only to the samples(s) tested. This Test Report cannot be reproduced except, in full, without prior approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this test report is unlawful and offenders may be prosecuted to the fullest extent of the law. この検査報告書は認された、もしくはhttp://www.sgs.comで入手が可能なサービスに関する一般的条件に則して発行されます。そちらに明記されている弊社の負うべき債務・補償の範囲及び司法音輪の項目をご注意ください。他に特に明記のない限り、この検査報告書に記載された結果は、検査した試料のみに属します。この書面全体の複製以外には、弊社からの事前の許可を得ること無く複製することを禁じます。この検査報告書を無断で変更、偽造、改ざんすることは違法であり、違反者に対しては法的手段を講じることとなります。



REPORT NO. JP/2023/031552

DATE: April 13,2023


PAGE: 8 OF 9

MITSUBISHI MATERIALS CORPORATION

12-6 TECHNOPARK SANDA-SHI HYOGO JAPAN

分析フローチャート MEASUREMENT FLOW CHART

<u>フタル酸エステル</u> **PHTHALATES**



This Test Report is issued by the Company under its General Conditions of Service printed overleaf or available on request and accessible at http://www.sgs.com. Attention is drawn Inis lest Heport is issued by the Company under its General Conditions of Service printed overleaf or available on request and accessible at nttp://www.sgs.com. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Unless otherwise stated the results shown in this Test Report refer only to the samples(s) tested. This Test Report cannot be reproduced except, in full, without prior approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this test report is unlawful and offenders may be prosecuted to the fullest extent of the law. この検査報告書は認された、もしくはhttp://www.sgs.comで入手が可能なサービスに関する一般的条件に則して発行されます。そちらに明記されている弊社の負うべき債務・補償の範囲及び司法音輪の項目をご注意ください。他に特に明記のない限り、この検査報告書に記載された結果は、検査した試料のみに属します。この書面全体の複製以外には、弊社からの事前の許可を得ること無く複製することを禁じます。この検査報告書を無断で変更、偽造、改ざんすることは違法であり、違反者に対しては法的手段を講じることとなります。



REPORT NO. JP/2023/031552

DATE: April 13,2023

PAGE: 9 OF 9

MITSUBISHI MATERIALS CORPORATION

12-6 TECHNOPARK SANDA-SHI HYOGO JAPAN

SAMPLE IMAGE

JP/2023/031552



<END>

This Test Report is issued by the Company under its General Conditions of Service printed overleaf or available on request and accessible at http://www.sgs.com. Attention is drawn This Test Report is issued by the Company direder its General Continuous of Service Printed Overland and accessible at map, however, and the continuous of the Company and the state of the limitation of liability, indemnification and jurisdiction issues defined therein. Unless otherwise stated the results shown in this Test Report refer only to the samples(s) tested. This Test Report cannot be reproduced except, in full, without prior approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this test report is unlawful and offenders may be prosecuted to the fullest extent of the law. この検査報告書に記載された、もしくはhttp://www.sgs.comで入手が可能なサービスに関する一般的条件に則して発行されます。そちらに明記されている弊社の負うべき債務・補償の範囲及び司法管轄の項目をご注意ください。他に特に明記のない限り、この検査報告書に記載された結果は、検査した試料のみに属します。この書面全体の複製以外には、弊社からの事前の許可を得ること無く複製することを禁じます。この検査報告書を無断で変更、偽造、改ざんすることは違法であり、違反者に対しては法的手段を講じることとなります。