

## Test Report

No. 6126125-08

Date: 06/MAY/2022

Page 1 of 2

Globalfoundries Dresden  
 Module One LLC & Co. KG  
 Ms. Hermanns  
 Wilschdorfer Landstrasse 101  
 01109 Dresden  
 GERMANY



### The following sample(s) was/were submitted and identified by/on behalf of the client as:

SGS Job file : 6126125  
 Order date : 17/MAR/2022  
 Order number : 813003903482  
 Sample receiving date : 21/MAR/2022  
 Sampling : by client or by a third party acting at the client's direction  
 Condition of the samples : appropriate for testing  
 Testing period : 21/MAR/2022 – 06/MAY/2022  
 Analytical scope : according to client's requirements

Sample No.	Sample designation	Sample material
220295895	Fab 1 300mm die patterned wafer, Tech Node 40nm	Wafer

### Applied analytical technique

#### Testing for selected metals:

Sample preparation : Pulverization/Homogenization of the sample material  
 Antimony (Sb) : ICP Screening analysis: Analysis was performed via inductively coupled plasma atomic emission spectrometry acc. to DIN EN ISO 11885:2009-09 after digestion with hydrofluoric acid

Test Results: please refer to next page(s).

### SGS INSTITUT FRESENIUS GmbH

i.V.

Wera Leonhard / sba  
 Projektleiterin / Project Manager  
 Connectivity & Products (C&P)  
 Tel. +49 (0)6128 / 744 - 186

i.A.

Dr. Stefan Graß  
 Customer Service Consultant  
 Connectivity & Products (C&P)  
 Tel. +49 (0)6128 / 744 - 280

**Test Report**

No. 6126125-08

Date: 06/MAY/2022


Page 2 of 2

Globalfoundries Dresden  
 Module One LLC & Co. KG  
 Wilschdorfer Landstrasse 101  
 01109 Dresden  
 GERMANY

**Test results**

Sample No.	220295895		RL
Test Item(s):	Unit		
Antimony (Sb)	mg/kg	n.d.	10**
<u>Note:</u> n.d.= not detected	RL = Report Limit	n.a.= not analyzed	(**)=elevated analytical deviation of results

**Sample Photo(s)**



\*\*\*End of Report\*\*\*

The test results refer exclusively to the examined test items and the date of the test under the test specifications. Written acknowledgement for publication and duplication of our analytical reports for promotional purpose, as well as fractional use for other purposes are mandatory. Numbers following „<“ represent limits of quantification. Determination of parameters marked with \* was performed with a cooperation partner.

This document is issued by the Company subject to its General Conditions of Service ([www.sgsgroup.de/agn](http://www.sgsgroup.de/agn)). Attention is drawn to the limitations of liability, indemnification and jurisdictional issues established therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instructions, if any. The Company's sole responsibility is to its client and this document does not exonerate parties to a transaction from exercising all their rights and under the transaction documents. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law.

Note: The sample(s) to which the findings recorded herein (the "findings") relate was (were) probably drawn and / or provided by the client or by a third party acting at the client's direction. In this case the findings constitute no warranty of the sample's representativeness of any goods and strictly relate to the sample(s). The company accepts no liability with regard to the origin or source from which the sample(s) is/are said to be extracted.

We would like to point out that measurement uncertainties are not taken into account for conclusions. On request, we can provide measurement uncertainties and take them into account for conclusions upon consultation.