



THE INDUSTRIAL ANALYSIS SERVICE LTD.

TEL:+81-48-924-7151 FAX:+81-48-928-3587 e-mail:ias@sangyobunseki.co.jp

2-11-7 Yatsuka Souka Saitama 340-0028 Japan

TEST REPORT

Request No. 10035353327
Report No. ES220000000588-01
Date of issue: 10 March 2022

To. KYOCERA Corporation

Address:1-1 Kokubuyamashita Kirishima Kagoshima Japan

Name of sample: NCO-165PZ, PZB

Date of receipt of sample: 1 March 2022

Measurement days: 1 March 2022 ~ 10 March 2022

The following is the report on the requested test of the sample

Table with 5 columns: Test Items, Unit, Test result, D.L., Test Method. Rows include F, Cl, Br, I, and a remainder of page intentionally left blank.

Note: The results shown in this test report refer only to the sample(s) tested. DL=Determination Limit

N.D.means the analysis result is less than fixed quality lower limit level calculated according to our established precision management condition. mg/kg=ppm

THE INDUSTRIAL ANALYSIS SERVICE LTD.

Handwritten signature: 吉田 貴則

TAKANORI YOSHIDA


Flow chart

Report No. : ES22000000588-01

Measurement days : 1 March 2022 ~ 10 March 2022


Operator : Norio Watanabe

F, Cl, Br, I



IC : DIONEX ICS-1100 RFIC

Report No. ES220000000588-01



THE INDUSTRIAL ANALYSIS SERVICE LTD.