

Test Report

Applicant: Leading Technologies
1153 Industrial Park Rd,
Leechburg, PA 15656, USA

Number : TWNC01012118
Issue Date : Aug 27, 2021 .

Sample Description:

One (1) Group of Submitted Samples Said To Be :

Sample Description : D
Date Sample Received : Aug 18, 2021
Date Test Started : Aug 18, 2021

Test Conducted:


As requested by the applicant, for details please refer to attached pages.

Authorized By:
On behalf of Intertek Testing Services
Taiwan Limited


Matt Wang
Director



Signed by:


Thomas Chou
Manager



Page 1 of 10



Test Conducted :

Test Result Summary:

Test Item	Unit	Test Method	Result	RL
			Golden metal	
Heavy Metal				
Cadmium (Cd) Content	ppm	With reference to IEC 62321-5: 2013, by microwave or acid digestion and determined by ICP-OES.	ND	2
Lead (Pb) Content	ppm	With reference to IEC 62321-5: 2013, by microwave or acid digestion and determined by ICP-OES.	14	2
Mercury (Hg) Content	ppm	With reference to IEC 62321-4:2013+AMD1:2017, by microwave or acid digestion and determined by ICP-OES.	ND	2
Beryllium (Be) Content	ppm	With reference to USEPA 3052, by microwave digestion and determined by ICP-OES.	ND	2
Antimony (Sb) Content	ppm	With reference to USEPA 3052, by microwave digestion and determined by ICP-OES.	ND	2
Chromium VI (Cr(VI)) Content @	µg/ cm ²	With reference to IEC 62321-7-1: 2015, by boiling water extraction and determined by UV-Vis Spectrophotometer or visual observation.	Negative	0.10
Polybrominated Biphenyls (PBBs)				
Monobrominated Biphenyls (MonoBB)	ppm	With reference to IEC 62321-6: 2015, by solvent extraction and determined by GC-MS and further HPLC-DAD confirmation when necessary.	ND	5
Dibrominated Biphenyls (DiBB)	ppm		ND	5
Tribrominated Biphenyls (TriBB)	ppm		ND	5
Tetrabrominated Biphenyls (TetraBB)	ppm		ND	5
Pentabrominated Biphenyls (PentaBB)	ppm		ND	5
Hexabrominated Biphenyls (HexaBB)	ppm		ND	5
Heptabrominated Biphenyls (HeptaBB)	ppm		ND	5
Octabrominated Biphenyls (OctaBB)	ppm		ND	5
Nonabrominated Biphenyls (NonaBB)	ppm		ND	5
Decabrominated Biphenyl (DecaBB)	ppm		ND	5



Test Conducted :

Test Item	Unit	Test Method	Result	RL
			Golden metal	
Polybrominated Diphenyl Ethers (PBDEs)				
Monobrominated Diphenyl Ethers (MonoBDE)	ppm	With reference to IEC 62321-6: 2015, by solvent extraction and determined by GC-MS and further HPLC-DAD confirmation when necessary.	ND	5
Dibrominated Diphenyl Ethers (DiBDE)	ppm		ND	5
Tribrominated Diphenyl Ethers (TriBDE)	ppm		ND	5
Tetrabrominated Diphenyl Ethers (TetraBDE)	ppm		ND	5
Pentabrominated Diphenyl Ethers (PentaBDE)	ppm		ND	5
Hexabrominated Diphenyl Ethers (HexaBDE)	ppm		ND	5
Heptabrominated Diphenyl Ethers (HeptaBDE)	ppm		ND	5
Octabrominated Diphenyl Ethers (OctaBDE)	ppm		ND	5
Nonabrominated Diphenyl Ethers (NonaBDE)	ppm		ND	5
Decabrominated Diphenyl Ether (DecaBDE)	ppm		ND	5
Phthalates				
Di(2-ethylhexyl) Phthalate (DEHP)	ppm	With reference to IEC 62321-8:2017, by solvent extraction and determined by GC-MS.	ND	50
Dibutyl Phthalate (DBP)	ppm		ND	50
Benzyl Butyl Phthalate (BBP)	ppm		ND	50
Diisobutyl Phthalate (DIBP)	ppm		ND	50
Halogen Content				
Fluorine (F)	ppm	With reference to EN 14582:2016 by combustion bomb with oxygen and determined by Ion Chromatography.	ND	50
Chlorine (Cl)	ppm		ND	50
Bromine (Br)	ppm		ND	50
Iodine (I)	ppm		ND	50

Remarks: ppm = Parts per million based on weight of tested sample = mg/kg

ND = Not detected

RL = Reporting limit, quantitation limit of analyte in sample



Test Conducted :

@ The explanation of Chromium VI (Cr(VI)) analysis results

Colorimetric result	Qualitative Result	Explanation
< 0.10 µg/cm ²	Negative	The result of sample is negative for Cr(VI). The sample coating is considered a non-Cr(VI) based coating.
≥ 0.10 µg/cm ² and ≤ 0.13 µg/cm ²	Inconclusive	The result of sample is considered to be inconclusive. If addition samples are available, recommend to add trials and get the average result for the final determination.
> 0.13 µg/cm ²	Positive	The result of sample is positive for Cr(VI). The sample coating is considered to contain Cr(VI). A result expresses as Positive, while not an actual value, which indicates a visual observation was used.

Responsibility of Chemist: Melody Lee/ Vita Fu

Date Sample Received : Aug 18, 2021
Test Period : Aug 18, 2021 to Aug 26, 2021

RoHS Limit

Restricted Substances	Limits
Cadmium (Cd) content	0.01% (100ppm)
Lead (Pb) content	0.1% (1000ppm)
Mercury (Hg) content	0.1% (1000ppm)
Chromium VI (Cr(VI)) content	0.1% (1000ppm)
Polybrominated Biphenyls (PBBs)	0.1% (1000ppm)
Polybrominated Diphenyl Ethers (PBDEs)	0.1% (1000ppm)
Di(2-ethylhexyl) Phthalate (DEHP)	0.1% (1000ppm)
Dibutyl Phthalate (DBP)	0.1% (1000ppm)
Benzyl Butyl Phthalate (BBP)	0.1% (1000ppm)
Diisobutyl Phthalate (DIBP)	0.1% (1000ppm)

The limits were quoted from Annex II of 2011/65/EU and Amendment (EU) 2015/863 for homogeneous material.



Test Conducted :

Measurement Flowchart:


Test for Cd/Pb/Hg/Chromium (VI)/PBBs/PBDEs Content

Reference Standard : Cd/Pb: IEC 62321-5:2013; Hg: IEC 62321-4:2013+AMD1:2017;

Chromium (VI): IEC 62321-7-1:2015 (boiling water extraction);

Chromium (VI): IEC 62321-7-2:2017 (solvent and alkaline extraction);

PBBs/PBDEs: IEC 62321-6:2015



Test Conducted :

Remarks:

*1: List of Appropriate Acid :

Material	Acid Added for Digestion
Polymers	HNO ₃ ,HCl,HF,H ₂ O ₂ ,H ₃ BO ₃
Metals	HNO ₃ ,HCl,HF
Electronics	HNO ₃ ,HCl,H ₂ O ₂ ,HBF ₄


*2: If sample solution is significantly more intense than 0.13 µg/cm² equivalent comparison standard, Chromium VI would be determined as detected, the result of visual observation is positive.



Test Conducted :

Measurement Flowchart:


Test For Heavy Metal (Be, Sb) Content
Reference Standard : USEPA 3052



Test Conducted :

Measurement Flowchart:

Test for Phthalates Content
Reference Method : IEC 62321-8:2017




Test Conducted :

Number : TWNC01012118


Measurement Flowchart:

Test For Halogen Content

Reference Standard : EN 14582:2016



Sample photo:



End of Report

Except where explicitly agreed in writing, all work and services performed by Intertek is subject to our standard Terms and Conditions which can be obtained at our website: <http://www.intertek-twn.com/terms/>. Intertek's responsibility and liability are limited to the terms and conditions of the agreement.

This report is made solely on the basis of your instructions and / or information and materials supplied by you and provide no warranty on the tested sample(s) be truly representative of the sample source. The report is not intended to be a recommendation for any particular course of action, you are responsible for acting as you see fit on the basis of the report results. Intertek is under no obligation to refer to or report upon any facts or circumstances which are outside the specific instructions received and accepts no responsibility to any parties whatsoever, following the issue of the report, for any matters arising outside the agreed scope of the works. This report does not discharge or release you from your legal obligations and duties to any other person. You are the only one authorized to permit copying or distribution of this report (and then only in its entirety). Any such third parties to whom this report may be circulated rely on the content of the report solely at their own risk

Reporting Statements of Conformity: *Please note that the test results contain statement of conformity with the decision rules which are based on the specifications of customers, regulations and standards, and does not consider measurement uncertainty.*

