

Test Report No.: SHAEC23007008901 **Date:** Jun 02, 2023 Page 1 of 10

Client Name: HENKEL CORPORATION

Client Address: 14000 Jamboree Road, Irvine, CA 92606

Sample Name: 2025D
Style/Item No.: 2025D
Sample Description: Adhesive

The above sample(s) and information were provided by the client.

SGS Job No.: SP23-010491 Sample Receiving Date: May 29, 2023

Testing Period: May 29, 2023 ~ Jun 02, 2023

Test Requested: Select test(s) as requested by the client.

Test Method(s): Please refer to next page(s).

Test Result(s): Please refer to next page(s).

Test Requirement	Conclusion
Hexabromocyclododecane (HBCDD)	See Results
Beryllium (Be)	See Results
Phthalates Content	See Results
RoHS Directive (EU) 2015/863 amending Annex II to Directive 2011/65/EU	Pass

Signed for and on behalf of

SGS-CSTC Standards Technical Services (Shanghai) Co., Ltd.

Carol Luo

Approved Signatory





Unless otherwise agreed in writing, this document is issued by the Company subject to its General Conditions of Service printer overleaf, available on request or accessible at http://www.sgs.com/en/Terms-and-Conditions.aspx and, for electronic format documents subject to Terms and Conditions for Electronic Documents at http://www.sgs.com/en/Terms-and-Conditions/Terms-en-Document.aspx Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits or Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction form exercising all their rights and obligations under the transaction documents. This document components to the content of appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.

Attention: To check the authenticity of testing /inspection report & certificate, please contact us at telephone: (86-755) 8307 1443

3^{re}Building,No.889 Yishan Road Xuhui District,Shanghai China 200233 中国・上海・徐江区宜山路889号3号楼 邮编: 200233

t E&E (86–21) 61402553 f E&E (86–21)64953679 t HL (86–21) 61402594 f HL (86–21)61156899

e sgs.china@sgs.com



Test Report No.: SHAEC23007008901 **Date:** Jun 02, 2023 Page 2 of 10

Test Result(s):

Test Part Description:

SN ID	Sample No.	SGS Sample ID	Description
SN1	A1	SHA23-0070089-0001.C001	Red paste

Remarks:

- (1) 1 mg/kg = 1 ppm = 0.0001%
- (2) MDL = Method Detection Limit
- (3) ND = Not Detected (< MDL)
- (4) "-" = Not Regulated

Hexabromocyclododecane (HBCDD)

Test Method: With reference to IEC 62321-9:2021, analysis was performed by GC-MS.

Test Item(s)	CAS No.	Unit(s)	MDL	A1
	134237-50-6			
Hexabromocyclododecane (HBCDD)	/134237-51-7			
and all major diastereoisomers identified	/134237-52-8	mg/kg	20	ND
(α-HBCDD, β-HBCDD, γ-HBCDD)	/25637-99-4			
	/3194-55-6			

Beryllium (Be)

Test Method: With reference to US EPA 3052:1996, analysis was performed by ICP-OES.

Test Item(s)	Unit(s)	MDL	A1
Beryllium (Be)	mg/kg	2	ND

Phthalates Content

Test Method: With reference to IEC 62321-8:2017, analysis was performed by GC-MS.

Test Item(s)	CAS No.	Unit(s)	MDL	A1
Diicananyi Phthalata (DIND)	28553-12-0	mg/kg	50	ND
Diisononyl Phthalate (DINP)	/68515-48-0			
Di-n-octyl Phthalate (DNOP)	117-84-0	mg/kg	50	ND
Diisodecyl Phthalate (DIDP)	26761-40-0	mg/kg	50	ND
Dilsodecyi Pfilifalale (DIDP)	/68515-49-1		50	

RoHS Directive (EU) 2015/863 amending Annex II to Directive 2011/65/EU

Test Method:

- (1) With reference to IEC 62321-5:2013, determination of Cadmium by ICP-OES.
- (2) With reference to IEC 62321-5:2013, determination of Lead by ICP-OES.
- (3) With reference to IEC 62321-4:2013+AMD1:2017, determination of Mercury by ICP-OES.
- (4) With reference to IEC 62321-7-2:2017, determination of Hexavalent Chromium by UV-
- (5) With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.
- (6) With reference to IEC 62321-8:2017, determination of phthalates by GC-MS.



Unless otherwise agreed in writing, this document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at http://www.sgs.com/en/Terms-and-Conditions.aspx and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at http://www.sgs.com/en/Terms-and-Conditions/Terms-p-Document.aspx. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction form exercising all their rights and obligations under the transaction documents. This document cannot be reproduced except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.

**Attention: To check the authenticity of testing /inspection report & certificate, please contact us at telephone: (86-755) 8307 1443,

3rdBuilding,No.889 Yishan Road Xuhui District,Shanghai China 200233 中国・上海・徐汇区宜山路889号3号楼 邮编: 200233



Test Report No.: SHAEC23007008901 **Date:** Jun 02, 2023 Page 3 of 10

Test Item(s)	Limit	Unit(s)	MDL	A1
Cadmium(Cd)	100	mg/kg	2	ND
Lead(Pb)	1000	mg/kg	2	ND
Mercury(Hg)	1000	mg/kg	2	ND
Hexavalent Chromium(Cr(VI))	1000	mg/kg	8	ND
Sum of PBBs	1000	mg/kg	-	ND
Monobromobiphenyl	-	mg/kg	5	ND
Dibromobiphenyl	-	mg/kg	5	ND
Tribromobiphenyl	-	mg/kg	5	ND
Tetrabromobiphenyl	-	mg/kg	5	ND
Pentabromobiphenyl	-	mg/kg	5	ND
Hexabromobiphenyl	-	mg/kg	5	ND
Heptabromobiphenyl	-	mg/kg	5	ND
Octabromobiphenyl	-	mg/kg	5	ND
Nonabromobiphenyl	-	mg/kg	5	ND
Decabromobiphenyl	-	mg/kg	5	ND
Sum of PBDEs	1000	mg/kg	-	ND
Monobromodiphenyl ether	-	mg/kg	5	ND
Dibromodiphenyl ether	-	mg/kg	5	ND
Tribromodiphenyl ether	-	mg/kg	5	ND
Tetrabromodiphenyl ether	-	mg/kg	5	ND
Pentabromodiphenyl ether	-	mg/kg	5	ND
Hexabromodiphenyl ether	-	mg/kg	5	ND
Heptabromodiphenyl ether	-	mg/kg	5	ND
Octabromodiphenyl ether	-	mg/kg	5	ND
Nonabromodiphenyl ether	-	mg/kg	5	ND
Decabromodiphenyl ether	-	mg/kg	5	ND
Dibutyl phthalate (DBP)	1000	mg/kg	50	ND
Butyl benzyl phthalate (BBP)	1000	mg/kg	50	ND
Bis (2-ethylhexyl) phthalate (DEHP)	1000	mg/kg	50	ND
Diisobutyl Phthalates (DIBP)	1000	mg/kg	50	ND

Notes:

- (1) The maximum permissible limit is quoted from RoHS Directive (EU) 2015/863.
- IEC 62321 series is equivalent to EN 62321 series
- (2) The restriction of DEHP, BBP, DBP and DIBP shall apply to medical devices, including in vitro medical devices, and monitoring and control instruments, including industrial monitoring and control instruments, from 22 July 2021.

Unless otherwise stated, the decision rule for conformity reporting is based on Binary Statement for Simple Acceptance Rule (w=0) stated in ILAC-G8:09/2019.



Unless otherwise agreed in writing, this document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at http://www.sgs.com/en/Terms-and-Conditions.aspx and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at http://www.sgs.com/en/Terms-and-Conditions/Terms-p-Document.aspx. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction form exercising all their rights and obligations under the transaction documents. This document cannot be reproduced except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.


**Attention: To check the authenticity of testing /inspection report & certificate, please contact us at telephone: (86-755) 8307 1443,

3rdBuilding,No.889 Yishan Road Xuhui District,Shanghai China 200233 中国·上海·徐汇区宜山路889号3号楼 邮编: 200233



No.: SHAEC23007008901 **Date:** Jun 02, 2023 Page 4 of 10

HBCDD Testing Flow Chart






Unless otherwise agreed in writing, this document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at http://www.sgs.com/en/Terms-and-Conditions.aspx and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at <a href="http://www.sgs.com/en/Terms-and-Conditions/Terms-and-Cond

3rdBuilding,No.889 Yishan Road Xuhui District,Shanghai China 200233 中国·上海·徐汇区宜山路889号3号楼 邮编: 200233



No.: SHAEC23007008901 **Date:** Jun 02, 2023 Page 5 of 10

Elements Testing Flow Chart






Unless otherwise agreed in writing, this document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at http://www.sgs.com/en/Terms-and-Conditions.aspx, dor electronic format documents, subject to Terms and Conditions for Electronic Documents at <a href="http://www.sgs.com/en/Terms-and-Conditions/Terms-and-Conditio

3rdBuilding,No.889 Yishan Road Xuhui District,Shanghai China 200233 中国·上海·徐汇区宜山路889号3号楼 邮编: 200233



No.: SHAEC23007008901 Page 6 of 10 **Date:** Jun 02, 2023

Phthalates Testing Flow Chart





Unless otherwise agreed in writing, this document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at http://www.sgs.com/en/Terms-and-Conditions.aspx and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at <a href="http://www.sgs.com/en/Terms-and-Conditions/Terms-and-Cond

3rdBuilding,No.889 Yishan Road Xuhui District,Shanghai China 200233 中国·上海·徐汇区宜山路889号3号楼 邮编: 200233




Test Report

ATTACHMENTS

No.: SHAEC23007008901 **Date:** Jun 02, 2023

Elements Testing Flow Chart

These samples were dissolved totally by pre-conditioning method according to below flow chart.





Unless otherwise agreed in writing, this document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at http://www.sgs.com/en/Terms-and-Conditions.aspx and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at http://www.sgs.com/en/Terms-and-Conditions/Terms-p-Document.aspx. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction form exercising all their rights and obligations under the transaction documents. This document cannot be reproduced except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.

**Attention: To check the authenticity of testing /inspection report & certificate, please contact us at telephone: (86-755) 8307 1443,

3rdBuilding,No.889 Yishan Road Xuhui District,Shanghai China 200233 中国·上海·徐汇区宜山路889号3号楼 邮编: 200233 t E&E (86-21) 61402553 f E&E (86-21)64953679 www.sgsgroup.com.cn t HL (86-21) 61402594 f HL (86-21)61156899

e sgs.china@sgs.com


Page 7 of 10



No.: SHAEC23007008901 **Date:** Jun 02, 2023

Page 8 of 10

Hexavalent Chromium (Cr(VI)) Testing Flow Chart






Unless otherwise agreed in writing, this document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at http://www.sgs.com/en/Terms-and-Conditions.aspx and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at <a href="http://www.sgs.com/en/Terms-and-Conditions/Terms-and-Cond

3rdBuilding,No.889 Yishan Road Xuhui District,Shanghai China 200233 中国·上海·徐汇区宜山路889号3号楼 邮编: 200233



No.: SHAEC23007008901 Page 9 of 10 **Date:** Jun 02, 2023

PBBs/PBDEs Testing Flow Chart





Unless otherwise agreed in writing, this document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at http://www.sgs.com/en/Terms-and-Conditions.aspx and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at <a href="http://www.sgs.com/en/Terms-and-Conditions/Terms-and-Cond

3rdBuilding,No.889 Yishan Road Xuhui District,Shanghai China 200233 中国·上海·徐汇区宜山路889号3号楼 邮编: 200233 t E&E (86-21) 61402553 f E&E (86-21)64953679 www.sgsgroup.com.cn t HL (86-21) 61402594 f HL (86-21)61156899

e sgs.china@sgs.com



Test Report No.: SHAEC23007008901 **Date:** Jun 02, 2023 Page 10 of 10

Sample Photo:



SGS authenticate the photo on original report only *** End of Report ***



Unless otherwise agreed in writing, this document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at http://www.sgs.com/en/Terms-and-Conditions.aspx and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at <a href="http://www.sgs.com/en/Terms-and-Conditions/Terms-and-Cond

3rdBuilding,No.889 Yishan Road Xuhui District,Shanghai China 200233 中国·上海·徐汇区宜山路889号3号楼 邮编: 200233 t E&E (86-21) 61402553 f E&E (86-21)64953679 www.sgsgroup.com.cn t HL (86-21) 61402594 f HL (86-21)61156899

e sgs.china@sgs.com