

Job Ref. CRS/2019-09-11-034

NAGASE (MALAYSIA) SDN BHD

SUIT 16.01, LEVEL 16, MENARA IGB, MID VALLEY CITY, LINGKARAN SYED PUTRA, 59200 KUALA LUMPUR.

The following sample(s) was/were submitted and identified by/on behalf of applicant as:

SAMPLE DESCRIPTION : LA322S Silicone Adhesive

SAMPLE RECEIVED : 11/09/2019

TESTING PERIOD : 11/09/2019 to 18/09/2019

TEST REQUESTED : Selected test(s) as requested by customer

TEST METHOD : -PLEASE REFER TO NEXT PAGE(S)-

TEST RESULTS : -PLEASE REFER TO NEXT PAGE(S)-

REMARKS : 1) Test performed on dry basis for PBB, PBDE and phthalates testing.

SIGNED FOR AND ON BEHALF OF SGS (MALAYSIA) SDN BHD

TAY SIAM PINE
TECHNICAL MANAGER
IKM No. M/3452/6047/11/12

Test Report Form No.: SGS/TR/CRS/013, Ver: 4.0, Effective Date: 12/07/2019

Page 1 of 8



Job Ref. CRS/2019-09-11-034

TEST RESULTS:

Test Part Description

Sample Description: -PLEASE REFER TO PAGE 1-

RoHS Directive (EU) 2015/863 amending Annex II to Directive 2011/65/EU

Test Item(s):	Unit	Test Method	Result	MDL	Limit
Cadmium (Cd)	mg/kg	With reference to IEC 62321-5:2013, determination of Cadmium by ICP-OES.	N.D.	2	Max 100
Lead (Pb)	mg/kg	With reference to IEC 62321-5:2013, determination of Lead by ICP-OES.	N.D.	2	Max 1000
Mercury (Hg)	mg/kg	With reference to IEC 62321-4:2013+A1:2017, determination of Mercury by ICP-OES.	N.D.	2	Max 1000
Hexavalent Chromium (CrVI)	mg/kg	With reference to IEC 62321-7-2:2017, determination of Hexavalent Chromium by Colorimetric Method using UV-Vis.	N.D.	8	Max 1000
Sum of PBBs	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	Max 1000
Monobromobiphenyl	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Dibromobiphenyl	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Tribromobiphenyl	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Tetrabromobiphenyl	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Pentabromobiphenyl	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Hexabromobiphenyl	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Heptabromobiphenyl	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Octabromobiphenyl	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Nonabromobiphenyl	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Decabromobiphenyl	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-

SIGNED FOR AND ON BEHALF OF SGS (MALAYSIA) SDN BHD

TAY SIAM PINE
TECHNICAL MANAGER
IKM No. M/3452/6047/11/12

Test Report Form No.: SGS/TR/CRS/013, Ver: 4.0, Effective Date: 12/07/2019

Page 2 of 8



Job Ref. CRS/2019-09-11-034

TEST RESULTS:

Test Part Description

Sample Description: -PLEASE REFER TO PAGE 1-

RoHS Directive (EU) 2015/863 amending Annex II to Directive 2011/65/EU

Test Item(s):	Unit	Test Method	Result	MDL	Limit
Sum of PBDEs	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	Max 1000
Monobromodiphenyl ether	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Dibromodiphenyl ether	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Tribromodiphenyl ether	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Tetrabromodiphenyl ether	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Pentabromodiphenyl ether	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Hexabromodiphenyl ether	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Heptabromodiphenyl ether	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Octabromodiphenyl ether	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Nonabromodiphenyl ether	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Decabromodiphenyl ether	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-

Note: (a) mg/kg = ppm; ug/kg = ppb (0.01 mg/kg = 10 ug/kg); 0.1wt% = 1000ppm

(b) N.D. = Not Detected

(c) MDL = Method Detection Limit

(d) - = Not regulated

SIGNED FOR AND ON BEHALF OF SGS (MALAYSIA) SDN BHD

TAY SIAM PINE
TECHNICAL MANAGER
IKM No. M/3452/6047/11/12

Test Report Form No.: SGS/TR/CRS/013, Ver: 4.0, Effective Date: 12/07/2019

Page 3 of 8



Job Ref. CRS/2019-09-11-034

TEST RESULTS:

Test Part Description

Sample Description: -PLEASE REFER TO PAGE 1-

RoHS Directive (EU) 2015/863 amending Annex II to Directive 2011/65/EU

Test Item(s):	Unit	Test Method	Result	MDL	Limit
Dibutyl phthalate (DBP) (CAS No. 84-74-2)	mg/kg	With reference to IEC 62321-8:2017, determination of phthalates by GC-MS.	N.D.	50	Max 1000
Benzyl butyl phthalate (BBP) (CAS No. 85-68-7)	mg/kg	With reference to IEC 62321-8:2017, determination of phthalates by GC-MS.	N.D.	50	Max 1000
Di(2-ethylhexyl) phthalate (DEHP) (CAS No. 117-81-7)	mg/kg	With reference to IEC 62321-8:2017, determination of phthalates by GC-MS.	N.D.	50	Max 1000
Diisobutyl phthalate (DIBP) (CAS No. 84-69-5)	mg/kg	With reference to IEC 62321-8:2017, determination of phthalates by GC-MS.	N.D.	50	Max 1000

Note: (a) mg/kg = ppm; ug/kg = ppb (0.01 mg/kg = 10 ug/kg); 0.1wt% = 1000ppm

(b) N.D. = Not Detected

(c) MDL = Method Detection Limit

(d) - = Not regulated

- (e) On 4 June 2015, Commission Directive (EU) 2015/863 was published in the Official Journal of the European Union (OJEU) to include the phthalates BBP, DBP, DEHP and DIBP into ANNEX II of the RoHS Recast Directive. The new law restricts each phthalate to no more than 0.1% in each homogeneous material of an electrical product.
- (f)The restriction of DEHP, BBP, DBP and DIBP shall apply to medical devices, including in vitro medical devices, and monitoring and control instruments, including industrial monitoring and control instruments, from 22 July 2021.
- (g)The restriction of DEHP, BBP, DBP and DIBP shall not apply to cables or spare parts for the repair, the reuse, the updating of functionalities or upgrading of capacity of EEE placed on the market before 22 July 2019, and of medical devices, including in vitro medical devices, and monitoring and control instruments, including industrial monitoring and control instruments, placed on the market before 22 July 2021.
- (h)The restriction of DEHP, BBP and DBP shall not apply to toys which are already subject to the restriction of DEHP, BBP and DBP through entry 51 of Annex XVII to Regulation (EC) No 1907/2006.

SIGNED FOR AND ON BEHALF OF SGS (MALAYSIA) SDN BHD

TECHNICAL MANAGER
IKM No. M/3452/6047/11/12

TAY SIAM PINE

Test Report Form No.: SGS/TR/CRS/013, Ver: 4.0, Effective Date: 12/07/2019

Page 4 of 8

10871



Job Ref. CRS/2019-09-11-034

TEST RESULTS BY CHEMICAL METHOD:

Test Part Description

Sample Description: -PLEASE REFER TO PAGE 1-

Test Item(s):	Unit	Test Method	Result	MDL
Halogen	-	-	-	-
Halogen-Bromine (Br)	mg/kg	With reference to BS EN 14582:2016, analysis performed by IC method for Bromine content.	N.D.	50
Halogen-Chlorine (CI)	mg/kg	With reference to BS EN 14582:2016, analysis performed by IC method for Chlorine content.	N.D.	50

Note: (a) mg/kg = ppm; ug/kg = ppb (0.01 mg/kg = 10 ug/kg); 0.1wt% = 1000ppm

(b) N.D. = Not Detected

(c) MDL = Method Detection Limit

(d) Negative = Undetectable / Positive = Detectable

SIGNED FOR AND ON BEHALF OF SGS (MALAYSIA) SDN BHD

TAY SIAM FINE
TECHNICAL MANAGER

IKM No. M/3452/6047/11/12

Test Report Form No.: SGS/TR/CRS/013, Ver: 4.0, Effective Date: 12/07/2019

Page 5 of 8



Job Ref. CRS/2019-09-11-034

Test Part Description:

Sample Description: -PLEASE REFER TO PAGE 1-

SGS authenticate the photo on original report only

SIGNED FOR AND ON BEHALF OF SGS (MALAYSIA) SDN BHD

TECHNICAL MANAGER
IKM No. M/3452/6047/11/12

TAY SIAM PINE

Test Report Form No.: SGS/TR/CRS/013, Ver: 4.0, Effective Date: 12/07/2019

Page 6 of 8



TEST REPORT:

No. CRSSA/190921729-CA20950 Job Ref. CRS/2019-09-11-034

1. DETERMINATION OF CADMIUM CONTENT BY IEC 62321-52013

Sample Receiving and Registration

Sample Preparation

Weigh sample (0.2-0.5g) into digestion vessel

Acid digestion (Microwave)

"Totally Dissolved"

Filtration

Analyses by ICP

2. DETERMINATION OF LEAD CONTENT BY IEC 62321-52013

REPORTED DATE: 23/09/2019

Sample Receiving and Registration

Sample Preparation

Weigh sample (0.2-0.5g) into digestion vessel

Acid digestion (Microwave)

"Totally Dissolved"

Filtration

Analyses by ICP

3. DETERMINATION OF MERCURY CONTENT BY IEC 62321-42013/AMD12017

Sample Receiving and Registration

Sample Preparation

Weigh sample (0.1-0.5g) into digestion vessel

Acid digestion(Microwave)

"TotallyDissolved"

Filtration

Analyses by ICP

4a. DETERMINATION OF HEXAVALENT CHROMIUM BY IEC 62321-7-22017 (Other Materials)

Sample Preparation

Digestionat 150~160°C

Separating to Obtain Aqueous Phase

pH Adjustment

Add Diphenyl-Carbazide for Color Development

Analyses by UV-Spectrophotometer (540 nm)

4b. DETERMINATION OF HEXAVALENT CHROMIUM BY IEC 62321-7-22017 (Soluble Polymers)

Sample Preparation

Add Digestion Solution

Ultrasonicate Sample

pH Adjustment

Add Diphenyl-Carbazide for Colour Development

Analyses by UV-Spectrophotometer (540 nm)

5. DETERMINATION OF PBB/PBDE WITH GC-MS BY IEC 62321-62015

Sample Preparation

Weigh sample (0.5-4.0g) into extraction thimble

Soxhlet Extraction with Toluene

Filter through 0.45 um membrane filter

Analyses by GC-MS (with appropriate dilution)

SIGNED FOR AND ON BEHALF OF

SIGNED FOLKAGE
SGS (MALAYSIA) SDN BHD 10871-TAY SIAM PINE TECHNICAL MANAGER IKM No. M/3452/6047/11/12

Test Report Form No.: SGS/TR/CRS/013, Ver: 4.0, Effective Date: 12/07/2019

Page 7 of 8

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at https://www.sgs.com/en/terms-and-conditions and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at https://www.sgs.com/en/terms-and-conditions/terms-e-document. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise states shown in this test report refer only to the sample(s) tested and such sample(s) are retained for 14 days (for perishable samples) or 90 days only.



TEST REPORT:

No. CRSSA/190921729-CA20950 Job Ref. CRS/2019-09-11-034

DETERMINATION OF PHTHALATES WITH GC-MS BY IEC 62321-8:2017 Sample Cutting / Preparation ↓ Sample Measurement ↓ Solvent Extraction ↓ Concentrate / Dilute extracted solution ↓ GC-MS analysis ↓

DETERMINATION OF HALOGEN CONTENT

DATA

Sample pre-treatment

Weighting and putting sample in cell

Combustion / Absorption

Dilution to fixed volume

Analyses by IC

SIGNED FOR AND ON BEHALF OF SGS (MALAYSIA) SDN BHD

TAY SIAM PINE
TECHNICAL MANAGER
IKM No. M/3452/6047/11/12

Test Report Form No.: SGS/TR/CRS/013, Ver: 4.0, Effective Date: 12/07/2019

*** End of test report ***

Page 8 of 8

REPORTED DATE: 23/09/2019

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at https://www.sgs.com/en/terms-and-conditions and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at https://www.sgs.com/en/terms-e-document. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction of exercising all their rights and obligations under the transaction documents. This document cannot be reproduced except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested and such sample(s) are retained for 14 days (for perishable samples) or 90 days only.