

Test Report No. F690101/LF-CTSAYAA22-14276

DUK SAN HI-METAL CO., LTD.

66, Muryong 1-ro Buk-gu, Ulsan Korea

The following sample(s) was/were submitted and identified by/on behalf of the client as:-

SGS File No. : AYAA22-14276

Product Name : Sn0.7Cu

Item No./Part No. : N/A

Received Date : 2022. 03. 22

Test Period : 2022. 03. 22 to 2022. 03. 25

Test Results : For further details, please refer to following page(s)

SGS Korea Co., Ltd.

Page 1 of 3

Issued Date: 2022. 03. 25

Tommy Oh / Chemical Lab Mgr

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at https://www.sgs.com/en/Terms-and-Conditions.aspx and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at https://www.sgs.com/en/terms-and-conditions/terms-e-document. Attention is drawn to the limitation of Libbility, indempitication and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced except in full, without prior written approval of the Company. Any unauthorized alteration, forgety or falsilication of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report reference only to the sample(s).



Test Report No. F690101/LF-CTSAYAA22-14276

Sample No. : AYAA22-14276.001

Sample Description : Sn0.7Cu Item No./Part No. : N/A Materials : N/A

Halogen Content

- Indiagon Conton				
Test Items	Unit	Test Method	MDL	Results
Bromine(Br)	mg/kg	With reference to BS EN 14582 : 2016, by IC	30	N.D.
Chlorine(Cl)	mg/kg	With reference to BS EN 14582 : 2016, by IC	30	N.D.
Fluorine(F)	mg/kg	With reference to BS EN 14582 : 2016, by IC	30	N.D.
lodine(I)	mg/kg	With reference to BS EN 14582 : 2016, by IC	50	N.D.


Issued Date: 2022. 03. 25

Page 2 of 3

NOTE: (1) N.D. = Not detected. (<MDL)

- (2) mg/kg = ppm, ug/kg = ppb, mg/L = ppm
- (3) MDL = Method Detection Limit
- (4) = No regulation
- (5) ** = Qualitative analysis (No Unit)
- (6) Negative = Undetectable / Positive = Detectable
- (7) The results shown in this test report refer only to the sample(s) tested unless otherwise stated.

This test report is not related to Korea Laboratory Accreditation Scheme.




This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at https://www.sgs.com/en/Terms-and-Conditions.aspx and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at https://www.sgs.com/en/terms-and-conditions/terms-e-document. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s).



Test Report No. F690101/LF-CTSAYAA22-14276

Page 3 of 3

Flow Chart for Halogen Test



Issued Date: 2022. 03. 25

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at https://www.sgs.com/en/Terms-and-Conditions.aspx and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at https://www.sgs.com/en/Terms-and-conditions/terms-e-document. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s).