

PART INFORMATION

Mfg Item Number	SP5746CSK1AMMJ6R
Mfg Item Name	MAPBGA 256 17*17*1.7P1.0

SUPPLIER

Company Name	Freescale Semiconductor Inc
Company Unique ID	14-141-7928
Response Date	2018-04-23
Response Document ID	00A9K00188D009A1.5
Contact Name	Freescale Semiconductor Inc
Contact Title	Product Technical Support
Contact Phone	1-800-521-6274
Contact Email	support@freescale.com
Authorized Representative	Daniel Binyon
Representative Title	EPP Customer Response
Representative Phone	512-895-3406
Representative Email	eppanlst@freescale.com
URL for Additional Information	www.freescale.com

DECLARATION

EU RoHS	Yes
Pb Free	Yes
HalogenFree	Yes
Plating Indicator	e2
EU RoHS Exemption(s)	

MANUFACTURING

Mfg Item Number	SP5746CSK1AMMJ6R
Mfg Item Name	MAPBGA 256 17*17*1.7P1.0
Version	ALL
Weight	0.617600
UoM	g
Unit Volume	EACH
J-STD-020 MSL Rating	3
Peak Processing Temperature	260 C
Max Time at Peak Temperature	40 seconds
Number of Processing Cycles	3

RoHS	
RoHS Directive	2011/65/EU
RoHS Definition	RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) of homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material of Cadmium
RoHS Legal Definition	Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part(s) identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a RoHS restricted substance) in excess of the applicable quantity limit identified below. If a homogeneous material within the part(s) contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Suppliers Standard Terms and Conditions of Sale applicable to such part(s) shall apply.
RoHS Declaration	1 - Item(s) do not contain RoHS restricted substances per the definition above
Supplier Acceptance	Accepted
Signature	Daniel Binyon
Exemption List Version	2012/51/EU
List of Freescale Accepted Exemptions	<p>6(a) : Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight</p> <p>6(b) : Lead as an alloying element in aluminium containing up to 0.4% lead by weight</p> <p>6(c) : Copper alloy containing up to 4% lead by weight</p> <p>7(a) : Lead in high melting temperature type solders (i.e. lead-based alloys containing 85% by weight or more lead)</p> <p>7(b) : Lead in solders for servers, storage and storage array systems, network infrastructure equipment for switching, signaling, transmission, and network management for telecommunications</p> <p>7(c)-I : Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound</p> <p>7(c)-II : Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher</p> <p>7(c)-III : Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC</p> <p>7(c)-IV : Lead in PZT based dielectric ceramic materials for capacitors being part of integrated circuits or discrete semiconductors</p> <p>15 : Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit flip chip packages</p>

MATERIAL COMPOSITION

Homogeneous Material	Weight	SubstanceClass	Substance	CAS	Exemption	SubstanceWeight	UoM	SubPart PPM	SubPart%	ARTICLEPPM	ARTICLE%
Non-Conductive Epoxy/Adhesive	0.0028						g				
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Proprietary Material-Other Epoxy resins	-		0.00021	g	75000	7.5	340	0.034
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Crosslinked acrylate polymer	25767-43-5		0.00056	g	200000	20	906	0.0906
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Other polymers	-		0.00021	g	75000	7.5	340	0.034
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Proprietary Material-Other polymers	-		0.00056	g	200000	20	906	0.0906
Non-Conductive Epoxy/Adhesive		Glass	Silica, vitreous	60676-86-0		0.00126	g	450000	45	2040	0.204
Solder Balls - Pb Free, Sn/Ag	0.031						g				
Solder Balls - Pb Free, Sn/Ag		Metals	Aluminum, metal	7429-90-5		0.0000099	g	32	0.0032	1	0.0001
Solder Balls - Pb Free, Sn/Ag		Antimony/Antimony Compounds	Antimony (metallic)	7440-36-0		0.0000388	g	125	0.0125	6	0.0006
Solder Balls - Pb Free, Sn/Ag		Arsenic/Arsenic Compounds	Arsenic	7440-38-2		0.0000233	g	75	0.0075	3	0.0003
Solder Balls - Pb Free, Sn/Ag		Bismuth/Bismuth Compounds	Bismuth	7440-69-9		0.0000583	g	188	0.0188	9	0.0009
Solder Balls - Pb Free, Sn/Ag		Cadmium/Cadmium Compounds	Cadmium	7440-43-9		0.0000004	g	13	0.0013	0	0
Solder Balls - Pb Free, Sn/Ag		Metals	Copper, metal	7440-50-8		0.0000195	g	63	0.0063	3	0.0003
Solder Balls - Pb Free, Sn/Ag		Metals	Gold, metal	7440-57-5		0.0000195	g	63	0.0063	3	0.0003
Solder Balls - Pb Free, Sn/Ag		Metals	Indium, metal	7440-74-6		0.0000195	g	63	0.0063	3	0.0003
Solder Balls - Pb Free, Sn/Ag		Solvents, additives, and other materials	Sulfur	7704-34-9		0.0000022	g	7	0.0007	0	0
Solder Balls - Pb Free, Sn/Ag		Solvents, additives, and other materials	Phosphorus, elemental (not containing red allotrope)	7723-14-0		0.0000195	g	63	0.0063	3	0.0003
Solder Balls - Pb Free, Sn/Ag		Metals	Iron, metal	7439-89-6		0.0000388	g	125	0.0125	6	0.0006
Solder Balls - Pb Free, Sn/Ag		Lead/Lead Compounds	Lead	7439-92-1		0.0000097	g	313	0.0313	15	0.0015
Solder Balls - Pb Free, Sn/Ag		Nickel (external applications only)	Nickel	7440-02-0		0.0000099	g	32	0.0032	1	0.0001
Solder Balls - Pb Free, Sn/Ag		Metals	Silver, metal	7440-22-4		0.0018506	g	35002	3.5002	1756	0.1756
Solder Balls - Pb Free, Sn/Ag		Metals	Tin, metal	7440-31-5		0.02987833	g	963817	96.3817	48378	4.8378
Solder Balls - Pb Free, Sn/Ag		Metals	Zinc, metal	7440-66-6		0.0000059	g	19	0.0019	0	0
Die Encapsulant, Halogen-free	0.342						g				
Die Encapsulant, Halogen-free		Plastics/polymers	Other Epoxy resins	-		0.02052	g	60000	6	33225	3.3225
Die Encapsulant, Halogen-free		Solvents, additives, and other materials	Carbon Black	1333-86-4		0.00342	g	10000	1	5537	0.5537
Die Encapsulant, Halogen-free		Solvents, additives, and other materials	Other inorganic compounds.	-		0.00684	g	20000	2	11075	1.1075
Die Encapsulant, Halogen-free		Plastics/polymers	Other phenolic resins	-		0.0171	g	50000	5	27687	2.7687
Die Encapsulant, Halogen-free		Glass	Silica, vitreous	60676-86-0		0.29412	g	860000	86	476252	47.6252
Organic Substrate	0.2073						g				
Organic Substrate		Solvents, additives, and other materials	Other aromatic amines and their salts	-		0.00003731	g	180	0.018	60	0.006
Organic Substrate		Metals	Barium sulfate	7727-43-7		0.00126142	g	6085	0.6085	2042	0.2042
Organic Substrate		Metals	Copper, metal	7440-50-8		0.0942948	g	454871	45.4871	152679	15.2679
Organic Substrate		Plastics/polymers	Phenolic Polymer Resin, Epikote 155	9003-36-5		0.003268	g	16247	1.6247	5453	0.5453
Organic Substrate		Plastics/polymers	Other Epoxy resins	-		0.0081699	g	39411	3.9411	13228	1.3228
Organic Substrate		Metals	Gold, metal	7440-57-5		0.00298657	g	14407	1.4407	4835	0.4835
Organic Substrate		Metals	Talc	14807-96-6		0.00063537	g	3065	0.3065	1028	0.1028
Organic Substrate		Nickel (external applications only)	Nickel	7440-02-0		0.0233084	g	112438	11.2438	37740	3.774
Organic Substrate		Glass	Fibrous-glass-wool	65997-17-3		0.04635726	g	223624	22.3624	75060	7.506
Organic Substrate		Glass	Silicon dioxide	7631-86-9		0.00608197	g	29339	2.9339	9847	0.9847
Organic Substrate		Solvents, additives, and other materials	Other Aromatic carbonyl compounds	-		0.0022632	g	1140	0.114	382	0.0382
Organic Substrate		Plastics/polymers	Triazine	25722-66-1		0.003268	g	16247	1.6247	5453	0.5453
Organic Substrate		Metals	Aluminum Hydroxide	21645-51-2		0.0083915	g	40480	4.048	13587	1.3587
Organic Substrate		Metals	Copper phthalocyanine	147-14-8		0.00001119	g	54	0.0054	18	0.0018
Organic Substrate		Solvents, additives, and other materials	Quinacridone pigment	1047-16-1		0.00001119	g	54	0.0054	18	0.0018
Organic Substrate		Solvents, additives, and other materials	3-methoxy-3-methyl-1-butyl acetate	103429-90-9		0.00138331	g	6673	0.6673	2239	0.2239
Organic Substrate		Solvents, additives, and other materials	Bis(3-ethyl-5-methyl-4-maleimidophenyl)methane	105391-33-1		0.003368	g	16247	1.6247	5453	0.5453
Organic Substrate		Plastics/polymers	Epoxy Resin	115254-47-2		0.0040183	g	19384	1.9384	6506	0.6506
Organic Substrate		Solvents, additives, and other materials	1,2,4-Trimethylbenzene	95-63-6		0.00001119	g	54	0.0054	18	0.0018
Bonding Wire, PdCu	0.0046						g				
Bonding Wire, PdCu		Metals	Copper, metal	7440-50-8		0.0045126	g	981000	98.1	7306	0.7306
Bonding Wire, PdCu		Metals	Gold, metal	7440-57-5		0.0000046	g	1000	0.1	7	0.0007
Bonding Wire, PdCu		Metals	Palladium, metal	7440-05-3		0.0000828	g	18000	1.8	134	0.0134
Silicon Semiconductor Die	0.0299						g				
Silicon Semiconductor Die		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%)	-		0.000598	g	20000	2	968	0.0968
Silicon Semiconductor Die		Glass	Silicon, doped	-		0.029302	g	980000	98	47444	4.7444

LINKS

MCD LINK	
NXP website	http://www.nxp.com
GENERAL ENVIRONMENTAL COMPLIANCE LINKS	
RoHS signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-ROHS-DECLARATION.pdf
China RoHS	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/china-rohs:ENV_CHINA_ROHS_STRATEGY
REACH signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-REACH-STATEMENT.pdf
ELV signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-ELV-STATEMENT.pdf
Conflict Minerals statement	http://www.nxp.com/files/corporate/doc/support_info/NXP-STATEMENT-CONFLICT-MINERALS.pdf
NXP ENVIRONMENTAL INFORMATION	
Environmental Compliance website	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization:ABUENVPRFPRDX
FAQ	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/eco-product-faqs:ENVIRON_FAQ
Technical Service Request	http://www.nxp.com/support/sales-and-support:SUPPORTHOME
LINKS TO BLANK IPC1752 FORMS	
Blank IPC1752 v1.1 Form	http://www.NXP.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf

IPC1752 XML LINKS

http://www.freescale.com/mcdfs/SP5746CSK1AMMJ6R_IPC1752_v11.xml

http://www.freescale.com/mcdfs/SP5746CSK1AMMJ6R_IPC1752A.xml