

检测报告
Test Report报告编号 A2250064266101002E
Report No. A2250064266101002E第 1 页 共 5 页
Page 1 of 5

报告抬头公司名称 西安宏星电子浆料科技股份有限公司
Company Name XI'AN HONGXING ELECTRONIC PASTE TECHNOLOGIES CO.,LTD.
shown on Report
地 址 陕西省西安市长安区定昆池三路1099号
Address 1099 DINGKUNCHI THIRD ROAD,CHANG'AN DISTRICT,XI'AN CITY,SHAANXI PROVINCE

以下测试之样品及样品信息由申请者提供并确认

The following sample(s) and sample information was/were submitted and identified by/on the behalf of the applicant

样品名称 C-1002(A-Z)
Sample Name C-1002(A-Z)
样品型号 C-1002(A-Z)
Model No. C-1002(A-Z)
样品批号 501-04-10
Lot No. 501-04-10
样品接收日期 2025.02.10
Sample Received Date Feb. 10, 2025
样品检测日期 2025.02.10-2025.02.14
Testing Period Feb. 10, 2025 to Feb. 14, 2025

检测要求 根据客户要求, 对所提交样品中的砷(As), 铍(Be), 锑(Sb)进行测试。
Test Requested As specified by client, to test Arsenic(As), Beryllium(Be), Antimony(Sb) in the submitted sample(s).

检测依据/检测结果 请参见下页。
Test Method/Test Result(s) Please refer to the following page(s).



郑晴涛

技术经理 Technical Manager

CTI Building, Xing Dong Community, Xin'an Sub-district, Bao'an District, Shenzhen City, Guangdong Province, P.R. China

日 期
Date

2025.02.14

No. R812811706

广东省深圳市宝安区新安街道兴东社区华测检测大楼

检测报告
Test Report

报告编号 A2250064266101002E

Report No. A2250064266101002E

第 2 页 共 5 页

Page 2 of 5

检测依据 Test Method

测试项目 Test Item(s)	测试方法 Test Method	测试仪器 Measured Equipment(s)
砷 Arsenic(As)	参考US EPA 3052:1996 & US EPA 6010D:2018 Refer to US EPA 3052:1996 & US EPA 6010D:2018	ICP-OES
铍 Beryllium(Be)	参考US EPA 3052:1996 & US EPA 6010D:2018 Refer to US EPA 3052:1996 & US EPA 6010D:2018	ICP-OES
锑 Antimony(Sb)	参考US EPA 3052:1996 & US EPA 6010D:2018 Refer to US EPA 3052:1996 & US EPA 6010D:2018	ICP-OES

检测结果 Test Result(s)

测试项目 Tested Item(s)	结果 Result	方法检出限 MDL
	002	
砷 Arsenic (As)	N.D.	10 mg/kg
铍 Beryllium (Be)	N.D.	2 mg/kg
锑 Antimony (Sb)	N.D.	5 mg/kg

样品/部位描述 Sample/Part Description

序号 No.	CTI样品ID CTI Sample ID	描述 Description
1	002	米灰色膏体 (干重) Beige grey paste(dry weight)

备注: -对于检测砷, 铍, 锑之样品已消解完全。

-测试样品经过105℃烘烤2小时后测试。

-N.D. = 未检出 (小于方法检出限)

-mg/kg = ppm = 百万分之一

Remark: -The sample(s) had been dissolved totally tested for Arsenic, Beryllium, Antimony.

-The sample was tested after drying for 2 hours under 105 °C.

-MDL = Method Detection Limit

-N.D. = Not Detected (<MDL)

-mg/kg = ppm = parts per million

注释: 本报告中的数据结果供科研、教学、企业内部质量控制、企业产品研发等目的用。

Note: The testing data and result(s) in this report is(are) just for scientific research, education, internal quality control and product development etc.

检测报告 Test Report


报告编号 A2250064266101002E

Report No. A2250064266101002E

第 3 页 共 5 页

Page 3 of 5

检测流程 Test Process



检测报告 Test Report

报告编号 A2250064266101002E
Report No. A2250064266101002E

第 4 页 共 5 页
Page 4 of 5

样品图片 Photo(s) of the sample(s)

烘干前 Before drying



烘干后 After drying



检测报告 Test Report

报告编号 A2250064266101002E

Report No. A2250064266101002E

第 5 页 共 5 页

Page 5 of 5

声明 Statement:

1. 检测报告无批准人签字、“专用章”及报告骑缝章无效;
This report is considered invalid without approved signature, special seal and the seal on the perforation;
2. 报告抬头公司名称及地址、样品及样品信息由申请者提供, 申请者应对其真实性负责, CTI未核实其真实性;
The Company Name shown on Report and Address, the sample(s) and sample information was/were provided by the applicant who should be responsible for the authenticity which CTI hasn't verified;
3. 本报告检测结果仅对受测样品负责;
The result(s) shown in this report refer(s) only to the sample(s) tested;
4. 除非另有说明, 报告参照ILAC-G8:09/2019 / CNAS-GL015:2022使用简单接受(w=0)二元判定规则进行符合性判定;
Unless otherwise stated, the decision rule for conformity reporting is based on Binary Statement for Simple Acceptance Rule (w=0) stated in ILAC-G8:09/2019 / CNAS-GL015:2022;
5. 未经CTI书面同意, 不得部分复制本报告;
Without written approval of CTI, this report can't be reproduced except in full;
6. 如检测报告中的英文内容与中文内容有差异, 以中文为准。
In case of any discrepancy between the English version and Chinese version of the testing reports (if generated), the Chinese version shall prevail.

报告结束

*** End of report ***

