









Page 1 of 7

**Company Name** 

ACKOTEC (ZHONG SHAN) ELECTRONIC PARTS CO., LTD.

shown on Report

Report No.

**Address** JU YE ROAD, ZHANGJIABIAN, TORCH DEVELOPMENT ZONE, ZHONGSHAN

CITY, GUANGDONG PROVINCE

The following sample(s) and sample information was/were submitted and identified by/on the behalf

of the applicant

Sample Name Silver plating solution

A2220510929101002

Sample Received Date Nov. 14, 2022

**Testing Period** Nov. 14, 2022 to Nov. 17, 2022

As specified by client, to test Lead (Pb), Cadmium (Cd), Mercury (Hg), **Test Requested** 

Hexavalent Chromium (Cr(VI)), Polybrominated Biphenyls (PBBs),

Polybrominated Diphenyl Ethers (PBDEs), Phthalates (DBP, BBP, DEHP, DIBP),

Beryllium(Be), Antimony(Sb) in the submitted sample(s).

**Test Method** Please refer to the following page(s).

Please refer to the following page(s). Test Result(s)

Conclusion

**Tested Sample** According to standard/directive Result **PASS** Submitted Sample RoHS Directive 2011/65/EU with amendment (EU) 2015/863

\*

PASS means that the results shown on the report comply with the limits set by RoHS Directive 2011/65/EU with amendment (EU) 2015/863.

ting Liternational Group Co.,Ltd.

Helen Liu Lab Authorized Signatory Reviewed by

Date

Nov. 17, 2022

Cathy Huang

No. R262624809



**Report No.** A2220510929101002 Page 2 of 7

**Test Method** 

Test Item(s)	Test Method	Measured Equipment(s)	
Lead (Pb)	IEC 62321-5:2013	ICP-OES	
Cadmium (Cd)	IEC 62321-5:2013	ICP-OES	
Mercury (Hg)	IEC 62321-4:2013+AMD1:2017 CSV	ICP-OES	
Hexavalent Chromium (Cr(VI))	IEC 62321-7-2:2017 and/or determination of Total Chromium by IEC 62321-5:2013	UV-Vis/ICP-OES	
Polybrominated Biphenyls (PBBs)	IEC 62321-6:2015	GC-MS	
Polybrominated Diphenyl Ethers (PBDEs)	IEC 62321-6:2015	GC-MS	
Phthalates (DBP, BBP, DEHP, DIBP)	IEC 62321-8:2017	GC-MS	
Beryllium(Be)	Refer to US EPA 3052:1996 & US EPA 6010D:2018	ICP-OES	
Antimony(Sb)	Refer to US EPA 3052:1996 & US EPA 6010D:2018	ICP-OES	

Hotline:400-6788-333 www.cti-cert.com E-mail:info@cti-cert.com Complaint call:0755-33681700 Complaint E-mail:complaint@cti-cert.com



**Report No.** A2220510929101002

Page 3 of 7

Test Result(s)

Tested Item(s)	Result	MDL	Limit
Lead (Pb)	N.D.	2 mg/kg	1000 mg/kg
Cadmium (Cd)	N.D.	2 mg/kg	100 mg/kg
Mercury (Hg)	N.D.	2 mg/kg	1000 mg/kg
Hexavalent Chromium (Cr(VI))	N.D.	8 mg/kg	1000 mg/kg
Tested Item(s)	Result	MDL	Limit
Polybrominated Biphenyls (PBBs)			
Monobromobiphenyl	N.D.	5 mg/kg	
Dibromobiphenyl	N.D.	5 mg/kg	
Tribromobiphenyl	N.D.	5 mg/kg	1000 mg/kg
Tetrabromobiphenyl	N.D.	5 mg/kg	
Pentabromobiphenyl	N.D.	5 mg/kg	
Hexabromobiphenyl	N.D.	5 mg/kg	
Heptabromobiphenyl	N.D.	5 mg/kg	
Octabromobiphenyl	N.D.	5 mg/kg	
Nonabromobiphenyl	N.D.	5 mg/kg	
Decabromobiphenyl	N.D.	5 mg/kg	
Tested Item(s)	Result	MDL	Limit
Polybrominated Diphenyl Ethers (PBDEs)			
Monobromodiphenyl ether	N.D.	5 mg/kg	
Dibromodiphenyl ether	N.D.	5 mg/kg	
Tribromodiphenyl ether	N.D.	5 mg/kg	
Tetrabromodiphenyl ether	N.D.	5 mg/kg	
Pentabromodiphenyl ether	N.D.	5 mg/kg	1000 mg/kg
Hexabromodiphenyl ether	N.D.	5 mg/kg	
Heptabromodiphenyl ether	N.D.	5 mg/kg	
Octabromodiphenyl ether	N.D.	5 mg/kg	
Nonabromodiphenyl ether	N.D.	5 mg/kg	
Decabromodiphenyl ether	N.D.	5 mg/kg	



**Report No.** A2220510929101002

Page 4 of 7

Test Result(s)

Tested Item(s)	Result	MDL		Limit		
Phthalates (DBP, BBP, DEHP, DIBP)						
Dibutyl phthalate (DBP) CAS#:84-74-2	N.D.	50 mg/kg		1000 mg/kg		
Butyl benzyl phthalate (BBP) CAS#:85-68-7	N.D.	50 mg/kg		1000 mg/kg		
Di-(2-ethylhexyl) phthalate (DEHP) CAS#:117-81-7	N.D.	50 mg/kg		1000 mg/kg		
Diisobutyl phthalate (DIBP) CAS#:84-69-5	N.D.	50 mg/kg		1000 mg/kg		
Tested Item(s)	Result			MDL		
Beryllium (Be)	N.D.			2 mg/kg		
Antimony (Sb)	N.D.			5 mg/kg		

Sample/Part Description

Light blue liquid

Remark:

The sample(s) had been dissolved totally tested for Lead, Cadmium, Mercury,

Beryllium, Antimony.

-MDL = Method Detection Limit

-N.D. = Not Detected (< MDL)

-mg/kg = ppm = parts per million


-1000 mg/kg = 0.1%




Page 5 of 7 Report No. A2220510929101002

#### **Test Process**

#### 1. Lead (Pb), Cadmium (Cd), Chromium (Cr)




#### Mercury (Hg)




TO TOUT CO. / STEE ST


#### 3. Hexavalent Chromium (Cr(VI))



#### 4. Polybrominated Biphenyls (PBBs), Polybrominated Diphenyl Ethers (PBDEs)











Report No. A2220510929101002 Page 7 of 7

### Photo(s) of the sample(s)



#### Statement:

- This report is considered invalid without approved signature, special seal and the seal on the perforation;
- The Company Name shown on Report and Address, the sample(s) and sample information was/were provided by the applicant who should be responsible for the authenticity which CTI hasn't verified;
- The result(s) shown in this report refer(s) only to the sample(s) tested;
- Without written approval of CTI, this report can't be reproduced except in full;
- In case of any discrepancy between the English version and Chinese version of the testing reports (if generated), the Chinese version shall prevail.

\*\*\* End of report \*\*\*