

MPF5020CMMACES – NXP Standard

Configuration report for PF5020-QM OTP program ID: AC rev A

Rev. 1.0 - 2021/6/24

Report

1 General description

The PF5020 is a power management integrated circuit (PMIC) featuring multiple high efficiency buck regulators designed to operate as a stand alone regulator or as a companion chip to a larger PMIC.

Built-in one time programmable memory stores key startup configurations, drastically reducing external components typically used to set output voltage and sequence of external regulators. Regulator parameters are adjustable through high-speed I2C after start up offering flexibility for different system states.

Note: Electrical characteristics are maintained in the PF5020 data sheet.

2 Features and benefits

- Up to three high efficiency buck converters
- One linear regulators with load switch options
- RTC supply and coin cell charger
- Watchdog timer/monitor
- Independent Voltage Monitoring circuit
- One time programmable device configuration
- 3.4 MHz I2C communication interface
- 40-pin QFN package with wettable flank and exposed pad

3 Applications

- Automotive Infotainment
- High - End Industrial

4 Ordering information


Table 1. Ordering information

Type number ^[1]	Package		
	Name	Description	Version
MPF5020CMMACES	HVQFN40	HVQFN40, plastic, thermally enhanced very thin quad flat pack; non-leaded wettable flank, 40 terminals; 0.5 mm pitch; 6 mm x 6 mm x 0.9 mm body	SOT618-17(D)


[1] To order parts in tape and reel, add the R2 suffix to the part number.



5 Power-up sequence summary



6 Hardware configuration diagram



7 System configuration

See PF5020 datasheet for parametric details. The OTP configuration summary for AC sequence ID is provided in Tables below.

Table 2. Device OTP configuration

Functional block	Feature	OTP selection
I2C Settings	I2C address	0x08
	I2C CRC	Disabled
VIN OV lockout	VIN_OVLO Mode	Enabled
	VIN_OVLO shutdown	Device Shutdown upon a VIN_OVLO
	VIN_OVLO debounce	100 us
Power good	PG check on power up	PG not checked at power up
	PG active mode	PGOOD mode
PWRON control	Power on event detection	Level sensitive mode
	PWRON debounce	32 ms
	TRESET time	2 s
	TRESET behavior	PMIC shuts down after push button pressed
STANDBY control	STANDBY polarity	Active High
EWARN timer	EWARN delay	100 us
XFAIL pin	XFAIL operation	Disabled
WDI control	WDI reset type	Hard WD Reset
	WDI polarity	Falling edge of WDI
	WDI detection in standby	Disabled in STBY
WD timer control	WD timer	WD Timer Disabled
	WD clear window	Cleared within 100%
	WD window duration	1 ms

Configuration report for PF5020-QM OTP program ID: AC rev A

	WD expire number	Event on step 1
	Maximum WD event counter	1 Event
	WD detection in standby	Disabled in STBY
Frequency control	Nominal switching frequency	2.50 MHz
	Switching Mode	PWM
	FSYNC mode	SYNCOUT
	SYNCIN range	2000KHz to 3000KHz
	SYNCOUT operation	Disabled
	Frequency spread spectrum	Disabled
	FSS range	+/- 5%

Table 3. OTP fault management configuration

Functional block	Feature	OTP selection
Fault management	Fault timer	1 ms
	Maximum fault counter	Disabled

Table 4. Sequencer OTP configuration

Functional block	Feature	OTP selection
Power up sequencing	Sequence TBASE	500 us
	RESETBMCU sequence slot	Slot 14
	PGOOD sequence slot	OFF
	SW1 sequence slot	Slot 13
	SW2 sequence slot	Slot 3
	SWND1 sequence slot	Slot 1
	LDO1 sequence slot	Slot 6
Power down sequencing	Power down mode	Mirror power down
	RESETBMCU Power down	Group 4

Configuration report for PF5020-QM OTP program ID: AC rev A

	PGOOD Power down group	Group 4
	SW1 Power down group	Group 4
	SW2 Power down group	Group 4
	SWND1 Power down group	Group 4
	LDO1 Power down group	Group 4
	RESETBMCU group delay	No delay
	Group 1 power down delay	120 us
	Group 2 power down delay	120 us
	Group 3 power down delay	120 us
	Group 4 power down delay	120 us
	Power down delay	No delay
	VTT power down	High impedance

Table 5. Regulator OTP configuration

Functional block	Feature	OTP selection
SW1	Output voltage	1.12500 V
	Current limit	4.5 A
	OV detection threshold	107 %
	UV detection threshold	93 %
	DVS ramp	3.91 mV/us
	Switching phase	45°
	Output inductor	1 uH (Default)
	PGOOD mode	Enabled
	SW1 WD Bypass	Bypass WDI
	SW1 OV Bypass	OV protection enabled

Configuration report for PF5020-QM OTP program ID: AC rev A

	SW1 UV Bypass	UV protection enabled
	SW1 ILIM Bypass	ILIM protection enabled
	SW1 Transconductance	65 umho
	SW1 multi-phase selector	SW1 and SW2 single phase
SW2	Output voltage	1.80000 V
	Current limit	4.5 A
	OV detection threshold	107 %
	UV detection threshold	93 %
	DVS ramp	3.91 mV/us
	Switching phase	90°
	Output inductor	1 µH (Default)
	VTT mode	Disabled
	PGOOD mode	Enabled
	SW2 WD Bypass	Bypass WDI
	SW2 OV Bypass	OV protection enabled
	SW2 UV Bypass	UV protection enabled
	SW2 ILIM Bypass	ILIM protection enabled
	SW2 Transconductance	65 umho
SWND1	Output voltage	3.30 V
	Current limit	4.5A
	OV detection threshold	107%
	UV detection threshold	93%
	Switching phase	135°
	Output inductor	1 uH (Default)

Configuration report for PF5020-QM OTP program ID: AC rev A

	PGOOD mode	Enabled
	SWND1 WD Bypass	Bypass WDI
	SWND1 OV Bypass	OV protection enabled
	SWND1 UV Bypass	UV protection enabled
	SWND1 ILIM Bypass	ILIM protection enabled
	SWND1 Transconductance	65 umho
	SWND1 resistance	56 KΩ
LDO1	Output voltage	2.8 V
	OV detection threshold	107 %
	UV detection threshold	93 %
	Operating mode	Normal Mode
	PGOOD mode	Enabled
	LDO1 WD Bypass	Bypass WDI
	LDO1 OV Bypass	OV protection enabled
	LDO1 UV Bypass	UV protection enabled
	LDO1 ILIM Bypass	ILIM protection enabled
VSNVS	Output voltage	3.3 V
PROGRAM ID	Program ID High	A
	Program ID Low	C

8 Legal information

8.1 Definitions

Draft - The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Limited warranty and liability - Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. NXP Semiconductors takes no responsibility for the content in this document if provided by an information source outside of NXP Semiconductors. In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory. Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of NXP Semiconductors.

Right to make changes - NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use - NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors and its suppliers accept no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications - Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification. Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products. NXP Semiconductors does not accept any liability related to any default, damage, costs or problem

which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

Limiting values - Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale - NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at <http://www.nxp.com/profile/terms>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors here by expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

No offer to sell or license - Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Suitability for use in automotive applications - This NXP Semiconductors product has been qualified for use in automotive applications. Unless otherwise agreed in writing, the product is not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors and its suppliers accept no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Export control - This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Translations - A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

8.2 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

NXP - is a trademark of NXP B.V.

Contents

1 General description	1
2 Features and benefits	1
3 Applications	1
4 Ordering information	1
5 Power up sequence summary	2
6 Hardware configuration diagram	2
7 OTP configuration	3
8 Legal information	8

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

© NXP B.V. 2021 .

All rights reserved.

For more information, please visit: <http://www.nxp.com>

For sales office addresses, please send an email to: salesaddresses@nxp.com

Date of release: 2021/6/24

Document identifier: R_MPF5020CMMACES