

No.: CE/2020/62791 Date: 2020/06/20 Page: 1 of 4

HENKEL CORPORATION

14000 JAMBOREE ROAD, IRVINE, CALIFORNIA, 92606 U.S.A.

The following sample(s) was/were submitted and identified by/on behalf of the applicant as:

Sample Submitted By : HENKEL CORPORATION

Sample Description : ADHESIVE Style/Item No. : 2033SC Sample Receiving Date : 2020/06/16

**Testing Period** : 2020/06/16 to 2020/06/20

: As specified by client, to test Halogen-Fluorine, Chlorine, Bromine, Iodine in the **Test Requested** 

submitted sample(s).

Test Result(s) : Please refer to following pages.

Signed for and behalf of SGS TAIWAN LTD. Chemical Laboratory - Taipei



This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <a href="https://twap.sgs.com/Terms-and-Conditions.html">https://twap.sgs.com/Terms-and-Conditions.html</a> and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at <a href="https://twap.sgs.com/Terms-and-Conditions.html">https://twap.sgs.com/Terms-and-Conditions.html</a>. Attention is drawn to the limits of instruction is drawn to the limits of instruction is drawn to the limits of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced, except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.



No.: CE/2020/62791 Date: 2020/06/20 Page: 2 of 4

HENKEL CORPORATION

14000 JAMBOREE ROAD, IRVINE, CALIFORNIA, 92606 U.S.A.

## Test Result(s)

PART NAME No.1 : RED PASTE

Test Item(s)	Unit	Method	MDL	Result
				No.1
Halogen				
Halogen-Fluorine (F) (CAS No.: 14762-94-8)	mg/kg	With reference to BS EN 14582 (2016). Analysis was performed by IC.	50	883
Halogen-Chlorine (CI) (CAS No.: 22537-15-1)	mg/kg	With reference to BS EN 14582 (2016). Analysis was performed by IC.	50	261
Halogen-Bromine (Br) (CAS No.: 10097-32-2)	mg/kg	With reference to BS EN 14582 (2016). Analysis was performed by IC.	50	n.d.
Halogen-lodine (I) (CAS No.: 14362-44-8)	mg/kg	With reference to BS EN 14582 (2016). Analysis was performed by IC.	50	n.d.

## Note:

1. mg/kg = ppm; 0.1wt% = 1000ppm

2. MDL = Method Detection Limit


3. n.d. = Not Detected



No.: CE/2020/62791 Date: 2020/06/20

HENKEL CORPORATION 14000 JAMBOREE ROAD, IRVINE, CALIFORNIA, 92606 U.S.A.

## Analytical flow chart - Halogen



This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <a href="https://twap.sgs.com/Terms-and-Conditions.html">https://twap.sgs.com/Terms-and-Conditions.html</a> and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at <a href="https://twap.sgs.com/Terms-and-Conditions.html">https://twap.sgs.com/Terms-and-Conditions.html</a>. Attention is drawn to the limits of initial ini

Page: 3 of 4



No.: CE/2020/62791

Date: 2020/06/20

Page: 4 of 4

HENKEL CORPORATION 14000 JAMBOREE ROAD, IRVINE, CALIFORNIA, 92606 U.S.A.

\* The tested sample / part is marked by an arrow if it's shown on the photo. \*

CE/2020/62791



\*\* End of Report \*\*

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <a href="https://twap.sgs.com/Terms-and-Conditions.html">https://twap.sgs.com/Terms-and-Conditions.html</a> and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at <a href="https://twap.sgs.com/Terms-and-Conditions.html">https://twap.sgs.com/Terms-and-Conditions.html</a>. Attention is drawn to the limits of initial ini