

No. : CE/2020/62792

Date : 2020/06/20

\_\_\_\_\_\_

Page: 1 of 4

HENKEL CORPORATION 14000 JAMBOREE ROAD, IRVINE, CALIFORNIA, 92606 U.S.A.

The following sample(s) was/were submitted and identified by/on behalf of the applicant as :

Sample Submitted By	
Sample Description	
Style/Item No.	
Sample Receiving Date	
Testing Period	

\_\_\_\_\_

: HENKEL CORPORATION

- : ADHESIVE : 2033SC
- : 2020/06/16
- : 2020/06/16 to 2020/06/20

Test Result(s)

: Please refer to following pages.





This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at https://twap.sgs.com/Terms-and-Conditions.html and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at https://twap.sgs.com/Terms-and-Conditions.html limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document be not exonerate parties to a transaction for exercising all their rights and obligations under the transaction documents. This document cannot be reproduced, except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.



No. : CE/2020/62792

Date : 2020/06/20

Page: 2 of 4

HENKEL CORPORATION

14000 JAMBOREE ROAD, IRVINE, CALIFORNIA, 92606 U.S.A.

#### Test Result(s)

PART NAME No.1 : RED PASTE

Test Item(s)	Unit	Method	MDL	Result No.1
Antimony (Sb)		With reference to US EPA 3052 (1996). Analysis was performed by ICP-OES.	2	n.d.

Note :

- 1. mg/kg = ppm ; 0.1wt% = 1000ppm
- 2. MDL = Method Detection Limit
- 3. n.d. = Not Detected

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <a href="https://twap.sgs.com/Terms-and-Conditions.html">https://twap.sgs.com/Terms-and-Conditions.html</a> and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at <a href="https://twap.sgs.com/Terms-and-Conditions.html">https://twap.sgs.com/Terms-and-Conditions.html</a> and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at <a href="https://twap.sgs.com/Terms-and-Conditions.html">https://twap.sgs.com/Terms-and-Conditions.html</a> ilmitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document document by any unauthorized alteration, forgery or faisification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.



No. : CE/2020/62792


Date : 2020/06/20

Page: 3 of 4

HENKEL CORPORATION 14000 JAMBOREE ROAD, IRVINE, CALIFORNIA, 92606 U.S.A.

#### Flow Chart of digestion for the elements analysis performed by ICP-OES

These samples were dissolved totally by pre-conditioning method according to below flow chart.



This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at https://twap.sgs.com/Terms-and-Conditions.html and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at https://twap.sgs.com/Terms-and-Conditions.html limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document be not exonerate parties to a transaction for exercising all their rights and obligations under the transaction documents. This document cannot be reproduced, except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.



No. : CE/2020/62792

Date : 2020/06/20

Page: 4 of 4

HENKEL CORPORATION 14000 JAMBOREE ROAD, IRVINE, CALIFORNIA, 92606 U.S.A.

\* The tested sample / part is marked by an arrow if it's shown on the photo. \*



CE/2020/62792

\*\* End of Report \*\*

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at https://twap.sgs.com/Terms-and-Conditions.html and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at https://twap.sgs.com/Terms-and-Conditions.html limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document be not exonerate parties to a transaction for exercising all their rights and obligations under the transaction documents. This document cannot be reproduced, except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.