



TEST REPORT

Lab No. : (6222)042-0265
Date : February 22, 2022
Page : 1 of 18

APPLICANT
申請人 : HON HAI PRECISION IND.CO., LTD.
No. 2, Ziyou St., Tucheng Dist, New Taipei City 23678, Taiwan (R.O.C.)
鴻海精密工業股份有限公司
23678 新北市土城區自由街 2 號

CONTACT PERSON
聯絡人 : —

DATE OF SUBMISSION
送樣日期 : February 11, 2022
2022 年 02 月 11 日

PERFORMANCE PERIOD
測試日期 : February 11, 2022 to February 22, 2022
2022 年 02 月 11 日至 2022 年 02 月 22 日

SAMPLE DESCRIPTION
樣品描述 : POTASSIUM GOLD CYANIDE
金氰化鉀

ITEM NO.
產品型號 : 903-0000-020

REMARK

If there are questions or concerns on this report, please contact:
若有任何疑問或諮詢, 請以 email 與我們聯絡

chemical.inquiry@bureauveritas.com/
vico.lin@bureauveritas.com

BUREAU VERITAS CONSUMER PRODUCTS SERVICES
(H.K.) LIMITED, TAIWAN BRANCH

VICO LIN
MANAGER
ANALYTICAL DEPARTMENT

PREPARED BY : Tiffany Chin

C/N /TC/JK

Bureau Veritas
Consumer Product Service (H.K.) Ltd.
Taiwan Branch
37, Zhongyang S Rd., Sec. 2, Beitou,
Taipei 112, Taiwan, R.O.C.

Tel : 886-2-2895-3666
Fax: 886-2-2895-6999
<http://www.cps.bureauveritas.com>

This report is governed by, and incorporates by reference, CPS Conditions of Service as posted at the date of issuance of this report at <http://www.bureauveritas.com/home/about-us/our-business/cps/about-us/terms-conditions> and is intended for your exclusive use. Any copying or replication of this report to or for any other person or entity, or use of our name or trademark, is permitted only with our prior written permission. This report sets forth our findings solely with respect to the test samples identified herein. The results set forth in this report are not indicative or representative of the quality or characteristics of the lot from which a test sample was taken or any similar or identical product unless specifically and expressly noted. Our report includes all of the tests requested by you and the results thereof based upon the information that you provided to us. Measurement uncertainty is only provided upon request for accredited tests. You have 60 days from date of issuance of this report to notify us of any material error or omission caused by our negligence or if you require measurement uncertainty; provided, however, that such notice shall be in writing and shall specifically address the issue you wish to raise. A failure to raise such issue within the prescribed time shall constitute your unqualified acceptance of the completeness of this report, the tests conducted and the correctness of the report contents.



**BUREAU
VERITAS**

Lab No. : (6222)042-0265
Date : February 22, 2022
Page : 2 of 18

Sample Description Assigned by Laboratory:

實驗室對樣品的描述:

Tested item 測試部件	
1.	White powder / 白色粉末

Note 註解:

N.D. = Not Detected (低於偵測極限) - = Empty (空白)

mg/kg = milligram per kilogram = ppm (毫克/公斤, 百萬分之一)

% = percent (百分率) 10000 mg/kg = 1 %

ppb = part(s) per billion (十億分之一) 1 mg/kg = 1 ppm = 1 000 ppb

Photo of the Submitted Sample

委送樣品照片



Sample



**BUREAU
VERITAS**

Lab No. : (6222)042-0265
Date : February 22, 2022
Page : 3 of 18

TEST RESULT 測試結果

**Heavy Metals and Flame Retardants – European Parliament and Council Directive 2011/65/EU on the Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment (RoHS)
重金屬和阻燃劑 - 有關歐盟委員會針對電子產品的指令(電子電氣禁用某些有害物質指令)，2011/65/EU**

Test Method 測試方法

Lead [Pb] / 鉛 : With reference to IEC 62321-5: 2013. (Analysis by ICP-OES).
Cadmium [Cd] / 鎘 : 參照 IEC 62321-5: 2013. (ICP-OES 分析)。
Mercury [Hg] / 汞 : With reference to IEC 62321-4: 2013+AMD 1:2017 CSV. (Analysis by ICP-OES).
參照 IEC 62321-4: 2013+AMD 1:2017 CSV. (ICP-OES 分析)。
Chromium (VI) [Cr(VI)] / 六價鉻 : With reference to IEC 62321-7-2:2017. (Analysis by UV-VIS).
參照 IEC 62321-7-2:2017. (UV-VIS 分析)。
Polybrominated Biphenyls [PBBs] and Polybrominated Diphenyl Ethers [PBDEs] / 多溴聯苯和多溴聯苯醚 : With reference to IEC 62321-6: 2015 (Analysis by GC-MS).
參照 IEC 62321-6: 2015. (GC-MS 分析)。

Compounds 化合物	Unit 單位	Result 結果	MDL 測試方法 偵測極限
		1	
Lead [Pb] / 鉛	mg/kg	N.D.	2
Cadmium [Cd] / 鎘	mg/kg	N.D.	2
Mercury [Hg] / 汞	mg/kg	N.D.	2
Chromium (VI) [Cr(VI)] / 六價鉻	mg/kg	N.D.	8
Polybrominated Biphenyls [PBBs] / 多溴聯苯			
Bromobiphenyls / 一溴聯苯	mg/kg	N.D.	5
Dibromobiphenyls / 二溴聯苯	mg/kg	N.D.	5
Tribromobiphenyls / 三溴聯苯	mg/kg	N.D.	5
Tetrabromobiphenyls / 四溴聯苯	mg/kg	N.D.	5
Pentabromobiphenyls / 五溴聯苯	mg/kg	N.D.	5
Hexabromobiphenyls / 六溴聯苯	mg/kg	N.D.	5
Heptabromobiphenyls / 七溴聯苯	mg/kg	N.D.	5
Octabromobiphenyls / 八溴聯苯	mg/kg	N.D.	5
Nonabromobiphenyls / 九溴聯苯	mg/kg	N.D.	5
Decabromobiphenyl / 十溴聯苯	mg/kg	N.D.	5
Sum of PBBs / 多溴聯苯總和	mg/kg	N.D.	—
Bromodiphenyl ethers / 一溴聯苯醚			
Bromodiphenyl ethers / 一溴聯苯醚	mg/kg	N.D.	5
Dibromodiphenyl ethers / 二溴聯苯醚	mg/kg	N.D.	5
Tribromodiphenyl ethers / 三溴聯苯醚	mg/kg	N.D.	5
Tetrabromodiphenyl ethers / 四溴聯苯醚	mg/kg	N.D.	5
Pentabromodiphenyl ethers / 五溴聯苯醚	mg/kg	N.D.	5
Hexabromodiphenyl ethers / 六溴聯苯醚	mg/kg	N.D.	5
Heptabromodiphenyl ethers / 七溴聯苯醚	mg/kg	N.D.	5
Octabromodiphenyl ethers / 八溴聯苯醚	mg/kg	N.D.	5
Nonabromodiphenyl ethers / 九溴聯苯醚	mg/kg	N.D.	5
Decabromodiphenyl ether / 十溴聯苯醚	mg/kg	N.D.	5
Sum of PBDEs / 多溴聯苯醚總和	mg/kg	N.D.	—

C/N / TC / JK



**BUREAU
VERITAS**

Lab No. : (6222)042-0265
Date : February 22, 2022
Page : 4 of 18

TEST RESULT 測試結果

Phthalates

鄰苯二甲酸鹽

Test Method: With reference to IEC 62321-8: 2017. (Analysis by GC-MS).
測試方法: 參照 IEC 62321-8: 2017 (GC-MS 分析)。

Test Item 測試項目	Unit 單位	Result 結果	MDL 測試方法 偵測極限
		1	
Di-butyl phthalate (DBP) 鄰苯二甲酸二丁酯 (DBP)	mg/kg	N.D.	50
Butyl benzyl phthalate (BBP) 鄰苯二甲酸丁基苄基酯 (BBP)	mg/kg	N.D.	50
Di-(ethylhexyl) phthalate (DEHP) 鄰苯二甲酸二(2-乙基己基)酯 (DEHP)	mg/kg	N.D.	50
Di-n-octyl phthalate (DNOP) 鄰苯二甲酸二正辛酯 (DNOP)	mg/kg	N.D.	50
Di-isodecyl phthalate (DIDP) 鄰苯二甲酸二異癸酯 (DIDP)	mg/kg	N.D.	50
Di-isononyl phthalate (DINP) 鄰苯二甲酸二異壬酯 (DINP)	mg/kg	N.D.	50
Diisobutyl phthalate (DiBP) 鄰苯二甲酸二異丁酯 (DiBP)	mg/kg	N.D.	50

Hexabromocyclododecane (HBCDD)

六溴環十二烷

Test Method: With reference to IEC 62321-6:2015. (Analysis by LC-MS).
測試方法: 參照 IEC 62321-6:2015 (LC-MS 分析)。

Test Item 測試項目	Unit 單位	Result 結果	MDL 測試方法 偵測極限
		1	
Hexabromocyclododecane (HBCDD) 六溴環十二烷	mg/kg	N.D.	5

TEST RESULT 測試結果

Halogen - Fluorine, Chlorine, Bromine and Iodine

鹵素 - 氟、氯、溴和碘

Test Method: With reference to EN14582:2016(E). (Analysis by Ion Chromatogram).

測試方法: 參照 EN14582:2016(E) (Ion Chromatogram 分析)。

Compounds 化合物	Unit 單位	Result 結果	MDL 測試方法 偵測極限
		1	
Fluorine [F] / 氟	mg/kg	N.D.	50
Chlorine [Cl] / 氯	mg/kg	N.D.	50
Bromine [Br] / 溴	mg/kg	N.D.	50
Iodine [I] / 碘	mg/kg	N.D.	50

Perfluorooctanoic acid (PFOA) and Perfluorooctane sulphonate (PFOS)

全氟辛酸和全氟辛烷磺酸

Test Method: With reference to DIN CEN/TS 15968:2010. (Analysis by LC-MS-MS).

測試方法: 參照 DIN CEN/TS 15968:2010. (LC-MS-MS 分析)。

Test Parameter 測試項目	Unit 單位	Result 結果	MDL 測試方法 偵測極限
		1	
Perfluorooctanoic acid (PFOA) 全氟辛酸	ppb	N.D.	10
Perfluorooctane sulphonate (PFOS) 全氟辛烷磺酸	ppb	N.D.	10

Dimethyl Fumarate

富馬酸二甲酯

Test Method: With reference to US EPA 3550C:2007. (Analysis by GC-MS).

測試方法: 參照 US EPA 3550C:2007 (GC-MS 分析)。

Test Parameter 測試項目	Unit 單位	Result 結果	MDL 測試方法 偵測極限
		1	
Dimethyl Fumarate 富馬酸二甲酯	mg/kg	N.D.	0.03



**BUREAU
VERITAS**

Lab No. : (6222)042-0265
Date : February 22, 2022
Page : 6 of 18

TEST RESULT 測試結果

Organotin Compounds

有機錫化合物

Test Method: Refer to ISO17353:2004 (Analysis by GC-MS).
測試方法: 參照 ISO17353:2004 (GC-MS 分析)。

Test Parameter 測試項目	Unit 單位	Result 結果	MDL 測試方法 偵測極限
		1	
Tributyltin (TBT) 三丁基錫	mg/kg	N.D.	0.03
Tripropyltin (TPT) 三苯基錫	mg/kg	N.D.	0.03
Tributyltin Oxide (TBTO) 三丁基錫氧化物	mg/kg	N.D.	0.03
Dibutyltin (DBT) 二丁基錫	mg/kg	N.D.	0.03
Triphenyltin (TPhT) 氫氧化三苯基錫	mg/kg	N.D.	0.03
Diocetyl tin (DOT) 二辛基錫	mg/kg	N.D.	0.03

Short Chain Chlorinated Paraffins (SCCPs) (C10 – C13)

短鏈氯化石蠟

Test Method: With reference to US EPA 3550C:2007. (Analysis by NCI-GCMS).
測試方法: 參照 US EPA 3550C:2007 (NCI-GCMS 分析)。

Test Parameter 測試項目	Unit 單位	Result 結果	MDL 測試方法 偵測極限
		1	
Short Chain Chlorinated Paraffins (SCCPs) (C10 – C13) 短鏈氯化石蠟	mg/kg	N.D.	100



**BUREAU
VERITAS**

Lab No. : (6222)042-0265
Date : February 22, 2022
Page : 7 of 18

TEST RESULT 測試結果

Polyvinyl Chloride (PVC) Identification

聚氯乙烯 (PVC) 鑑定

Test Method: With reference to Beilstein and FT-IR.
測試方法: 參照貝爾坦斯試驗法及傅裡葉變換紅外光譜法(FT-IR)。

Test Parameter 測試項目	Tested item 測試部件
	1
PVC Identification 聚氯乙烯鑑定	PVC is not found 未偵測到聚氯乙烯

Tetrabromobisphenol A (TBBPA)

四溴雙酚 A

Test Method: With reference to US EPA 3550C:2007. (Analysis by LC-MS).
測試方法: 參照 US EPA 3550C:2007 (LC-MS 分析)。

Test Parameter 測試項目	Unit 單位	Result 結果	MDL 測試方法 偵測極限
		1	
Tetrabromobisphenol A (TBBPA) 四溴雙酚 A	mg/kg	N.D.	5

Bisphenol A Content

雙酚 A 含量

Test Method: With reference to US EPA 3550C:2007. (Analysis by LC-MS).
測試方法: 參照 US EPA 3550C:2007 (LC-MS 分析)。

Test Parameter 測試項目	Unit 單位	Result 結果	MDL 測試方法 偵測極限
		1	
Bisphenol A Content 雙酚 A 含量	mg/kg	N.D.	0.1



**BUREAU
VERITAS**

Lab No. : (6222)042-0265
Date : February 22, 2022
Page : 8 of 18

TEST RESULT 測試結果

Polychlorinated Biphenyls (PCBs)

多氯聯苯

Test Method: With reference to US EPA 3550C:2007. (Analysis by GC-MS).
測試方法: 參照 US EPA 3550C:2007 (GC-MS 分析)。

Test Item 測試項目	Unit 單位	Result 結果	MDL 測試方法 偵測極限
		1	
Polychlorinated Biphenyls (PCBs) 多氯聯苯	mg/kg	N.D.	0.5

Polychlorinated Naphthalene (PCNs)

多氯奈

Test Method: With reference to US EPA 3550C:2007. (Analysis by GC-MS).
測試方法: 參照 US EPA 3550C:2007 (GC-MS 分析)。

Test Item 測試項目	Unit 單位	Result 結果	MDL 測試方法 偵測極限
		1	
Polychlorinated Naphthalene (PCNs) 多氯奈	mg/kg	N.D.	5

Polychlorinated Terphenyls (PCTs)

多氯三聯苯

Test Method: With reference to US EPA 3550C:2007. (Analysis by GC-MS).
測試方法: 參照 US EPA 3550C:2007 (GC-MS 分析)。

Test Item 測試項目	Unit 單位	Result 結果	MDL 測試方法 偵測極限
		1	
Polychlorinated Terphenyls Contents (PCTs) 多氯三聯苯	mg/kg	N.D.	0.5



**BUREAU
VERITAS**

Lab No. : (6222)042-0265
Date : February 22, 2022
Page : 9 of 18

TEST RESULT 測試結果

Total Arsenic (As)

總砷

Test Method: With reference to U.S. EPA 3052:1996 (Analysed by ICP-OES.)

測試方法: 參照 U.S. EPA 3052:1996 (ICP-OES 分析)。

Test Item 測試項目	Unit 單位	Result 結果	MDL 測試方法 偵測極限
		1	
Total Arsenic (As) 總砷	mg/kg	N.D.	2

Total Beryllium (Be)

總鉍

Test Method: With reference to U.S. EPA 3052:1996 (Analysed by ICP-OES.)

測試方法: 參照 U.S. EPA 3052:1996 (ICP-OES 分析)。

Test Item 測試項目	Unit 單位	Result 結果	MDL 測試方法 偵測極限
		1	
Total Beryllium (Be) 總鉍	mg/kg	N.D.	2

Total Antimony (Sb)

總銻

Test Method: With reference to U.S. EPA 3052:1996 (Analysed by ICP-OES.)

測試方法: 參照 U.S. EPA 3052:1996 (ICP-OES 分析)。

Test Item 測試項目	Unit 單位	Result 結果	MDL 測試方法 偵測極限
		1	
Total Antimony (Sb) 總銻	mg/kg	N.D.	2



Lab No. : (6222)042-0265
Date : February 22, 2022
Page : 10 of 18

TEST RESULT 測試結果

Total Phosphorum (P)

總磷

Test Method: With reference to U.S. EPA 3052:1996 (Analysed by ICP-OES.)
測試方法: 參照 U.S. EPA 3052:1996 (ICP-OES 分析)。

Test Item 測試項目	Unit 單位	Result 結果	MDL 測試方法 偵測極限
		1	
Total Phosphorus (P) 總磷	mg/kg	N.D.	2

Remark 備註:

1. The result only relates to the tested item. The report shall not be reproduced except full without the written approval of the testing laboratory. Parameters which are not covered by the lab's testing scope are subcontracted to laboratories with government approval. The accreditation relates to competences given in the accreditation certificate.
測試結果僅代表經測試部件。本報告未經測試實驗室認可不得複製。未在本實驗室測試範疇之測試均委外至經官方核可之實驗室。委外實驗室之能力經認證許可。
2. Samples test were conducted as per applicant's request.
樣品測試進行為依照申請人的要求。



BUREAU VERITAS


APPENDIX(附錄)

Test Flowchart of Heavy Metals and Flame Retardants

重金屬和阻燃劑的測試流程圖

1. 測試人員：吳毓琪, 謝明桓 / Name of the person who made measurement: Maggie Wu, Henry Hsieh

2. 測試負責人：宋文峯, 黃秉宏 / Name of the person in charge of measurement: Klaus Sung, Jerry Huang




APPENDIX(附錄)

Determinations of Phthalate, HBCDD, Perfluorooctanoic acid (PFOA), Perfluorooctane sulphonate (PFOS), Dimethyl Fumarate and Bisphenol A Content

鄰苯二甲酸鹽, 六溴環十二烷, 全氟辛酸與全氟辛烷磺酸, 富馬酸二甲酯和雙酚 A 含量的測試流程圖

1. 測試人員：梁維翰 / Name of the person who made measurement: Ben Liang

2. 測試負責人：宋文峯 / Name of the person in charge of measurement: Klaus Sung





**BUREAU
VERITAS**

Lab No. : (6222)042-0265
Date : February 22, 2022
Page : 13 of 18


APPENDIX(附錄)

Test Flowchart of Halogenated Compounds: F, Cl, Br, I

鹵素: 氟, 氯, 溴, 碘的測試流程圖

1. 測試人員: 謝明桓 / Name of the person who made measurement: Henry Hsieh

2. 測試負責人: 黃秉宏 / Name of the person in charge of measurement: Jerry Huang



APPENDIX(附錄)

Determinations of Organotin Compounds

有機錫化合物的測試流程圖

1. 測試人員：吳毓嫻 / Name of the person who made measurement: Maggie Wu
2. 測試負責人：宋文峯 / Name of the person in charge of measurement: Klaus Sung

Adding organic solvent and extracted
by Ultrasonic bath /
樣品加入溶劑，在超音波水浴下震盪

Add derivatizing agent and shaken by shaker /
加入衍生劑進行衍生，並以振盪器協助反應

Withdraw up layer and filtered to via by filter /
取上層澄清液，接著進行過濾至vial至瓶中

Solution analyzed by GC-MS/ UV-VIS /
萃取液利用 GC-MS/ UV-VIS 進行分析


APPENDIX(附錄)

Test Flowchart of TBBPA, PCBs, PCNs, PCTs

四溴雙酚 A, 多氯聯苯, 多氯奈和多氯三聯苯的測試流程圖

1. 測試人員：梁維翰 / Name of the person who made measurement: Ben Liang

2. 測試負責人：宋文峯 / Name of the person in charge of measurement: Klaus Sung




APPENDIX(附錄)

Test Flowchart of Short Chain Chlorinated Paraffins (SCCPs)

短鏈氯化石蠟的測試流程圖

1. 測試人員：梁維翰 / Name of the person who made measurement: Ben Liang

2. 測試負責人：宋文峯 / Name of the person in charge of measurement: Klaus Sung



APPENDIX(附錄)

Test Flowchart of Polyvinyl Chloride (PVC) Identification

聚氯乙烯 (PVC) 鑑定的測試流程圖

1. 測試人員：謝明桓 / Name of the person who made measurement: Henry Hsieh
2. 測試負責人：黃秉宏 / Name of the person in charge of measurement: Jerry Huang

Dissolve the sample with organic solvent, and placed in Ultrasonic bath at room temperature for 1 hr. / 以有機溶劑溶解，並以超音波在室溫下震盪一小時

Add ACN and stand for 30 minutes for precipitation. / 加入乙腈，並靜置 30 分鐘做為析出流程

Filter the precipitate then stand at room temperature until it is dried. / 利用濾紙過濾，靜置在室溫下使其乾燥


Using FTIR to identify. / 利用 FTIR 進行鑑定

APPENDIX(附錄)

Test Flowchart of Total Arsenic (As), Total Beryllium (Be), Total Antimony (Sb) and Total Phosphorus (P)

總砷, 總鉍, 總銻與總磷的測試流程圖

1. 測試人員：謝明桓 / Name of the person who made measurement: Henry Hsieh
2. 測試負責人：黃秉宏 / Name of the person in charge of measurement: Jerry Huang



- End 結束 -