

Test Report No: 10556491(1a) A1 Date: 28-Mar-2023 Page 1 of 4

GLOBALFOUNDRIES Singapore Pte Ltd 60 Woodlands Industrial Park D Street 2 Singapore 738406

Sample Name : One (1) 300mm die-patterned wafer Technode : 0.11um/0.13um/0.13um 8SW/90nm

Fab : 7

The above sample(s) and information were provided by the client.

Sample Receiving Date : 10-Mar-2023

Testing Period : 10-Mar-2023 to 28-Mar-2023

Test Result(s) : Please refer to next page(s).

Signed for and on behalf of SGS Testing & Control Services Singapore Pte Ltd

Y.C. Tham

Technical Manager, Multi-Lab

This document is issued by the Company under its General Conditions of Service accessible at http://www.sqs.com/en/Terms-and-Conditions.aspx and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at http://www.sqs.com/en/Terms-and-Conditions/Terms-e-Document.aspx. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested and such sample(s) are retained for 30 days only. This document cannot be reproduced except in full, without prior approval of the Company.

SGS Testing & Control Services Singapore Pte Ltd

30 Boon Lay Way, #03-01, Singapore 609957 t +65 6379 0111 e sg.genlab@sgs.com www.sgs.com



Test Report No: 10556491(1a) A1 Date: 28-Mar-2023 Page 2 of 4

Test Result(s):

Sample Description : Wafer

| Test Item(s): | Unit | Method | Results | MDL |
|-------------------------|-------|---|---------|-----|
| Halogen | | | | |
| Halogen - Bromine (Br) | mg/kg | With reference to BS EN 14582. Analysis was performed by IC | n.d. | 50 |
| Halogen - Chlorine (CI) | mg/kg | With reference to BS EN 14582. Analysis was performed by IC | n.d. | 50 |
| Halogen - Fluorine (F) | mg/kg | With reference to BS EN 14582. Analysis was performed by IC | n.d. | 50 |
| Halogen - Iodine (I) | mg/kg | With reference to BS EN 14582. Analysis was performed by IC | n.d. | 50 |

Note: (1) mg/kg = ppm ; 0.1wt% = 1000ppm

(2) n.d.= Not Detected

(3) MDL = Method Detection Limit

Lab Analyst(s): SR

This document is issued by the Company under its General Conditions of Service accessible at http://www.sqs.com/en/Terms-and-Conditions.aspx and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at http://www.sqs.com/en/Terms-and-Conditions/Terms-e-Document.aspx. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested and such sample(s) are retained for 30 days only. This document cannot be reproduced except in full, without prior approval of the Company.

Co. Reg. No: 199404065N

30 Boon Lay Way, #03-01, Singapore 609957 t +65 6379 0111 e sg.genlab@sgs.com www.sgs.com

GST Reg. No: MR-8500112-9

Member of SGS Group

SGS Testing & Control Services Singapore Pte Ltd




Test Report No: 10556491(1a) A1 Date: 28-Mar-2023 Page 3 of 4

Sample photo:

Sample Description : Wafer

SGS authenticate the photo on original report only



This document is issued by the Company under its General Conditions of Service accessible at http://www.sgs.com/en/Terms-and-Conditions.aspx and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at http://www.sgs.com/en/Terms-and-Conditions/Terms-e-Document.aspx. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested and such sample(s) are retained for 30 days only. This document cannot be reproduced except in full, without prior approval of the Company.

30 Boon Lay Way, #03-01, Singapore 609957 t +65 6379 0111 e sg.genlab@sgs.com www.sgs.com

Member of SGS Group

SGS Testing & Control Services Singapore Pte Ltd


Co. Reg. No: 199404065N GST Reg. No: MR-8500112-9



Test Report

No: 10556491(1a) A1 Date: 28-Mar-2023 Page 4 of 4

Process Flow of BS EN 14582 (Halogen Analysis)



End of Report

This document is issued by the Company under its General Conditions of Service accessible at http://www.sgs.com/en/Terms-and-Conditions.aspx and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at http://www.sgs.com/en/Terms-and-Conditions/Terms-e-Document.aspx. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested and such sample(s) are retained for 30 days only. This document cannot be reproduced except in full, without prior approval of the Company.

Co. Reg. No: 199404065N GST Reg. No: MR-8500112-9 Member of SGS Group

30 Boon Lay Way, #03-01, Singapore 609957 t +65 6379 0111 e sg.genlab@sgs.com www.sgs.com