











Report No. A2210276653101004

Company Name SEMICONDUCTOR MANUFACTURING NORTH CHINA (BEIJING) CORP.

shown on Report

Address 18 WENCHANG ROAD, BEIJING ECONOMIC-TECHNOLOGICAL

DEVELOPMENT AREA, CHINA, 100176

The following sample(s) and sample information was/were submitted and identified by/on the behalf of the applicant

Sample Name Wafer

Part No. SMNC(BJ) 40nm Production wafer

Jul. 19, 2021 Sample Received Date

Testing Period Jul. 19, 2021 to Jul. 22, 2021

As specified by client, to test Lead (Pb), Cadmium (Cd), Mercury (Hg), **Test Requested**

Hexavalent Chromium (Cr(VI)), Polybrominated Biphenyls (PBBs),

Polybrominated Diphenyl Ethers (PBDEs), Phthalates (DBP, BBP, DEHP, DIBP)

in the submitted sample(s).

Test Method Please refer to the following page(s).

Please refer to the following page(s). Test Result(s)

Conclusion

Tested Sample According to standard/directive Result **PASS** Submitted Sample RoHS Directive 2011/65/EU with amendment (EU) 2015/863

PASS means that the results shown on the report comply with the limits set by RoHS Directive 2011/65/EU with amendment (EU) 2015/863.

entreston glastite ferritional Pinbiao (Shanghai) Co., Ltd.

Wangdony
11 L.

Chen kaimin Lab Manager

Reviewed by

Date

Jul. 22, 2021

Hu Wei

No. R268851657

No.1351, Wanfang Road, Minhang District, Shanghai, China



Report No. A2210276653101004 Page 2 of 7

Test Method

Test Item(s)	Test Method	Measured Equipment(s)
Lead (Pb)	IEC 62321-5:2013	ICP-OES
Cadmium (Cd)	IEC 62321-5:2013	ICP-OES
Mercury (Hg)	IEC 62321-4:2013+AMD1:2017 CSV	ICP-OES
Hexavalent Chromium (Cr(VI))	IEC 62321-7-2:2017 and/or determination of Total Chromium by IEC 62321-5:2013	UV-Vis/ICP-OES
Polybrominated Biphenyls (PBBs)	IEC 62321-6:2015	GC-MS
Polybrominated Diphenyl Ethers (PBDEs)	IEC 62321-6:2015	GC-MS
Phthalates (DBP, BBP, DEHP, DIBP)	IEC 62321-8:2017	GC-MS

Hotline:400-6788-333 www.cti-cert.com E-mail:info@cti-cert.com Complaint call:0755-33681700 Complaint E-mail:complaint@cti-cert.com



Report No. A2210276653101004

Page 3 of 7

Test Result(s)

Tested Item(s)	Result	MDL	Limit
Lead(Pb)	N.D.	2 mg/kg	1000 mg/kg
Cadmium(Cd)	N.D.	2 mg/kg	100 mg/kg
Mercury(Hg)	N.D.	2 mg/kg	1000 mg/kg
Hexavalent Chromium(Cr(VI))	N.D.	8 mg/kg	1000 mg/kg
Tested Item(s)	Result	MDL	Limit
Polybrominated Biphenyls (PBBs)			
Monobromobiphenyl	N.D.	5 mg/kg	
Dibromobiphenyl	N.D.	5 mg/kg	
Tribromobiphenyl	N.D.	5 mg/kg	1000 mg/kg
Tetrabromobiphenyl	N.D.	5 mg/kg	
Pentabromobiphenyl	N.D.	5 mg/kg	
Hexabromobiphenyl	N.D.	5 mg/kg	
Heptabromobiphenyl	N.D.	5 mg/kg	
Octabromobiphenyl	N.D.	5 mg/kg	
Nonabromobiphenyl	N.D.	5 mg/kg	
Decabromobiphenyl	N.D.	5 mg/kg	
Tested Item(s)	Result	MDL	Limit
Polybrominated Diphenyl Ethers (PBDEs)			
Monobromodiphenyl ether	N.D.	5 mg/kg	
Dibromodiphenyl ether	N.D.	5 mg/kg	1000 mg/kg
Tribromodiphenyl ether	N.D.	5 mg/kg	
Tetrabromodiphenyl ether	N.D.	5 mg/kg	
Pentabromodiphenyl ether	N.D.	5 mg/kg	
Hexabromodiphenyl ether	N.D.	5 mg/kg	
Heptabromodiphenyl ether	N.D.	5 mg/kg	
Octabromodiphenyl ether	N.D.	5 mg/kg	
Nonabromodiphenyl ether	N.D.	5 mg/kg	
Decabromodiphenyl ether	N.D.	5 mg/kg	



Report No. A2210276653101004

Page 4 of 7

Test Result(s)

Tested Item(s)	Result	MDL	Limit		
Phthalates (DBP, BBP, DEHP, DIBP)					
Dibutyl phthalate(DBP) CAS#:84-74-2	N.D.	50 mg/kg	1000 mg/kg		
Butyl benzyl phthalate(BBP) CAS#:85-68-7	N.D.	50 mg/kg	1000 mg/kg		
Di-(2-ethylhexyl) phthalate(DEHP) CAS#:117-81-7	N.D.	50 mg/kg	1000 mg/kg		
Diisobutyl phthalate(DIBP) CAS#:84-69-5	N.D.	50 mg/kg	1000 mg/kg		

Sample/Part Description

Wafer

Remark: The sample(s) had been dissolved totally tested for Lead, Cadmium, Mercury.

-MDL = Method Detection Limit

-N.D. = Not Detected (<MDL)

-mg/kg = ppm = parts per million

-1000 mg/kg = 0.1%


A R




Report No. A2210276653101004 Page 5 of 7

Test Process

1. Lead (Pb), Cadmium (Cd), Chromium (Cr)




2. Mercury (Hg)




* WESTAN CO, LY

3. Hexavalent Chromium (Cr(VI))



4. Polybrominated Biphenyls (PBBs), Polybrominated Diphenyl Ethers (PBDEs)





Report No. A2210276653101004

5. Phthalates (DBP, BBP, DEHP, DIBP)

Extracted with organic solvent

Concentrate the extract organic solvent

Make up with organic solvent volumetric flask


Hotline:400-6788-333 www.cti-cert.com E-mail:info@cti-cert.com Complaint call:0755-33681700 Complaint E-mail:complaint@cti-cert.com



Report No. A2210276653101004

Page 7 of 7

Photo(s) of the sample(s)



Statement:

- 1. This report is considered invalid without approved signature, special seal and the seal on the perforation;
- 2. The Company Name shown on Report and Address, the sample(s) and sample information was/were provided by the applicant who should be responsible for the authenticity which CTI hasn't verified;
- 3. The result(s) shown in this report refer(s) only to the sample(s) tested;
- 4. Without written approval of CTI, this report can't be reproduced except in full;
- 5. In case of any discrepancy between the English version and Chinese version of the testing reports (if generated), the Chinese version shall prevail.

*** End of report ***