

No.: EKR22401078 Date: 22-Apr-2022 Page: 1 of 14

LINTEC CORPORATION

1-1-1 KOISHIKAWA, BUNKYO-KU, TOKYO 112-0002 JAPAN

The following sample(s) was/were submitted and identified by the applicant as:

Sample Submitted By : LINTEC CORPORATION

Sample Name : ADWILL LC28X6 SERIES (REGARDLESS OF THICKNESS AND SIZE)

Style/Item No. : ADWILL LC2826H, ADWILL LC2846, ADWILL LC86R SERIES

Order No. : 220414-LT-RA-01-107

Sample Receiving Date :

: 15-Apr-2022

Testing Period : 15-Apr-2022 to 22-Apr-2022

Test Requested : (1) As specified by client, with reference to RoHS 2011/65/EU Annex II and amending

Directive (EU) 2015/863 to determine Cadmium, Lead, Mercury, Cr(VI), PBBs, PBDEs,

DBP, BBP, DEHP, DIBP contents in the submitted sample(s).

(2) Please refer to next pages for the other item(s).

Test Results :

Please refer to following pages.

Conclusion : (1) Based on the performed tests on selected part of submitted sample(s), the test

results of Cadmium, Lead, Mercury, Cr(VI), PBBs, PBDEs, DBP, BBP, DEHP, DIBP

comply with the limits as set by RoHS Directive (EU) 2015/863 amending Annex II to

Directive 2011/65/EU.

Ray Chang, Ph.D./Departmen Manager Signed for and on behalf Manager SGS TAIWAN LTD. Chemical Laboratory-Kaohsiung



PIN CODE: 5C12C036

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <a href="https://www.sgs.com.tw/terms-of-service">https://www.sgs.com.tw/terms-of-service</a> and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at <a href="https://www.sgs.com.tw/terms-of-service">https://www.sgs.com.tw/terms-of-service</a>. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document cannot experience and this document and this document and this document period on the company. The company is a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced, except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.



No.: EKR22401078 Date: 22-Apr-2022 Page: 2 of 14

LINTEC CORPORATION 1-1-1 KOISHIKAWA, BUNKYO-KU, TOKYO 112-0002 JAPAN

### **Test Part Description**

No.1 : BLACK PLASTIC FILM (EXCLUDING THE RELEASE LINNER)

#### Test Result(s)

| Test Item(s)                         | Method                                 | Unit  | MDL | Result | Limit |
|--------------------------------------|--|-------|-----|--------|-------|
|                                      |  |       |     | No.1   |       |
| Cadmium (Cd) (CAS No.: 7440-43-9)    | With reference to IEC 62321-5: 2013,   | mg/kg | 2   | n.d.   | 100   |
|                                      | analysis was performed by ICP-OES.     |       |     |        |       |
| Lead (Pb) (CAS No.: 7439-92-1)       | With reference to IEC 62321-5: 2013,   | mg/kg | 2   | n.d.   | 1000  |
|                                      | analysis was performed by ICP-OES.     |       |     |        |       |
| Mercury (Hg) (CAS No.: 7439-97-6)    | With reference to IEC 62321-4: 2013+   | mg/kg | 2   | n.d.   | 1000  |
|                                      | AMD1: 2017, analysis was performed     |       |     |        |       |
|                                      | by ICP-OES.                            |       |     |        |       |
| Hexavalent Chromium Cr(VI) (CAS No.: | With reference to IEC 62321-7-2: 2017, | mg/kg | 8   | n.d.   | 1000  |
| 18540-29-9)                          | analysis was performed by UV-VIS.      |       |     |        |       |
| Monobromobiphenyl                    |  | mg/kg | 5   | n.d.   | -     |
| Dibromobiphenyl                      |  | mg/kg | 5   | n.d.   | -     |
| Tribromobiphenyl                     |  | mg/kg | 5   | n.d.   | -     |
| Tetrabromobiphenyl                   | ]                                      | mg/kg | 5   | n.d.   | ì     |
| Pentabromobiphenyl                   |  | mg/kg | 5   | n.d.   | 1     |
| Hexabromobiphenyl                    |  | mg/kg | 5   | n.d.   | -     |
| Heptabromobiphenyl                   |  | mg/kg | 5   | n.d.   | 1     |
| Octabromobiphenyl                    |  | mg/kg | 5   | n.d.   | -     |
| Nonabromobiphenyl                    |  | mg/kg | 5   | n.d.   | ı     |
| Decabromobiphenyl                    |  | mg/kg | 5   | n.d.   | ı     |
| Sum of PBBs                          | With reference to IEC 62321-6: 2015,   | mg/kg | 1   | n.d.   | 1000  |
| Monobromodiphenyl ether              | analysis was performed by GC/MS.       | mg/kg | 5   | n.d.   | 1     |
| Dibromodiphenyl ether                |  | mg/kg | 5   | n.d.   | -     |
| Tribromodiphenyl ether               |  | mg/kg | 5   | n.d.   | -     |
| Tetrabromodiphenyl ether             |  | mg/kg | 5   | n.d.   | -     |
| Pentabromodiphenyl ether             |  | mg/kg | 5   | n.d.   | =     |
| Hexabromodiphenyl ether              |  | mg/kg | 5   | n.d.   | -     |
| Heptabromodiphenyl ether             |  | mg/kg | 5   | n.d.   | -     |
| Octabromodiphenyl ether              |  | mg/kg | 5   | n.d.   |       |
| Nonabromodiphenyl ether              |  | mg/kg | 5   | n.d.   | -     |
| Decabromodiphenyl ether              |  | mg/kg | 5   | n.d.   | -     |
| Sum of PBDEs                         |  | mg/kg | -   | n.d.   | 1000  |



No.: EKR22401078 Date: 22-Apr-2022 Page: 3 of 14

LINTEC CORPORATION

1-1-1 KOISHIKAWA, BUNKYO-KU, TOKYO 112-0002 JAPAN

| Test Item(s)  | Method  | Unit  | MDL    | Result<br>No.1 | Limit |
|---|---|-------|--------|----------------|-------|
| Butyl benzyl phthalate (BBP) (CAS No.: 85-68-7)                         |   | mg/kg | 50     | n.d.           | 1000  |
| Dibutyl phthalate (DBP) (CAS No.: 84-74-2)                              |   | mg/kg | 50     | n.d.           | 1000  |
| Di-(2-ethylhexyl) phthalate (DEHP)<br>(CAS No.: 117-81-7)               |   | mg/kg | 50     | n.d.           | 1000  |
| Diisobutyl phthalate (DIBP) (CAS No.: 84-69-5)                          | With reference to IEC 62321-8: 2017, analysis was performed by GC/MS.   | mg/kg | 50     | n.d.           | 1000  |
| Diisodecyl phthalate (DIDP) (CAS No.: 26761-40-0, 68515-49-1)           |   | mg/kg | 50     | n.d.           | -     |
| Diisononyl phthalate (DINP) (CAS No.: 28553-12-0, 68515-48-0)           |   | mg/kg | 50     | n.d.           | -     |
| Di-n-octyl phthalate (DNOP) (CAS No.: 117-84-0)                         |   | mg/kg | 50     | n.d.           | -     |
| Antimony (Sb) (CAS No.: 7440-36-0)                                      | With reference to US EPA 3052: 1996, analysis was performed by ICP-OES. | mg/kg | 2      | n.d.           | -     |
| Beryllium (Be) (CAS No.: 7440-41-7)                                     | With reference to US EPA 3052: 1996, analysis was performed by ICP-OES. | mg/kg | 2      | n.d.           | -     |
| Polychlorinated biphenyls (PCBs)  | With reference to US EPA 3550C: 2007, analysis was performed by GC/MS.  | mg/kg | 0.5    | n.d.           | -     |
| Polychlorinated naphthalene (PCNs)                                      | With reference to US EPA 3550C: 2007, analysis was performed by GC/MS.  | mg/kg | 5      | n.d.           | -     |
| Polychlorinated terphenyls (PCTs)                                       | With reference to US EPA 3550C: 2007, analysis was performed by GC/MS.  | mg/kg | 0.5    | n.d.           | -     |
| Short Chain Chlorinated Paraffins(C10-C13) (SCCP) (CAS No.: 85535-84-8) | With reference to ISO 18219: 2015, analysis was performed by GC/MS.     | mg/kg | 50     | n.d.           | -     |
| Fluorine (F) (CAS No.: 14762-94-8)                                      |   | mg/kg | 50     | n.d.           | -     |
| Chlorine (Cl) (CAS No.: 22537-15-1)                                     | With reference to BS EN 14582: 2016,                                    | mg/kg | 50     | 180            | -     |
| Bromine (Br) (CAS No.: 10097-32-2)                                      | analysis was performed by IC.   | mg/kg | 50     | n.d.           | -     |
| lodine (I) (CAS No.: 14362-44-8)  |   | mg/kg | 50     | n.d.           | -     |
| Tributyl tin (TBT)  | With reference to ISO 17353: 2004, analysis was performed by GC/FPD.    | mg/kg | 0.03   | n.d.           | -     |
| Triphenyl tin (TPT)   | With reference to ISO 17353: 2004, analysis was performed by GC/FPD.    | mg/kg | 0.03   | n.d.           | -     |
| Bis(tributyltin) oxide (TBTO) (CAS No.:<br>56-35-9)                     | Calculated from the result of Tributyl<br>Tin (TBT).                    | mg/kg | 0.03 🛦 | n.d.           | -     |



No.: EKR22401078 Date: 22-Apr-2022 Page: 4 of 14

LINTEC CORPORATION

1-1-1 KOISHIKAWA, BUNKYO-KU, TOKYO 112-0002 JAPAN

| Test Item(s)                           | Method                                | Unit  | MDL  | Result   | Limit |
|--|---------------------------------------|-------|------|----------|-------|
|  |                                       |       |      | No.1     |       |
| Dibutyl tin (DBT)                      | With reference to ISO 17353: 2004,    | mg/kg | 0.03 | n.d.     | -     |
|  | analysis was performed by GC/FPD.     |       |      |          |       |
| Dioctyl tin (DOT)                      | With reference to ISO 17353: 2004,    | mg/kg | 0.03 | n.d.     | -     |
|  | analysis was performed by GC/FPD.     |       |      |          |       |
| PFOS and its salts (CAS No.: 1763-23-1 | With reference to CEN/TS 15968: 2010, | mg/kg | 0.01 | n.d.     | -     |
| and its salts)                         | analysis was performed by LC/MS/MS.   |       |      |          |       |
| Perfluorooctanoic acid (PFOA) and it's | With reference to CEN/TS 15968: 2010, | mg/kg | 0.01 | n.d.     | -     |
| salt (CAS No.: 335-67-1 and its salts) | analysis was performed by LC/MS/MS.   |       |      |          |       |
| Hexabromocyclododecane (HBCDD)         | With reference to IEC 62321: 2008,    | mg/kg | 5    | n.d.     | -     |
| and all major diastereoisomers         | analysis was performed by GC/MS.      |       |      |          |       |
| identified (α- HBCDD, β- HBCDD, γ-     |                                       |       |      |          |       |
| HBCDD) (CAS No.: 25637-99-4, 3194-     |                                       |       |      |          |       |
| 55-6 (134237-51-7, 134237-50-6,        |                                       |       |      |          |       |
| 134237-52-8))                          |                                       |       |      |          |       |
| Polyvinyl chloride (PVC)               | With reference to ASTM E1252: 2013,   | **    | -    | Negative | -     |
|  | analysis was performed by FT-IR and   |       |      |          |       |
|  | Flame Test.                           |       |      |          |       |

#### Note:

- 1. mg/kg = ppm; 0.1wt% = 0.1% = 1000ppm
- 2. MDL = Method Detection Limit
- 3. n.d. = Not Detected (Less than MDL)
- 4. "-" = Not Regulated
- 5. \*\*= Qualitative analysis (No Unit)
- 6. Negative = Undetectable; Positive = Detectable
- 7. PFOS and its salts including:

CAS No.: 29081-56-9, 2795-39-3, 29457-72-5, 70225-14-8, 56773-42-3, 251099-16-8, 307-35-7.

- 8. PFOA and its salts including:
  - CAS No.: 3825-26-1, 335-95-5, 2395-00-8, 335-93-3, 335-66-0.
- 9. ▲ : The MDL was evaluated for element / tested substance.

Conversion Formula :  $AX = A \times F$ 

| AX                           | Α                  | F     |
|------------------------------|--------------------|-------|
| Bis(tributyltin)oxide (TBTO) | Tributyl Tin (TBT) | 1.024 |

Parameter Conversion Table: https://eecloud.sgs.com/Region\_TW/DocDownload.aspx#otherDoc

10. Unless otherwise stated, the decision rule for conformity reporting is based on Binary Statement for Simple Acceptance Rule (w=0) stated in ILAC-G8:09/2019. According to this rule, the judgement of conformity is based on the comparing test results with limits.




No.: EKR22401078 Date: 22-Apr-2022 Page: 5 of 14

LINTEC CORPORATION 1-1-1 KOISHIKAWA, BUNKYO-KU, TOKYO 112-0002 JAPAN

#### **Analytical flow chart of Heavy Metal**

These samples were dissolved totally by pre-conditioning method according to below flow chart. ( Cr<sup>6+</sup> test method excluded )






No.: EKR22401078 Date: 22-Apr-2022 Page: 6 of 14

LINTEC CORPORATION 1-1-1 KOISHIKAWA, BUNKYO-KU, TOKYO 112-0002 JAPAN

#### PBB/PBDE analytical FLOW CHART






No.: EKR22401078 Date: 22-Apr-2022 Page: 7 of 14

LINTEC CORPORATION 1-1-1 KOISHIKAWA, BUNKYO-KU, TOKYO 112-0002 JAPAN

#### Analytical flow chart of phthalate content

[Test method: IEC 62321-8]





LINTEC CORPORATION 1-1-1 KOISHIKAWA, BUNKYO-KU, TOKYO 112-0002 JAPAN


No.: EKR22401078

#### Analytical flow chart of Elements (Heavy metal included)

Date: 22-Apr-2022

These samples were dissolved totally by pre-conditioning method according to below flow chart.

【Reference method: US EPA 3051 \ US EPA 3052】



\* US EPA 3051 method does not add HF.

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <a href="https://www.sgs.com.tw/terms-of-service">https://www.sgs.com.tw/terms-of-service</a>. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced, except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.

Page: 8 of 14




LINTEC CORPORATION 1-1-1 KOISHIKAWA, BUNKYO-KU, TOKYO 112-0002 JAPAN

No.: EKR22401078

### Analytical flow chart

Date: 22-Apr-2022

\* Apply to: PCBs, PCNs, PCTs, Mirex, Chlorinated Paraffins, DBBT



This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <a href="https://www.sgs.com.tw/terms-of-service">https://www.sgs.com.tw/terms-of-service</a>. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced, except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.

Page: 9 of 14




LINTEC CORPORATION 1-1-1 KOISHIKAWA, BUNKYO-KU, TOKYO 112-0002 JAPAN

No.: EKR22401078

#### Analytical flow chart of Halogen

Date: 22-Apr-2022



This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <a href="https://www.sgs.com.tw/terms-of-service">https://www.sgs.com.tw/terms-of-service</a>. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced, except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.


Page: 10 of 14



No.: EKR22401078 Date: 22-Apr-2022 Page: 11 of 14

LINTEC CORPORATION 1-1-1 KOISHIKAWA, BUNKYO-KU, TOKYO 112-0002 JAPAN

#### **Analytical flow chart - Organic-Tin**






No.: EKR22401078 Date: 22-Apr-2022 Page: 12 of 14

LINTEC CORPORATION 1-1-1 KOISHIKAWA, BUNKYO-KU, TOKYO 112-0002 JAPAN

### Analytical flow chart - PFAS (including PFOA/PFOS/its related compound, etc.)






LINTEC CORPORATION 1-1-1 KOISHIKAWA, BUNKYO-KU, TOKYO 112-0002 JAPAN

No.: EKR22401078

#### **Analytical flow chart - HBCDD**

Date: 22-Apr-2022



This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <a href="https://www.sgs.com.tw/terms-of-service">https://www.sgs.com.tw/terms-of-service</a>. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced, except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.

Page: 13 of 14




No.: EKR22401078 Date: 22-Apr-2022 Page: 14 of 14

LINTEC CORPORATION 1-1-1 KOISHIKAWA, BUNKYO-KU, TOKYO 112-0002 JAPAN

\* The tested sample / part is marked by an arrow if it's shown on the photo. \*

### EKR22401078



\*\* End of Report \*\*