

Test Report

號碼(No.): ETR22A04718 日期(Date): 04-Nov-2022 頁數(Page): 1 of 13

旭德科技股份有限公司 (SUBTRON TECHNOLOGY CO., LTD.)

新竹縣湖口工業區光復北路8號 (NO. 8, KUANG FU NORTH ROAD, HU KOU, HSIN-CHU INDUSTRIAL PARK, HSIN-CHU, TAIWAN, R. O. C.)

以下測試樣品係由申請廠商所提供及確認 (The following sample(s) was/were submitted and identified by the applicant as):

送樣廠商(Sample Submitted By)

旭德科技股份有限公司 (SUBTRON TECHNOLOGY CO., LTD.)

樣品名稱(Sample Name)

Ni PLATING LAYER

收件日(Sample Receiving Date)

28-Oct-2022

測試期間(Testing Period)

: 28-Oct-2022 to 04-Nov-2022

測試需求(Test Requested)

(1) 依據客戶指定、參考RoHS 2011/65/EU Annex II及其修訂指令(EU) 2015/863測 試鎘、鉛、汞、六價鉻、多溴聯苯、多溴聯苯醚, DBP, BBP, DEHP, DIBP。 (As specified by client, with reference to RoHS 2011/65/EU Annex II and amending Directive (EU) 2015/863 to determine Cadmium, Lead, Mercury, Cr(VI), PBBs, PBDEs, DBP, BBP, DEHP, DIBP contents in the submitted sample(s).)

(2) 其他測試項目請見下一頁。 (Please refer to next pages for the other item(s).) 請參閱下一頁 (Please refer to following pages.)

測試結果(Test Results) :

結 論(Conclusion) :

(1) 根據客戶所提供的樣品,其編、鉛、汞、六價鉻、多溴聯苯、多溴聯苯醚, DBP, BBP, DEHP, DIBP的測試結果符合RoHS 2011/65/EU Annex II暨其修訂指令(EU)

sample(s), the test results of Cadmium, Lead, Mercury, Cr(VI), PBBs, PBDEs, DBP, BBP, DEHP, DIBP comply with the limits as set by RoHS Directive (EU)

2015/863 amending Annex II to Directive 2011/65/EU.)

Troy Chang / Department Malager
Signed for and on behalf of Alwah
SGS TAIWAN LTD.
Chemical Laboratory - Taipei



PIN CODE: 4BF4AB5B



Test Report

號碼(No.): ETR22A04718 日期(Date): 04-Nov-2022

頁數(Page): 2 of 13

旭德科技股份有限公司 (SUBTRON TECHNOLOGY CO., LTD.)

新竹縣湖口工業區光復北路8號 (NO. 8, KUANG FU NORTH ROAD, HU KOU, HSIN-CHU INDUSTRIAL PARK, HSIN-CHU, TAIWAN, R. O. C.)

測試部位敘述 (Test Part Description)

No.1 : 銀色金屬片 (SILVER COLORED METAL SHEET)

測試結果 (Test Results)

測試項目	測試方法	單位	MDL	結果	限值
(Test Items)	(Method)	(Unit)		(Result)	(Limit)
				No.1	
鎘 (Cd) (Cadmium (Cd)) (CAS No.: 7440-	參考IEC 62321-5: 2013,以感應耦合電漿	mg/kg	2	n.d.	100
43-9)	發射光譜儀分析。(With reference to IEC				
	62321-5: 2013, analysis was performed				
	by ICP-OES.)				
鉛 (Pb) (Lead (Pb)) (CAS No.: 7439-92-1)		mg/kg	2	n.d.	1000
	發射光譜儀分析。(With reference to IEC				
	62321-5: 2013, analysis was performed				
	by ICP-OES.)				
汞 (Hg) (Mercury (Hg)) (CAS No.: 7439-	參考IEC 62321-4: 2013+ AMD1: 2017 ·	mg/kg	2	n.d.	1000
97-6)	以感應耦合電漿發射光譜儀分析。(With				
	reference to IEC 62321-4: 2013+ AMD1:				
	2017, analysis was performed by ICP-				
\ \(\tag{\frac{1}{2}} \)	OES.)				
六價鉻 (Hexavalent Chromium) Cr(VI)	參考IEC 62321-7-1: 2015 · 以紫外光-可見	μg/cm²	0.1	n.d.	-
(CAS No.: 18540-29-9) (#2)	光分光光度計分析。(With reference to				
	IEC 62321-7-1: 2015, analysis was				
\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\	performed by UV-VIS.)				
一溴聯苯 (Monobromobiphenyl)		mg/kg	5	n.d.	-
二溴聯苯 (Dibromobiphenyl)		mg/kg	5	n.d.	-
三溴聯苯 (Tribromobiphenyl)		mg/kg	5	n.d.	-
四溴聯苯 (Tetrabromobiphenyl)	参考IEC 62321-6: 2015,以氣相層析儀/質	mg/kg	5	n.d.	-
五溴聯苯 (Pentabromobiphenyl)	譜儀分析。(With reference to IEC 62321-6: 2015, analysis was performed by	mg/kg	5	n.d.	-
六溴聯苯 (Hexabromobiphenyl)		mg/kg	5	n.d.	-
七溴聯苯 (Heptabromobiphenyl)	GC/MS.)	mg/kg	5	n.d.	-
八溴聯苯 (Octabromobiphenyl)		mg/kg	5	n.d.	-
九溴聯苯 (Nonabromobiphenyl)		mg/kg	5	n.d.	-
十溴聯苯 (Decabromobiphenyl)		mg/kg	5	n.d.	-
多溴聯苯總和 (Sum of PBBs)		mg/kg	-	n.d.	1000



Test Report

號碼(No.): ETR22A04718 日期(Date): 04-Nov-2022 頁數(Page): 3 of 13

旭德科技股份有限公司 (SUBTRON TECHNOLOGY CO., LTD.) 新竹縣湖口工業區光復北路8號 (NO. 8, KUANG FU NORTH ROAD, HU KOU, HSIN-CHU INDUSTRIAL PARK, HSIN-CHU, TAIWAN, R. O. C.)

測試項目	測試方法	單位	MDL	結果	限值
(Test Items)	(Method)	(Unit)		(Result)	(Limit)
				No.1	
一溴聯苯醚 (Monobromodiphenyl ether)		mg/kg	5	n.d.	-
二溴聯苯醚 (Dibromodiphenyl ether)		mg/kg	5	n.d.	-
三溴聯苯醚 (Tribromodiphenyl ether)		mg/kg	5	n.d.	-
四溴聯苯醚 (Tetrabromodiphenyl ether)	 參考IEC 62321-6: 2015,以氣相層析儀/質	mg/kg	5	n.d.	-
五溴聯苯醚 (Pentabromodiphenyl ether)	iii 儀分析。(With reference to IEC 62321-	mg/kg	5	n.d.	-
六溴聯苯醚 (Hexabromodiphenyl ether)	6: 2015, analysis was performed by	mg/kg	5	n.d.	-
七溴聯苯醚 (Heptabromodiphenyl ether)	GC/MS.)	mg/kg	5	n.d.	-
八溴聯苯醚 (Octabromodiphenyl ether)	GC/1413.)	mg/kg	5	n.d.	-
九溴聯苯醚 (Nonabromodiphenyl ether)		mg/kg	5	n.d.	-
十溴聯苯醚 (Decabromodiphenyl ether)		mg/kg	5	n.d.	-
多溴聯苯醚總和 (Sum of PBDEs)		mg/kg	-	n.d.	1000
鄰苯二甲酸丁苯甲酯 (BBP) (Butyl benzyl		mg/kg	50	n.d.	1000
phthalate (BBP)) (CAS No.: 85-68-7)					
鄰苯二甲酸二丁酯 (DBP) (Dibutyl		mg/kg	50	n.d.	1000
phthalate (DBP)) (CAS No.: 84-74-2)					
鄰苯二甲酸二(2-乙基己基)酯 (DEHP) (Di-		mg/kg	50	n.d.	1000
(2-ethylhexyl) phthalate (DEHP)) (CAS					
No.: 117-81-7)	 參考IEC 62321-8: 2017 · 以氣相層析儀/質				
鄰苯二甲酸二異丁酯 (DIBP) (Diisobutyl	iii 儀分析。(With reference to IEC 62321-	mg/kg	50	n.d.	1000
phthalate (DIBP)) (CAS No.: 84-69-5)	8: 2017, analysis was performed by				
鄰苯二甲酸二異癸酯 (DIDP) (Diisodecyl	GC/MS.)	mg/kg	50	n.d.	-
phthalate (DIDP)) (CAS No.: 26761-40-	3 5, 1113.9				
0, 68515-49-1)					
鄰苯二甲酸二異壬酯 (DINP) (Diisononyl		mg/kg	50	n.d.	-
phthalate (DINP)) (CAS No.: 28553-12-					
0, 68515-48-0)					
鄰苯二甲酸二正辛酯 (DNOP) (Di-n-octyl		mg/kg	50	n.d.	-
phthalate (DNOP)) (CAS No.: 117-84-0)					



Test Report

號碼(No.): ETR22A04718 日

日期(Date): 04-Nov-2022

頁數(Page): 4 of 13

旭德科技股份有限公司 (SUBTRON TECHNOLOGY CO., LTD.)

新竹縣湖口工業區光復北路8號 (NO. 8, KUANG FU NORTH ROAD, HU KOU, HSIN-CHU INDUSTRIAL PARK, HSIN-CHU, TAIWAN, R. O. C.)

測試項目	測試方法	單位	MDL	結果	限值
(Test Items)	(Method)	(Unit)		(Result)	(Limit)
				No.1	
六溴環十二烷及所有主要被辨別出的異構	參考IEC 62321: 2008 · 以氣相層析儀/質譜	mg/kg	5	n.d.	-
物(HBCDD) (α- HBCDD, β- HBCDD, γ-	儀分析。(With reference to IEC 62321:				
HBCDD) (Hexabromocyclododecane	2008, analysis was performed by				
(HBCDD) and all major	GC/MS.)				
diastereoisomers identified (α - HBCDD,					
β- HBCDD, γ- HBCDD)) (CAS No.:					
25637-99-4, 3194-55-6 (134237-51-7,					
134237-50-6, 134237-52-8))					
氟 (F) (Fluorine (F)) (CAS No.: 14762-94-		mg/kg	50	n.d.	-
8)					
氯 (CI) (Chlorine (CI)) (CAS No.: 22537-	參考BS EN 14582: 2016,以離子層析儀分	mg/kg	50	n.d.	=
15-1)	析。(With reference to BS EN 14582:				
溴 (Br) (Bromine (Br)) (CAS No.: 10097-	2016, analysis was performed by IC.)	mg/kg	50	n.d.	=
32-2)					
碘 (I) (Iodine (I)) (CAS No.: 14362-44-8)		mg/kg	50	n.d.	-
全氟辛烷磺酸及其鹽類 (PFOS and its	參考CEN/TS 15968: 2010 · 以液相層析串	mg/kg	0.01	n.d.	=
salts) (CAS No.: 1763-23-1 and its salts)	聯質譜儀分析。(With reference to				
全氟辛酸及其鹽類 (PFOA and its salts)	CEN/TS 15968: 2010, analysis was	mg/kg	0.01	n.d.	-
(CAS No.: 335-67-1 and its salts)	performed by LC/MS/MS.)				
銻 (Sb) (Antimony (Sb)) (CAS No.: 7440-	參考US EPA 3050B: 1996,以感應耦合電	mg/kg	2	n.d.	-
36-0)	漿發射光譜儀分析。(With reference to				
	US EPA 3050B: 1996, analysis was				
	performed by ICP-OES.)				
鈹 (Be) (Beryllium (Be)) (CAS No.: 7440-	參考US EPA 3050B: 1996 · 以感應耦合電	mg/kg	2	n.d.	-
41-7)	漿發射光譜儀分析。(With reference to				
	US EPA 3050B: 1996, analysis was				
	performed by ICP-OES.)				



Test Report

號碼(No.): ETR22A04718 日期(Date): 04-Nov-2022 頁數(Page): 5 of 13

旭德科技股份有限公司 (SUBTRON TECHNOLOGY CO., LTD.)

新竹縣湖口工業區光復北路8號 (NO. 8, KUANG FU NORTH ROAD, HU KOU, HSIN-CHU INDUSTRIAL PARK, HSIN-CHU, TAIWAN, R. O. C.)

備註(Note):

- 1. mg/kg = ppm; 0.1wt% = 0.1% = 1000ppm
- 2. MDL = Method Detection Limit (方法偵測極限值)
- 3. n.d. = Not Detected (未檢出); 小於MDL / Less than MDL
- 4. "-" = Not Regulated (無規格值)
- 5. 全氟辛烷磺酸及其鹽類包含等物質 (PFOS and its salts including): CAS No.: 1763-23-1, 2795-39-3, 29457-72-5, 29081-56-9, 70225-14-8, 56773-42-3, 251099-16-8, 307-35-7, 91036-71-4, 4021-47-0 and others.
- 6. 全氟辛酸及其鹽類包含等物質 (PFOA and its salts including): CAS No.: 335-67-1, 335-95-5, 2395-00-8, 335-93-3, 335-66-0, 3825-26-1 and others.
- 7. (#2) =
 - a. 當六價鉻結果大於 $0.13~\mu g/cm^2$ ·表示樣品表層含有六價鉻。(The sample is positive for Cr(VI) if the Cr(VI) concentration is greater than $0.13~\mu g/cm^2$. The sample coating is considered to contain Cr(VI).) b. 當六價鉻結果為n.d. (濃度小於 $0.10~\mu g/cm^2$)·表示表層不含六價鉻。(The sample is negative for Cr(VI) if Cr(VI) is n.d. (concentration less than $0.10~\mu g/cm^2$). The coating is considered a non-Cr(VI) based coating) c. 當六價鉻結果介於0.10~D0.13 $\mu g/cm^2$ 時,無法確定塗層是否含有六價鉻。(The result between $0.10~\mu g/cm^2$ and $0.13~\mu g/cm^2$ is considered to be inconclusive unavoidable coating variations may influence the determination.)
- 8. 除非另有說明·參照ILAC-G8:09/2019·採用簡單二元(w=0)允收規則進行符合性判定;根據此規則·符合性結果之判定係以測試結果與限值做比較。(Unless otherwise stated, the decision rule for conformity reporting is based on Binary Statement for Simple Acceptance Rule (w=0) stated in ILAC-G8:09/2019. According to this rule, the judgement of conformity is based on the comparing test results with limits.)



Test Report

號碼(No.): ETR22A04718

日期(Date): 04-Nov-2022

頁數(Page): 6 of 13


旭德科技股份有限公司 (SUBTRON TECHNOLOGY CO., LTD.)

新竹縣湖口工業區光復北路8號 (NO. 8, KUANG FU NORTH ROAD, HU KOU, HSIN-CHU INDUSTRIAL PARK, HSIN-CHU, TAIWAN, R. O. C.)

重金屬流程圖 / Analytical flow chart of heavy metal

根據以下的流程圖之條件,樣品已完全溶解。(六價鉻測試方法除外)

These samples were dissolved totally by pre-conditioning method according to below flow chart. (Cr^{6+} test method excluded)





Test Report

號碼(No.): ETR22A04718


日期(Date): 04-Nov-2022

頁數(Page): 7 of 13

旭德科技股份有限公司 (SUBTRON TECHNOLOGY CO., LTD.)

新竹縣湖口工業區光復北路8號 (NO. 8, KUANG FU NORTH ROAD, HU KOU, HSIN-CHU INDUSTRIAL PARK, HSIN-CHU, TAIWAN, R. O. C.)

多溴聯苯/多溴聯苯醚分析流程圖 / Analytical flow chart - PBBs/PBDEs





Test Report

號碼(No.): ETR22A04718


日期(Date): 04-Nov-2022

頁數(Page): 8 of 13

旭德科技股份有限公司 (SUBTRON TECHNOLOGY CO., LTD.) 新竹縣湖口工業區光復北路8號 (NO. 8, KUANG FU NORTH ROAD, HU KOU, HSIN-CHU INDUSTRIAL PARK, HSIN-CHU, TAIWAN, R. O. C.)

可塑劑分析流程圖 / Analytical flow chart - Phthalate

【測試方法/Test method: IEC 62321-8】





Test Report


號碼(No.): ETR22A04718 日期(Date): 04-Nov-2022

頁數(Page): 9 of 13

旭德科技股份有限公司 (SUBTRON TECHNOLOGY CO., LTD.)

新竹縣湖口工業區光復北路8號 (NO. 8, KUANG FU NORTH ROAD, HU KOU, HSIN-CHU INDUSTRIAL PARK, HSIN-CHU, TAIWAN, R. O. C.)

六溴環十二烷分析流程圖 / Analytical flow chart - HBCDD





Test Report

號碼(No.): ETR22A04718


日期(Date): 04-Nov-2022

頁數(Page): 10 of 13

旭德科技股份有限公司 (SUBTRON TECHNOLOGY CO., LTD.)

新竹縣湖口工業區光復北路8號 (NO. 8, KUANG FU NORTH ROAD, HU KOU, HSIN-CHU INDUSTRIAL PARK, HSIN-CHU, TAIWAN, R. O. C.)

鹵素分析流程圖 / Analytical flow chart - Halogen





Test Report

號碼(No.): ETR22A04718


日期(Date): 04-Nov-2022

頁數(Page): 11 of 13

旭德科技股份有限公司 (SUBTRON TECHNOLOGY CO., LTD.)

新竹縣湖口工業區光復北路8號 (NO. 8, KUANG FU NORTH ROAD, HU KOU, HSIN-CHU INDUSTRIAL PARK, HSIN-CHU, TAIWAN, R. O. C.)

全氟化合物(包含全氟辛酸/全氟辛烷磺酸/其相關化合物等等)分析流程圖 / Analytical flow chart – PFAS (including PFOA/PFOS/its related compound, etc.)





Test Report

號碼(No.): ETR22A04718

日期(Date): 04-Nov-2022

頁數(Page): 12 of 13


旭德科技股份有限公司 (SUBTRON TECHNOLOGY CO., LTD.)

新竹縣湖口工業區光復北路8號 (NO. 8, KUANG FU NORTH ROAD, HU KOU, HSIN-CHU INDUSTRIAL PARK, HSIN-CHU, TAIWAN, R. O. C.)

元素以 ICP-OES 分析的消化流程圖

(Flow chart of digestion for the elements analysis performed by ICP-OES)

根據以下的流程圖之條件,樣品已完全溶解。 / These samples were dissolved totally by pre-conditioning method according to below flow chart.



鋼,銅,鋁,焊錫 / Steel, copper, aluminum, solder	王水,硝酸,鹽酸,氫氟酸,雙氧水 / Aqua regia, HNO ₃ , HCl, HF, H ₂ O ₂
玻璃 / Glass	硝酸,氫氟酸 / HNO ₃ ,HF
金,鉑,鈀,陶瓷 / Gold, platinum, palladium, ceramic	王水 / Aqua regia
銀 / Silver	硝酸 / HNO ₃
塑膠 / Plastic	硫酸,雙氧水,硝酸,鹽酸 / H ₂ SO ₄ , H ₂ O ₂ , HNO ₃ , HCl
其他 / Others	加入適當的試劑至完全溶解 / Added appropriate reagent to total digestion



Test Report

號碼(No.): ETR22A04718 日期(Date): 04-Nov-2022

頁數(Page): 13 of 13

旭德科技股份有限公司 (SUBTRON TECHNOLOGY CO., LTD.) 新竹縣湖口工業區光復北路8號 (NO. 8, KUANG FU NORTH ROAD, HU KOU, HSIN-CHU INDUSTRIAL PARK, HSIN-CHU, TAIWAN, R. O. C.)

* 照片中如有箭頭標示,則表示為實際檢測之樣品/部位. * (The tested sample / part is marked by an arrow if it's shown on the photo.)

ETR22A04718



** 報告結尾 (End of Report) **