

## Test Report No. F690101/LF-CTSAYAA22-14274

Issued Date : 2022. 03. 25

Page 1 of 3

#### DUK SAN HI-METAL CO., LTD.

66, Muryong 1-ro Buk-gu, Ulsan Korea

The following sample(s) was/were submitted and identified by/on behalf of the client as:-

SGS File No.	: AYAA22-14274		
Product Name	: Sn0.7Cu		
Item No./Part No.	: N/A		
Received Date	: 2022. 03. 22		
Test Period	: 2022. 03. 22 to 2022. 03. 25		
Test Results	: For further details, please refer to following page(s)		

SGS Korea Co., Ltd.

Tommy Oh / Chemical Lab Mgr

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <<u>http://www.sgs.com/en/Terms-and-Conditions.aspx></u> and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at <a href="https://www.sgs.com/en/terms-and-conditions/terms-e-document">https://www.sgs.com/en/terms-and-conditions.aspx></a> and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at <a href="https://www.sgs.com/en/terms-and-conditions/terms-e-document">https://www.sgs.com/en/terms-and-conditions/terms-e-document</a>. Attention is drawn to the limitation of Hability, indemnitication and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its information only and whith the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced except in full, without prior written approval of the Company. Any unauthorized alteration, forger or taskingation of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s).



322, The O valley, 76, LS-ro, Dongan-gu, Anyang-si, Gyeonggi-do, Korea 14117 t +82 (0)31 4608 000 f +82 (0)31 4608 059 <u>http://www.sasgroup.kr.</u>



# Test Report No. F690101/LF-CTSAYAA22-14274

Issued Date : 2022. 03. 25

Page 2 of 3

Sample No.	: AYAA22-14274.001
Sample Description	: Sn0.7Cu
Item No./Part No.	: N/A
Materials	: N/A

#### **Phthalates**

Test Items	Unit	Test Method	MDL	Results
Di-(2-ethylhexyl) phthalate (DEHP)	mg/kg	With reference to IEC 62321-8 : 2017, by GC-MS	50	N.D.
Di-butyl phthalate (DBP)	mg/kg	With reference to IEC 62321-8 : 2017, by GC-MS	50	N.D.
Benzyl butyl phthalate (BBP)	mg/kg	With reference to IEC 62321-8 : 2017, by GC-MS	50	N.D.
Di-isobutyl phthalate (DIBP)	mg/kg	With reference to IEC 62321-8 : 2017, by GC-MS	50	N.D.

NOTE: (1) N.D. = Not detected. (<MDL)

(2) mg/kg = ppm, ug/kg = ppb, mg/L = ppm

(3) MDL = Method Detection Limit


(4) - = No regulation

(5) \*\* = Qualitative analysis (No Unit)

(6) Negative = Undetectable / Positive = Detectable

(7) The results shown in this test report refer only to the sample(s) tested unless otherwise stated.

This test report is not related to Korea Laboratory Accreditation Scheme.




This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <<u>http://www.sgs.com/en/Terms-and-Conditions.aspx></u> and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at <a href="https://www.sgs.com/en/terms-and-conditions/terms-e-document">https://www.sgs.com/en/terms-and-conditions/terms-e-document</a>. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or faisification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s).

322, The O valley, 76, LS-ro, Dongan-gu, Anyang-si, Gyeonggi-do, Korea 14117 t+82 (0)31 4608 000 f+82 (0)31 4608 059 <u>http://www.sgsgroup.kr</u>



Test Report No. F690101/LF-CTSAYAA22-14274



### Flow Chart for PhthalateTest

\*\*\* End of Report \*\*\*

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <<u>http://www.sgs.com/en/Terms-and-Conditions.aspx></u> and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at <a href="https://www.sgs.com/en/terms-and-conditions/terms-e-document">https://www.sgs.com/en/terms-and-conditions.terms-e-document</a>. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s).

322, The O valley, 76, LS-ro, Dongan-gu, Anyang-si, Gyeonggi-do, Korea 14117 t +82 (0)31 4608 000 f +82 (0)31 4608 059 <u>http://www.sgsgroup.kr</u>.