

No. CPSA/231123746-CB33993 Job Ref. C&P/2023-10-23-006

REPORTED DATE:

01-December-2023

RESONAC MATERIALS MALAYSIA SDN BHD

NO. 2512, JALAN PERUSAHAAN BARU, KAWASAN PERUSAHAAN PERAI, 13600 PERAI, PENANG, MALAYSIA.

The following sample(s) was/were submitted and identified by applicant as:

SAMPLE DESCRIPTION	: EPOXY MOLDING COMPOUND CEL-8240HF 16 SERIES			
SAMPLE RECEIVED	: 23-October-2023			
TESTING PERIOD	: 23-October-2023 to 01-December-2023			
TEST REQUESTED TEST METHOD TEST RESULTS	 Selected test(s) as requested by customer -PLEASE REFER TO NEXT PAGE(S)- -PLEASE REFER TO NEXT PAGE(S)- 			



Page 1 of 7

SIGNED FOR AND ON BEHALF OF SGS (MALAYSIA) SDN BHD 10871-1 TAY SIAM, PINE TECHNICAL MANAGER IKM NO. M/3452/6047/11/12

Test Report Form No.: SGS/TR/CP/001, Ver: 2.0, Effective Date: 15/03/2021

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at https://www.sgs.com/en/terms-and-conditions and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at <a href="https://www.sgs.com/en/terms-end-conditions/terms-end-condi

SGS (Malaysia) Sdn.Bhd. (Company No. 10871-T)

Lot 4, Persiaran Jubli Perak, Seksyen 22, 40300 Shah Alam, Selangor Darul Ehsan, Malaysia. t +6(03) 7627 0080 f +6 (03) 7627 0082 www.sgs.com



No. CPSA/231123746-CB33993 Job Ref. C&P/2023-10-23-006

REPORTED DATE:

01-December-2023

TEST RESULTS:

Test Part Description

Sample Description: -PLEASE REFER TO PAGE 1-

RoHS Directive (EU) 2015/863 amending Annex II to Directive 2011/65/EU

Test Parameter(s):	Unit	Unit Test Method		MDL	Limit
Cadmium (Cd)	mg/kg	With reference to IEC 62321-5:2013, determination of Cadmium by ICP-OES.	N.D.	2	Max 100
Lead (Pb)	mg/kg	With reference to IEC 62321-5:2013, determination of Lead by ICP-OES.	N.D.	2	Max 1000
Mercury (Hg)	mg/kg	With reference to IEC 62321-4:2013+A1:2017, determination of Mercury by ICP-OES.	N.D.	2	Max 1000
Hexavalent Chromium (CrVI)	mg/kg	With reference to IEC 62321-7-2:2017, determination of Hexavalent Chromium by Colorimetric Method using UV-Vis.	N.D.	8	Max 1000
Sum of PBBs	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	Max 1000
Monobromobiphenyl	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Dibromobiphenyl	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Tribromobiphenyl	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Tetrabromobiphenyl	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Pentabromobiphenyl	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Hexabromobiphenyl	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Heptabromobiphenyl	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Octabromobiphenyl	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Nonabromobiphenyl	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Decabromobiphenyl	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-

SIGNED FOR AND ON BEHALF OF



Test Report Form No.: SGS/TR/CP/001, Ver: 2.0, Effective Date: 15/03/2021

Page 2 of 7

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at https://www.sgs.com/en/terms-and-conditions and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at <a href="https://www.sgs.com/en/terms-end-conditions/terms-end-condi

SGS (Malaysia) Sdn.Bhd. (Company No. 10871-T)

Lot 4, Persiaran Jubli Perak, Seksyen 22, 40300 Shah Alam, Selangor Darul Ehsan, Malaysia. t +6(03) 7627 0080 $\,$ f +6 (03) 7627 0082 $\,$ www.sgs.com



No. CPSA/231123746-CB33993 Job Ref. C&P/2023-10-23-006

REPORTED DATE:

01-December-2023

TEST RESULTS:

Test Part Description

Sample Description: -PLEASE REFER TO PAGE 1-

RoHS Directive (EU) 2015/863 amending Annex II to Directive 2011/65/EU

Test Parameter(s):	Parameter(s): Unit Test Method		Result	MDL	Limit
Sum of PBDEs	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	Max 1000
Monobromodiphenyl ether	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Dibromodiphenyl ether	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Tribromodiphenyl ether	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Tetrabromodiphenyl ether	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Pentabromodiphenyl ether	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Hexabromodiphenyl ether	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Heptabromodiphenyl ether	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Octabromodiphenyl ether	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Nonabromodiphenyl ether	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-
Decabromodiphenyl ether	mg/kg	With reference to IEC 62321-6:2015, determination of PBBs and PBDEs by GC-MS.	N.D.	5	-

SIGNED FOR AND ON BEHALF OF SGS (MALAYSIA) SDN BHD ŝ

TAY SIAM, PINE TECHNICAL MANAGER IKM NO. M/3452/6047/11/12

Test Report Form No.: SGS/TR/CP/001, Ver: 2.0, Effective Date: 15/03/2021

Page 3 of 7

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at https://www.sgs.com/en/terms-and-conditions and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at <a href="https://www.sgs.com/en/terms-end-conditions/terms-end-condi

SGS (Malaysia) Sdn.Bhd. (Company No. 10871-T)

10871-T

Lot 4, Persiaran Jubli Perak, Seksyen 22, 40300 Shah Alam, Selangor Darul Ehsan, Malaysia. t +6(03) 7627 0080 $\,$ f +6 (03) 7627 0082 $\,$ www.sgs.com



No. CPSA/231123746-CB33993 Job Ref. C&P/2023-10-23-006

REPORTED DATE: 01-December-2023

TEST RESULTS:

Test Part Description

Sample Description: -PLEASE REFER TO PAGE 1-

RoHS Directive (EU) 2015/863 amending Annex II to Directive 2011/65/EU

Test Parameter(s):	Unit	Test Method	Result	MDL	Limit
Dibutyl phthalate (DBP) (CAS No. 84-74-2)	mg/kg	With reference to IEC 62321-8:2017, determination of phthalates by GC-MS.	N.D.	50	Max 1000
Benzyl butyl phthalate (BBP) (CAS No. 85-68-7)	mg/kg	With reference to IEC 62321-8:2017, determination of phthalates by GC-MS.	N.D.	50	Max 1000
Di(2-ethylhexyl) phthalate (DEHP) (CAS No. 117-81-7)	mg/kg	With reference to IEC 62321-8:2017, determination of phthalates by GC-MS.	N.D.	50	Max 1000
Diisobutyl phthalate (DIBP) mg/kg With reference to IEC 62321-8:2017, determination of phthalates by GC-MS.		N.D.	50	Max 1000	

Note : (a) mg/kg = ppm ; (0.1wt% = 1000ppm)

- (b) N.D. = Not Detected
- (c) MDL = Method Detection Limit
- (d) = Not regulated

(e) The maximum permissible limit is quoted from RoHS Directive (EU) 2015/863.

- (f) a. The sample is positive for CrVI if the CrVI concentration is greater than 0.13 μg/cm². The sample coating is considered to contain CrVI.
 - b. The sample is negative for CrVI if CrVI is N.D. (concentration less than 0.10 µg/cm²). The coating is considered a non-CrVI based coating.
 - c. The result between 0.10 µg/cm² and 0.13 µg/cm² is considered to be inconclusive unavoidable coating variations may influence the determination.

For corrosion protection coatings on metals: Information on storage conditions and production date of the tested sample is unavailable and thus results of Cr(VI) represent status of the sample at the time of testing.

(g)The restriction of DEHP, BBP, DBP and DIBP shall apply to medical devices, including in vitro medical devices, and monitoring and control instruments, including industrial monitoring and control instruments, from 22 July 2021.



Test Report Form No.: SGS/TR/CP/001, Ver: 2.0, Effective Date: 15/03/2021

Page 4 of 7

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at https://www.sgs.com/en/terms-and-conditions and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at <a href="https://www.sgs.com/en/terms-end-conditions/terms-end-condi

SGS	(Mala	ysia) Sdn.Bhd.	L
(Compai	ny Ni	b. 10871-T)	L

n.Bhd. 871-1) Lot 4, Persiaran Jubli Perak,Seksyen 22, 40300 Shah Alam, Selangor Darul Ehsan, Malaysia. t +6(03) 7627 0080 f +6 (03) 7627 0082 www.sgs.com



No. CPSA/231123746-CB33993 Job Ref. C&P/2023-10-23-006

REPORTED DATE: 01-De

01-December-2023

Test Part Description :

Sample Description:

-PLEASE REFER TO PAGE 1-



SGS authenticate the photo on original report only



Test Report Form No.: SGS/TR/CP/001, Ver: 2.0, Effective Date: 15/03/2021


Page 5 of 7

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at https://www.sgs.com/en/terms-and-conditions and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at <a href="https://www.sgs.com/en/terms-end-conditions/terms-end-condi

SGS (Malaysia) Sdn.Bhd. (Company No. 10871-T)

n.Bhd. 871-T) Lot 4, Persiaran Jubli Perak,Seksyen 22, 40300 Shah Alam, Selangor Darul Ehsan, Malaysia. t +6(03) 7627 0080 f +6 (03) 7627 0082 www.sgs.com







Test Report Form No.: SGS/TR/CP/001, Ver: 2.0, Effective Date: 15/03/2021

Page 6 of 7

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at https://www.sgs.com/en/terms-and-conditions and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at <a href="https://www.sgs.com/en/terms-end-conditions/terms-end-conditins/terms-end-condit

SGS (Malaysia) Sdn.Bhd. (Company No. 10871-T)


 Bhd.
 Lot 4, Persiaran Jubli Perak, Seksyen 22, 40300 Shah Alam, Selangor Darul Ehsan, Malaysia.

 11-1)
 t +6(03) 7627 0080 f +6 (03) 7627 0082 www.sgs.com



No. CPSA/231123746-CB33993 Job Ref. C&P/2023-10-23-006

REPORTED DATE: 01-December-2023





Test Report Form No.: SGS/TR/CP/001, Ver: 2.0, Effective Date: 15/03/2021

*** End of test report ***

Page 7 of 7

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at https://www.sgs.com/en/terms-and-conditions and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at <a href="https://www.sgs.com/en/terms-end-conditions/terms-end-condi

SGS (Malaysia) Sdn.Bhd. (Company No. 10871-T)

Lot 4, Persiaran Jubli Perak, Seksyen 22, 40300 Shah Alam, Selangor Darul Ehsan, Malaysia. t +6(03) 7627 0080 $\,$ f +6 (03) 7627 0082 $\,$ www.sgs.com