

**Report No.** A2220149517101002







Page 1 of 11

| Company Name<br>shown on Report | MITSUI HIGH-TEC INC.  |  |
|---------------------------------|---|--|
| Address                         | 10-1, KOMINE2-CHOME, YAHATANISHIKU KITAKYUSHU,  | 807-8588, JAPAN  |
| The following sample applicant  | e(s) and sample information was/were submitted and identified by  | y/on the behalf of the   |
| Sample Name                     | Ni plating  |  |
| Sample Received Date            | e Apr. 20, 2022   |  |
| Testing Period                  | Apr. 20, 2022 to Apr. 29, 2022  |  |
| Test Requested                  | As specified by client, to test Lead (Pb), Cadmium (Cd), Mer<br>Chromium (Cr(VI)), Polybrominated Biphenyls (PBBs), Poly<br>Ethers (PBDEs), Beryllium(Be), Antimony(Sb), Hexabromoc<br>Fluorine (F), Chlorine (Cl), Bromine (Br), Iodine (I), Polychl<br>(PCNs), Polychlorinated terphenyls (PCTs), Polychlorinated<br>Phthalates, Short Chain Chlorinated Paraffins (SCCPs), Orga<br>Polyvinyl Chloride (PVC), Perfluorooctane Sulfonates(PFOS<br>Acid(PFOA) in the submitted sample(s). | brominated Diphenyl<br>cyclododecane (HBCDD),<br>orinated Naphthalenes<br>Biphenyls(PCBs),<br>notin compounds, |
| Test Method                     | Please refer to the following page(s).  |  |
| Test Result(s)                  | Please refer to the following page(s).  |  |
| *****                           | ***************************************   | *****  |
| Conclusion                      |   |  |
| Tested Sample                   | According to standard/directive   | Result   |
| Submitted Samp                  | RoHS Directive 2011/65/EU with amendment<br>(EU) 2015/863   | PASS   |

PASS means that the results shown on the report comply with the limits set by RoHS Directive 2011/65/EU with amendment (EU) 2015/863.



maan

Geoage Fong Lab Manager Reviewed by

Polly Cheng

Date

May 3, 2022

No. R392331263

5F-6, No.9, Sec.2, Nankan Rd, Luzhu Dist., Taoyuan, Taiwan



**Report No.** A2220149517101002

**Test Method** 

Page 2 of 11

| Test Item(s)  | Test Method  | Measured<br>Equipment(s) |
|---|--|--------------------------|
| Lead (Pb)   | Refer to IEC 62321-5:2013                          | ICP-OES                  |
| Cadmium (Cd)  | Refer to IEC 62321-5:2013                          | ICP-OES                  |
| Mercury (Hg)  | Refer to IEC 62321-4:2013+AMD1:2017 CSV            | ICP-OES                  |
| Hexavalent Chromium (Cr(VI))                        | IEC 62321-7-1:2015                                 | UV-Vis                   |
| Polybrominated Biphenyls (PBBs)                     | IEC 62321-6:2015                                   | GC-MS                    |
| Polybrominated Diphenyl Ethers (PBDEs)              | IEC 62321-6:2015                                   | GC-MS                    |
| Phthalates (DBP, BBP, DEHP, DIBP)                   | IEC 62321-8:2017                                   | GC-MS                    |
| Beryllium(Be)                                       | Refer to US EPA 3050B:1996 &<br>US EPA 6010D:2018* | ICP-OES                  |
| Antimony(Sb)  | Refer to US EPA 3050B:1996 &<br>US EPA 6010D:2018* | ICP-OES                  |
| Hexabromocyclododecane (HBCDD)                      | Refer to IEC 62321-9:2021*                         | GC-MS                    |
| Fluorine (F)  | EN 14582:2016                                      | IC                       |
| Chlorine (Cl)                                       | EN 14582:2016                                      | IC                       |
| Bromine (Br)  | EN 14582:2016                                      | IC                       |
| Iodine (I)  | EN 14582:2016                                      | IC                       |
| Polychlorinated Naphthalenes (PCNs)                 | Refer to US EPA 3550C:2007 &<br>US EPA 8270E:2017* | GC-MS                    |
| Polychlorinated terphenyls (PCTs)                   | Refer to US EPA 3550C:2007 &<br>US EPA 8270E:2017* | GC-MS                    |
| Polychlorinated Biphenyls(PCBs)                     | Refer to US EPA 3540C:1996 & US EPA 8270E:2017*    | GC-MS                    |
| Perfluorooctane Sulfonates(PFOS)                    | Refer to CEN/TS 15968:2010*                        | LC-MS-MS/LC-MS           |
| Short Chain Chlorinated Paraffins (SCCPs)           | Refer to US EPA 3550C:2007 &<br>US EPA 8270E:2017* | GC-MS(NCI)               |
| Organotin compounds                                 | Refer to ISO 17353:2004(E)*                        | GC-MS                    |
| Polyvinyl Chloride (PVC)                            | Refer to JY/T 001-1996*                            | FT-IR                    |
| Perfluorooctanoic Acid(PFOA)                        | Refer to CEN/TS 15968:2010*                        | LC-MS-MS/LC-MS           |
| Phthalates(DMEP,DNHP,DIDP,DINP,DNOP,<br>DIHP,DHNUP) | Refer to EN 14372:2004(E)*                         | GC-MS                    |



**Report No.** A2220149517101002

| Tested Item(s)                       | Result | MDL                           | Limit      |  |
|--------------------------------------|--------|-------------------------------|------------|--|
| Lead(Pb)                             | N.D.   | 2 mg/kg                       | 1000 mg/kg |  |
| Cadmium(Cd)                          | N.D.   | 2 mg/kg                       | 100 mg/kg  |  |
| Mercury(Hg)                          | N.D.   | 2 mg/kg                       | 1000 mg/kg |  |
| Hexavalent Chromium(Cr(VI))          | N.D. 🔻 | 0.10 μg/cm <sup>2</sup> (LOQ) | 1000 mg/kg |  |
| Tested Item(s)                       | Result | MDL                           | Limit      |  |
| Polybrominated Biphenyls (PBBs)      |        |                               |            |  |
| Monobromobiphenyl                    | N.D.   | 5 mg/kg                       |            |  |
| Dibromobiphenyl                      | N.D.   | 5 mg/kg                       |            |  |
| Tribromobiphenyl                     | N.D.   | 5 mg/kg                       |            |  |
| Tetrabromobiphenyl                   | N.D.   | 5 mg/kg                       |            |  |
| Pentabromobiphenyl                   | N.D.   | 5 mg/kg                       | 1000 mg/kg |  |
| Hexabromobiphenyl                    | N.D.   | 5 mg/kg                       |            |  |
| Heptabromobiphenyl                   | N.D.   | 5 mg/kg                       |            |  |
| Octabromobiphenyl                    | N.D.   | 5 mg/kg                       |            |  |
| Nonabromobiphenyl                    | N.D.   | 5 mg/kg                       |            |  |
| Decabromobiphenyl                    | N.D.   | 5 mg/kg                       |            |  |
| Tested Item(s)                       | Result | MDL                           | Limit      |  |
| Polybrominated Diphenyl Ethers (PBDE | Ls)    |                               |            |  |
| Monobromodiphenyl ether              | N.D.   | 5 mg/kg                       |            |  |
| Dibromodiphenyl ether                | N.D.   | 5 mg/kg                       |            |  |
| Tribromodiphenyl ether               | N.D.   | 5 mg/kg                       | -          |  |
| Tetrabromodiphenyl ether             | N.D.   | 5 mg/kg                       |            |  |
| Pentabromodiphenyl ether             | N.D.   | 5 mg/kg                       | 1000 mg/kg |  |
| Hexabromodiphenyl ether              | N.D.   | 5 mg/kg                       |            |  |
| Heptabromodiphenyl ether             | N.D.   | 5 mg/kg                       |            |  |
| Octabromodiphenyl ether              | N.D.   | 5 mg/kg                       |            |  |
| Nonabromodiphenyl ether              | N.D.   | 5 mg/kg                       |            |  |
| Decabromodiphenyl ether              | N.D.   | 5 mg/kg                       |            |  |



**Report No.** A2220149517101002

| Test Result(s)                                     |        |          | -          |
|--|--------|----------|------------|
| Tested Item(s)                                     | Result | MDL      | Limit      |
| Phthalates (DBP, BBP, DEHP, DIBP)                  |        |          |            |
| Dibutyl phthalate(DBP)<br>CAS#:84-74-2             | N.D.   | 50 mg/kg | 1000 mg/kg |
| Butyl benzyl phthalate(BBP)<br>CAS#:85-68-7        | N.D.   | 50 mg/kg | 1000 mg/kg |
| Di-(2-ethylhexyl) phthalate(DEHP)<br>CAS#:117-81-7 | N.D.   | 50 mg/kg | 1000 mg/kg |
| Diisobutyl phthalate(DIBP)<br>CAS#:84-69-5         | N.D.   | 50 mg/kg | 1000 mg/kg |
| Tested Item(s)                                     | Result |          | MDL        |
| Beryllium(Be)                                      | N.D.   |          | 10 mg/kg   |
| Antimony(Sb)                                       | N.D.   |          | 10 mg/kg   |
| Tested Item(s)                                     | Result |          | MDL        |
| Hexabromocyclododecane(HBCDD)                      | N.D.   |          | 20 mg/kg   |
| Tested Item(s)                                     | Result |          | MDL        |
| Fluorine(F)  | N.D.   |          | 50 mg/kg   |
| Chlorine(Cl)                                       | N.D.   |          | 50 mg/kg   |
| Bromine(Br)  | N.D.   |          | 50 mg/kg   |
| Iodine(I)  | N.D.   |          | 50 mg/kg   |
| Tested Item(s)                                     | Result |          | MDL        |
| Polychlorinated Naphthalenes(PCNs)                 | N.D.   |          | 5 mg/kg    |
| Tested Item(s)                                     | Result |          | MDL        |
| Polychlorinated Triphenyls(PCTs)                   | N.D.   |          | 5 mg/kg    |

Page 4 of 11



**Report No.** A2220149517101002

Test Result(s)

| Tested Item(s)   | Result | MDL       |
|--|--------|-----------|
| Phthalates   |        |           |
| Di-n-octyl phthalate(DNOP)<br>CAS#:117-84-0  | N.D.   | 50 mg/kg  |
| Di-isononyl phthalate(DINP)<br>CAS#:28553-12-0,68515-48-0  | N.D.   | 50 mg/kg  |
| Di-iso-decyl phthalate(DIDP)<br>CAS#:26761-40-0,68515-49-1   | N.D.   | 50 mg/kg  |
| Di-n-hexyl phthalate(DNHP)<br>CAS#:84-75-3   | N.D.   | 50 mg/kg  |
| Bis(2-methoxyethyl) phthalate(DMEP)<br>CAS#:117-82-8   | N.D.   | 50 mg/kg  |
| * <sup>1</sup> 1,2-Benzenedicarboxylic acid,<br>di-(C7-11)-branched and linear alkyl<br>esters(DHNUP)<br>CAS#:68515-42-4                               | N.D.   | 100 mg/kg |
| <ul> <li>*<sup>1</sup>1,2-Benzenedicarboxylic acid,</li> <li>di-C6-8-branched alkyl esters,</li> <li>C7-rich(DIHP)</li> <li>CAS#:71888-89-6</li> </ul> | N.D.   | 100 mg/kg |
| Tested Item(s)   | Result | MDL       |
| Polychlorinated Biphenyls(PCBs)  |        |           |
| Monochlorobiphenyl   | N.D.   | 5 mg/kg   |
| Dichlorobiphenyl   | N.D.   | 5 mg/kg   |
| Trichlorobiphenyl  | N.D.   | 5 mg/kg   |
| Tetrachlorobiphenyl  | N.D.   | 5 mg/kg   |
| Pentachlorobiphenyl  | N.D.   | 5 mg/kg   |
| Hexachlorobiphenyl   | N.D.   | 5 mg/kg   |
| Heptachlorobiphenyl  | N.D.   | 5 mg/kg   |
| Octachlorobiphenyl   | N.D.   | 5 mg/kg   |
| Nonachlorobiphenyl   | N.D.   | 5 mg/kg   |
| Decachlorobiphenyl   | N.D.   | 5 mg/kg   |
| Tested Item(s)   | Result | MDL       |
| Short Chain Chlorinated<br>Paraffins(SCCPs)  | N.D.   | 100 mg/kg |

Page 5 of 11

章 55



**Report No.** A2220149517101002

| Test Result(s)                   |          |            |
|----------------------------------|----------|------------|
| Tested Item(s)                   | Result   | MDL        |
| Organotin compounds              |          |            |
| Dibutyltin(DBT)                  | N.D.     | 5 mg/kg    |
| Tributyltin(TBT)                 | N.D.     | 5 mg/kg    |
| Tributyltin oxide(TBTO) *2       | N.D.     | 5 mg/kg    |
| Dioctyltin(DOT)                  | N.D.     | 5 mg/kg    |
| Triphenyltin(TPHT)               | N.D.     | 5 mg/kg    |
| Tested Item(s)                   | Result   | MDL        |
| Polyvinyl Chloride(PVC)          | Negative | /          |
| Tested Item(s)                   | Result   | MDL        |
| Perfluorooctanoic Acid(PFOA)     | N.D.     | 0.01 mg/kg |
| Tested Item(s)                   | Result   | MDL        |
| Perfluorooctane Sulfonates(PFOS) | N.D.     | 0.01 mg/kg |

Sample/Part Description Silvery plating

#### Remark: The sample(s) had been dissolved totally tested for Lead, Cadmium, Mercury, Beryllium, Antimony.

-MDL = Method Detection Limit

-N.D. = Not Detected (<MDL or LOQ)

-mg/kg = ppm = parts per million

-1000 mg/kg = 0.1%

-LOQ = Limit of Quantification, The LOQ of Hexavalent chromium is 0.10  $\mu$ g/cm<sup>2</sup>

- The sample is negative for Cr(VI) – The Cr(VI) concentration is below 0.10 µg/cm? The coating is considered a non-Cr(VI) based coating.

-Negative = Not contained Polyvinyl Chloride(PVC)

-\*1= In view of the substances are established as UVCB substances (substances of

unknown or variable composition, complex reaction products or biological materials)

consisting of different and variable constituents, the test results are calculated based


on the main constituents of the representative compounds for substances.

-\*<sup>2</sup>= concentration value of Tributyltin oxide by the conversion from the test results of Tributyl Tins.


Note: "\*"indicates the method(s) is (are) not in TAF accreditation scope.

Page 6 of 11












#### **Report No.** A2220149517101002

9. Polychlorinated Naphthalenes (PCNs)





Page 9 of 11



#### **Report No.** A2220149517101002

Page 10 of 11








**Report No.** A2220149517101002

#### Photo(s) of the sample(s)



Statement:

- 1. This report is considered invalid without approved signature, special seal and the seal on the perforation;
- 2. The Company Name shown on Report and Address, the sample(s) and sample information was/were provided by the applicant who should be responsible for the authenticity which CTI hasn't verified;
- 3. The result(s) shown in this report refer(s) only to the sample(s) tested;
- 4. Without written approval of CTI, this report can't be reproduced except in full;
- 5. In case of any discrepancy between the English version and Chinese version of the testing reports (if generated), the Chinese version shall prevail.

\*\*\* End of report \*\*\*

Page 11 of 11