

**Application Note** 

Document Number: AN3409 Rev. 0, 01/2007

# Basic Refrigerator Control Using the MC9RS08KA2

by: Jose Ruiz RTAC Americas

## 1 Introduction

Some refrigerators still have a basic electromechanical circuit that controls the temperature. This application shows how to implement a low-cost, basic temperature control for refrigerators using the MC9RS08KA2. This method can be implemented to control the temperature of any device using a thermoresistor, a potentiometer, resistors and a capacitor.

## 2 Requirements

- MC9RS08KA2 microcontroller (MCU)
- One potentiometer
- One thermoresistor
- One ceramic capacitor
- Two ¼ watt resistors
- CodeWarrior 5.1 development tool

## **Contents**

1	Introduction				
2	Requirements				
3	Imp	lementation			
	3.1	Control Value			
	3.2	Temperature Sensor			
	3.3	Temperature Control Application			
	3.4	Schematic			
4	Cor	nclusion			
	Appendix A				
	NCP18WB333J03RB Thermistor Range Table				
	Appendix B				
	Code Implementation				





# 3 Implementation

The temperature control is implemented with a single potentiometer and a capacitor connected to one MC9RS08KA2 MCU I/O pin. The temperature sensor is a basic voltage divider formed by a resistor and a thermistor. The output is an I/O pin connected to a relay that switches the supply of the refrigerator.

The flow of the program consists of reading the control wheel value followed by reading the sensor voltage and, finally, switching the output ON or OFF according to the control and sensor values.

## 3.1 Control Value

The refrigerator temperature control is a basic RC network connected to an I/O pin. By measuring the charging time of the RC network, we can determine the potentiometer resistance, and therefore, the value you entered. The charge curve of the RC network is used to determine the time the curve takes to go from 0 V to the input-high voltage ( $V_{IH}$ ). This method is used because the MC9RS08KA2 MCU does not have an integrated analog-to-digital converter (ADC).




Figure 1. Temperature Control Implementation

The first step is configuring the control pin as output. Set the pin value to 0 to discharge the capacitor. After the capacitor is fully discharged, change the control pin direction to an input. The capacitor starts charging to  $V_{DD}$ .

When the voltage of the capacitor gets to  $V_{IH}$ , the pin state changes from 0 to 1.

A variable resistor (potentiometer) is used to modify the time the capacitor takes to reach  $V_{IH}$ . Adjusting its resistance varies that time.






Figure 2. Charge Capacitor Waveform

The capacitor voltage is given by the following equation:

$$Vc = Vdd \left(1 - e^{-\frac{t}{rc}}\right)$$
Solving for time
$$t = -rc \ln\left(1 - \frac{Vc}{Vdd}\right)$$

- Vc Voltage of the capacitor
- $\bullet \quad V_{DD} Supply \ voltage \ of \ RC \ network$
- t Time (seconds)
- r Resistance
- c Capacitor

A 10 k $\Omega$  potentiometer and 33 nF capacitor were used in this application note.

From the MC9RS08KA2 datasheet, we know that when  $V_{DD}\!>\!2.3$  V, the  $V_{IH}$  for the inputs is 0.70 x  $V_{DD}$ .

Basic Refrigerator Control Using the MC9RS08KA2, Rev. 0



If the MC9RS08 MCU is supplied with 3.3 V then:

$$V_{IH} = 0.70 \text{ x } V_{DD} = (0.70 \text{ x } 3.3.) = 2.31 \text{ V}$$

Table 1 shows the difference in time using the above with different resistance commercial values.

**Table 1. Time Result According Resistance Values** 

V <sub>DD</sub>	V <sub>IH</sub>	R	С	time
3.3	2.31	1k	33nF	3.973E-05
3.3	2.31	3k	33nF	0.0001192
3.3	2.31	5k	33nF	0.0001987
3.3	2.31	7k	33nF	0.0002781
3.3	2.31	10k	33nF	0.0003973




Figure 3. Charge Curve with Different Resistor

5



## NOTE

The resistor value must not reach 0, or a short circuit can occur.

## 3.1.1 Code Implementation

The first step is to configure the control pin as output, and setting a low level on it, (0). Then wait for the RC network to discharge completely;

```
Pin_Measure:

bset control,PTADD ; Set control pin as Output
bclr control,PTAD ; Discharge RC network
clr ControlValue
lda #$FE

Discharge2:
dbnza Discharge2
```

The following step is to configure the control pin as input and increment a counter while pin state is 0:

```
bclr control,PTADD ; Set Control pin as Input
measure_pin:
    inc ControlValue
    brclr control,PTAD,measure_pin; Inc value while pin is in low state
    rts
```

The controlvalue variable represents the time taken for the capacitor to reach V<sub>IH</sub>.

After the pin reaches the high level, we know the approximate position of the potentiometer entered by the user.

## 3.2 Temperature Sensor

A basic voltage divider with one resistor and one thermoresistor is used to implement the temperature sensor. The thermoresistor resistance depends on the temperature. For each temperature, we have a different voltage in the divider. This value is effectively measured with the ADC implemented by software that uses one resistor, one capacitor, and the analog comparator included in the MC9RS08KA2 MCU.

The voltage divider is composed of the thermoresistor NCP18WB333J03RB and a 82 ohms resistor. It is better to have a big variation in the output voltage of the sensor with a little variation in the temperature.

The supply voltage of the RC network in this application note is 3.3 V and the output voltage of the sensor can be calculated with the next equation.

$$Vout = Vdd \left( \frac{NTC}{NTC + R} \right) = 3.3 \left( \frac{NTC}{NTC + 82} \right)$$



According to the thermoresistor specifications, the resistor range is between 89.61  $\Omega$  to 116.16  $\Omega$  in a range of 4 °C to –0.5 °C (Section Appendix A, "NCP18WB333J03RB Thermistor Range Table"). With those values the following data is calculated:

Temperature	NTC Value	Resistor	V <sub>DD</sub>	Sensor Output
<b>–</b> 1	119.11	82	3.3	1.9544677
- 0.5	116.16	82	3.3	1.9344368
0	113.21	82	3.3	1.9138005
0.5	110.26	82	3.3	1.8925309
1	107.31	82	3.3	1.8705985
1.5	104.36	82	3.3	1.8479717
2	101.41	82	3.3	1.824617
2.5	98.46	82	3.3	1.8004987
3	95.51	82	3.3	1.7755788
3.5	92.56	82	3.3	1.7498167
4	89.61	82	3.3	1.7231688

**Table 2. Sensor Output Voltage** 

Instead of having an ADC module, the MC9RS08KA2 MCU has a basic ADC implemented by software using the analog comparator module. This software ADC is basically composed by a RC network and the analog voltage to be measured. The software measures the time taken by the RC network to reach the sensor input voltage. This ADC by software is fully detailed in the RS08 Quick Reference Guide (RS08QRUG). Download the document at http://www.freescale.com




Figure 4. Sensor Value Input (ADC by Software)

Basic Refrigerator Control Using the MC9RS08KA2, Rev. 0



The formula to calculate the time taken for the capacitor to charge is the same as the temperature control formula:

$$Vc = Vdd \left(1 - e^{-\frac{t}{rc}}\right)$$
 Solving for time  $t = -rc \ln\left(1 - \frac{Vc}{Vdd}\right)$ 

But, for the ADC by software the RC network is fixed. In this case, the resistor value is 10 k $\Omega$ . The capacitor is 0.1  $\mu$ F.

If the sensor values and the capacitor charging curve are graphed together the result is the time the RC network takes to reach the sensor output voltage.




Figure 5. Capacitor Charge Versus Sensor Output Voltage



Based on the bus speed (8 MHz for this application), it is effective to build a table with the timer value according the sensor voltage.

To calculate the timer counts of each sensor voltage the next formula must be applied:

$$TimerCounts = VIH \ time \left( \frac{BusClock}{prescaler} \right)$$

Table 3. Temperature, Sensor Output, and Microcontroller Counts

			Timer	Timer
Temperature	V sensor	V <sub>IH</sub> Time	counts	counts
			(Bus/32)	(Bus/32)
-0.5°C	1.93444	0.0008824	220.5889	110.2944
0°C	1.9138	0.0008674	216.8392	108.4196
0.5°C	1.89253	0.0008521	213.0323	106.5162
1°C	1.8706	0.0008367	209.1667	104.5833
1.5°C	1.84797	0.000821	205.2403	102.6201
2°C	1.82462	0.000805	201.2512	100.6256
2.5°C	1.8005	0.0007888	197.1975	98.59874
3°C	1.77558	0.0007723	193.0769	96.53846
3.5°C	1.74982	0.0007555	188.8873	94.44366
4°C	1.72317	0.0007385	184.6263	92.31315

## 3.2.1 Code Implementation:

```
ADC_Single_conversion:
         ; Discharge Capacitor
bset 1,PTADD
        bclr 1,PTAD
        lda #$FE
waste:
        dbnza waste
        mov #ACMP_ENABLE, ACMPSC
                                           ; ACMP Enabled
        mov #MTIM_ENABLE,MTIMSC
                                           ; Timer Counter Enabled
        wait
                                           ; Wait for Analog Comparator Interrupt
        bset 4,MTIMSC
                                           ; Stop MTIM
        lda MTIMCNT
                                           ; read counter timer value
        sta ADCValue
                                           ;store counter value
        mov #MTIM_STOP_RESET,MTIMSC
                                           ;Stop and reset counter
        mov #HIGH_6_13(SIP1), PAGESEL
        brset 3, MAP_ADDR_6(SIP1),Conv_OK ; branch if ACMP interrupt arrives
        bra ADC_Single_conversion
Conv_OK:
        mov #ACMP_DISABLED, ACMPSC
                                           ; ACMP Disabled, Clear Interrupt flag
        rts
```

Basic Refrigerator Control Using the MC9RS08KA2, Rev. 0



## 3.3 Temperature Control Application

The refrigerator's temperature control has four positions, the range of each one is:

- Position 4:  $0 \, ^{\circ}\text{C} 1 \, ^{\circ}\text{C}$
- Position 3:  $1 \, ^{\circ}\text{C} 2 \, ^{\circ}\text{C}$
- Position 2:  $2 \, ^{\circ}\text{C} 3 \, ^{\circ}\text{C}$
- Position 1:  $3 \, ^{\circ}\text{C} 4 \, ^{\circ}\text{C}$

The control switches on the relay when the temperature is over range. It switches it off when the temperature reaches the window value.

Because of temperature inertia, the window temperature is 1.5 °C. Figure 6 shows the window and the values from it.




Figure 6. Temperature Control Range

Basic Refrigerator Control Using the MC9RS08KA2, Rev. 0



For example, when the temperature position is 1, if the temperature is higher than 4 °C, the relay is closed, and the refrigerator compressor is on. Next, when the temperature reaches 2.5 °C, the application opens the relay and the compressor stops.

This guarantees that the temperature is stable for long periods of time between the ranges and, no matter what; the temperature is never more than 4 °C.

Each temperature limit can be easily changed in the definition part of the main code.

```
; Variable definitions
; Prescaler /64
                SET 92
TEMP1_ON
               SET 99
TEMP1_OFF
TEMP2_ON
                SET 97
TEMP2_OFF
                SET 103
TEMP3_ON
                SET 100
TEMP3_OFF
                SET 107
                 SET 105
TEMP4_ON
TEMP4_OFF
                 SET 111
```

The definition\_ON is the value that closes the relay, and definition\_OFF opens the relay. And the resolution of these values can be adjusted with the timer prescaler.

## 3.3.1 Code Implementation

```
; *
           Comparation (Control vs Temp)
; **********************
comparation:
      lda ControlValue
cmp #65
blo Temp1_4
      cmp #130
blo Temp2_4
      cmp #195
      blo Temp3_4
       mov #04,ControlValue ; selector = 4 (Coldest)
       lda ADCValue
       cmp #TEMP4_ON
       blo Compresor_ON
       cmp #TEMP4_OFF
       bhs Compresor_OFF
       rts
Temp3_4:
       mov #03,ControlValue
                            ; selector = 3 (Mid-Low)
       lda ADCValue
       cmp #TEMP3_ON
       blo Compresor_ON
       cmp #TEMP3_OFF
       bhs Compresor_OFF
Temp2_4:
```

Basic Refrigerator Control Using the MC9RS08KA2, Rev. 0





```
mov #02,ControlValue ; selector = 2 (Mid-High)
        lda ADCValue
        cmp #TEMP2_ON
        blo Compresor_ON
        cmp #TEMP2_OFF
        bhs Compresor_OFF
        rts
Temp1_4:
        mov #01,ControlValue ; selector = 1 (Hot)
        lda ADCValue
        cmp #TEMP1_ON
        blo Compresor_ON
        cmp #TEMP1_OFF
        bhs Compresor_OFF
        rts
Compresor_ON:
                                                    ; Compresor ON
        bset output, PTAD
        rts
Compresor_OFF:
                                                    ; Compresor OFF
        bclr output,PTAD
        rts
```



Conclusion

## 3.4 Schematic




Figure 7. Hardware Schematic

# 4 Conclusion

This application note shows how to implement a simple on-off control system with a low-end 8-bit microcontroller.



# Appendix A NCP18WB333J03RB Thermistor Range Table

Temp (°C)	Resistance (K)
-40	1227.263
-35	874.449
-30	630.851
-25	460.457
-20	339.797
-15	253.363
-10	190.766
-5	144.964
0	111.087
5	85.842
10	66.861
15	52.470
20	41.471
25	33.000
30	26.430
35	21.298
40	17.266
45	14.076
50	11.538
55	9.506
60	7.870
65	6.549
70	5.475
75	4.595
80	3.874
85	3.282
90	2.789
95	2.379
100	2.038
105	1.751
110	1.509
115	1.306
120	1.134
125	0.987



#### Conclusion

# **Appendix B Code Implementation**

```
INCLUDE 'derivative.inc'
                                   ; Include derivative-specific definitions
; export symbols
          XDEF _Startup
          ABSENTRY _Startup
; Variable declarations
ACMP_ENABLE SET
                   $92
ACMP_DISABLED
             SET
                    $20
MTIM_INIT SET MTIM_ENABLE SET
                    $50
                    $40
MTIM_STOP_RESET SET
                   $30
MTIM_64_DIV
              SET
                   $06
FREE_RUN
                   $00
              SET
DEBUG_MODE
              SET
                   $00
RUN_MODE
              SET $01
control
                      SET $04
                      SET $05
output
              SET 94
TEMP1_ON
TEMP1_OFF
              SET 100
TEMP2_ON
              SET 98
TEMP2_OFF
              SET 104
TEMP3_ON
              SET 102
TEMP3_OFF
              SET 108
              SET 106
TEMP4_ON
              SET 112
TEMP4_OFF
MODE:
              EQU
                    DEBUG_MODE
; variable/data section
   ORG RAMStart
ADCValue:
             DS.B 1
             DS.B 1
ControlValue
             DS.B 1
; code section
    ORG ROMStart
MACRO DECLARATION
TRIM_ICS: MACRO
                         ; Macro used to configure the ICS with TRIM
   mov #$FF,PAGESEL
                                ; change to last page
   lda #$FA
                                 ; load the content which TRIM value is store
   tax
                                 ; move A content to X
   lda ,x
                                ; read D[X]
   sta ICSTRM
                                 ; Store TRIM value
```

Basic Refrigerator Control Using the MC9RS08KA2, Rev. 0



```
ENDM
ACK_RTI: MACRO
   mov #HIGH_6_13(SRTISC), PAGESEL
   bset 6,MAP_ADDR_6(SRTISC)
   ENDM
Comparation (Control vs Temp)
comparation:
   lda ControlValue
   cmp #65
   blo Temp1_4
   cmp #130
   blo Temp2_4
   cmp #195
   blo Temp3_4
  mov #04,ControlValue ; selector = 4 (Coldest)
  lda ADCValue
  cmp #TEMP4_ON
  blo Compresor_ON
  cmp #TEMP4_OFF
  bhs Compresor_OFF
  rts
Temp3_4:
  mov #03,ControlValue; selector = 3 (Mid-Low)
  lda ADCValue
  cmp #TEMP3_ON
  blo Compresor_ON
  cmp #TEMP3_OFF
  bhs Compresor_OFF
  rts
Temp2_4:
  mov #02,ControlValue ; selector = 2 (Mid-High)
  lda ADCValue
  cmp #TEMP2_ON
  blo Compresor_ON
  cmp #TEMP2_OFF
  bhs Compresor_OFF
  rts
Temp1_4:
  mov #01,ControlValue; selector = 1 (Hot)
  lda ADCValue
  cmp #TEMP1_ON
  blo Compresor_ON
  cmp #TEMP1_OFF
  bhs Compresor_OFF
  rts
```



#### Conclusion

```
Compresor_ON:
                     ; Compresor ON
  bset output,PTAD
  rts
Compresor_OFF:
                     ; Compresor OFF
  bclr output,PTAD
  rts
CONFIGURES SYSTEM CONTROL
Init mc:
  mov #HIGH_6_13(SOPT), PAGESEL
  mov #$E3, MAP_ADDR_6(SOPT)
                            ; Enable STOP mode and COP with long timeout period
  clr ICSC1
                            ; FLL is selected as Bus Clock
   TRIM_ICS
   clr ICSC2
   bset output, PTADD ; Enable PTA5 as output
; **********************
; *
  Modulus Timer Configuration for ADC
MTIM_ADC_Init:
                            ; Select bus clock as reference, Set prescaler with 64
   mov #MTIM_64_DIV,MTIMCLK
   mov #FREE_RUN,MTIMMOD
                             ; Configure Timer as free running
   mov #MTIM_STOP_RESET,MTIMSC
   rts
; **********************
; *
               ADC Single Conversion
; **********************
ADC_Single_conversion:
  ; Discharge Capacitor
  bset 1,PTADD
  bclr 1,PTAD
   lda #$FE
waste:
  dbnza waste
  ; Start Conversion
  mov #ACMP_ENABLE,ACMPSC
                       ; ACMP Enabled, ACMP+ pin active, Interrupt enabled,
Rising edges detections
  mov #MTIM_ENABLE,MTIMSC
                              ; Timer Counter Enabled
  wait
                                   ; Wait for Analog Comparator Interrupt (match
signals)
  bset 4,MTIMSC
                            ; Stop MTIM
   lda MTIMCNT
                              ; read counter timer value
   sta ADCValue
                           ; store counter value
   mov #MTIM_STOP_RESET,MTIMSC
                             ; Stop and reset counter
   mov #HIGH_6_13(SIP1), PAGESEL
   brset 3, MAP_ADDR_6(SIP1), Conv_OK; branch if ACMP interrupt arrives
   bra ADC_Single_conversion
   ; Comparator Interrupt OK
```



```
Conv_OK:
  mov #ACMP_DISABLED, ACMPSC
                        ; ACMP Disabled, Clear Interrupt flag
Control Value
; *
Pin_Measure:
 \verb|bset control,PTADD| \qquad \textit{ ; Set control pin as Output}
 bclr control, PTAD
                       ; Discharge RC network
 clr ControlValue
  lda #$FE
Discharge2:
  dbnza Discharge2
  bclr control, PTADD ; Set Control pin as Input
measure_pin:
 inc ControlValue
 brclr control, PTAD, measure_pin; Inc value while pin is in low state
; *
           RTI Module Configuration
; **********************
Init_RTI:
 mov #HIGH_6_13(SRTISC), PAGESEL
 mov #$37, MAP_ADDR_6(SRTISC)
                       ; Enable RTI (1 sec period)
; *
                 MAIN
_Startup:
 bsr Init_mc
 bsr Init_RTI
 bsr MTIM_ADC_Init
                        ; Configure MITM for ADC module
  ; Application Loop
mainLoop:
 feed_watchdog
                       ; Clear COP timer
 bsr ADC_Single_conversion ; ADC Conversion
 bsr Pin_Measure
                       ; Control Measure
 jsr comparation
                       ; Comparation
                             ; Enter in STOP mode
 stop
 ACK_RTI
                       ; Ack for RTI Interrupt
 bra mainLoop
; *
            Startup Vector
ORG $3FFD
   JMP _Startup
                          ; Reset
```



#### How to Reach Us:

**Home Page:** 

www.freescale.com

support@freescale.com

**USA/Europe or Locations Not Listed:** 

Freescale Semiconductor Technical Information Center, CH370 1300 N. Alma School Road Chandler, Arizona 85224 +1-800-521-6274 or +1-480-768-2130 support@freescale.com

**Europe, Middle East, and Africa:** Freescale Halbleiter Deutschland GmbH Technical Information Center Schatzbogen 7 81829 Muenchen, Germany +44 1296 380 456 (English) +46 8 52200080 (English) +49 89 92103 559 (German) +33 1 69 35 48 48 (French) support@freescale.com

#### Japan:

Freescale Semiconductor Japan Ltd. Headquarters ARCO Tower 15F 1-8-1, Shimo-Meguro, Meguro-ku, Tokyo 153-0064 0120 191014 or +81 3 5437 9125 support.japan@freescale.com

#### Asia/Pacific:

Freescale Semiconductor Hong Kong Ltd. Technical Information Center 2 Dai King Street Tai Po Industrial Estate Tai Po, N.T., Hong Kong +800 2666 8080 support.asia@freescale.com

For Literature Requests Only:

Freescale Semiconductor Literature Distribution Center P.O. Box 5405 Denver, Colorado 80217 1-800-441-2447 or 303-675-2140 Fax: 303-675-2150 LDCForFreescaleSemiconductor@hibbertgroup.com

Document Number: AN3409 Rev. 0 01/2007

Information in this document is provided solely to enable system and software implementers to use Freescale Semiconductor products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits or integrated circuits based on the information in this document.

Freescale Semiconductor reserves the right to make changes without further notice to any products herein. Freescale Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Freescale Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters that may be provided in Freescale Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals", must be validated for each customer application by customer's technical experts. Freescale Semiconductor does not convey any license under its patent rights nor the rights of others. Freescale Semiconductor products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Freescale Semiconductor product could create a situation where personal injury or death may occur. Should Buyer purchase or use Freescale Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold Freescale Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Freescale Semiconductor was negligent regarding the design or manufacture of the part.

Freescale™ and the Freescale logo are trademarks of Freescale Semiconductor, Inc. All other product or service names are the property of their respective owners.

© Freescale Semiconductor, Inc. 2007. All rights reserved.

RoHS-compliant and/or Pb-free versions of Freescale products have the functionality and electrical characteristics as their non-RoHS-compliant and/or non-Pb-free counterparts. For further information, see http://www.freescale.com or contact your Freescale sales representative.

For information on Freescale's Environmental Products program, go to http://www.freescale.com/epp.

