PMIC solution for TI AWR2243 radar transceiver Rev. 1.0 — 29 September 2022

**Application note** 

#### **Document information**

Information	Content
Keywords	power solution, ADAS, radar, automotive, PMIC, PF502x, PF71, FS56, MMIC
Abstract	This application note illustrates the use of NXP FS56 and PF series power management ICs (PMICs) to power TI AWR2243 monolithic microwave integrated circuits (MMICs).



Revision history		
Revision	Date	Description
v.1	20220929	Initial version.

### **1** Device introduction

The AWR2243 device is a single-chip FMCW transceiver integrated PLL, transmitter, receiver, baseband and ADC, capable of operating in the 76 to 81 GHz frequency band. It is an ideal solution for extremely small form factor, self-monitoring, low-power, ultra-accurate radar systems in the automotive field.

The AWR2243 has 76 to 81 GHz coverage with 5 GHz available bandwidth. It has four receiver channels and three transmit channels with PLL and ADC converters. The device incorporates an ultra-accurate chip engine based on Fractional-N PLLs. AWR2243 supports the SPI or I<sup>2</sup>C interface with an external processor. Its manufacturer supplies documentation to support functional safety system design up to ASIL D and hardware integrity up to ASIL B. Its scalable sensor portfolio supports the design and development of ADAS system solutions for a wide range of performance, applications and sensor configurations in all vehicles, from comfort to safety functions.

## 2 NXP PMIC Overview

NXP's power management portfolio delivers scalability and flexibility for your next designs. Whether you are developing automotive, industrial or consumer applications, the NXP PMIC portfolio optimizes power and simplifies supply sequencing for various application processors. These PMICs integrate both switching and linear regulators required for a total system solution. They may also integrate battery management functions that include the battery charger, coin cell charger and power path selection. Most of NXP's PMICs can be configured via OTP and combined to provide a dedicated system solution that includes deliverables for QM and ASIL B/D functional safety requirements.

In this application note, we illustrate the use of three LV PMICs to provide different voltages and an HV PMIC to match the system from the battery.

#### 2.1 LV PMIC: PF5020

The PF5020 device is an NXP multi-channel PMIC designed for high performance automotive and industrial applications. The device is also highly configurable, making it a perfect companion and fit for various system level power requirements. PF5020 integrates independent voltage monitoring circuits to ensure compliance with ISO26262 standard and functional safety up to ASIL B level. The PF5020 is also available as a standard non-safety device for applications that don't require ISO compliance. The PF5020 is suitable for a variety of applications, including infotainment, ADAS, vision and radar, either as a standalone power solution or as a companion to another NXP PMIC like FS5600. Figure 1 shows the PF5020 PMIC block diagram.





Figure 1. PF5020 PMIC block diagram

#### 2.2 LV PMIC: PF5023

Both PF5020 and PF5023 belong to the PF502x family. This family also includes the PF5024. All the PF502x devices are integrated independent voltage monitoring circuits that ensure compliance with the ISO 26262 standard and functional safety up to ASIL B level. PF5023 has three functionally similar bucks which can supply voltage from 0.4 V to


AN13651



1.8 V. These bucks can work in dual phase and triple phase. <u>Figure 2</u> shows the PF5023 PMIC block diagram.

#### 2.3 LV PMIC: PF7100

The PF7100 device features five high efficiency buck converters and two linear regulators for powering the processor, memory and miscellaneous peripherals. PF7100 is also suitable for applications requiring functional safety up to the ASIL B level. See <u>Figure 3</u> for a block diagram.




#### 2.4 HV PMIC: FS5600

The FS56 System Basis Chip (SBC) for Automotive applications features two battery connected DC-DC buck controllers. FS56 provides functional safety features such as

Figure 2. PF5023 PMIC block diagram

independent voltage monitors, windowed watchdog timer, I/O monitoring via ERRMON and FCCU, and built-in-self test. The FS56 is offered in QM, ASIL B and enhanced ASIL B versions. We chose an FS56 with two HV bucks as the pre-buck for the radar system power solution illustrated in this application note. See Figure 4 for an FS56 block diagram.





## 3 Introduction to AWR2243 power solution

As the automotive industry continues to develop towards high automatic performance and high reliability, radar is used more and more in automotive systems. Standards are emerging for 4D millimeter-wave imaging radar, and this technology is expected to support one of the core sensors in automotive driver assistance (ADAS) systems.

Using NXP's HV PMIC FS56 and LV PMIC PF series solutions to implement the NXP power solution for the AWR2243 monolithic microwave IC (MMIC) enables a total system for automotive radar. For MCU/CPU power solutions, refer to <u>NXP PMICs and SBCs for Multi-Vendor Processors</u>.

The FS56 can connect to the 12 V battery and produce an intermediate voltage from battery voltage. This device is aimed at replacing discrete battery connected regulators in the system while providing value in functional safety and integration. The PF series PMICS provide matched voltages for various processors and DDRs.

This application note illustrates how the FS56 can be used to produce 5 V for LV PMICs and 3.3 V for an MCU that controls and communicates with the controller MMIC and target MMICs.

Clock synchronization is required in radar applications to facilitate the removal of random noise from various devices. FS56, PF71, and PF502x all support a clock synchronization input using their configurable SYNCIN pin. PF71 also supports a clock synchronization output with its SYNCOUT pin.





Figure 5 shows a block diagram for single, dual, and quad AWR2243 power solutions.


#### 3.1 Power tree

Figure 6, Figure 7, and Figure 8 show use of NXP LV PMICs for AWR22443. For a single AWR2243, the PF5020 is the best solution, because it fulfills all the AWR2243 requirements. For dual parts, the PF7100 is the best solution, and for quad parts, the PF5023 + PF7100 is the best solution.

NXP PMICs feature one-time programming (OTP). The PMIC OTP memory can store key startup configurations, greatly reducing the number of external components used to set the output voltages and sequence of external regulators. Because of this function, both the dual part and quad part configurations can use the PF7100 PMIC with the same part number.


#### 3.1.1 PMICs for single AWR2243





#### 3.1.2 PMICs for dual AWR2243

AN13651 Application note



#### 3.1.3 PMICs for quad AWR2243

#### 3.2 Power up and power down sequence


In the solution for quad AWR2243s, the customer should connect the XFAILB pins of PF5023 and PF7100 together. NXP multiple PMICs effectively synchronize accurate

power-up and power-down sequencing for all power rails through the PMIC itself, without the need for MCU control. This combination of devices acts as "one PMIC" for power up/down sequences through the NXP PMIC internal power-up sequencer PWRON and XFAILB functions.

Table 1. PMIC configuration for single/dual/quad AWR2243

Single AWR2243	Dual AWR2243	Quad AWR2243	Voltage	Power up delay	Power down delay	Power rail
SW1/PF5020	SW1 and SW2/PF71	SW1 and SW2/ PF5023 + SW1 and SW2/ PF71	1.2 V	0.5 ms-slot1	1.5 ms-Group4	VDDIN, VIN_ SRAM VNWA
SW2/PF5020	SW3 and SW4/PF71	SW3 and SW4/PF71	1 V or 1.3 V	1 ms-slot2	1.5 ms-Group4	VIN_13RF1 VIN_13RF2
SW3/PF5020	SW5/PF71	SW3/PF5023 + SW5/PF71	1.8 V	1 ms-slot2	1.5 ms-Group4	VIOIN_18 VIN18_CLK VIOIN_18DIFF VIN18_BB
LDO/PF5020	LDO1 and LDO2/ PF71	LDO1 and LDO2/ PF71	3.3 V	1.5 ms-slot3	1.5 ms-Group4	VIOIN
RESETBMCU				2.0 ms-slot4		nRESET


The AWR2243 device expects all external voltage rails and sense of power (SOP) lines to be stable before reset is de-asserted. See <u>Figure 9</u> for the PMIC power-up and power-down sequence for AWR2243.



AN13651 Application note

## **4** Schematics

See  $\underline{Figure \ 10}$  and  $\underline{Figure \ 11}$  for schematics of AWR2243 power solutions based on NXP PMICs.



## 5 Bill of materials

#### Table 2. BOM for PF502x

Value	Quantity	Description	Part Number	Vendor
0.1 µF	6	CAP CER 0.1 µF 16 V 10% X7R AEC-Q200 0402	GCM155R71C104KA55D	MURATA
4.7 µF	4	CAP CER 4.7 µF 16 V 10% X7R AEC-Q200 0805	CGA4J3X7R1C475K125AB	ТДК
22 µF	6	CAP CER 22 µF 10 V 10% X7R AEC-Q200 1206	LMJ316BB7226KLHT	TAIYO YUDEN
1 µF	5	CAP CER 1 µF 10 V 10% X7S AEC-Q200 0402	GCM155C71A105KE38D	MURATA
2.2 µF	1	CAP CER 2.2 µF 10 V 10% X7S AEC-Q200 0402	GRT155C71A225KE13	MURATA
1 µH	3	IND PWR 1.0 µH@1 MHZ 4.7 A 20% AEC-Q200 SMD	TFM252012ALMA1R0MTAA	ТДК
100K	12	RES MF 100K OHM 1% 1/10 W AEC-Q200 0402	ERJ-2RKF1003X	PANASONIC
0	2	RES MF ZERO 1/8 W AEC-Q200 0805	MCR10EZPJ000	ROHM
PF502x	1	IC POWER MANAGEMENT 5.5 V AEC-Q100 QFN40	PF502x <sup>[1]</sup>	NXP SEMICONDUCTORS

[1] For a single AWR2243, it is PF5020; for quad AWR2243s, it is PF5023.

#### Table 3. BOM for PF7100

Value	Quantity	Description	Part Number	Vendor
1 µF	5	CAP CER 1 µF 10 V 10% X7S AEC-Q200 0402	GCM155C71A105KE38D	MURATA
2.2 µF	2	CAP CER 2.2 µF 10 V 10% X7S AEC-Q200 0402	GRT155C71A225KE13	MURATA
0.1 µF	6	CAP CER 0.1 µF 16 V 10% X7R AEC-Q200 0402	GCM155R71C104KA55D	MURATA
4.7 µF	7	CAP CER 4.7 µF 16 V 10% X7S 0603	GRM188C71C475KE21	MURATA
22 µF	10	CAP CER 22 µF 10 V 20% X6S AEC-Q200 0805	GRT21BC81A226ME13	MURATA
1 µH	5	IND PWR 1.0 µH@1 MHZ 4.7 A 20% AEC-Q200 SMD	TFM252012ALMA1R0MTAA	TDK
100K	13	RES MF 100K OHM 1% 1/10 W AEC-Q200 0402	ERJ-2RKF1003X	PANASONIC
0	5	RES MF ZERO 1/8 W AEC-Q200 0805	MCR10EZPJ000	ROHM
PPF7100	1	IC POWER MANAGEMENT 7-CH 2.7-5.5V AEC-Q100 HVQFN48	PPF7100BMBA0ES	NXP SEMICONDUCTORS

## 6 Reference Resources

PF5020 information and tools can be found at this link: <u>https://www.nxp.com/products/</u> power-management/pmics-and-sbcs/pmics/multi-channel-5-pmic-for-automotiveapplications-4-high-power-and-1-low-power-fit-for-asil-b-safety-level:PF5020

PF5023 information and tools can be found at this link: <u>https://www.nxp.com/products/power-management/pmics-and-sbcs/pmics/multi-channel-3-pmic-for-automotive-applications-3-high-power-fit-for-asil-b-safety-level:PF5023</u>

PF7100 information and tools can be found at this link: <u>https://www.nxp.com/products/</u>power-management/pmics-and-sbcs/pmics/7-channel-power-management-integratedcircuit-for-high-performance-applications-fit-for-asil-b-safety-level:PF7100

FS56 information can be found at this link: <u>https://www.nxp.com/products/power-manage</u> ment/pmics-and-sbcs/safety-sbcs/automotive-dual-buck-regulator-and-controller-withvoltage-monitors-and-watchdog-timer:FS5600

#### PMIC solution for TI AWR2243 radar transceiver

## 7 Legal information

### 7.1 Definitions

**Draft** — A draft status on a document indicates that the content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included in a draft version of a document and shall have no liability for the consequences of use of such information.

### 7.2 Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. NXP Semiconductors takes no responsibility for the content in this document if provided by an information source outside of NXP Semiconductors.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of NXP Semiconductors.

**Right to make changes** — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

Terms and conditions of commercial sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

**Evaluation products** — This product is provided on an "as is" and "with all faults" basis for evaluation purposes only. NXP Semiconductors, its affiliates and their suppliers expressly disclaim all warranties, whether express, implied or statutory, including but not limited to the implied warranties of non-infringement, merchantability and fitness for a particular purpose. The entire risk as to the quality, or arising out of the use or performance, of this product remains with customer.

In no event shall NXP Semiconductors, its affiliates or their suppliers be liable to customer for any special, indirect, consequential, punitive or incidental damages (including without limitation damages for loss of business, business interruption, loss of use, loss of data or information, and the like) arising out the use of or inability to use the product, whether or not based on tort (including negligence), strict liability, breach of contract, breach of warranty or any other theory, even if advised of the possibility of such damages.

Notwithstanding any damages that customer might incur for any reason whatsoever (including without limitation, all damages referenced above and all direct or general damages), the entire liability of NXP Semiconductors, its affiliates and their suppliers and customer's exclusive remedy for all of the foregoing shall be limited to actual damages incurred by customer based on reasonable reliance up to the greater of the amount actually paid by customer for the product or five dollars (US\$5.00). The foregoing limitations, exclusions and disclaimers shall apply to the maximum extent permitted by applicable law, even if any remedy fails of its essential purpose.

**Translations** — A non-English (translated) version of a document, including the legal information in that document, is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

Security — Customer understands that all NXP products may be subject to unidentified vulnerabilities or may support established security standards or specifications with known limitations. Customer is responsible for the design and operation of its applications and products throughout their lifecycles to reduce the effect of these vulnerabilities on customer's applications and products. Customer's responsibility also extends to other open and/or proprietary technologies supported by NXP products for use in customer's applications. NXP accepts no liability for any vulnerability. Customer should regularly check security updates from NXP and follow up appropriately.

Customer shall select products with security features that best meet rules, regulations, and standards of the intended application and make the ultimate design decisions regarding its products and is solely responsible for compliance with all legal, regulatory, and security related requirements concerning its products, regardless of any information or support that may be provided by NXP.

NXP has a Product Security Incident Response Team (PSIRT) (reachable at <u>PSIRT@nxp.com</u>) that manages the investigation, reporting, and solution release to security vulnerabilities of NXP products.

Suitability for use in automotive applications (functional safety) -This NXP product has been qualified for use in automotive applications. It has been developed in accordance with ISO 26262, and has been ASIL classified accordingly. If this product is used by customer in the development of, or for incorporation into, products or services (a) used in safety critical applications or (b) in which failure could lead to death, personal injury, or severe physical or environmental damage (such products and services hereinafter referred to as "Critical Applications"), then customer makes the ultimate design decisions regarding its products and is solely responsible for compliance with all legal, regulatory, safety, and security related requirements concerning its products, regardless of any information or support that may be provided by NXP. As such, customer assumes all risk related to use of any products in Critical Applications and NXP and its suppliers shall not be liable for any such use by customer. Accordingly, customer will indemnify and hold NXP harmless from any claims, liabilities, damages and associated costs and expenses (including attorneys' fees) that NXP may incur related to customer's incorporation of any product in a Critical Application.

AN13651

#### PMIC solution for TI AWR2243 radar transceiver

NXP — wordmark and logo are trademarks of NXP B.V.

## 7.3 Trademarks

Notice: All referenced brands, product names, service names, and trademarks are the property of their respective owners.

PMIC solution for TI AWR2243 radar transceiver

## **Tables**

Tab. 1.	PMIC configuration for single/dual/quad	Tab. 2.	BOM for PF502x	. 13
	AWR2243 11	Tab. 3.	BOM for PF7100	. 13

#### PMIC solution for TI AWR2243 radar transceiver

## Figures

Fig. 1.	PF5020 PMIC block diagram	4
Fig. 2.	PF5023 PMIC block diagram	
Fig. 3.	PF7100 PMIC block diagram	5
Fig. 4.	FS56 Functional Block Diagram	6
Fig. 5.	NXP FS56 + PF Series PMICs power	
	solution for single/dual/quad AWR2243	7
Fig. 6.	LV PMIC PF5020 power solution for single	
	AWR2243	8
Fig. 7.	LV PMIC PF7100 power solution for dual	
	AWR2243	9

Fig. 8.	LV PMIC PF5023 + PF7100 power solution	
	for quad AWR2243	10
Fig. 9.	PMIC Power-up and Power-down	
	Sequence for AWR2243	11
Fig. 10.	PF502x schematic for single/quad	
	AWR2243 power rails	12
Fig. 11.	PF7100 schematic for dual/quad AWR2243	
-	power rails	12

#### PMIC solution for TI AWR2243 radar transceiver

### Contents

1	Device introduction	3
2	NXP PMIC Overview	4
2.1	LV PMIC: PF5020	4
2.2	LV PMIC: PF5023	4
2.3	LV PMIC: PF7100	5
2.4	HV PMIC: FS5600	5
3	Introduction to AWR2243 power solution	7
3.1	Power tree	7
3.1.1	PMICs for single AWR2243	8
3.1.2	PMICs for dual AWR2243	9
3.1.3	PMICs for quad AWR2243	10
3.2	Power up and power down sequence	
4	Schematics	
5	Bill of materials	13
6	Reference Resources	14
7	Legal information	15

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

© 2022 NXP B.V.

All rights reserved.

For more information, please visit: http://www.nxp.com