

MPL115A1 Miniature SPI digital barometer, 50 to 115 kPa Rev. 8 – 10 October 2017 Data s

1 General description

The MPL115A1 is an absolute pressure sensor with a digital SPI output targeting low cost applications. A miniature 5 x 3 x 1.2 mm LGA package is ideally suited for the space constrained requirements of portable electronic devices. Low current consumptions of 5 μ A during Active mode and 1 μ A during Shutdown (Sleep) mode are essential when focusing on low-power applications. The wide operating temperature range spans from – 40 °C to +105 °C to fit demanding environment conditions.

The MPL115A1 employs a MEMS pressure sensor with a conditioning IC to provide accurate pressure measurements from 50 to 115 kPa. An integrated ADC converts pressure and temperature sensor readings to digitized outputs via a SPI port. Factory calibration data is stored internally in an on-board ROM. Utilizing the raw sensor output and calibration data, the host microcontroller executes a compensation algorithm to render *Compensated Absolute Pressure* with ±1 kPa accuracy.

The MPL115A1 pressure sensor's small form factor, low power capability, precision, and digital output optimize it for barometric measurement applications.

2 Features

- Digitized pressure and temperature information together with programmed calibration coefficients for host micro use.
- · Factory calibrated
- 50 kPa to 115 kPa absolute pressure
- ±1 kPa accuracy
- 2.375 V to 5.5 V supply
- Integrated ADC
- SPI Interface
- · Monotonic pressure and temperature data outputs
- Surface mount RoHS compliant package

3 Applications

- Barometry (portable and desktop)
- Altimeters
- Weather stations
- Hard-disk drives (HDD)
- Industrial equipment
- Health monitoring
- Air control systems



4 Ordering information


| Table 1. Ordering information | | | | | | | |
|-------------------------------|---------|---|-----------|--|--|--|--|
| Type number | Package | Package | | | | | |
| | Name | Description | Version | | | | |
| MPL115A1 | TSON8 | LGA 8 I/O, 3 X 5 X 1.25 PITCH, SENSOR 1.2MAX MM PKG | SOT1769-1 | | | | |

4.1 Ordering options

Table 2. Ordering options

| Device Name Package Options | | # of Ports | | | Pressure Type | | | Digital |
|-----------------------------|--------------------|------------|--------|------|---------------|--------------|----------|-----------|
| | | None | Single | Dual | Gauge | Differential | Absolute | Interface |
| MPL115A1 | Tray | • | | | | | • | SPI |
| MPL115A1T1 | Tape & Reel (1000) | • | | | | | • | SPI |

5 Block diagram



Miniature SPI digital barometer, 50 to 115 kPa

6 **Pinning information**

6.1 Pinning

| | | MPL115 | A1 | |
|-----------------------------|------|---------------|---------|------|
| | VDD | o 1 | 8 | SCLK |
| | CAP | 2 | 7 | DIN |
| | GND | 3 | 6 | DOUT |
| s | SHDN | 4 | 5 | CS |
| | t | ransparent to | op view | 1 |
| Figure 2. Pin configuration | | | | |

6.2 Pin description

Table 3. Pin description

| Pin | Name | Function |
|-----|------|--|
| 1 | VDD | Power Supply Connection. VDD range is 2.375 V to 5.5 V. |
| 2 | CAP | External Capacitor: Output decoupling capacitor for main internal regulator. Connect a 1 μF ceramic capacitor to ground. |
| 3 | GND | Ground |
| 4 | SHDN | Shutdown: Connect to GND to disable the device. When in shut down the part draws no more than 1 μ A supply current and all communications pins (\overline{CS} , SCLK, DOUT, DIN) are high impedance. Connect to VDD for normal operation. |
| 5 | CS | Chip Select line. |
| 6 | DOUT | Serial data output |
| 7 | DIN | Serial data input |
| 8 | SCLK | Serial clock input. |

7 Handling and Board Mount Recommendations

The sensor die is sensitive to light exposure. Direct light exposure through the port hole can lead to varied accuracy of pressure measurement. Avoid such exposure to the port during normal operation.

7.1 Methods of Handling

Components can be picked from the carrier tape using either the vacuum assist or the mechanical type pickup heads. A vacuum assist nozzle type is most common due to its lower cost of maintenance and ease of operation. The recommended vacuum nozzle configuration should be designed to make contact with the device directly on the metal cover and avoid vacuum port location directly over the vent hole in the metal cover of the

device. Multiple vacuum ports within the nozzle may be required to effectively handle the device and prevent shifting during movement to placement position.

Vacuum pressure required to adequately support the component should be approximately 25 inches Hg (85 kPa). This level is typical of in-house vacuum supply. Pickup nozzles are available in various sizes and configurations to suit a variety of component geometries. To select the nozzle best suited for the specific application, it is recommended that the customer consult their pick and place equipment supplier to determine the correct nozzle. In some cases it may be necessary to fabricate a special nozzle depending on the equipment and speed of operation.

Tweezers or other mechanical forms of handling that have a sharp point are not recommended since they can inadvertently be inserted into the vent hole of the device. This can lead to a puncture of the MEMS element that will render the device inoperable.

7.2 Board Mount Recommendations

Components can be mounted using solder paste stencil, screen printed or dispensed onto the PCB pads prior to placement of the component. The volume of solder paste applied to the PCB is normally sufficient to secure the component during transport to the subsequent reflow soldering process. Use of adhesives to secure the component is not recommended, but where necessary can be applied to the underside of the device.

Solder pastes are available in variety of metal compositions, particle size and flux types. The solder paste consists of metals and flux required for a reliable connection between the component lead and the PCB pad. Flux aids the removal of oxides that may be present on PCB pads and prevents further oxidation from occurring during the solder process.


The use of a No-Clean (NC) flux is recommended for exposed cavity components. Using pressure spray, wire brush, or other methods of cleaning is not recommended since it can puncture the MEMS device and render it unusable. If cleaning of the pcb is performed, Water Soluble (WS) flux can be used. However, it is recommended the component cavity is protected by adhesive Kapton tape, vinyl cap or other means prior to the cleaning process. This covering will prevent damage to the MEMS device, contamination, and foreign materials from being introduced into device cavity as result of cleaning processes.

Ultrasonic cleaning is not recommended as the frequencies can damage wire bond interconnections and the MEMS device.

MPL115A1

Miniature SPI digital barometer, 50 to 115 kPa

8 Functional description



The MPL115A interfaces to a host (or system) microcontroller in the user's application. All communications are via SPI. A typical usage sequence is as follows:

Initial power-up

All circuit elements are active. SPI port pins are high impedance and associated registers are cleared. The device then enters standby mode.

Reading coefficient data

The user then typically accesses the part and reads the coefficient data. The main circuits within the slave device are disabled during read activity. The coefficients are usually stored in the host microcontoller local memory but can be re-read at any time.

Reading of the coefficients may be executed only once and the values stored in the host microcontroller. It is not necessary to read this multiple times because the coefficients within a device are constant and do not change. However, note that the coefficients will be different from device to device, and cannot be used for another part.

Data conversion

This is the first step that is performed each time a new pressure reading is required which is initiated by the host sending the CONVERT command. The main system circuits are activated (wake) in response to the command and after the conversion completes, the result is placed into the Pressure and Temperature ADC output registers.

The conversion completes within the maximum conversion time, tc (see row $\underline{6}$, in <u>Table 11</u>). The device then enters standby mode.

MPL115A1

© NXP B.V. 2017. All rights reserved.

Miniature SPI digital barometer, 50 to 115 kPa

Compensated pressure reading

After the conversion has been given sufficient time to complete, the host microcontroller reads the result from the ADC output registers and calculates the Compensated Pressure, a barometric/atmospheric pressure value which is compensated for changes in temperature and pressure sensor linearity. This is done using the coefficient data from the MPL115A and the raw sampled pressure and temperature ADC output values, in a compensation equation (detailed later). Note that this is an absolute pressure measurement with a vacuum as a reference.

From this step the host controller may either wait and then return to the Data Conversion step to obtain the next pressure reading or it may go to the Shutdown step.

Shutdown

For longer periods of inactivity the user may assert the SHDN input by driving this pin low to reduce system power consumption. This removes power from all internal circuits, including any registers. In the shutdown state, the Pressure and Temperature registers will be reset, losing any previous ADC output values.

This step is exited by taking the \overline{SHDN} pin high. Wait for the maximum wakeup time, tw (see row $\underline{7}$, in $\underline{Table 11}$), after which another pressure reading can be taken by transitioning to the data Conversion step.

| Address | Name | Description |
|---------|-------------------------|---|
| 00h | Padc_MSB | 10-bit Pressure ADC output value MSB |
| 01h | Padc_LSB | 10-bit Pressure ADC output value LSB |
| 02h | Tadc_MSB | 10-bit Temperature ADC output value MSB |
| 03h | Tacd_LSB | 10-bit Temperature ADC output value LSB |
| 04h | a0_MSB | a0 coefficient MSB |
| 05h | a0_LSB | a0 coefficient LSB |
| 06h | b1_MSB | b1 coefficient MSB |
| 07h | b1_LSB | b1 coefficient LSB |
| 08h | b2_MSB | b2 coefficient MSB |
| 09h | b2_LSB | b2 coefficient LSB |
| 0Ah | c12_MSB | c12 coefficient MSB |
| 0Bh | c12_LSB | c12 coefficient LSB |
| 0Ch | reserved ^[1] | _ |
| 0Dh | reserved ^[1] | - |
| 0Eh | reserved ^[1] | — |
| 0Fh | reserved ^[1] | — |

Table 4. Device memory map

Miniature SPI digital barometer, 50 to 115 kPa

| Address | Name | Description |
|---------|----------|---|
| 10h | reserved | — |
| 11h | reserved | — |
| 12h | CONVERT | Start Pressure and Temperature Conversion |

[1] This register is set to 00h. It is reserved, and was previously utilized as Coefficient values, c11 and c22, which were always 00h.

For values with less than 16 bits, the lower LSBs are zero. For example, c12 is 14 bits and is stored into 2 bytes as follows:

c12 MS byte = c12[13:6] = [c12_{b13}, c12_{b12}, c12_{b11}, c12_{b10}, c12_{b9}, c12_{b8}, c12_{b7}, c12_{b6}] c12 LS byte = c12[5:0] & "00" = [c12_{b5}, c12_{b4}, c12_{b3}, c12_{b2}, c12_{b1}, c12_{b0}, 0, 0]

8.1 Pressure, temperature and coefficient bit-width specifications

The table below specifies the initial coefficient bit-width specifications for the compensation algorithm and the specifications for Pressure and Temperature ADC values.

| | a0 | b1 | b2 | c12 | Padc | Tadc |
|-----------------|----|----|----|-----|------|------|
| Total Bits | 16 | 16 | 16 | 14 | 10 | 10 |
| Sign Bits | 1 | 1 | 1 | 1 | 0 | 0 |
| Integer Bits | 12 | 2 | 1 | 0 | 10 | 10 |
| Fractional Bits | 3 | 13 | 14 | 13 | 0 | 0 |
| dec pt zero pad | 0 | 0 | 0 | 9 | 0 | 0 |

Table 5. Pressure, temperature and compensation coefficient specifications

Example Binary Format Definitions:

| a0 Signed, Integer Bits = 12, Fractional Bits = 3 : | Coeff a0 = S $I_{11} I_{10} I_9 I_8 I_7 I_6 I_5 I_4 I_3 I_2 I_1 I_0 . F_2 F_1 F_0$ |
|---|---|
| b1 Signed, Integer Bits = 2, Fractional Bits = 13 : | Coeff b1 = S $I_1 I_0$. F ₁₂ F ₁₁ F ₁₀ F ₉ F ₈ F ₇ F ₆ F ₅ F ₄ F ₃ F ₂ F ₁ F ₀ |
| b2 Signed, Integer Bits = 1, Fractional Bits = 14 : | Coeff b2 = S I_0 . $F_{13} F_{12} F_{11} F_{10} F_9 F_8 F_7 F_6 F_5 F_4 F_3 F_2 F_1 F_0$ |
| c12 Signed, Integer Bits = 0, Fractional Bits = 13, dec pt zero pad = 9 : | Coeff c12 = S 0 . 000 000 000 F ₁₂ F ₁₁ F ₁₀ F ₉ F ₈ F ₇ F ₆ F ₅ F ₄ F ₃ F ₂ F ₁ F ₀ |
| Padc Unsigned, Integer Bits = 10 : | Padc U = I ₉ I ₈ I ₇ I ₆ I ₅ I ₄ I ₃ I ₂ I ₁ I ₀ |
| Tadc Unsigned, Integer Bits =10 : | Tadc U = I ₉ I ₈ I ₇ I ₆ I ₅ I ₄ I ₃ I ₂ I ₁ I ₀ |
| | |

Note: Negative coefficients are coded in 2's complement notation.

8.2 Compensation

The 10-bit compensated pressure output, Pcomp, is calculated as follows:

Miniature SPI digital barometer, 50 to 115 kPa

$$Pcomp = a0 + (b1 + c12 \cdot Tadc) \cdot Padc + b2 \cdot Tadc$$
(1)

Where:

Padc is the 10-bit pressure ADC output of the MPL115A Tadc is the 10-bit temperature ADC output of the MPL115A a0 is the pressure offset coefficient b1 is the pressure sensitivity coefficient b2 is the temperature coefficient of offset (TCO) c12 is the temperature coefficient of sensitivity (TCS)

Pcomp will produce a value of 0 with an input pressure of 50 kPa and will produce a full-scale value of 1023 with an input pressure of 115 kPa.


Pressure (kPa) =
$$Pcomp \cdot \left[\frac{115-50}{1023}\right] + 50$$
 (2)

8.3 Evaluation sequence, arithmetic circuits

The following is an example of the calculation for Pcomp, the compensated pressure output. Input values are in **bold**.


c12x2 = c12 * Tadc a1 = b1 + c12x2 a1x1 = a1 * Padc y1 = a0 + a1x1 a2x2 = b2 * Tadc Pcomp = y1 + a2x2

This can be calculated as a succession of Multiply Accumulates (MACs) operations of the form y = a + b * x:



The polynomial can be evaluated (Equation 1) as a sequence of 3 MACs:

Miniature SPI digital barometer, 50 to 115 kPa



Please refer to NXP application note AN3785 for more detailed notes on implementation.

8.4 SPI device read/write operations

All device read/write operations are memory mapped. Device actions e.g. "Start Conversions" are controlled by writing to the appropriate memory address location. All memory address locations are 6-bit (see <u>Table 2</u>).

The 8-bit command word comprises:

- the most significant bit which is the Read/Write identifier which is '1' for read operations and '0' for write operations.
- the 6-bit address (from <u>Table 4</u>);
- the least significant bit which is not used and is don't care (X).

The device write commands are shown in Table 6.

Table 6. SPI write command

Legend: X = don't care

| Command | Binary | HEX ^[1] |
|-------------------|----------|--------------------|
| Start Conversions | 0010010X | 24h |

[1] The command byte needs to be paired with a 00h as part of the SPI exchange to complete the passing of *Start Conversions*.

The actions taken by the part in response to each command are as follows:

Table 7. SPI Write command description

| Command | Action taken | | | |
|-------------------|---|--|--|--|
| Start Conversions | Wake main circuits. Start clock. Allow supply stabilization time. Select pressure sensor input. Apply positive sensor excitation and perform A to D conversion. Select temperature input. Perform A to D conversion. Load the Pressure and Temperature registers with the result. Shut down main circuits and clock. | | | |

Miniature SPI digital barometer, 50 to 115 kPa

SPI Read operations are performed by sending the required address with a leading *Read* bit set to '1'. SPI operations require that each byte be addressed individually. All data is transmitted most significant bit first.

Table 8. Example SPI Read Commands

Legend: X = don't care

| Command | Binary | HEX ^[1] |
|------------------------------|----------|--------------------|
| Read Pressure MSB | 100000X | 80h |
| Read Pressure LSB | 1000001X | 82h |
| Read Temperature MSB | 1000010X | 84h |
| Read Temperature LSB | 1000011X | 86h |
| Read Coefficient data byte 1 | 1000100X | 88h |


[1] The command byte needs to be paired with a 00h as part of the SPI exchange to complete the passing of stated command.

8.5 SPI timing

Table 9. SPI timing

Table 9 and Figure 4 describe the timing requirements for the SPI system.

| Ref | Symbol | Function | Min | Мах | Unit |
|-----|--------|----------------------------------|------|-----|------|
| 1 | Of | Operating Frequency | | 8 | MHz |
| 2 | tSCLK | SCLK Period | 125 | — | ns |
| 3 | tCLKH | SCLK High time | 62.5 | _ | ns |
| 4 | tCLKL | SCLK Low time | 62.5 | — | ns |
| 5 | tSCS | Enable lead time | 125 | | ns |
| 6 | tHCS | Enable lag time | 125 | | ns |
| 7 | tSET | Data setup time | 30 | | ns |
| 8 | tHOLD | Data hold time | 30 | | ns |
| 9 | tDDLY | Data valid (after SCLK low edge) | | 32 | ns |
| 10 | tWCS | Width CS High | 30 | | ns |



Miniature SPI digital barometer, 50 to 115 kPa

8.6 Example of SPI reading of coefficients

These are MPL115A1 SPI commands to read coefficients, execute Pressure and Temperature conversions, and to read Pressure and Temperature data. The sequence of the commands for the interaction is given as an example to operate the MPL115A1. Utilizing this gathered data, an example of the calculating the Compensated Pressure reading is given in floating point notation.

SPI Commands (simplified for communication)

Command to Write "Convert Pressure and Temperature" = 24h Command to Read "Pressure ADC High byte" = 80h Command to Read "Pressure ADC Low byte" = 82h Command to Read "Temperature ADC High byte" = 84h Command to Read "Temperature ADC Low byte" = 86h Command to Read "Coefficient data byte 1 High byte" = 88h

Read coefficients:

[CS=0], [88h], [00h], [8Ah], [00h], [8Ch], [00h], [8Eh], [00h], [90h], [00h], [92h], [00h], [94h], [00h], [96h], [00h], [00h], [CS=1]

Start pressure and temperature conversion, read raw pressure:

[CS=0], [24h], [00h], [CS=1], [3 ms Delay]

[CS=0], [80h], [00h], [82h], [00h], [84h], [00h], [86h], [00h], [00h], [CS=1]

Note: Extra [00h] at the end of each sequence to output the last data byte on the slave side of the SPI.


| SP] | 88 00 8A 00 8C 00 8E 00 90 00 92 00 94 00 95 00 00 |
|-----------|--|
| • | |
| | |
| DOUT | |
| ακ | |
| CSB | |
| Figure 5. | SPI read coefficient datagram |

NXP Semiconductors

MPL115A1

Miniature SPI digital barometer, 50 to 115 kPa

| a0 coefficient MSB | = | 41h | | | | | |
|---------------------|---|-----|-----------------|---|-------|---|------------|
| a0 coefficient LSB | = | DFh | a0 coefficient | = | 41DFh | = | 2107.875 |
| | | | | | | | |
| b1 coefficient MSB | = | B0h | | | | | |
| b1 coefficient LSB | = | 28h | b1 coefficient | = | B028h | = | -2.49512 |
| | | | | | | | |
| b2 coefficient MSB | = | BEh | | | | | |
| b2 coefficient LSB | = | ADh | b2 coefficient | = | BEADh | = | -1.02069 |
| | | | | | | | |
| c12 coefficient MSB | = | 38h | | | | | |
| c12 coefficient LSB | = | CCh | c12 coefficient | = | 38CCh | = | 0.00086665 |
| | | | | | | | |



Command to start pressure and temperature conversion, 24h

| SPI DIN DOUT CCB Figure 7. SPI read | resi | ults da | | | |
|---|------|------------|-------------|---------|---|
| Pressure MSB Pressure LSB | = | 67h C0h | Pressure | = 67C0h | 0110 0111 11 00 0000 415 ADC counts |
| Temperature MSB Temperature LSB | = | 80h 40h | Temperature | = 8040h | = 1000 0000 01 00 0000 = 513 ADC counts |

Miniature SPI digital barometer, 50 to 115 kPa

8.7 Example of pressure compensated calculation in floating-point notation

| a0 coefficient | = | 2107.875 |
|-----------------|---|----------------|
| b1 coefficient | = | -2.49512 |
| b2 coefficient | = | -1.02069 |
| c12 coefficient | = | 0.00086665 |
| Pressure | = | 415 ADC counts |
| Temperature | = | 513 ADC counts |

Pressure compensation

$$Pcomp = a0 + (b1 + c12 \cdot Tadc) \cdot Padc + b(c)$$

Using the evaluation sequence

The evaluation sequence is located in <u>Section 8.3</u>.

| c12x2 | = c12 * Tadc | = 0.00086665 * 513 | = 0.44459 |
|-------|--------------|---------------------------------|--------------|
| a1 | = b1 + c12x2 | = -2.49512 + 0.44459 | = -2.05052 |
| a1x1 | = a1 * Padc | = -2.05052 * 415 | = -850.96785 |
| y1 | = a0 + a1x1 | = 2107.875 + (-850.96785) | = 1256.90715 |
| a2x2 | = b2 * Tadc | = -1.02069 * 513 | = -523.61444 |
| PComp | = y1 + a2x2 | = 1256.90715 + (- 523.61444) | = 733.29270 |

Pressure (kPa) = $Pcomp \cdot \left[\frac{115-50}{1023}\right] + 50$

= 96.59kPa

$$= 733.19 \cdot \left[\frac{115-50}{1023}\right] + 50$$

© NXP B.V. 2017. All rights reserved.

MPL115A1

9 Maximum ratings

Table 10. Maximum ratings

Voltage (with respect to GND unless otherwise noted)

| Symbol | Value | Units |
|--|-------------------------------|-------|
| V _{DD} | -0.3 to +5.5 | V |
| SHDN, SCLK, CS, D _{IN} , D _{OUT} | –0.3 to V _{DD} + 0.3 | V |
| Operating Temperature Range | -40 to +105 | °C |
| Storage Temperature Range | -40 to +125 | °C |
| Overpressure | 1000 | kPa |

10 Mechanical and electrical characteristics

Table 11. Mechanical and electrical characteristics

 V_{DD} = 2.375 V to 5.5 V, T_A = -40 °C to +105 °C, unless otherwise noted. Typical values are at V_{DD} = 3.3 V, T_A = +25 °C.


| Ref | Parameters | Symbol | Conditions | Min | Тур | Мах | Units |
|--------|---|-------------------|---|--------------------------|------|-------------|-------|
| 1 | Operating Supply Voltage | V _{DD} | | 2.375 | 3.3 | 5.5 | V |
| 2 | Supply Current | I _{DD} | Shutdown (SHDN = GND) | — | | 1 | μA |
| | | | Standby | — | 3.5 | 10 | μA |
| | | | Average – at one measurement per second | — | 5 | — | μA |
| Press | sure Sensor | | | | | | |
| 3 | Range | | | 50 | | 115 | kPa |
| 4 | Resolution | | | — | 0.15 | _ | kPa |
| 5 | Accuracy | | –20 °C to 85 °C | — | | ±1 | kPa |
| 6 | Conversion Time (Start Pressure and Temperature Conversion) | tc | Time between start convert command and data available in the Pressure and Temperature registers | — | 1.6 | 3 | ms |
| 7 | Wakeup Time | tw | Time between leaving Shutdown mode (SHDN goes high) and communicating with the device to issue a command or read data. | _ | 3 | 5 | ms |
| SPI li | nputs: SCLK, CS , D _{IN} | 1 | 1 | <u> </u> | | | |
| 8 | SCLK Clock Frequency | f _{SCLK} | [1] | _ | | 8 | MHz |
| 9 | Low Level Input Voltage | VIL | | — | | $0.3V_{DD}$ | V |
| 10 | High Level Input Voltage | VIH | | 0.7V _{DD} | | _ | V |
| | | 1 | SPI Outputs: D _{OUT} | | | | |
| 11 | Low Level Output Voltage | VOL1 | At 3 mA sink current | 0 | | 0.4 | V |
| | | VOL2 | At 6 mA sink current | 0 | | 0.6 | |
| 12 | High Level Output Voltage | VOH1 | At 3 mA source current | V _{DD} - 0.4 | — | — | |

MPL115A1 Data sheet: technical data © NXP B.V. 2017. All rights reserved.

Miniature SPI digital barometer, 50 to 115 kPa

[1] Nominal maximum SPI clock frequency.

11 Package outline



NXP Semiconductors

MPL115A1

Miniature SPI digital barometer, 50 to 115 kPa






Figure 8. Package outline SOT1769-1 (TSON8)

Miniature SPI digital barometer, 50 to 115 kPa

12 Packing information





Miniature SPI digital barometer, 50 to 115 kPa


13 Soldering

- 1. Use SAC solder alloy, i.e., Sn-Ag-Cu, with a melting point of about 217 °C. It is recommended to use SAC305, i.e., Sn-3.0 wt.% Ag-0.5 wt.% Cu.
- 2. Reflow
 - Ramp up rate: 2 to 3 °C/s.
 - Preheat flat (soak): 110 to 130 s.
 - Reflow peak temperature: 250 °C to 260 °C (depends on exact SAC alloy composition).
 - Time above 217°C: 40 to 90s (depends on board type, thermal mass of the board/ quantities in the reflow).
 - Ramp down: 5 to 6 °C/s.
 - Using an inert reflow environment (with O₂ level about 5 to 15 ppm).

Note: The stress level and signal offset of the device also depends on the board type, board core material, board thickness and metal finishing of the board.

14 Soldering/landing pad information

The LGA package is compliant with the RoHS standard. It is recommended to use a noclean solder paste to reduce cleaning exposure to high pressure and chemical agents that can damage or reduce life span of the Pressure sensing element.



Data sheet: technical data

MPL115A1

15 Revision history

| Table 12. Revision h | istory | | | | | | |
|----------------------|---|--|---------------|--------------|--|--|--|
| Document ID | Release date | Data sheet status | Change notice | Supersedes | | | |
| MPL115A1 v.8 | 20171010 | Technical data | — | MPL115A1 v.7 | | | |
| Modifications: | of NXP Semico • Legal texts have • Removed the fin • Added <u>Section</u> <u>Recommendation</u> | The format of this data sheet has been redesigned to comply with the new identity guidelines of NXP Semiconductors. Legal texts have been adapted to the new company name where appropriate. Removed the first paragraph of <u>Section 7</u>. Added <u>Section 7.1</u> and <u>Section 7.2</u> in <u>Section 7 "Handling and Board Mount Recommendations"</u> Updated Figure 8. No technical changes. | | | | | |
| MPL115A1 v.7 | 02/2013 | Technical data | — | — | | | |

16 Legal information

16.1 Data sheet status

| Document status ^{[1][2]} | Product status ^[3] | Definition |
|---|-------------------------------|--|
| [short] Data sheet: product preview | Development | This document contains certain information on a product under development. NXP reserves the right to change or discontinue this product without notice. |
| [short] Data sheet: advance information | Qualification | This document contains information on a new product. Specifications and information herein are subject to change without notice. |
| [short] Data sheet: technical data | Production | This document contains the product specification. NXP Semiconductors reserves the right to change the detail specifications as may be required to permit improvements in the design of its products. |

[1] Please consult the most recently issued document before initiating or completing a design.

The term 'short data sheet' is explained in section "Definitions".
 The product status of device(s) described in this document may

The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nxp.com.

16.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a technical data data sheet shall define the specification of the product as agreed between NXP Semiconductors and its customer, unless NXP Semiconductors and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the NXP Semiconductors product is deemed to offer functions and qualities beyond those described in the technical data data sheet.

16.3 Disclaimers

Limited warranty and liability - Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. NXP Semiconductors takes no responsibility for the content in this document if provided by an information source outside of NXP Semiconductors. In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory. Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of NXP Semiconductors.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without

limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors and its suppliers accept no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification. Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products. NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors hereby expressly objects to

All information provided in this document is subject to legal disclaimers.

© NXP B.V. 2017. All rights reserved.

MPL115A1

Miniature SPI digital barometer, 50 to 115 kPa

applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Non-automotive qualified products — Unless this data sheet expressly states that this specific NXP Semiconductors product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. NXP Semiconductors accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications. In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall

use the product without NXP Semiconductors' warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond NXP Semiconductors' specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies NXP Semiconductors for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond NXP Semiconductors' standard warranty and NXP Semiconductors' product specifications.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

16.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

NXP — is a trademark of NXP B.V.

Miniature SPI digital barometer, 50 to 115 kPa

Tables

| Tab. 1. | Ordering information | 2 |
|---------|--|---|
| Tab. 2. | Ordering options | 2 |
| Tab. 3. | Pin description | |
| Tab. 4. | Device memory map | |
| Tab. 5. | Pressure, temperature and compensation | |
| | coefficient specifications | 7 |
| Tab. 6. | SPI write command | 9 |

| Tab. 7. | SPI Write command description | 9 |
|----------|---|------|
| Tab. 8. | Example SPI Read Commands | 10 |
| Tab. 9. | SPI timing | .10 |
| Tab. 10. | Maximum ratings | . 14 |
| Tab. 11. | Mechanical and electrical characteristics | . 14 |
| Tab. 12. | Revision history | . 19 |

Figures

| Fig. 1. Fig. 2. | Block diagram of MPL115A12 Pin configuration | |
|--------------------|---|--|
| Fig. 3. | Sequence flow chart 5 | |
| Fig. 4. | SPI timing diagram10 | |
| Fig. 5. | SPI read coefficient datagram11 | |
| Fig. 6. | SPI start conversion datagram12 | |

| Fig. 7. | SPI read results datagram12 |
|----------|--------------------------------------|
| Fig. 8. | Package outline SOT1769-1 (TSON8)15 |
| Fig. 9. | LGA (3 x 5) embossed carrier tape |
| | dimensions 17 |
| Fig. 10. | Device orientation in chip carrier17 |
| Fig. 11. | Recommended PCB landing pattern18 |

NXP Semiconductors

MPL115A1

Miniature SPI digital barometer, 50 to 115 kPa

Contents

| 1 | General description | 1 |
|-----|--|----|
| 2 | Features | 1 |
| 3 | Applications | 1 |
| 4 | Ordering information | |
| 4.1 | Ordering options | 2 |
| 5 | Block diagram | |
| 6 | Pinning information | |
| 6.1 | Pinning | |
| 6.2 | Pin description | 3 |
| 7 | Handling and Board Mount | |
| | Recommendations | 3 |
| 7.1 | Methods of Handling | |
| 7.2 | Board Mount Recommendations | |
| 8 | Functional description | |
| 8.1 | Pressure, temperature and coefficient bit- | |
| | width specifications | 7 |
| 8.2 | Compensation | 7 |
| 8.3 | Evaluation sequence, arithmetic circuits | |
| 8.4 | SPI device read/write operations | |
| 8.5 | SPI timing | |
| 8.6 | Example of SPI reading of coefficients | |
| 8.7 | Example of pressure compensated | |
| - | calculation in floating-point notation | 13 |
| 9 | Maximum ratings | |
| 10 | Mechanical and electrical characteristics | |
| 11 | Package outline | |
| 12 | Packing information | |
| 13 | Soldering | |
| 14 | Soldering/landing pad information | |
| 15 | Revision history | |
| 16 | Legal information | |
| | | |

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

© NXP B.V. 2017.

All rights reserved.

For more information, please visit: http://www.nxp.com For sales office addresses, please send an email to: salesaddresses@nxp.com

Date of release: 10 October 2017 Document identifier: MPL115A1