

#### Addendum

HC908LJ12AD/D Rev. 0, 6/2003

Addendum to MC68HC908LJ12 Technical Data

This addendum provides information to the following MCU devices:

- MC68HLC908LJ12 (see page 1)
- MC68HC08LJ12 (see page 9)

The entire MC68HC908LJ12 Technical Data, Rev. 2 (Motorola document number MC68HC908LJ12/D) applies to the these two devices, with exceptions outlined in this addendum.

Amendments to MC68HC908LJ12/D, Rev. 2, are documented on page 13.

### MC68HLC908LJ12

The MC68HLC908LJ12 is a low-voltage version of the MC68HC908LJ12, with an operating voltage range of 2.4 to 3.3 V.

**FLASH Memory** The FLASH memory can be read at operating voltages from 2.4 to 3.3 V.

Program or erase operations require a minimum operating voltage of 2.7V.

Low-Voltage Inhibit

(LVI)

The LVI module is not designed for the MC68HLC908LJ12. After an MCU reset, the LVI module is disabled (LVIPWRD = 1 in CONFIG1). The LVIPWRD

bit should be left as logic 1 (the default setting).

Electrical Electrical specifications for the MC68HLC908LJ12 device are given in the **Specifications** 

following tables.





Functional Operating Range

HC908LJ12AD/D

**Table 1. Operating Range** 

Characteristic	Symbol	Value		Unit
Operating temperature range	T <sub>A</sub>	-40 to +85		°C
Operating voltage range	V <sub>DD</sub>	2.4 to 2.7	2.7 to 3.3	V
Maximum internal operating frequency	f <sub>OP</sub>	2	4	MHz
Operating voltage for FLASH memory program and erase operations	V <sub>DD</sub>	2.7 to 3.3		V

DC Electrical Characteristics

Table 2. DC Electrical Characteristics (2.4 to 2.7V)

Characteristic <sup>(1)</sup>	Symbol	Min	Typ <sup>(2)</sup>	Max	Unit
Output high voltage (I <sub>LOAD</sub> = −1.0 mA) All ports	V <sub>OH</sub>	V <sub>DD</sub> -0.4	_	_	V
Output low voltage (I <sub>LOAD</sub> = 0.8mA) All ports (I <sub>LOAD</sub> = 4.0 mA) PTB2-PTB5 (I <sub>LOAD</sub> = 10.0 mA) PTB0/TxD-PTB1	V <sub>OL</sub>	_	_	0.4	V
Input high voltage All ports, RST, IRQ, OSC1	V <sub>IH</sub>	$0.7 \times V_{DD}$	_	V <sub>DD</sub>	V
Input low voltage All ports, RST, IRQ, OSC1	V <sub>IL</sub>	V <sub>SS</sub>	_	$0.3 \times V_{DD}$	>
$V_{DD}$ supply current $Run^{(3)}$ , $f_{OP} = 2$ MHz with all modules on with ADC on with ADC off $Wait^{(4)}$ , $f_{OP} = 2$ MHz (all modules off) $Stop$ , $f_{OP} = 8$ kHz <sup>(5)</sup> $25^{\circ}C$ (with OSC, RTC, LCD <sup>(6)</sup> , LVI on) $25^{\circ}C$ (with OSC, RTC on) $25^{\circ}C$ (all modules off)	I <sub>DD</sub>			5.2 3.8 2.8 2.3 200 27 15 1	m A A A A A A A A A A A A A A A A A A A
Digital I/O ports Hi-Z leakage current All ports, RST	I <sub>IL</sub>	_	_	± 10	μΑ



HC908LJ12AD/D MC68HLC908LJ12

Table 2. DC Electrical Characteristics (2.4 to 2.7 V) (Continued)

Characteristic <sup>(1)</sup>	Symbol	Min	Typ <sup>(2)</sup>	Max	Unit
Input current IRQ	I <sub>IN</sub>	_	_	± 1	μΑ
Capacitance Ports (as input or output)	C <sub>OUT</sub> C <sub>IN</sub>	_	_	12 8	pF
POR re-arm voltage <sup>(7)</sup>	V <sub>POR</sub>	0	_	100	mV
POR rise-time ramp rate <sup>(8)</sup>	R <sub>POR</sub>	0.02	_	_	V/ms
Monitor mode entry voltage (at IRQ pin)	V <sub>HI</sub>	$1.5 \times V_{DD}$	_	$2 \times V_{DD}$	V
Pullup resistors <sup>(9)</sup> PTA0-PTA3, PTD4-PTD7 configured as KBI0-KBI7 RST, IRQ	R <sub>PU1</sub> R <sub>PU2</sub>		25 27	_ _	kΩ kΩ

- 1.  $V_{DD}$  = 2.4 to 2.7 Vdc,  $V_{SS}$  = 0 Vdc,  $T_A$  =  $T_L$  to  $T_H$ , unless otherwise noted.
- Typical values reflect average measurements at midpoint of voltage range, 25 °C only.
   Run (operating) I<sub>DD</sub> measured using external square wave clock source. All inputs 0.2 V from rail. No dc loads. Less than 100 pF on all outputs. C<sub>L</sub> = 20 pF on OSC2. All ports configured as inputs. OSC2 capacitance linearly affects run I<sub>DD</sub>.
- 4. Wait I<sub>DD</sub> measured using external square wave clock source. All inputs 0.2 V from rail. No dc loads. Less than 100 pF on all outputs.  $C_L = 20$  pF on OSC2. All ports configured as inputs. OSC2 capacitance linearly affects wait  $I_{DD}$ .
- 5. The 8kHz clock is from a 32kHz clock input at OSC1, for the driving the RTC.
- 6. LCD driver configured for low current mode.
- 7. Maximum is highest voltage that POR is guaranteed.
- 8. If minimum V<sub>DD</sub> is not reached before the internal POR reset is released, RST must be driven low externally until minimum V<sub>DD</sub> is reached.
- 9.  $R_{PU1}$  and  $R_{PU2}$  are measured at  $V_{DD}$  = 2.6 V.

Table 3. DC Electrical Characteristics (2.7 to 3.3 V)

Characteristic <sup>(1)</sup>	Symbol	Min	Тур <sup>(2)</sup>	Max	Unit
Output high voltage (I <sub>LOAD</sub> = -1.0 mA) All ports	V <sub>OH</sub>	V <sub>DD</sub> -0.4	_	_	V
Output low voltage (I <sub>LOAD</sub> = 0.8mA) All ports (I <sub>LOAD</sub> = 4.0 mA) PTB2-PTB5 (I <sub>LOAD</sub> = 10.0 mA) PTB0/TxD-PTB1	V <sub>OL</sub>	_	_	0.4	V
Input high voltage All ports, RST, IRQ, OSC1	V <sub>IH</sub>	$0.7 \times V_{DD}$	_	V <sub>DD</sub>	V
Input low voltage All ports, RST, IRQ, OSC1	V <sub>IL</sub>	V <sub>SS</sub>	_	$0.3 \times V_{DD}$	V

Table 3. DC Electrical Characteristics (2.7 to 3.3 V) (Continued)

Characteristic <sup>(1)</sup>	Symbol	Min	Typ <sup>(2)</sup>	Max	Unit
V <sub>DD</sub> supply current					
$Run^{(3)}$ , $f_{OP} = 4 MHz$					
with all modules on		_	_	8	mA
with ADC on with ADC off		_	_	6 5	mA mA
Wait <sup>(4)</sup> , f <sub>OP</sub> = 4 MHz (all modules off)		_	_	3.5	mA
	I <sub>DD</sub>	_	_	3.5	IIIA
Stop, $f_{OP} = 8 \text{ kHz}^{(5)}$				000	•
25°C (with OSC, RTC, LCD <sup>(6)</sup> , LVI on)		_	_	280	μΑ
25°C (with OSC, RTC, LCD <sup>(6)</sup> on)			_	38 15	μA μA
25°C (with OSC, RTC on) 25°C (all modules off)		_	_	1	μΑ
,					•
Digital I/O ports Hi-Z leakage current All ports, RST	I <sub>IL</sub>	_	_	± 10	μΑ
Input current IRQ	I <sub>IN</sub>	_	_	± 1	μΑ
Capacitance	C <sub>OUT</sub>	_	_	12	,, F
Ports (as input or output)	C <sub>IN</sub>	_	_	8	pF
POR re-arm voltage <sup>(7)</sup>	V <sub>POR</sub>	0	_	100	mV
POR rise-time ramp rate <sup>(8)</sup>	R <sub>POR</sub>	0.02	_	_	V/ms
Monitor mode entry voltage (at IRQ pin)	V <sub>HI</sub>	$1.5 \times V_{DD}$	_	$2 \times V_{DD}$	V
Pullup resistors <sup>(9)</sup> PTA0–PTA3, PTD4–PTD7 configured as KBI0–KBI7 RST, IRQ	R <sub>PU1</sub> R <sub>PU2</sub>		25 27	_ _	kΩ kΩ

- 1.  $V_{DD}$  = 2.7 to 3.3 Vdc,  $V_{SS}$  = 0 Vdc,  $T_A$  =  $T_L$  to  $T_H$ , unless otherwise noted. 2. Typical values reflect average measurements at midpoint of voltage range, 25 °C only. 3. Run (operating)  $I_{DD}$  measured using external square wave clock source. All inputs 0.2 V from rail. No dc loads. Less than
- 100 pF on all outputs. C<sub>L</sub> = 20 pF on OSC2. All ports configured as inputs. OSC2 capacitance linearly affects run I<sub>DD</sub>.

  4. Wait I<sub>DD</sub> measured using external square wave clock source. All inputs 0.2 V from rail. No dc loads. Less than 100 pF on all outputs. C<sub>L</sub> = 20 pF on OSC2. All ports configured as inputs. OSC2 capacitance linearly affects wait I<sub>DD</sub>.
- 5. The 8kHz clock is from a 32kHz clock input at OSC1, for the driving the RTC.
- 6. LCD driver configured for low current mode.
- 7. Maximum is highest voltage that POR is guaranteed.
- 8. If minimum V<sub>DD</sub> is not reached before the internal POR reset is released, RST must be driven low externally until minimum V<sub>DD</sub> is reached.
- 9.  $R_{PU1}$  and  $R_{PU2}$  are measured at  $V_{DD} = 3V$ .



HC908LJ12AD/D MC68HLC908LJ12

Oscillator Characteristics

Table 4. Oscillator Specifications (2.4 to 2.7V)

Characteristic	Symbol	Min	Тур	Max	Unit
Internal oscillator clock frequency	f <sub>ICLK</sub>	_	See Figure 1.	_	Hz
External reference clock to OSC1 <sup>(1)</sup>	fosc	dc	_	8M	Hz
Crystal reference frequency <sup>(2)</sup>	f <sub>XCLK</sub>		32.768k	4.9152M	Hz
Crystal load capacitance <sup>(3)</sup>	C <sub>L</sub>	_	_	_	
Crystal fixed capacitance	C <sub>1</sub>	_	2 × C <sub>L</sub> (25p)	_	F
Crystal tuning capacitance	C <sub>2</sub>	_	2 × C <sub>L</sub> (25p)	_	F
Feedback bias resistor	R <sub>B</sub>	_	10M	_	Ω
Series resistor <sup>(4)</sup>	R <sub>S</sub>	_	100k	_	Ω

- 1. No more than 10% duty cycle deviation from 50%.
- 2. Fundamental mode crystals only.
- 3. Consult crystal manufacturer's data.
- 4. Not Required for high frequency crystals.

Table 5. Oscillator Specifications (2.7 to 3.3 V)

Characteristic	Symbol	Min	Тур	Max	Unit
Internal oscillator clock frequency	f <sub>ICLK</sub>	_	See Figure 1.	_	Hz
External reference clock to OSC1 <sup>(1)</sup>	f <sub>OSC</sub>	dc	_	16M	Hz
Crystal reference frequency <sup>(2)</sup>	f <sub>XCLK</sub>		32.768k	4.9152M	Hz
Crystal load capacitance <sup>(3)</sup>	C <sub>L</sub>	_	_	_	
Crystal fixed capacitance	C <sub>1</sub>	_	2 × C <sub>L</sub> (25p)	_	F
Crystal tuning capacitance	C <sub>2</sub>	_	2 × C <sub>L</sub> (25p)	_	F
Feedback bias resistor	R <sub>B</sub>	_	10M	_	Ω
Series resistor <sup>(4)</sup>	R <sub>S</sub>	_	100k	_	Ω

- No more than 10% duty cycle deviation from 50%.
   Fundamental mode crystals only.
- 3. Consult crystal manufacturer's data.
- 4. Not Required for high frequency crystals.



HC908LJ12AD/D

## 

Figure 1. Typical Internal Oscillator Frequency


ADC Electrical Characteristics

Table 6. ADC Electrical Characteristics (2.4 to 3.3 V)

Characteristic	Symbol	Min	Max	Unit	Notes
Supply voltage	$V_{DDA}$	2.4	3.3	V	
Input range	V <sub>ADIN</sub>	0	$V_{DDA}$	V	$V_{ADIN} \le V_{DDA}$
Resolution	B <sub>AD</sub>	10	10	bits	1,024 counts
Absolute accuracy	A <sub>AD</sub>	See Figure 2	and Figure 3.		Includes quantization. ±1 ADC count = ±0.5 LSB
ADC internal clock	f <sub>ADIC</sub>	32 k	2 M	Hz	$t_{ADIC} = 1/f_{ADIC}$
Conversion range	R <sub>AD</sub>	$V_{REFL}$	V <sub>REFH</sub>	V	
ADC voltage reference high	V <sub>REFH</sub>	_	V <sub>DDA</sub> + 0.1	V	
ADC voltage reference low	V <sub>REFL</sub>	V <sub>SSA</sub> - 0.1	_	V	$V_{\rm SSA}$ is tied to $V_{\rm SS}$ internally.
Conversion time	t <sub>ADC</sub>	16	17	t <sub>ADIC</sub> cycles	
Sample time	t <sub>ADS</sub>	5	_	t <sub>ADIC</sub> cycles	
Monotonically	M <sub>AD</sub>	(	Guaranteed		
Zero input reading	Z <sub>ADI</sub>	000	001	HEX	$V_{ADIN} = V_{REFL}$
Full-scale reading	F <sub>ADI</sub>	3FC	3FF	HEX	V <sub>ADIN</sub> = V <sub>REFH</sub>
Input capacitance	C <sub>ADI</sub>	_	20	pF	Not tested.
Input impedance	R <sub>ADI</sub>	20M	_	Ω	Measured at 5V
V <sub>REFH</sub> /V <sub>REFL</sub>	I <sub>VREF</sub>	_	1.6	mA	Not tested.



HC908LJ12AD/D MC68HLC908LJ12



Note: ADC performance increases with increase in operating voltage and temperature.

Figure 2. Typical ADC Accuracy (2.4V and 2.7V)






Figure 3. Typical ADC Accuracy (3V and 3.3V)

Memory Characteristics

At an operating voltage of less than 2.7 V, the FLASH memory can only be read. Program and erase are achieved at an operating voltage of 2.7 to 3.3 V. The program and erase parameters in the MC68HC908LJ12 Technical Data are for  $V_{DD} = 2.7$  to 3.3V only.

#### MC68HLC908LJ12 **Order Numbers**

Table 7 shows the ordering numbers for the MC68HLC908LJ12.

Table 7. MC68HLC908LJ12 Order Numbers

MC Order Number <sup>(1)</sup>	Package	Operating Temperature Range
MC68HLC98LJ12CFB	52-pin LQFP	−40 °C to +85 °C
MC68HLC98LJ12CPB	64-pin LQFP	−40 °C to +85 °C
MC68HLC98LJ12CFU	64-pin QFP	−40 °C to +85 °C

1. The missing "0" in "908" is intentional.



HC908LJ12AD/D MC68HC08LJ12

#### MC68HC08LJ12

The MC68HC08LJ12 is the ROM part equivalent to the MC68HC908LJ12.

Table 8. Summary of MC68HC08LJ12 and MC68HC908LJ12 Differences

	MC68HC08LJ12	MC68HC908LJ12
Operating voltages	— 5.0 V ± 10%	3.3V ± 10% 5.0V ± 10%
Memory (\$C000-\$EFFF)	12,288 bytes ROM	12,288 bytes FLASH
User vectors (\$FFD0-\$FFFF)	48 bytes ROM	48 bytes FLASH
Registers at \$FE08 and \$FF09	Not used; locations are reserved.	FLASH related registers. \$FE08 — FLCR \$FF09 — FLBPR
Monitor ROM (\$FC00-\$FDFF and \$FE10-\$FFCF)	Used for testing purposes only.	Used for testing and FLASH programming/erasing.
Available packages	52-pin LQFP 64-pin LQFP 64-pin QFP	52-pin LQFP 64-pin LQFP 64-pin QFP

MCU Block Diagram Figure 4 shows the block diagram of the MC68HC08LJ12.

Memory Map The MC68HC08LJ128 has 12,288 bytes of user ROM from \$C000 to \$EFFF,

and 48 bytes of user ROM vectors from \$FFD0 to \$FFFF. On the MC68HC908LJ12 these memory locations are FLASH memory.

Figure 5 shows the memory map of the MC68HC08LJ12.

MC68HC08LJ12.

On the MC68HC908LJ12, these two locations are the FLASH control register

and the FLASH block protect register respectively.

Monitor ROM The monitor program (monitor ROM: \$FE10-\$FFCF and \$FC00-\$FDFF) on

the MC68HC08LJ12 is for device testing only.



HC908LJ12AD/D




Figure 4. MC68HC08LJ12 Block Diagram



HC908LJ12AD/D MC68HC08LJ12

\$0000	I/O Registers
↓ \$005F	96 Bytes
\$0060	
<b>\</b>	RAM 512 Bytes
\$025F	312 bytes
\$0260	Unimplemented
↓ \$BFFF	48,544 Bytes
\$C000	2011
<b>\</b>	ROM 12,288 Bytes
\$EFFF	12,200 Bytos
\$F000	Unimplemented
\$FBFF	3,072 Bytes
\$FC00	Marifa de DOMA
<b>↓</b>	Monitor ROM 1 512 Bytes
\$FDFF	·
\$FE00	SIM Break Status Register (SBSR)
\$FE01	SIM Reset Status Register (SRSR)
\$FE02	Reserved
\$FE03	SIM Break Flag Control Register (SBFCR)
\$FE04	Interrupt Status Register 1 (INT1)
\$FE05	Interrupt Status Register 2 (INT2)
\$FE06	Interrupt Status Register 3 (INT3)
\$FE07	Reserved
\$FE08	Reserved
\$FE09	Reserved
\$FE0A	Reserved
\$FE0B	Reserved
\$FE0C	Break Address Register High (BRKH)
\$FE0D	Break Address Register Low (BRKL)
\$FE0E	Break Status and Control Register (BRKSCR)
\$FE0F	LVI Status Register (LVISR)
\$FE10	Monitor ROM 2
↓ \$FFCF	448 Bytes
\$FFD0	POM \/actoro
↓ \$FFFF	ROM Vectors 48 Bytes

Figure 5. MC68HC08LJ12 Memory Map



#### HC908LJ12AD/D

Electrical Specifications

Electrical specifications for the MC68HC908LJ12 apply to the MC68HC08LJ12 except for the parameters indicated below.

Functional Operating Range

**Table 9. Operating Range** 

Characteristic	Symbol	Value	Unit
Operating temperature range	T <sub>A</sub>	-40 to +85	°C
Operating voltage range	$V_{DD}$	5.0V ± 10%	V

RAM Memory Characteristics

**Table 10. Memory Characteristics** 

Characteristic	Symbol	Min.	Max.	Unit
RAM data retention voltage	$V_{RDR}$	1.3	_	V

Notes:

Since MC68HC08LJ12 is a ROM device, FLASH memory electrical characteristics do not apply.

MC68HC08LJ12
Order Numbers

These part numbers are generic numbers only. To place an order, ROM code must be submitted to the ROM Processing Center (RPC).

Table 11. MC68HC08LJ12 Order Numbers

MC Order Number	Package	Operating Temperature Range
MC68HC08LJ12CFB	52-pin LQFP	−40 °C to +85 °C
MC68HC08LJ12CPB	64-pin LQFP	−40 °C to +85 °C
MC68HC08LJ12CFU	64-pin QFP	−40 °C to +85 °C



HC908LJ12AD/D AMENDMENTS TO MC68HC908LJ12/D, REV. 2

## AMENDMENTS TO MC68HC908LJ12/D, REV. 2

5.0V DC Electrical Characteristics

Pages 394 and 395, Table 23-4 5.0V DC Electrical Characteristics —

Delete LVI typical values and correct note 6.

#### From:

Characteristic	Symbol	Min	Тур	Max	Unit
Low-voltage inhibit, trip falling voltage	$V_{TRIPF}$	4.00	4.32	4.70	V
Low-voltage inhibit, trip rising voltage	V <sub>TRIPR</sub>	4.00	4.32	4.70	V

#### Notes:

6. LCD driver configured for high current mode.

#### To:

Characteristic	Symbol	Min	Тур	Max	Unit
Low-voltage inhibit, trip falling voltage	V <sub>TRIPF</sub>	4.00	_	4.70	V
Low-voltage inhibit, trip rising voltage	V <sub>TRIPR</sub>	4.00	_	4.70	V

#### Notes:

6. LCD driver configured for low current mode.

# 3.3V DC Electrical Characteristics

Pages 396 and 397, Table 23-5 3.3V DC Electrical Characteristics —

Delete LVI typical values and correct note 6.

#### From:

Characteristic	Symbol	Min	Тур	Max	Unit
Low-voltage inhibit, trip falling voltage	$V_{TRIPF}$	2.40	2.57	2.88	V
Low-voltage inhibit, trip rising voltage	V <sub>TRIPR</sub>	2.46	2.63	2.97	V

#### Notes:

6. LCD driver configured for high current mode.

#### To:

Characteristic	Symbol	Min	Тур	Max	Unit
Low-voltage inhibit, trip falling voltage	$V_{TRIPF}$	2.40	_	2.88	V
Low-voltage inhibit, trip rising voltage	V <sub>TRIPR</sub>	2.46	_	2.97	V

#### Notes:

6. LCD driver configured for low current mode.



## HC908LJ12AD/D

Oscillator Characteristics Page 398, *Table 23-8 5.0V Oscillator Specifications* and *Table 23-9 3.3V Oscillator Specifications* — Replace *Internal oscillator clock frequency* values.

From:

Characteristic	Symbol	Min	Тур	Max	Unit
Internal oscillator clock frequency	f <sub>ICLK</sub>	46k	47k	48k	Hz

Characteristic	Symbol	Min	Тур	Max	Unit
Internal oscillator clock frequency	f <sub>ICLK</sub>	42.8k	43.4k	44k	Hz

To: See Figure 1 . Typical Internal Oscillator Frequency on page 6 of this document.

- END -





Home Page:

www.freescale.com

email:

support@freescale.com

**USA/Europe or Locations Not Listed:** 

Freescale Semiconductor Technical Information Center, CH370 1300 N. Alma School Road Chandler, Arizona 85224 (800) 521-6274 480-768-2130

support@freescale.com

Europe, Middle East, and Africa:

Freescale Halbleiter Deutschland GmbH

**Technical Information Center** 

Schatzbogen 7

81829 Muenchen, Germany

+44 1296 380 456 (English)

+46 8 52200080 (English)

+49 89 92103 559 (German)

+33 1 69 35 48 48 (French)

support@freescale.com

Japan:

Freescale Semiconductor Japan Ltd.

Headquarters

ARCO Tower 15F

1-8-1, Shimo-Meguro, Meguro-ku

Tokyo 153-0064, Japan

0120 191014

+81 2666 8080

support.japan@freescale.com

Asia/Pacific:

Freescale Semiconductor Hong Kong Ltd.

**Technical Information Center** 

2 Dai King Street

Tai Po Industrial Estate,

Tai Po, N.T., Hong Kong

+800 2666 8080

support.asia@freescale.com

For Literature Requests Only:

Freescale Semiconductor

Literature Distribution Center

P.O. Box 5405 Denver, Colorado 80217

(800) 441-2447

303-675-2140

Fax: 303-675-2150

LDCForFreescaleSemiconductor

@hibbertgroup.com

RoHS-compliant and/or Pb- free versions of Freescale products have the functionality and electrical characteristics of their non-RoHS-compliant and/or non-Pb- free counterparts. For further information, see http://www.freescale.com or contact your Freescale sales representative.

For information on Freescale.s Environmental Products program, go to http://www.freescale.com/epp.

Information in this document is provided solely to enable system and software implementers to use Freescale Semiconductor products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits or integrated circuits based on the information in this document. Freescale Semiconductor reserves the right to make changes without further notice to any products herein. Freescale Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Freescale Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters which may be provided in Freescale Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. Freescale Semiconductor does not convey any license under its patent rights nor the rights of others. Freescale Semiconductor products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Freescale Semiconductor product could create a situation where personal injury or death may occur. Should Buyer purchase or use Freescale Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold Freescale Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Freescale Semiconductor was negligent regarding the design or manufacture of the part.

