PCA9955B

16-channel Fm+ I²C-bus 57 mA constant current LED driver Rev. 2.3 — 27 September 2024

Product data sheet



General description

The PCA9955B is an I²C-bus controlled 16-channel constant current LED driver optimized for dimming and blinking 57 mA Red/Green/Blue/Amber (RGBA) LEDs in amusement products. Each LED output has its own 8bit resolution (256 steps) fixed frequency individual PWM controller that operates at 31.25 kHz with a duty cycle that is adjustable from 0 % to 100 % to allow the LED to be set to a specific brightness value. An additional 8-bit resolution (256 steps) group PWM controller has both a fixed frequency of 122 Hz and an adjustable frequency between 15 Hz to every 16.8 seconds with a duty cycle that is adjustable from 0 % to 99.6 % that is used to either dim or blink all LEDs with the same value.

Each LED output can be off, on (no PWM control), set at its individual PWM controller value or at both individual and group PWM controller values. The PCA9955B operates with a supply voltage range of 3 V to 5.5 V and the constant current sink LED outputs allow up to 20 V for the LED supply. The output peak current is adjustable with an 8-bit linear DAC from 225 µA to 57 mA.

Gradation control for all current sources is achieved via the I²C-bus serial interface and allows user to ramp current automatically without MCU intervention. 8-bit DACs are available to adjust brightness levels for each LED current source. There are four selectable gradation control groups and each group has independently four registers to control ramp-up and ramp-down rate, step time, hold ON/OFF time and final hold ON output current. Two gradation operation modes are available for each group, one is single shot mode (output pattern once) and the other is continuous mode (output pattern repeat). Each channel can be set to either gradation mode or normal mode and assigned to any one of these four gradation control groups.

This device has built-in open, short load and overtemperature detection circuitry. The error information from the corresponding register can be read via the l²C-bus. Additionally, a thermal shutdown feature protects the device when internal junction temperature exceeds the limit allowed for the process.

The PCA9955B device has a Fast-mode Plus (Fm+) I²C-bus interface. Fm+ devices offer higher frequency (up to 1 MHz) or more densely populated bus operation (up to 4000 pF).

The active LOW output enable input pin (OE) blinks all the LED outputs and can be used to externally PWM the outputs, which is useful when multiple devices need to be dimmed or blinked together without using software control.

Software programmable LED Group and three Sub Call I²C-bus addresses allow all or defined groups of PCA9955B devices to respond to a common I²C-bus address, allowing for example, all red LEDs to be turned on or off at the same time or marquee chasing effect, thus minimizing I²C-bus commands. On power-up, PCA9955B has a unique Sub Call address to identify it as a 16-channel LED driver. This unique address allows mixing of devices with different channel widths. Three hardware address pins on PCA9955B allow up to 125 devices on the same bus.

The Software Reset (SWRST) function allows the master to perform a reset of the PCA9955B through the I²Cbus, identical to the Power-On Reset (POR) that initializes the registers to their default state causing the output current switches to be OFF (LED off). This allows an easy and quick way to reconfigure all device registers to the same condition.



16-channel Fm+ I²C-bus 57 mA constant current LED driver

2 Features and benefits

- 16 LED drivers. Each output programmable at:
 - Off
 - **–** On
 - Programmable LED brightness
 - Programmable group dimming/blinking mixed with individual LED brightness
 - Programmable LED output delay to reduce EMI and surge currents
- · Gradation control for all channels
 - Each channel can assign to one of four gradation control groups
 - Programmable gradation time and rate for ramp-up and/or ramp-down operations
 - Programmable step time (6-bit) from 0.5 ms (minimum) to 512 ms (maximum)
 - Programmable hold-on time after ramp-up and hold-off time after ramp-down (3-bit) from 0 s to 6 s
 - Programmable final ramp-up and hold-on current
 - Programmable brightness current output adjustment, either linear or exponential curve
- 16 constant current output channels can sink up to 57 mA, tolerate up to 20 V when OFF
- Output current adjusted through an external resistor (Rext input)
- · Output current accuracy
 - ±4 % between output channels
 - ±6 % between PCA9955B devices
- Open/short load/overtemperature detection mode to detect individual LED errors (R_{ext} < 3 kΩ)
- 1 MHz Fast-mode Plus compatible I²C-bus interface with 30 mA high drive capability on SDA output for driving high capacitive buses
- 256-step (8-bit) linear programmable brightness per LED output varying from fully off (default) to maximum brightness fully ON using a 31.25 kHz PWM signal
- 256-step group brightness control allows general dimming (using a 122 Hz PWM signal) from fully off to maximum brightness (default)
- 256-step group blinking with frequency programmable from 15 Hz to 16.8 s and duty cycle from 0 % to 99.6 %
- Output state change programmable on the Acknowledge or the STOP condition to update outputs byte-bybyte or all at the same time (default to 'Change on STOP').
- Active LOW Output Enable (OE) input pin allows for hardware blinking and dimming of the LEDs
- Three quinary hardware address pins allow 125 PCA9955B devices to be connected to the same I²C-bus and to be individually programmed
- 4 software programmable I²C-bus addresses (one LED Group Call address and three LED Sub Call addresses) allow groups of devices to be addressed at the same time in any combination (for example, one register used for 'All Call' so that all the PCA9955Bs on the I²C-bus can be addressed at the same time and the second register used for three different addresses so that ¹/₃ of all devices on the bus can be addressed at the same time in a group). Software enable and disable for each programmable I²C-bus address.
- Unique power-up default Sub Call address allows mixing of devices with different channel widths
- Software Reset feature (SWRST Call) allows the device to be reset through the I²C-bus
- 8 MHz internal oscillator requires no external components
- · Internal power-on reset
- Noise filter on SDA/SCL inputs
- · No glitch on LEDn outputs on power-up
- · Low standby current
- Operating power supply voltage (V_{DD}) range of 3 V to 5.5 V
- 5.5 V tolerant inputs on non-LED pins
- -40 °C to +105 °C operation

PCA9955E

- ESD protection exceeds 4000 V HBM per JESD22-A114
- Latch-up testing is done to JEDEC Standard JESD78 which exceeds 100 mA
- Packages offered: HTSSOP28
 - PCA9955BTW/Q900 for automotive

16-channel Fm+ I²C-bus 57 mA constant current LED driver

3 Applications

- · Amusement products
- RGB or RGBA LED drivers
- LED status information
- LED displays
- · LCD backlights
- Keypad backlights for cellular phones or handheld devices
- Fade-in and fade-out for breathlight control
- Automotive lighting (PCA9955BTW/Q900)

16-channel Fm+ I²C-bus 57 mA constant current LED driver

4 Ordering information

Table 1. Ordering information

| Type number | Topside mark | Package | | | | |
|--------------------------------|--------------|----------|--|-----------|--|--|
| | | Name | Description | Version | | |
| PCA9955BTW | PCA9955BTW | HTSSOP28 | plastic thermal enhanced thin shrink small outline package; 28 leads; body width 4.4 mm; lead pitch 0.65 mm; exposed die pad | SOT1172-3 | | |
| PCA9955BTW/Q900 ^[1] | PCA9955BTW | HTSSOP28 | plastic thermal enhanced thin shrink small outline package; 28 leads; body width 4.4 mm; lead pitch 0.65 mm; exposed die pad | SOT1172-3 | | |

^[1] PCA9955BTW/Q900 is AEC-Q100 compliant.


4.1 Ordering options

Table 2. Ordering options

| rante at the state of the state | | | | | | | | | | | |
|--|--------------------------|----------|--------------------------------------|------------------------|--------------------------------------|--|--|--|--|--|--|
| Type number | Orderable part number | Package | Packing method | Minimum order quantity | Temperature | | | | | | |
| PCA9955BTW | PCA9955BTWJ | HTSSOP28 | Reel 13" Q1/T1 *Standard mark SMD | 2500 | T _{amb} = -40 °C to +105 °C | | | | | | |
| PCA9955BTW/Q900 | PCA9955BTW/Q900J | HTSSOP28 | Reel 13" Q1/T1 *Standard mark SMD | 2500 | T _{amb} = -40 °C to +105 °C | | | | | | |

16-channel Fm+ I²C-bus 57 mA constant current LED driver

5 Block diagram



Dim repetition rate = 122 Hz


Blink repetition rate = 15 Hz to every 16.8 seconds

Figure 1. Block diagram of PCA9955B

16-channel Fm+ I²C-bus 57 mA constant current LED driver

6 Pinning information

6.1 Pinning



6.2 Pin description

Table 3. Pin description

| Symbol | Pin | Туре | Description |
|--------|-----|------|--|
| REXT | 1 | I | current set resistor input; resistor to ground |
| AD0 | 2 | I | address input 0 |
| AD1 | 3 | I | address input 1 |
| AD2 | 4 | I | address input 2 |
| ŌĒ | 5 | I | active LOW output enable for LEDs |
| LED0 | 6 | 0 | LED driver 0 |
| LED1 | 7 | 0 | LED driver 1 |
| LED2 | 8 | 0 | LED driver 2 |
| LED3 | 9 | 0 | LED driver 3 |
| LED4 | 11 | 0 | LED driver 4 |
| LED5 | 12 | 0 | LED driver 5 |
| LED6 | 13 | 0 | LED driver 6 |
| LED7 | 14 | 0 | LED driver 7 |
| LED8 | 15 | 0 | LED driver 8 |
| LED9 | 16 | 0 | LED driver 9 |
| LED10 | 17 | 0 | LED driver 10 |
| LED11 | 18 | 0 | LED driver 11 |

Table 3. Pin description...continued

| Symbol | Pin | Туре | Description |
|-----------------|---------------------------|--------------|---|
| LED12 | 20 | 0 | LED driver 12 |
| LED13 | 21 | 0 | LED driver 13 |
| LED14 | 22 | 0 | LED driver 14 |
| LED15 | 23 | 0 | LED driver 15 |
| RESET | 25 | I | active LOW reset input with external 10 kΩ pull-up resistor |
| SCL | 26 | 1 | serial clock line |
| SDA | 27 | I/O | serial data line |
| V _{SS} | 10, 19, 24 ^[1] | ground | supply ground |
| V_{DD} | 28 | power supply | supply voltage |

^[1] HTSSOP28 package supply ground is connected to both V_{SS} pins and exposed center pad. V_{SS} pins must be connected to supply ground for proper device operation. For enhanced thermal, electrical, and board level performance, the exposed pad must be soldered to the board using a corresponding thermal pad on the board and for proper heat conduction through the board, thermal vias must be incorporated in the printed-circuit board in the thermal pad region.

16-channel Fm+ I²C-bus 57 mA constant current LED driver

7 Functional description

Refer to Figure 1.

7.1 Device addresses

Following a START condition, the bus master must output the address of the slave it is accessing.

For PCA9955B there are a maximum of 125 possible programmable addresses using the three quinary hardware address pins.

7.1.1 Regular I²C-bus slave address

The I^2 C-bus slave address of the PCA9955B is shown in <u>Figure 3</u>. The 7-bit slave address is determined by the quinary input pads AD0, AD1 and AD2. Each pad can have one of five states (GND, pull-up, floating, pull-down, and V_{DD}) based on how the input pad is connected on the board. At power-up or hardware/software reset, the quinary input pads are sampled and set the slave address of the device internally. To conserve power, once the slave address is determined, the quinary input pads are turned off and will not be sampled until the next time the device is power cycled. <u>Table 4</u> lists the five possible connections for the quinary input pads along with the external resistor values that must be used.

Table 4. Quinary input pad connection

| Pad connection (pins AD2, AD1, AD0) ^[1] | Mnemonic | External resistor (kΩ) | | | |
|--|-----------------|------------------------|------|--|--|
| | | Min. | Max. | | |
| tie to ground | GND | 0 | 17.9 | | |
| resistor pull-down to ground | PD | 34.8 | 270 | | |
| open (floating) | FLT | 503 | ∞ | | |
| resistor pull-up to V _{DD} | PU | 31.7 | 340 | | |
| tie to V _{DD} | V _{DD} | 0 | 22.1 | | |

^[1] These AD[2:0] inputs must be stable before the supply V_{DD} to the chip.

<u>Table 5</u> lists all 125 possible slave addresses of the device based on all combinations of the five states connected to three address input pins AD0, AD1 and AD2.

Table 5. I²C-bus slave address

| Hardware selectable input pins | | | I ² C-bus slave address for PCA9955B | | | | |
|--------------------------------|-----|----------|---|-------------|------------------------|-------------------|--|
| AD2 | AD1 | AD0 | Decimal | Hexadecimal | Binary (A[6:0]) | Address (R/W = 0) | |
| GND | GND | GND | 1 | 01 | 0000001 ^[1] | 02h | |
| GND | GND | PD | 2 | 02 | 0000010 ^[1] | 04h | |
| GND | GND | FLT | 3 | 03 | 0000011 ^[1] | 06h | |
| GND | GND | PU | 4 | 04 | 0000100 ^[1] | 08h | |
| GND | GND | V_{DD} | 5 | 05 | 0000101 ^[1] | 0Ah | |
| GND | PD | GND | 6 | 06 | 0000110 ^[1] | 0Ch | |
| GND | PD | PD | 7 | 07 | 0000111 ^[1] | 0Eh | |
| GND | PD | FLT | 8 | 08 | 0001000 | 10h | |
| GND | PD | PU | 9 | 09 | 0001001 | 12h | |

PCA9955E

Table 5. I²C-bus slave address...continued

| Hardware | selectable in | put pins | I ² C-bus sI | I ² C-bus slave address for PCA9955B | | | | | |
|----------|---------------|----------|-------------------------|---|-----------------|-------------------|--|--|--|
| AD2 | AD1 | AD0 | Decimal | Hexadecimal | Binary (A[6:0]) | Address (R/W = 0) | | | |
| GND | PD | V_{DD} | 10 | 0A | 0001010 | 14h | | | |
| GND | FLT | GND | 11 | ОВ | 0001011 | 16h | | | |
| GND | FLT | PD | 12 | 0C | 0001100 | 18h | | | |
| GND | FLT | FLT | 13 | 0D | 0001101 | 1Ah | | | |
| GND | FLT | PU | 14 | 0E | 0001110 | 1Ch | | | |
| GND | FLT | V_{DD} | 15 | 0F | 0001111 | 1Eh | | | |
| GND | PU | GND | 16 | 10 | 0010000 | 20h | | | |
| GND | PU | PD | 17 | 11 | 0010001 | 22h | | | |
| GND | PU | FLT | 18 | 12 | 0010010 | 24h | | | |
| GND | PU | PU | 19 | 13 | 0010011 | 26h | | | |
| GND | PU | V_{DD} | 20 | 14 | 0010100 | 28h | | | |
| GND | V_{DD} | GND | 21 | 15 | 0010101 | 2Ah | | | |
| GND | V_{DD} | PD | 22 | 16 | 0010110 | 2Ch | | | |
| GND | V_{DD} | FLT | 23 | 17 | 0010111 | 2Eh | | | |
| GND | V_{DD} | PU | 24 | 18 | 0011000 | 30h | | | |
| GND | V_{DD} | V_{DD} | 25 | 19 | 0011001 | 32h | | | |
| PD | GND | GND | 26 | 1A | 0011010 | 34h | | | |
| PD | GND | PD | 27 | 1B | 0011011 | 36h | | | |
| PD | GND | FLT | 28 | 1C | 0011100 | 38h | | | |
| PD | GND | PU | 29 | 1D | 0011101 | 3Ah | | | |
| PD | GND | V_{DD} | 30 | 1E | 0011110 | 3Ch | | | |
| PD | PD | GND | 31 | 1F | 0011111 | 3Eh | | | |
| PD | PD | PD | 32 | 20 | 0100000 | 40h | | | |
| PD | PD | FLT | 33 | 21 | 0100001 | 42h | | | |
| PD | PD | PU | 34 | 22 | 0100010 | 44h | | | |
| PD | PD | V_{DD} | 35 | 23 | 0100011 | 46h | | | |
| PD | FLT | GND | 36 | 24 | 0100100 | 48h | | | |
| PD | FLT | PD | 37 | 25 | 0100101 | 4Ah | | | |
| PD | FLT | FLT | 38 | 26 | 0100110 | 4Ch | | | |
| PD | FLT | PU | 39 | 27 | 0100111 | 4Eh | | | |
| PD | FLT | V_{DD} | 40 | 28 | 0101000 | 50h | | | |
| PD | PU | GND | 41 | 29 | 0101001 | 52h | | | |
| PD | PU | PD | 42 | 2A | 0101010 | 54h | | | |
| PD | PU | FLT | 43 | 2B | 0101011 | 56h | | | |
| PD | PU | PU | 44 | 2C | 0101100 | 58h | | | |

Table 5. I²C-bus slave address...continued

| Hardware | e selectable in | put pins | I ² C-bus sI | I ² C-bus slave address for PCA9955B | | | | | |
|----------|-----------------|-----------------|-------------------------|---|-----------------|-------------------|--|--|--|
| AD2 | AD1 | AD0 | Decimal | Hexadecimal | Binary (A[6:0]) | Address (R/W = 0) | | | |
| PD | PU | V _{DD} | 45 | 2D | 0101101 | 5Ah | | | |
| PD | V_{DD} | GND | 46 | 2E | 0101110 | 5Ch | | | |
| PD | V_{DD} | PD | 47 | 2F | 0101111 | 5Eh | | | |
| PD | V_{DD} | FLT | 48 | 30 | 0110000 | 60h | | | |
| PD | V_{DD} | PU | 49 | 31 | 0110001 | 62h | | | |
| PD | V_{DD} | V _{DD} | 50 | 32 | 0110010 | 64h | | | |
| FLT | GND | GND | 51 | 33 | 0110011 | 66h | | | |
| FLT | GND | PD | 52 | 34 | 0110100 | 68h | | | |
| FLT | GND | FLT | 53 | 35 | 0110101 | 6Ah | | | |
| FLT | GND | PU | 54 | 36 | 0110110 | 6Ch | | | |
| FLT | GND | V_{DD} | 55 | 37 | 0110111 | 6Eh | | | |
| FLT | PD | GND | 56 | 38 | 0111000 | 70h | | | |
| FLT | PD | PD | 57 | 39 | 0111001 | 72h | | | |
| FLT | PD | FLT | 58 | 3A | 0111010 | 74h | | | |
| FLT | PD | PU | 59 | 3B | 0111011 | 76h | | | |
| FLT | PD | V_{DD} | 60 | 3C | 0111100 | 78h | | | |
| FLT | FLT | GND | 61 | 3D | 0111101 | 7Ah | | | |
| FLT | FLT | PD | 62 | 3E | 0111110 | 7Ch | | | |
| FLT | FLT | FLT | 63 | 3F | 0111111 | 7Eh | | | |
| FLT | FLT | PU | 64 | 40 | 1000000 | 80h | | | |
| FLT | FLT | V_{DD} | 65 | 41 | 1000001 | 82h | | | |
| FLT | PU | GND | 66 | 42 | 1000010 | 84h | | | |
| FLT | PU | PD | 67 | 43 | 1000011 | 86h | | | |
| FLT | PU | FLT | 68 | 44 | 1000100 | 88h | | | |
| FLT | PU | PU | 69 | 45 | 1000101 | 8Ah | | | |
| FLT | PU | V_{DD} | 70 | 46 | 1000110 | 8Ch | | | |
| FLT | V_{DD} | GND | 71 | 47 | 1000111 | 8Eh | | | |
| FLT | V_{DD} | PD | 72 | 48 | 1001000 | 90h | | | |
| FLT | V_{DD} | FLT | 73 | 49 | 1001001 | 92h | | | |
| FLT | V_{DD} | PU | 74 | 4A | 1001010 | 94h | | | |
| FLT | V_{DD} | V_{DD} | 75 | 4B | 1001011 | 96h | | | |
| PU | GND | GND | 76 | 4C | 1001100 | 98h | | | |
| PU | GND | PD | 77 | 4D | 1001101 | 9Ah | | | |
| PU | GND | FLT | 78 | 4E | 1001110 | 9Ch | | | |
| PU | GND | PU | 79 | 4F | 1001111 | 9Eh | | | |

Table 5. I²C-bus slave address...continued

| Hardware | e selectable in | put pins | I ² C-bus sI | I ² C-bus slave address for PCA9955B | | | | | |
|-----------------|-----------------|-----------------|-------------------------|---|-----------------|-------------------|--|--|--|
| AD2 | AD1 | AD0 | Decimal | Hexadecimal | Binary (A[6:0]) | Address (R/W = 0) | | | |
| PU | GND | V _{DD} | 80 | 50 | 1010000 | A0h | | | |
| PU | PD | GND | 81 | 51 | 1010001 | A2h | | | |
| PU | PD | PD | 82 | 52 | 1010010 | A4h | | | |
| PU | PD | FLT | 83 | 53 | 1010011 | A6h | | | |
| PU | PD | PU | 84 | 54 | 1010100 | A8h | | | |
| PU | PD | V _{DD} | 85 | 55 | 1010101 | AAh | | | |
| PU | FLT | GND | 86 | 56 | 1010110 | ACh | | | |
| PU | FLT | PD | 87 | 57 | 1010111 | AEh | | | |
| PU | FLT | FLT | 88 | 58 | 1011000 | B0h | | | |
| PU | FLT | PU | 89 | 59 | 1011001 | B2h | | | |
| PU | FLT | V_{DD} | 90 | 5A | 1011010 | B4h | | | |
| PU | PU | GND | 91 | 5B | 1011011 | B6h | | | |
| PU | PU | PD | 92 | 5C | 1011100 | B8h | | | |
| PU | PU | FLT | 93 | 5D | 1011101 | BAh | | | |
| PU | PU | PU | 94 | 5E | 1011110 | BCh | | | |
| PU | PU | V _{DD} | 95 | 5F | 1011111 | BEh | | | |
| PU | V_{DD} | GND | 96 | 60 | 1100000 | C0h | | | |
| PU | V_{DD} | PD | 97 | 61 | 1100001 | C2h | | | |
| PU | V_{DD} | FLT | 98 | 62 | 1100010 | C4h | | | |
| PU | V_{DD} | PU | 99 | 63 | 1100011 | C6h | | | |
| PU | V_{DD} | V _{DD} | 100 | 64 | 1100100 | C8h | | | |
| V_{DD} | GND | GND | 101 | 65 | 1100101 | CAh | | | |
| V_{DD} | GND | PD | 102 | 66 | 1100110 | CCh | | | |
| V_{DD} | GND | FLT | 103 | 67 | 1100111 | CEh | | | |
| V _{DD} | GND | PU | 104 | 68 | 1101000 | D0h | | | |
| V_{DD} | GND | V_{DD} | 105 | 69 | 1101001 | D2h | | | |
| V_{DD} | PD | GND | 106 | 6A | 1101010 | D4h | | | |
| V_{DD} | PD | PD | 107 | 6B | 1101011 | D6h | | | |
| V_{DD} | PD | FLT | 108 | 6C | 1101100 | D8h | | | |
| V_{DD} | PD | PU | 109 | 6D | 1101101 | DAh | | | |
| V_{DD} | PD | V_{DD} | 110 | 6E | 1101110 | DCh | | | |
| V_{DD} | FLT | GND | 111 | 6F | 1101111 | DEh | | | |
| V _{DD} | FLT | PD | 112 | 70 | 1110000 | E0h | | | |
| V_{DD} | FLT | FLT | 113 | 71 | 1110001 | E2h | | | |
| V_{DD} | FLT | PU | 114 | 72 | 1110010 | E4h | | | |

16-channel Fm+ I²C-bus 57 mA constant current LED driver


Table 5. I²C-bus slave address...continued

| Hardware selectable input pins | | | I ² C-bus slave address for PCA9955B | | | | | |
|--------------------------------|----------|-----------------|---|-------------|------------------------|-------------------|--|--|
| AD2 | AD1 | AD0 | Decimal | Hexadecimal | Binary (A[6:0]) | Address (R/W = 0) | | |
| V_{DD} | FLT | V _{DD} | 115 | 73 | 1110011 | E6h | | |
| V_{DD} | PU | GND | 116 | 74 | 1110100 | E8h | | |
| V_{DD} | PU | PD | 117 | 75 | 1110101 | EAh | | |
| V_{DD} | PU | FLT | 118 | 76 | 1110110 | ECh | | |
| V_{DD} | PU | PU | 119 | 77 | 1110111 | EEh | | |
| V_{DD} | PU | V_{DD} | 120 | 78 | 1111000 ^[1] | F0h | | |
| V_{DD} | V_{DD} | GND | 121 | 79 | 1111001 ^[1] | F2h | | |
| V_{DD} | V_{DD} | PD | 122 | 7A | 1111010 ^[1] | F4h | | |
| V_{DD} | V_{DD} | FLT | 123 | 7B | 1111011 ^[1] | F6h | | |
| V_{DD} | V_{DD} | PU | 124 | 7C | 1111100 ^[1] | F8h | | |
| V_{DD} | V_{DD} | V _{DD} | 125 | 7D | 1111101 ^[1] | FAh | | |

^[1] See 'Remark' below.

Remark: Reserved I²C-bus addresses must be used with caution since they can interfere with:

- 'reserved for future use' I²C-bus addresses (0000 011, 1111 1XX)
- slave devices that use the 10-bit addressing scheme (1111 0XX)
- slave devices that are designed to respond to the General Call address (0000 000)
- High-speed mode (Hs-mode) master code (0000 1XX)



1. This slave address must match one of the 125 internal addresses as shown in Table 5

Figure 3. PCA9955B slave address

The last bit of the address byte defines the operation to be performed. When set to logic 1 a read is selected, while a logic 0 selects a write operation.

7.1.2 LED All Call I²C-bus address

- Default power-up value (ALLCALLADR register): E0h or 1110 000X
- Programmable through I²C-bus (volatile programming)
- At power-up, LED All Call I²C-bus address is enabled. PCA9955B sends an ACK when E0h (R/ \overline{W} = 0) or E1h (R/ \overline{W} = 1) is sent by the master.

See Section 7.3.11 for more detail.

Remark: The default LED All Call I²C-bus address (E0h or 1110 000X) must not be used as a regular I²C-bus slave address since this address is enabled at power-up. All of the PCA9955Bs on the I²C-bus acknowledge the address if sent by the I²C-bus master.

16-channel Fm+ I²C-bus 57 mA constant current LED driver

7.1.3 LED Sub Call I²C-bus addresses

- 3 different I²C-bus addresses can be used
- Default power-up values:
 - SUBADR1 register: ECh or 1110 110XSUBADR2 register: ECh or 1110 110X
 - SUBADR3 register: ECh or 1110 110X
- Programmable through I²C-bus (volatile programming)
- At power-up, SUBADR1 is enabled while SUBADR2 and SUBADR3 I²C-bus addresses are disabled.

Remark: At power-up SUBADR1 identifies this device as a 16-channel driver.

See Section 7.3.10 for more detail.


Remark: The default LED Sub Call I²C-bus addresses may be used as regular I²C-bus slave addresses as long as they are disabled.

7.2 Control register

Following the successful acknowledgement of the slave address, LED All Call address or LED Sub Call address, the bus master sends a byte to the PCA9955B, which is stored in the Control register.

The lowest 7 bits are used as a pointer to determine which register is accessed (D[6:0]). The highest bit is used as Auto-Increment Flag (AIF).

This bit along with the MODE1 register bit 5 and bit 6 provide the Auto-Increment feature.



When the Auto-Increment Flag is set (AIF = logic 1), the seven low-order bits of the Control register are automatically incremented after a read or write. This allows the user to program the registers sequentially. Four different types of Auto-Increment are possible, depending on AI1 and AI0 values of MODE1 register.

Table 6. Auto-Increment options

| AIF | Al1 ^[1] | AI0 ^[1] | Function |
|-----|--------------------|--------------------|--|
| 0 | 0 | 0 | no Auto-Increment |
| 1 | 0 | 0 | Auto-Increment for registers (00h to 43h). D[6:0] roll over to 00h after the last register 43h is accessed. |
| 1 | 0 | 1 | Auto-Increment for individual brightness registers only (08h to 17h). D[6:0] roll over to 08h after the last register (17h) is accessed. |
| 1 | 1 | 0 | Auto-Increment for MODE1 to IREF15 control registers (00h to 27h). D[6:0] roll over to 00h after the last register (27h) is accessed. |
| 1 | 1 | 1 | Auto-Increment for global control registers and individual brightness registers (06h to 17h). D[6:0] roll over to 06h after the last register (17h) is accessed. |

^[1] Al1 and Al0 come from MODE1 register.

PCA9955E

16-channel Fm+ I²C-bus 57 mA constant current LED driver

Remark: Other combinations not shown in <u>Table 6</u> (AIF + AI[1:0] = 001b, 010b and 011b) are reserved and must not be used for proper device operation.

AIF + AI[1:0] = 000b is used when the same register must be accessed several times during a single I^2 C-bus communication, for example, changes the brightness of a single LED. Data is overwritten each time the register is accessed during a write operation.

AIF + AI[1:0] = 100b is used when all the registers must be sequentially accessed, for example, power-up programming.

AIF + AI[1:0] = 101b is used when the 16 LED drivers must be individually programmed with different values during the same I^2 C-bus communication, for example, changing color setting to another color setting.

AIF + AI[1:0] = 110b is used when MODE1 to IREF15 registers must be programmed with different settings during the same I^2 C-bus communication.

AIF + AI[1:0] = 111b is used when the 16 LED drivers must be individually programmed with different values in addition to global programming.

Only the 7 least significant bits D[6:0] are affected by the AIF, AI1 and AI0 bits.

When the Control register is written, the register entry point determined by D[6:0] is the first register that will be addressed (read or write operation), and can be anywhere between 00h and 49h (as defined in <u>Table 7</u>). When AIF = 1, the Auto-Increment Flag is set and the rollover value at which the register increment stops and goes to the next one is determined by AIF, AI1 and AI0. See <u>Table 6</u> for rollover values. For example, if MODE1 register bit AI1 = 0 and AI0 = 1 and if the Control register = 1001 0000, then the register addressing sequence is (in hexadecimal): $10 \rightarrow 11 \rightarrow ... \rightarrow 17 \rightarrow 08 \rightarrow 09 \rightarrow ... \rightarrow 17 \rightarrow 08 \rightarrow 09 \rightarrow ...$ as long as the master keeps sending or reading data.

If MODE1 register bit AI1 = 0 and AI0 = 1 and if the Control register = 1010 0010, then the register addressing sequence is (in hexadecimal): $22 \rightarrow 23 \rightarrow ... \rightarrow 43 \rightarrow 00 \rightarrow 01 \rightarrow ... \rightarrow 17 \rightarrow 08 \rightarrow 09 \rightarrow ...$ as long as the master keeps sending or reading data.

If MODE1 register bit AI1 = 0 and AI0 = 1 and if the Control register = 1000 0101, then the register addressing sequence is (in hexadecimal): $05 \rightarrow 06 \rightarrow ... \rightarrow 17 \rightarrow 08 \rightarrow 09 \rightarrow ... \rightarrow 17 \rightarrow 08 \rightarrow 09 \rightarrow ...$ as long as the master keeps sending or reading data.

Remark: Writing to registers marked 'not used' returns NACK.

7.3 Register definitions

Table 7. Register summary

| Register number (hex) | D6 | D5 | D4 | D3 | D2 | D1 | D0 | Name | Туре | Function |
|-----------------------|----|----|----|----|----|----|----|---------|------------|--------------------------|
| 00h | 0 | 0 | 0 | 0 | 0 | 0 | 0 | MODE1 | read/write | Mode register 1 |
| 01h | 0 | 0 | 0 | 0 | 0 | 0 | 1 | MODE2 | read/write | Mode register 2 |
| 02h | 0 | 0 | 0 | 0 | 0 | 1 | 0 | LEDOUT0 | read/write | LED output state 0 |
| 03h | 0 | 0 | 0 | 0 | 0 | 1 | 1 | LEDOUT1 | read/write | LED output state 1 |
| 04h | 0 | 0 | 0 | 0 | 1 | 0 | 0 | LEDOUT2 | read/write | LED output state 2 |
| 05h | 0 | 0 | 0 | 0 | 1 | 0 | 1 | LEDOUT3 | read/write | LED output state 3 |
| 06h | 0 | 0 | 0 | 0 | 1 | 1 | 0 | GRPPWM | read/write | group duty cycle control |
| 07h | 0 | 0 | 0 | 0 | 1 | 1 | 1 | GRPFREQ | read/write | group frequency |
| 08h | 0 | 0 | 0 | 1 | 0 | 0 | 0 | PWM0 | read/write | brightness control LED0 |
| 09h | 0 | 0 | 0 | 1 | 0 | 0 | 1 | PWM1 | read/write | brightness control LED1 |

PCA9955E

Table 7. Register summary...continued

| Register number (hex) | D6 | D5 | D4 | D3 | D2 | D1 | D0 | Name | Туре | Function |
|-----------------------|----|----|----|----|----|----|----|----------------|------------|--|
| 0Ah | 0 | 0 | 0 | 1 | 0 | 1 | 0 | PWM2 | read/write | brightness control LED2 |
| 0Bh | 0 | 0 | 0 | 1 | 0 | 1 | 1 | PWM3 | read/write | brightness control LED3 |
| 0Ch | 0 | 0 | 0 | 1 | 1 | 0 | 0 | PWM4 | read/write | brightness control LED4 |
| 0Dh | 0 | 0 | 0 | 1 | 1 | 0 | 1 | PWM5 | read/write | brightness control LED5 |
| 0Eh | 0 | 0 | 0 | 1 | 1 | 1 | 0 | PWM6 | read/write | brightness control LED6 |
| 0Fh | 0 | 0 | 0 | 1 | 1 | 1 | 1 | PWM7 | read/write | brightness control LED7 |
| 10h | 0 | 0 | 1 | 0 | 0 | 0 | 0 | PWM8 | read/write | brightness control LED8 |
| 11h | 0 | 0 | 1 | 0 | 0 | 0 | 1 | PWM9 | read/write | brightness control LED9 |
| 12h | 0 | 0 | 1 | 0 | 0 | 1 | 0 | PWM10 | read/write | brightness control LED10 |
| 13h | 0 | 0 | 1 | 0 | 0 | 1 | 1 | PWM11 | read/write | brightness control LED11 |
| 14h | 0 | 0 | 1 | 0 | 1 | 0 | 0 | PWM12 | read/write | brightness control LED12 |
| 15h | 0 | 0 | 1 | 0 | 1 | 0 | 1 | PWM13 | read/write | brightness control LED13 |
| 16h | 0 | 0 | 1 | 0 | 1 | 1 | 0 | PWM14 | read/write | brightness control LED14 |
| 17h | 0 | 0 | 1 | 0 | 1 | 1 | 1 | PWM15 | read/write | brightness control LED15 |
| 18h | 0 | 0 | 1 | 1 | 0 | 0 | 0 | IREF0 | read/write | output gain control register 0 |
| 19h | 0 | 0 | 1 | 1 | 0 | 0 | 1 | IREF1 | read/write | output gain control register 1 |
| 1Ah | 0 | 0 | 1 | 1 | 0 | 1 | 0 | IREF2 | read/write | output gain control register 2 |
| 1Bh | 0 | 0 | 1 | 1 | 0 | 1 | 1 | IREF3 | read/write | output gain control register 3 |
| 1Ch | 0 | 0 | 1 | 1 | 1 | 0 | 0 | IREF4 | read/write | output gain control register 4 |
| 1Dh | 0 | 0 | 1 | 1 | 1 | 0 | 1 | IREF5 | read/write | output gain control register 5 |
| 1Eh | 0 | 0 | 1 | 1 | 1 | 1 | 0 | IREF6 | read/write | output gain control register 6 |
| 1Fh | 0 | 0 | 1 | 1 | 1 | 1 | 1 | IREF7 | read/write | output gain control register 7 |
| 20h | 0 | 1 | 0 | 0 | 0 | 0 | 0 | IREF8 | read/write | output gain control register 8 |
| 21h | 0 | 1 | 0 | 0 | 0 | 0 | 1 | IREF9 | read/write | output gain control register 9 |
| 22h | 0 | 1 | 0 | 0 | 0 | 1 | 0 | IREF10 | read/write | output gain control register 10 |
| 23h | 0 | 1 | 0 | 0 | 0 | 1 | 1 | IREF11 | read/write | output gain control register 11 |
| 24h | 0 | 1 | 0 | 0 | 1 | 0 | 0 | IREF12 | read/write | output gain control register 12 |
| 25h | 0 | 1 | 0 | 0 | 1 | 0 | 1 | IREF13 | read/write | output gain control register 13 |
| 26h | 0 | 1 | 0 | 0 | 1 | 1 | 0 | IREF14 | read/write | output gain control register 14 |
| 27h | 0 | 1 | 0 | 0 | 1 | 1 | 1 | IREF15 | read/write | output gain control register 15 |
| 28h | 0 | 1 | 0 | 1 | 0 | 0 | 0 | RAMP_RATE_GRP0 | read/write | ramp enable and rate control for group 0 |
| 29h | 0 | 1 | 0 | 1 | 0 | 0 | 1 | STEP_TIME_GRP0 | read/write | step time control for group 0 |
| 2Ah | 0 | 1 | 0 | 1 | 0 | 1 | 0 | HOLD_CNTL_GRP0 | read/write | hold ON/OFF time control for group 0 |
| 2Bh | 0 | 1 | 0 | 1 | 0 | 1 | 1 | IREF_GRP0 | read/write | output gain control for group 0 |

Table 7. Register summary...continued

| Register number (hex) | D6 | D5 | D4 | D3 | D2 | D1 | D0 | Name | Туре | Function |
|-----------------------|----|----|----|----|----|----|----|----------------|------------|--|
| 2Ch | 0 | 1 | 0 | 1 | 1 | 0 | 0 | RAMP_RATE_GRP1 | read/write | ramp enable and rate control for group 1 |
| 2Dh | 0 | 1 | 0 | 1 | 1 | 0 | 1 | STEP_TIME_GRP1 | read/write | step time control for group 1 |
| 2Eh | 0 | 1 | 0 | 1 | 1 | 1 | 0 | HOLD_CNTL_GRP1 | read/write | hold ON/OFF time control for group 1 |
| 2Fh | 0 | 1 | 0 | 1 | 1 | 1 | 1 | IREF_GRP1 | read/write | output gain control for group 1 |
| 30h | 0 | 1 | 1 | 0 | 0 | 0 | 0 | RAMP_RATE_GRP2 | read/write | ramp enable and rate control for group 2 |
| 31h | 0 | 1 | 1 | 0 | 0 | 0 | 1 | STEP_TIME_GRP2 | read/write | step time control for group 2 |
| 32h | 0 | 1 | 1 | 0 | 0 | 1 | 0 | HOLD_CNTL_GRP2 | read/write | hold ON/OFF time control for group 2 |
| 33h | 0 | 1 | 1 | 0 | 0 | 1 | 1 | IREF_GRP2 | read/write | output gain control for group 2 |
| 34h | 0 | 1 | 1 | 0 | 1 | 0 | 0 | RAMP_RATE_GRP3 | read/write | ramp enable and rate control for group 3 |
| 35h | 0 | 1 | 1 | 0 | 1 | 0 | 1 | STEP_TIME_GRP3 | read/write | step time control for group 3 |
| 36h | 0 | 1 | 1 | 0 | 1 | 1 | 0 | HOLD_CNTL_GRP3 | read/write | hold ON/OFF time control for group 3 |
| 37h | 0 | 1 | 1 | 0 | 1 | 1 | 1 | IREF_GRP3 | read/write | output gain control for group 3 |
| 38h | 0 | 1 | 1 | 1 | 0 | 0 | 0 | GRAD_MODE_SEL0 | read/write | gradation mode select register for channel 7 to channel 0 |
| 39h | 0 | 1 | 1 | 1 | 0 | 0 | 1 | GRAD_MODE_SEL1 | read/write | gradation mode select register for channel 15 to channel 8 |
| 3Ah | 0 | 1 | 1 | 1 | 0 | 1 | 0 | GRAD_GRP_SEL0 | read/write | gradation group select for channel 3 to channel 0 |
| 3Bh | 0 | 1 | 1 | 1 | 0 | 1 | 1 | GRAD_GRP_SEL1 | read/write | gradation group select for channel 7 to channel 4 |
| 3Ch | 0 | 1 | 1 | 1 | 1 | 0 | 0 | GRAD_GRP_SEL2 | read/write | gradation group select for channel 11 to channel 8 |
| 3Dh | 0 | 1 | 1 | 1 | 1 | 0 | 1 | GRAD_GRP_SEL3 | read/write | gradation group select for channel 15 to channel 12 |
| 3Eh | 0 | 1 | 1 | 1 | 1 | 1 | 0 | GRAD_CNTL | read/write | gradation control register for all four groups |
| 3Fh | 0 | 1 | 1 | 1 | 1 | 1 | 1 | OFFSET | read/write | Offset/delay on LEDn outputs |
| 40h | 1 | 0 | 0 | 0 | 0 | 0 | 0 | SUBADR1 | read/write | I ² C-bus subaddress 1 |
| 41h | 1 | 0 | 0 | 0 | 0 | 0 | 1 | SUBADR2 | read/write | I ² C-bus subaddress 2 |
| 42h | 1 | 0 | 0 | 0 | 0 | 1 | 0 | SUBADR3 | read/write | I ² C-bus subaddress 3 |
| 43h | 1 | 0 | 0 | 0 | 0 | 1 | 1 | ALLCALLADR | read/write | All Call I ² C-bus address |
| 44h | 1 | 0 | 0 | 0 | 1 | 0 | 0 | PWMALL | write only | brightness control for all LEDn |
| 45h | 1 | 0 | 0 | 0 | 1 | 0 | 1 | IREFALL | write only | output gain control for all registers IREF0 to IREF15 |
| 46h | 1 | 0 | 0 | 0 | 1 | 1 | 0 | EFLAG0 | read only | output error flag 0 |

16-channel Fm+ I²C-bus 57 mA constant current LED driver

Table 7. Register summary...continued

| Register number (hex) | D6 | D5 | D4 | D3 | D2 | D1 | D0 | Name | Туре | Function |
|-----------------------|----|----|----|----|----|----|----|----------|-----------|-------------------------|
| 47h | 1 | 0 | 0 | 0 | 1 | 1 | 1 | EFLAG1 | read only | output error flag 1 |
| 48h | 1 | 0 | 0 | 1 | 0 | 0 | 0 | EFLAG2 | read only | output error flag 2 |
| 49h | 1 | 0 | 0 | 1 | 0 | 0 | 1 | EFLAG3 | read only | output error flag 3 |
| 4Ah to 7Fh | - | - | - | - | - | - | - | reserved | read only | not used ^[1] |

^[1] Reserved registers should not be written to and will always read back as zeros.

7.3.1 MODE1 — Mode register 1

Table 8. MODE1 - Mode register 1 (address 00h) bit description

Legend: * default value.

| Bit | Symbol | Access | Value | Description | |
|-----|-------------|-----------|-------|---|--|
| 7 | AIF | read only | 0 | Register Auto-Increment disabled. | |
| | | | 1* | Register Auto-Increment enabled. | |
| 6 | Al1 | R/W | 0* | Auto-Increment bit 1 = 0. Auto-increment range as defined in <u>Table 6</u> . | |
| | | | 1 | Auto-Increment bit 1 = 1. Auto-increment range as defined in <u>Table 6</u> . | |
| 5 | Al0 R/W | | 0* | Auto-Increment bit 0 = 0. Auto-increment range as defined in <u>Table 6</u> . | |
| | | | 1 | Auto-Increment bit 0 = 1. Auto-increment range as defined in <u>Table 6</u> . | |
| 4 | 4 SLEEP R/W | | 0* | Normal mode ^[1] . | |
| | | | 1 | Low power mode. Oscillator off ^{[2][3]} . | |
| 3 | SUB1 | R/W | 0 | PCA9955B does not respond to I ² C-bus subaddress 1. | |
| | | | 1* | PCA9955B responds to I ² C-bus subaddress 1. | |
| 2 | SUB2 | R/W | 0* | PCA9955B does not respond to I ² C-bus subaddress 2. | |
| | | | 1 | PCA9955B responds to I ² C-bus subaddress 2. | |
| 1 | SUB3 | R/W | 0* | PCA9955B does not respond to I ² C-bus subaddress 3. | |
| | | | 1 | PCA9955B responds to I ² C-bus subaddress 3. | |
| 0 | ALLCALL | R/W | 0 | PCA9955B does not respond to LED All Call I ² C-bus address. | |
| | | | 1* | PCA9955B responds to LED All Call I ² C-bus address. | |

It takes 500 µs max. for the oscillator to be up and running once SLEEP bit has been set to logic 0. Timings on LEDn outputs are not guaranteed if PWMx, Reference Solve Britas. In the oscillator to be up and utilining office SEEEP bit has been set to logic 0. Thinlings office of GRPPWM or GRPFREQ registers are accessed within the 500 µs window.

No blinking, dimming or gradation control is possible when the oscillator is off.

The device must be reset if the LED driver output state is set to LDRx=11 after the device is set back to Normal mode.

7.3.2 MODE2 — Mode register 2

Table 9. MODE2 - Mode register 2 (address 01h) bit description

Legend: * default value.


| Bit | Symbol | Access | Value | Description |
|-----|----------|-----------|-------|---------------------------|
| 7 | OVERTEMP | read only | 0* | O.K. |
| | | | 1 | overtemperature condition |

16-channel Fm+ I²C-bus 57 mA constant current LED driver

Table 9. MODE2 - Mode register 2 (address 01h) bit description...continued Legend: * default value.

| Bit | Symbol | Access | Value | Description |
|-----|-------------------|-----------|-------|---|
| 6 | ERROR | read only | 0* | no error at LED outputs |
| | | | 1 | any open or short-circuit detected in error flag registers (EFLAGn) |
| 5 | DMBLNK | R/W | 0* | group control = dimming |
| | | | 1 | group control = blinking |
| 4 | CLRERR write only | | 0* | self clear after write '1' |
| | | | 1 | Write '1' to clear all error status bits in EFLAGn register and ERROR (bit 6). The EFLAGn and ERROR bit sets to '1' if open or short-circuit is detected again. |
| 3 | OCH | R/W | 0* | outputs change on STOP condition |
| | | | 1 | outputs change on ACK |
| 2 | EXP_EN | R/W | 0* | linear adjustment for gradation control |
| | | | 1 | exponential adjustment for gradation control |
| 1 | - | read only | 0* | reserved |
| 0 | - | read only | 1* | reserved |

Brightness adjustment for gradation control is either linear or exponential by setting the EXP_EN bit as shown in <u>Figure 5</u>. When EXP_EN = 0, linear adjustment scale is used. When EXP_EN = 1, exponential scale is used.



16-channel Fm+ I²C-bus 57 mA constant current LED driver

7.3.3 LEDOUT0 to LEDOUT3, LED driver output state

Table 10. LEDOUT0 to LEDOUT3 - LED driver output state registers (address 02h to 05h) bit description Legend: * default value.

| Address | Register | Bit | Symbol | Access | Value | Description |
|---------|----------|-----|--------|--------|-------|----------------------------|
| 02h | LEDOUT0 | 7:6 | LDR3 | R/W | 10* | LED3 output state control |
| | | 5:4 | LDR2 | R/W | 10* | LED2 output state control |
| | | 3:2 | LDR1 | R/W | 10* | LED1 output state control |
| | | 1:0 | LDR0 | R/W | 10* | LED0 output state control |
| 03h | LEDOUT1 | 7:6 | LDR7 | R/W | 10* | LED7 output state control |
| | | 5:4 | LDR6 | R/W | 10* | LED6 output state control |
| | | 3:2 | LDR5 | R/W | 10* | LED5 output state control |
| | | 1:0 | LDR4 | R/W | 10* | LED4 output state control |
| 04h | LEDOUT2 | 7:6 | LDR11 | R/W | 10* | LED11 output state control |
| | | 5:4 | LDR10 | R/W | 10* | LED10 output state control |
| | | 3:2 | LDR9 | R/W | 10* | LED9 output state control |
| | | 1:0 | LDR8 | R/W | 10* | LED8 output state control |
| 05h | LEDOUT3 | 7:6 | LDR15 | R/W | 10* | LED15 output state control |
| | | 5:4 | LDR14 | R/W | 10* | LED14 output state control |
| | | 3:2 | LDR13 | R/W | 10* | LED13 output state control |
| | | 1:0 | LDR12 | R/W | 10* | LED12 output state control |

LDRx = 00

LED driver x is off (x = 0 to 15).

LDRx = 01

LED driver x is fully on (individual brightness and group dimming/blinking not controlled). The \overline{OE} pin can be used as external dimming/blinking control in this state.

LDRx = 10

LED driver x individual brightness can be controlled through its PWMx register (default power-up state) or PWMALL register for all LEDn outputs.

LDRx = 11

LED driver x individual brightness and group dimming/blinking can be controlled through its PWMx register and the GRPPWM registers.

Remark: Setting the device in low power mode while being on group dimming/blinking mode may cause the LED output state to be in an unknown state after the device is set back to normal mode. The device must be reset and all register values reprogrammed.

16-channel Fm+ I²C-bus 57 mA constant current LED driver

7.3.4 GRPPWM, group duty cycle control

Table 11. GRPPWM - Group brightness control register (address 06h) bit description Legend: * default value

| Address | Register | Bit | Symbol | Access | Value | Description |
|---------|----------|-----|----------|--------|------------|-----------------|
| 06h | GRPPWM | 7:0 | GDC[7:0] | R/W | 1111 1111* | GRPPWM register |

When DMBLNK bit (MODE2 register) is programmed with logic 0, a 122 Hz fixed frequency signal is superimposed with the 31.25 kHz individual brightness control signal. GRPPWM is then used as a global brightness control allowing the LED outputs to be dimmed with the same value. The value in GRPFREQ is then a 'Don't care'.

General brightness for the 16 outputs is controlled through 255 linear steps from 00h (0 % duty cycle = LED output off) to FFh (99.6 % duty cycle = maximum brightness). Applicable to LED outputs programmed with LDRx = 11 (LEDOUT0 to LEDOUT3 registers).

When DMBLNK bit is programmed with logic 1, GRPPWM and GRPFREQ registers define a global blinking pattern, where GRPFREQ contains the blinking period (from 67 ms to 16.8 s) and GRPPWM the duty cycle (ON/OFF ratio in %).

$$dutycycle = \frac{GDC[7:0]}{256} (1)$$

7.3.5 GRPFREQ, group frequency

Table 12. GRPFREQ - Group frequency register (address 07h) bit description Legend: * default value.

| Address | Register | Bit | Symbol | Access | Value | Description |
|---------|----------|-----|-----------|--------|------------|------------------|
| 07h | GRPFREQ | 7:0 | GFRQ[7:0] | R/W | 0000 0000* | GRPFREQ register |

GRPFREQ is used to program the global blinking period when DMBLNK bit (MODE2 register) is equal to 1. Value in this register is a 'Don't care' when DMBLNK = 0. Applicable to LED outputs programmed with LDRx = 11 (LEDOUT0 to LEDOUT3 registers).

Blinking period is controlled through 256 linear steps from 00h (67 ms, frequency 15 Hz) to FFh (16.8 s).

$$globalblinkingperiod = \frac{GFRQ[7:0]+1}{15.26} (s) (2)$$

7.3.6 PWM0 to PWM15, individual brightness control

Table 13. PWM0 to PWM15 - PWM registers 0 to 15 (address 08h to 17h) bit description Legend: * default value.

| Address | Register | Bit | Symbol | Access | Value | Description |
|---------|----------|-----|-----------|--------|------------|----------------------------|
| 08h | PWM0 | 7:0 | IDC0[7:0] | R/W | 0000 0000* | PWM0 Individual Duty Cycle |
| 09h | PWM1 | 7:0 | IDC1[7:0] | R/W | 0000 0000* | PWM1 Individual Duty Cycle |
| 0Ah | PWM2 | 7:0 | IDC2[7:0] | R/W | 0000 0000* | PWM2 Individual Duty Cycle |
| 0Bh | PWM3 | 7:0 | IDC3[7:0] | R/W | 0000 0000* | PWM3 Individual Duty Cycle |
| 0Ch | PWM4 | 7:0 | IDC4[7:0] | R/W | 0000 0000* | PWM4 Individual Duty Cycle |
| 0Dh | PWM5 | 7:0 | IDC5[7:0] | R/W | 0000 0000* | PWM5 Individual Duty Cycle |
| 0Eh | PWM6 | 7:0 | IDC6[7:0] | R/W | 0000 0000* | PWM6 Individual Duty Cycle |

PCA9955E

16-channel Fm+ I²C-bus 57 mA constant current LED driver

Table 13. PWM0 to PWM15 - PWM registers 0 to 15 (address 08h to 17h) bit description...continued Legend: * default value.

| Address | Register | Bit | Symbol | Access | Value | Description |
|---------|----------|-----|------------|--------|------------|-----------------------------|
| 0Fh | PWM7 | 7:0 | IDC7[7:0] | R/W | 0000 0000* | PWM7 Individual Duty Cycle |
| 10h | PWM8 | 7:0 | IDC8[7:0] | R/W | 0000 0000* | PWM8 Individual Duty Cycle |
| 11h | PWM9 | 7:0 | IDC9[7:0] | R/W | 0000 0000* | PWM9 Individual Duty Cycle |
| 12h | PWM10 | 7:0 | IDC10[7:0] | R/W | 0000 0000* | PWM10 Individual Duty Cycle |
| 13h | PWM11 | 7:0 | IDC11[7:0] | R/W | 0000 0000* | PWM11 Individual Duty Cycle |
| 14h | PWM12 | 7:0 | IDC12[7:0] | R/W | 0000 0000* | PWM12 Individual Duty Cycle |
| 15h | PWM13 | 7:0 | IDC13[7:0] | R/W | 0000 0000* | PWM13 Individual Duty Cycle |
| 16h | PWM14 | 7:0 | IDC14[7:0] | R/W | 0000 0000* | PWM14 Individual Duty Cycle |
| 17h | PWM15 | 7:0 | IDC15[7:0] | R/W | 0000 0000* | PWM15 Individual Duty Cycle |

A 31.25 kHz fixed frequency signal is used for each output. Duty cycle is controlled through 255 linear steps from 00h (0 % duty cycle = LED output off) to FEh (99.2 % duty cycle = LED output at maximum brightness) and FFh (100 % duty cycle = LED output completed ON). Applicable to LED outputs programmed with LDRx = 10 or 11 (LEDOUT0 to LEDOUT3 registers).

$$dutycycle = \frac{IDCx[7:0]}{256} (3)$$

Remark: The first lower end 8 steps of PWM and the last (higher end) steps of PWM will not have effective brightness control of LEDs due to edge rate control of LED output pins.

7.3.7 IREF0 to IREF15, LED output current value registers

These registers reflect the gain settings for output current for LED0 to LED15.

Table 14. IREF0 to IREF15 - LED output gain control registers (address 18h to 27h) bit description Legend: * default value.

| Address | Register | Bit | Access | Value | Description |
|---------|----------|-----|--------|-------|------------------------------|
| 18h | IREF0 | 7:0 | R/W | 00h* | LED0 output current setting |
| 19h | IREF1 | 7:0 | R/W | 00h* | LED1 output current setting |
| 1Ah | IREF2 | 7:0 | R/W | 00h* | LED2 output current setting |
| 1Bh | IREF3 | 7:0 | R/W | 00h* | LED3 output current setting |
| 1Ch | IREF4 | 7:0 | R/W | 00h* | LED4 output current setting |
| 1Dh | IREF5 | 7:0 | R/W | 00h* | LED5 output current setting |
| 1Eh | IREF6 | 7:0 | R/W | 00h* | LED6 output current setting |
| 1Fh | IREF7 | 7:0 | R/W | 00h* | LED7 output current setting |
| 20h | IREF8 | 7:0 | R/W | 00h* | LED8 output current setting |
| 21h | IREF9 | 7:0 | R/W | 00h* | LED9 output current setting |
| 22h | IREF10 | 7:0 | R/W | 00h* | LED10 output current setting |
| 23h | IREF11 | 7:0 | R/W | 00h* | LED11 output current setting |
| 24h | IREF12 | 7:0 | R/W | 00h* | LED12 output current setting |


16-channel Fm+ I²C-bus 57 mA constant current LED driver

Table 14. IREF0 to IREF15 - LED output gain control registers (address 18h to 27h) bit description...continued Legend: * default value.

| Address | Register | Bit | Access | Value | Description |
|---------|----------|-----|--------|-------|------------------------------|
| 25h | IREF13 | 7:0 | R/W | 00h* | LED13 output current setting |
| 26h | IREF14 | 7:0 | R/W | 00h* | LED14 output current setting |
| 27h | IREF15 | 7:0 | R/W | 00h* | LED15 output current setting |

7.3.8 Gradation control

Gradation control is designed to use four independent groups of registers to program the full cycle of the gradation timing to implement on each selected channel. Each group has four registers to define the ramp rate, step time, hold ON/OFF time, and final hold ON current, as shown in <u>Figure 6</u>.



- The 'final' and 'hold ON' current is defined in IREF_GRPx register value × (225 μ A if R_{ext} = 1 k Ω , or 112.5 μ A if R_{ext} = 2 k Ω).
- Ramp rate value and enable/disable ramp operation is defined in RAMP RATE GRPx register.
- Total number of ramp steps (or level changes) is calculated as 'IREF_GRPx value' ÷ 'ramp rate value in RAMP RATE GRPx'. Rounds a number up to the next integer if the total number is not an integer.
- Time for each step is calculated as 'cycle time' × 'multiple factor' bits in STEP_TIME_GRPx register. Minimum time for one step is 0.5 ms (0.5 ms × 1) and maximum time is 512 ms (8 ms × 64).
- The ramp-up or ramp-down time (T1 or T3) is calculated as '(total steps + 1)' × 'step time'.
- Hold ON or OFF time (T2 or T4) is defined in HOLD_CNTL_GRPx register in the range of 0/0.25/0.5/0.75/1/2/4/6 seconds.
- Gradation start or stop with single shot mode (one full cycle only) or continuous mode (repeat full cycle) is defined in the GRAD_CNTL register for all groups.
- Each channel can be assigned to one of these four groups in the GRAD_GRP_SELx register.
- Each channel can set either normal mode or gradation mode operation in the GRAD MODE SELx register.

To enable the gradation operation, the following steps are required:

- 1. Program all gradation control registers except the gradation start bit in GRAD_CNTL register.
- 2. Program either LDRx = 01 (LED fully ON mode) only, or LDRx = 10 or 11 (PWM control mode) with individual brightness control PWMx register for duty cycle.
- 3. Program output current value IREFx register to non-zero, which will enable LED output.
- 4. Set the gradation start bit in GRAD_CNTL register for enabling gradation operation.

16-channel Fm+ I²C-bus 57 mA constant current LED driver

7.3.8.1 RAMP_RATE_GRP0 to RAMP_RATE_GRP3, ramp rate control registers

Table 15. RAMP_RATE_GRP[0:3] - Ramp enable and rate control registers (address 28h, 2Ch, 30h, 34h) for each group bit description

Legend: * default value.

| Address | Register | Bit | Access | Value | Description |
|------------|--|-----|--------|-------|--|
| 28h | RAMP_RATE_GRP0 | 7 | R/W | 0* | Ramp-up disable |
| 2Ch 30h | RAMP_RATE_GRP1 RAMP_RATE_GRP2 RAMP_RATE_GRP3 | | | 1 | Ramp-up enable |
| 34h | | 6 | R/W | 0* | Ramp-down disable |
| | | | | 1 | Ramp-down enable |
| | | 5:0 | R/W | 0x00* | Ramp rate value per step is defined from 1 (00h) to 64 (3Fh) ^{[1][2]} |

^[1] Total number of ramp steps is defined as 'IREF_GRP[7:0]' ÷ 'ramp_rate[5:0]'. (Round up to next integer if it is not an integer number.)

7.3.8.2 STEP_TIME_GRP0 to STEP_TIME_GRP3, step time control registers

Table 16. STEP_TIME_GRP[0:3] - Step time control registers (address 29h, 2Dh, 31h, 35h) for each group bit description

Legend: * default value.

| Address | Register | Bit | Access | Value | Description |
|------------|----------------------------------|-----|-----------|-------|--|
| 29h | STEP_TIME_GRP0 | 7 | read only | 0* | reserved |
| 2Dh 31h | STEP_TIME_GRP1 STEP TIME GRP2 | 6 | R/W | 0* | Cycle time is set to 0.5 ms |
| 35h | STEP_TIME_GRP3 | | | 1 | Cycle time is set to 8 ms |
| | | 5:0 | R/W | 0x00* | Multiple factor per step, the multiple factor is defined from 1 (00h) to 64 (3Fh) ^[1] |

^[1] Step time = cycle time (0.5 ms or 8 ms) × multiple factor (1 ~ 64); minimum step time is 0.5 ms and maximum step time is 512 ms.

7.3.8.3 HOLD CNTL GRP0 to HOLD CNTL GRP3, hold ON and OFF control registers

Table 17. HOLD_CNTL_GRP[0:3] - Hold ON and OFF enable and time control registers (address 2Ah, 2Eh, 32h, 36h) for each group bit description

Legend: * default value.

| Address | Register | Bit | Access | Value | Description |
|------------|----------------------------------|-----|--------|-------|-------------------------------------|
| 2Ah | HOLD_CNTL_GRP0 | 7 | R/W | 0* | Hold ON disable |
| 2Eh | HOLD_CNTL_GRP1 | | | 1 | Hold ON enable |
| 32h 36h | HOLD_CNTL_GRP2 HOLD_CNTL_GRP3 | 6 | R/W | 0* | Hold OFF disable |
| | | | | 1 | Hold OFF enable |
| | | 5:3 | R/W | 000* | Hold ON time select: ^[1] |
| | | | | | 000: 0 s |
| | | | | | 001: 0.25 s |
| | | | | | 010: 0.5 s |
| | | | | | 011: 0.75 s |
| | | | | | 100: 1 s |
| | | | | | 101: 2 s |

PCA9955E

All information provided in this document is subject to legal disclaimers.

© 2024 NXP B.V. All rights reserved.

^[2] Per step current increment or decrement is calculated by the (ramp_rate × I_{ref}), where the I_{ref} reference current is 112.5 μA (R_{ext} = 2 kΩ) or 225 μA (R_{ext} = 1 kΩ).

16-channel Fm+ I²C-bus 57 mA constant current LED driver

Table 17. HOLD_CNTL_GRP[0:3] - Hold ON and OFF enable and time control registers (address 2Ah, 2Eh, 32h, 36h) for each group bit description...continued

Legend: * default value.

| Address | Register | Bit | Access | Value | Description |
|---------|----------|-----|--------|-------|--------------------------------------|
| | | | | | 110: 4 s |
| | | | | | 111: 6 s |
| | | 2:0 | R/W | 000* | Hold OFF time select: ^[1] |
| | | | | | 000: 0 s |
| | | | | | 001: 0.25 s |
| | | | | | 010: 0.5 s |
| | | | | | 011: 0.75 s |
| | | | | | 100: 1 s |
| | | | | | 101: 2 s |
| | | | | | 110: 4 s |
| | | | | | 111: 6 s |

^[1] Hold ON or OFF minimum time is 0 s and maximum time is 6 s

7.3.8.4 IREF_GRP0 to IREF_GRP3, output gain control

Table 18. IREF_GRP[0:3] - Final and hold ON output gain setting registers (address 2Bh, 2Fh, 33h, 37h) for each group bit description

Legend: * default value.

| Address | Register | Bit | Access | Value | Description |
|---------|-----------|-----|--------|-------|--|
| 2Bh | IREF_GRP0 | 7:0 | R/W | 00h* | Final ramp-up and hold ON output current |
| 2Fh | IREF_GRP1 | | | | gain setting ^[1] |
| 33h | IREF_GRP2 | | | | |
| 37h | IREF_GRP3 | | | | |

^[1] Output current = I_{ref} × IREF_GRPx[7:0], where I_{ref} is reference current. I_{ref} = 112.5 μA if R_{ext} = 2 kΩ, or I_{ref} = 225 μA if R_{ext} = 1 kΩ

7.3.8.5 GRAD_MODE_SEL0 to GRAD_MODE_SEL1, Gradation mode select registers

Table 19. GRAD_MODE_SEL[0:1] - Gradation mode select register for channel 15 to channel 0 (address 38h, 39h) bit description

Legend: * default value.

| Address | Register | Bit | Access | Value | Description ^{[1][2]} |
|---------|----------------|-----|--------|-------|--|
| 38h | GRAD_MODE_SEL0 | 7:0 | R/W | 00* | Normal operation mode for channel 7 to channel 0 |
| | | | | FFh | Gradation operation mode for channel 7 to channel 0 |
| 39h | GRAD_MODE_SEL1 | 7:0 | R/W | 00* | Normal operation mode for channel 15 to channel 8 |
| | | | | FFh | Gradation operation mode for channel 15 to channel 8 |

^[1] Each bit represents one channel that can set either 0 for normal mode (use IREFx to set individual LED output current), or 1 for gradation mode (use IREF_GRPx to set group LEDs output current.).

PCA9955B

^[2] In gradation mode, it only affects the source of the IREF current level and does not affect the PWMx operation or LEDOUTx registers' function. It is possible to use the gradation feature, individual PWMx and group PWM simultaneously.

16-channel Fm+ I²C-bus 57 mA constant current LED driver

7.3.8.6 GRAD_GRP_SEL0 to GRAD_GRP_SEL3, Gradation group select registers

Table 20. GRAD_GRP_SEL[0:3] - Gradation group select register for channel 15 to channel 0 (address 3Ah, 3Bh, 3Ch, 3Dh) bit description

Legend: * default value.

| Address | Register | Bit | Access | Value | Description ^[1] |
|---------|---------------|-----|--------|-------|---|
| 3Ah | GRAD_GRP_SEL0 | 7:6 | R/W | 00* | Gradation group select for LED3 output |
| | | 5:4 | R/W | 00* | Gradation group select for LED2 output |
| | | 3:2 | R/W | 00* | Gradation group select for LED1 output |
| | | 1:0 | R/W | 00* | Gradation group select for LED0 output |
| 3Bh | GRAD_GRP_SEL1 | 7:6 | R/W | 01* | Gradation group select for LED7 output |
| | | 5:4 | R/W | 01* | Gradation group select for LED6 output |
| | | 3:2 | R/W | 01* | Gradation group select for LED5 output |
| | | 1:0 | R/W | 01* | Gradation group select for LED4 output |
| 3Ch | GRAD_GRP_SEL2 | 7:6 | R/W | 10* | Gradation group select for LED11 output |
| | | 5:4 | R/W | 10* | Gradation group select for LED10 output |
| | | 3:2 | R/W | 10* | Gradation group select for LED9 output |
| | | 1:0 | R/W | 10* | Gradation group select for LED8 output |
| 3Dh | GRAD_GRP_SEL3 | 7:6 | R/W | 11* | Gradation group select for LED15 output |
| | | 5:4 | R/W | 11* | Gradation group select for LED14 output |
| | | 3:2 | R/W | 11* | Gradation group select for LED13 output |
| | | 1:0 | R/W | 11* | Gradation group select for LED12 output |

^[1] Each bit represents one channel that can set either 0 for normal mode (use IREFx to set individual LED output current), or 1 for gradation mode (use IREF_GRPx to set group LEDs output current.).

7.3.8.7 GRAD_CNTL, Gradation control register

Table 21. GRAD_CNTL - Gradation control register for group 3 to group 0 (address 3Eh) bit description Legend: * default value.

| Address | Register | Bit | Access | Value | Description |
|---------|-----------|-----|--------|-------|---|
| 3Eh | GRAD_CNTL | 7 | R/W | 0* | Gradation stop or done for group 3 ^[1] |
| | | | | 1 | Gradation start for group 3 ^[2] |
| | | 6 | R/W | 0* | Single shot operation for group 3 |
| | | | | 1 | Continuous operation for group 3 |
| | | 5 | R/W | 0* | Gradation stop or done for group 2 ^[1] |
| | | | | 1 | Gradation start for group 2 ^[2] |
| | | 4 | R/W | 0* | Single shot operation for group 2 |
| | | | | 1 | Continuous operation for group 2 |
| | | 3 | R/W | 0* | Gradation stop or done for group 1 ^[1] |

PCA9955E

^{1.} LED[3:0] outputs default assigned to group 0; LED[7:4] outputs default assigned to group 1; LED[11:8] outputs default assigned to group 2; LED[15:12] outputs default assigned to group 3.


16-channel Fm+ I²C-bus 57 mA constant current LED driver

Table 21. GRAD_CNTL - Gradation control register for group 3 to group 0 (address 3Eh) bit description...continued Legend: * default value.

| Address | Register | Bit | Access | Value | Description |
|---------|----------|-----|--------|-------|---|
| | | | | 1 | Gradation start for group 1 ^[2] |
| | | 2 | R/W | 0* | Single shot operation for group 1 |
| | | | | 1 | Continuous operation for group 1 |
| | | 1 | R/W | 0* | Gradation stop or done for group 0 ^[1] |
| | | | | 1 | Gradation start for group 0 ^[2] |
| | | 0 | R/W | 0* | Single shot operation for group 0 |
| | | | | 1 | Continuous operation for group 0 |

- [1] When the gradation operation is forced to stop, the output current stops immediately and is frozen at the last output level.
- [2] This bit will be self-cleared when single mode is completed, and writing 0 to this bit will force to stop the gradation operation when single mode is not completed or continuous mode is running.

7.3.8.8 Ramp control — equation and calculation example




- t1 (step time) = cycle time × multiple factor, where:
 - Cycle time = 0.5 ms (fast ramp) or 8 ms (slow ramp) in STEP TIME GRPx[6]
 - Multiple factor = 6-bit, from 1 (00h) to 64 (3Fh) counts in STEP TIME GRPx[5:0]
- s1 (step current) = ramp_rate × I_{ref}, where:
 - ramp rate = 6-bit, from 1 (00h) to 64 (3Fh) counts in RAMP RATE GRPx[5:0]
 - I_{ref} = reference current either 112.5 μA if R_{ext} = 2 kΩ, or 225 μA if R_{ext} = 1 kΩ
- S (total steps) = (IREF_GRPx / ramp_rate), where:
 - IREF GRPx = output current gain setting, 8-bit, up to 255 counts
 - ramp rate = 6-bit, up to 64 counts in RAMP RATE GRPx[5:0]
 - If it is not an integer, then round up to next integer number.
- T (ramp time) = (S (total steps) + 1) × t1 (step time)
 - Ramp-up time starts from zero current and ends at the maximum current
 - Ramp-down time starts from the maximum current and ends at the zero current

Calculation example 1 (Figure 7):

16-channel Fm+ I²C-bus 57 mA constant current LED driver


- · Assumption:
 - I_{ref} = 225 μ A if R_{ext} = 1 $k\Omega$
 - Output hold ON current = 225 μ A × 250 = 56.25 mA (IREF_GRPx[7:0] = FAh)
 - Cycle time = 0.5 ms (STEP_TIME_GRPx[6] = 0)
 - Multiple factor = 64 (STEP_TIME_GRPx[5:0] = 3Fh)
 - Ramp rate = 50 (RAMP RATE GRPx[5:0] = 31h)
 - Hold ON = 0.25 s (HOLD_CNTL_GRPx[5:3] = 001)
 - Hold OFF = 0.5 s (HOLD_CNTL_GRPx[2:0] = 010)
- t1 (step time) = cycle time (0.5 ms) × multiple (64) = 32 ms
- Step current = ramp_rate × I_{ref} = 50 × 225 µA = 11.25 mA
- S (total steps) = (IREF GRPx ÷ ramp rate) = (250 ÷ 50) = 5 steps
- T (ramp time) = $(S + 1) \times t1 = 6 \times 32 \text{ ms} = 192 \text{ ms}$



Calculation example 2:

- · Assumption:
 - I_{ref} = 225 μA if R_{ext} = 1 $k\Omega$
 - Output hold ON current = 225 μ A × 240 = 54 mA (IREF GRPx[7:0] = F0h)
 - Cycle time = 0.5 ms (STEP_TIME_GRPx[6] = 0)
 - Multiple factor = 64 (STEP_TIME_GRPx[5:0] = 3Fh)
 - Ramp rate = 50 (RAMP_RATE_GRPx[5:0] = 31h)
 - Hold ON = 0.25 s (HOLD CNTL GRPx[5:3] = 001)
 - Hold OFF = 0.5 s (HOLD CNTL GRPx[2:0] = 010)
- t1 (step time) = cycle time (0.5 ms) × multiple (64) = 32 ms
- Step current = ramp_rate × I_{ref} = 50 × 225 μA = 11.25 mA (except the last one)
- S (total steps) = IREF GRPx ÷ ramp rate = 240 ÷ 50 = 4.8 steps (round up to next integer) = 5 steps
- T (ramp time) = $(S + 1) \times t1 = 6 \times 32 \text{ ms} = 192 \text{ ms}$

16-channel Fm+ I²C-bus 57 mA constant current LED driver



7.3.9 OFFSET — LEDn output delay offset register

Table 22. OFFSET - LEDn output delay offset register (address 3Fh) bit description Legend: * default value.

| Address | Register | Bit | Access | Value | Description |
|---------|----------|-----|-----------|-------|---------------------------------|
| 3Fh | OFFSET | 7:4 | read only | 0000* | not used |
| | | 3:0 | R/W | 1000* | LEDn output delay offset factor |

The PCA9955B can be programmed to have turn-on delay between LED outputs. This helps to reduce peak current for the V_{DD} supply and reduces EMI.

The order in which the LED outputs are enabled will always be the same (channel 0 will enable first and channel 15 will enable last).

OFFSET control register bits [3:0] determine the delay used between the turn-on times as follows:

0000 = no delay between outputs (all on, all off at the same time) 0001 = delay of 1 clock cycle (125 ns) between successive outputs 0010 = delay of 2 clock cycles (250 ns) between successive outputs 0011 = delay of 3 clock cycles (375 ns) between successive outputs

PCA9955B

All information provided in this document is subject to legal disclaimers.

© 2024 NXP B.V. All rights reserved.

16-channel Fm+ I²C-bus 57 mA constant current LED driver

1111 = delay of 15 clock cycles (1.875 µs) between successive outputs

Example: If the value in the OFFSET register is 1000 the corresponding delay = 8×125 ns = 1 μ s delay between successive outputs.

channel 0 turns on at time 0 µs

channel 1 turns on at time 1 µs

channel 2 turns on at time 2 µs

channel 3 turns on at time 3 µs

channel 4 turns on at time 4 µs

channel 5 turns on at time 5 μs

channel 6 turns on at time 6 µs

channel 7 turns on at time 7 µs

channel 8 turns on at time 8 µs

channel 9 turns on at time 9 µs

channel 10 turns on at time 10 µs

channel 11 turns on at time 11 µs

channel 12 turns on at time 12 µs

channel 13 turns on at time 13 µs

channel 14 turns on at time 14 µs

channel 15 turns on at time 15 µs

7.3.10 LED Sub Call I²C-bus addresses for PCA9955B

Table 23. SUBADR1 to SUBADR3 - I²C-bus subaddress registers 1 to 3 (address 40h to 42h) bit description *Legend:* * *default value.*

| Address | Register | Bit | Symbol | Access | Value | Description |
|---------|----------|-----|---------|--------|-----------|-----------------------------------|
| 40h | SUBADR1 | 7:1 | A1[7:1] | R/W | 1110 110* | I ² C-bus subaddress 1 |
| | | 0 | A1[0] | R only | 0* | reserved |
| 41h | SUBADR2 | 7:1 | A2[7:1] | R/W | 1110 110* | I ² C-bus subaddress 2 |
| | | 0 | A2[0] | R only | 0* | reserved |
| 42h | SUBADR3 | 7:1 | A3[7:1] | R/W | 1110 110* | I ² C-bus subaddress 3 |
| | | 0 | A3[0] | R only | 0* | reserved |

Default power-up values are ECh, ECh, ECh. At power-up, SUBADR1 is enabled while SUBADR2 and SUBADR3 are disabled. The power-up default bit subaddress of ECh indicates that this device is a 16-channel LED driver.

All three subaddresses are programmable. Once subaddresses have been programmed to their right values, SUBx bits need to be set to logic 1 in order to have the device acknowledging these addresses (MODE1 register) (0). When SUBx is set to logic 1, the corresponding I²C-bus subaddress can be used during either an I²C-bus read or write sequence.

16-channel Fm+ I²C-bus 57 mA constant current LED driver

7.3.11 ALLCALLADR, LED All Call I²C-bus address

Table 24. ALLCALLADR - LED All Call I²C-bus address register (address 43h) bit description Legend: * default value.

| Address | Register | Bit | Symbol | Access | Value | Description |
|---------|------------|-----|---------|--------|-------|---|
| 43h | ALLCALLADR | 7:1 | AC[7:1] | R/W | | ALLCALL I ² C-bus address register |
| | | 0 | AC[0] | R only | 0* | reserved |

The LED All Call I²C-bus address allows all the PCA9955Bs on the bus to be programmed at the same time (ALLCALL bit in register MODE1 must be equal to logic 1 [power-up default state]). This address is programmable through the I²C-bus and can be used during either an I²C-bus read or write sequence. The register address can also be programmed as a Sub Call.

Only the 7 MSBs representing the All Call I²C-bus address are valid. The LSB in ALLCALLADR register is a read-only bit (0).

If ALLCALL bit = 0 in MODE1 register, the device does not acknowledge the address programmed in register ALLCALLADR.

7.3.12 PWMALL — brightness control for all LEDn outputs

When programmed, the value in this register will be used for PWM duty cycle for all the LEDn outputs and will be reflected in PWM0 through PWM15 registers.

Table 25. PWMALL - brightness control for all LEDn outputs register (address 44h) bit description Legend: * default value.

| Address | Register | Bit | Access | Value | Description |
|---------|----------|-----|------------|------------|---------------------------------|
| 44h | PWMALL | 7:0 | write only | 0000 0000* | duty cycle for all LEDn outputs |

Remark: Write to any of the PWM0 to PWM15 registers will overwrite the value in corresponding PWMn register programmed by PWMALL.

7.3.13 IREFALL register: output current value for all LED outputs

The output current setting for all outputs is held in this register. When this register is written to or updated, all LED outputs will be set to a current corresponding to this register value.

Writes to IREF0 to IREF15 will overwrite the output current settings.

Table 26. IREFALL - Output gain control for all LED outputs (address 45h) bit description Legend: * default value.

| Address | Register | Bit | Access | Value | Description |
|---------|----------|------------------------|--------|-------|---|
| 45h | IREFALL | IREFALL 7:0 write only | | 00h* | Current gain setting for all LED outputs. |

7.3.14 LED driver constant current outputs

In LED display applications, PCA9955B provides nearly no current variations from channel to channel and from device to device. The maximum current skew between channels is less than ±4 % and less than ±6 % between devices.

16-channel Fm+ I²C-bus 57 mA constant current LED driver

7.3.14.1 Adjusting output current

The PCA9955B scales up the reference current (I_{ref}) set by the external resistor (R_{ext}) to sink the output current (I_O) at each output port. The maximum output current for the outputs can be set using R_{ext} . In addition, the constant value for current drive at each of the outputs is independently programmable using command registers IREF0 to IREF15. Alternatively, programming the IREFALL register allows all outputs to be set at one current value determined by the value in IREFALL register.


Equation 4 and Equation 5 can be used to calculate the minimum and maximum constant current values that can be programmed for the outputs for a chosen R_{ext} .

$$I_{O}_LED_MIN = \frac{900mV}{R_{ext}} \times \frac{1}{4} \, (\, \text{minimum constant current} \,) \, \, (4)$$

$$I_{O}_LED_MAX = \left(255 \times I_{O}_LED_MIN\right) = \left(\frac{900mV}{R_{ext}} \times \frac{255}{4}\right) (5)$$

For a given IREFx setting,
$$I_{O}$$
_ LED = $IREFx \times \frac{900mV}{R_{ext}} \times \frac{1}{4}$.

Remark: The open/short circuit source voltage is influenced by the external resistor R_{ext} and may falsely trigger the open condition if R_{ext} is bigger than 3.6 k Ω . Use 3 k Ω or smaller R_{ext} to guarantee no false open triggers; if smaller analog currents are required with R_{ext} larger than 3 k Ω then don't use the open/short detection.



 $I_{O(LEDn)}$ (mA) = IREFx × (0.9 / 4) / R_{ext} (k Ω)


maximum $I_{O(LEDn)}$ (mA) = 255 × (0.9 / 4) / R_{ext} (k Ω)

Remark: Default IREFx at power-up = 0 Figure 10. Maximum I_{LED} versus R_{ext}

Example 1: If $R_{ext} = 1 \text{ k}\Omega$, I_{O} _LED_MIN = 225 μ A, I_{O} _LED_MAX = 57.375 mA (as shown in Figure 11).


So each channel can be programmed with its individual IREFx in 256 steps and in 225 μ A increments to a maximum output current of 57.375 mA independently.

16-channel Fm+ I²C-bus 57 mA constant current LED driver



Example 2: If $R_{ext} = 2 k\Omega$, I_{O} LED_MIN = 112.5 μ A, I_{O} LED_MAX = 28.687 mA (as shown in Figure 12).

So each channel can be programmed with its individual IREFx in 256 steps and in 112.5 μ A increments to a maximum output channel of 28.687 mA independently.



7.3.15 LED error detection

The PCA9955B is capable of detecting an LED open or a short condition at its open-drain LED outputs. Users will recognize these faults by reading the status of a pair of error bits (ERRx) in error flag registers (EFLAGn) for each channel. Both LDRx value in LEDOUTx registers and IREFx value must be set to '00' for those unused LED output channels. If the output is selected to be fully on, individual dim, or individual and group dim, that channel will be tested.

The user can poll the ERROR status bit (bit 6 in MODE2 register) to check if there is a fault condition in any of the 16 channels. The EFLAGn registers can then be read to determine which channels are at fault and the type of fault in those channels. The error status reported by the EFLAGn register is real time information that will get self cleared once the error is fixed and write '1' to CLRERR bit (bit 4 in MODE2 register).

Remark: When LED outputs programmed with LDRx = 10 or 11 in LEDOUT[3:0] registers, checks for open and short-circuit will not occur if the PWM value in PWM0 to PWM15 registers is less than 8 or 255 (100 % duty cycle).

16-channel Fm+ I²C-bus 57 mA constant current LED driver

Remark: The open/short circuit source voltage is influenced by the external resistor R_{ext} and may falsely trigger the open condition if R_{ext} is bigger than 3.6 k Ω . Use 3 k Ω or smaller R_{ext} to guarantee no false open triggers; if smaller analog currents are required with R_{ext} larger than 3 k Ω then don't use the open/short detection.

Table 27. EFLAG0 to EFLAG3 - Error flag registers (address 46h to 49h) bit description Legend: * default value.

| Address | Register | Bit | Symbol | Access | Value | Description |
|---------|----------|-----|--------|--------|-------|-------------------------------|
| 46h | EFLAG0 | 7:6 | ERR3 | R only | 00* | Error status for LED3 output |
| | | 5:4 | ERR2 | R only | 00* | Error status for LED2 output |
| | | 3:2 | ERR1 | R only | 00* | Error status for LED1 output |
| | | 1:0 | ERR0 | R only | 00* | Error status for LED0 output |
| 47h | EFLAG1 | 7:6 | ERR7 | R only | 00* | Error status for LED7 output |
| | | 5:4 | ERR6 | R only | 00* | Error status for LED6 output |
| | | 3:2 | ERR5 | R only | 00* | Error status for LED5 output |
| | | 1:0 | ERR4 | R only | 00* | Error status for LED4 output |
| 48h | EFLAG2 | 7:6 | ERR11 | R only | 00* | Error status for LED11 output |
| | | 5:4 | ERR10 | R only | 00* | Error status for LED10 output |
| | | 3:2 | ERR9 | R only | 00* | Error status for LED9 output |
| | | 1:0 | ERR8 | R only | 00* | Error status for LED8 output |
| 49h | EFLAG3 | 7:6 | ERR15 | R only | 00* | Error status for LED15 output |
| | | 5:4 | ERR14 | R only | 00* | Error status for LED14 output |
| | | 3:2 | ERR13 | R only | 00* | Error status for LED13 output |
| | | 1:0 | ERR12 | R only | 00* | Error status for LED12 output |

Table 28. ERRx bit description

| LED error detection status | ERRx | | Description |
|----------------------------|------|-------|--------------------------------------|
| Bit 1 Bit 0 | | Bit 0 | |
| No error | 0 | 0 | In normal operation and no error |
| Short-circuit | 0 | 1 | Detected LED short-circuit condition |
| Open-circuit | 1 | 0 | Detected LED open-circuit condition |
| DNE (Do Not Exist) | 1 1 | | This condition does not exist |

7.3.15.1 Open-circuit detection principle

The PCA9955B LED open-circuit detection compares the effective current level I_O with the open load detection threshold current $I_{th(det)}$. If I_O is below the threshold $I_{th(det)}$, the PCA9955B detects an open load condition. This error status can be read out as an error flag through the EFLAGn registers. For open-circuit error detection of an output channel, that channel must be ON.

16-channel Fm+ I²C-bus 57 mA constant current LED driver

Table 29. Open-circuit detection

| State of output port | Condition of output current | Error status code | Description |
|----------------------|--|---|------------------------|
| OFF | I _O = 0 mA | 0 | detection not possible |
| ON | I _O < I _{th(det)} ^[1] | 1 | open-circuit |
| | $I_{O} \ge I_{th(det)}^{[1]}$ | this channel open error status bit is 0 | normal |

^[1] $I_{th(det)} = 0.5 \times I_{O(target)}$ (typical). This threshold may be different for each I/O and only depends on IREFx and R_{ext}

7.3.15.2 Short-circuit detection principle

The LED short-circuit detection compares the effective output voltage level (V_O) with the shorted-load detection threshold voltages $V_{th(trig)}$. If V_O is above the $V_{th(trig)}$ threshold, the PCA9955B detects a shorted-load condition. If V_O is below the $V_{th(trig)}$ threshold, no error is detected and error bit is set to '0'. This error status can be read out as an error flag through the EFLAGn registers. For short-circuit error detection of an output channel, that channel must be ON.

Table 30. Short-circuit detection

| State of output port | Condition of output voltage | Error status code | Description |
|----------------------|------------------------------|--|------------------------|
| OFF | - | 0 | detection not possible |
| ON | $V_O \ge V_{th(trig)}^{[1]}$ | 1 | short-circuit |
| | $V_{O} < V_{th(trig)}^{[1]}$ | this channel short error status bit is 0 | normal |

^[1] $V_{th} \cong 2.85 \text{ V}.$

Remark: The error status distinguishes between an LED short condition and an LED open condition. Upon detecting an LED short or open, the corresponding LED outputs should be turned OFF to prevent heat dissipation for a short in the chip. Although an open event will not be harmful, the outputs should be turned OFF for both occasions to repair the LED string.

7.3.16 Overtemperature protection

If the PCA9955B chip temperature exceeds its limit ($T_{th(otp)}$ rising, see <u>Table 33</u>), all output channels will be disabled until the temperature drops below its limit minus a small hysteresis ($T_{th(otp)}$ hysteresis, see <u>Table 33</u>). When an overtemperature situation is encountered, the OVERTEMP flag (bit 7) is set in the MODE2 register. Once the die temperature reduces below the $T_{th(otp)}$ rising - $T_{th(otp)}$ hysteresis, the chip will return to the same condition it was prior to the overtemperature event and the OVERTEMP flag will be cleared.

7.4 Active LOW output enable input

The active LOW output enable (OE) pin on PCA9955B allows to enable or disable all the LED outputs at the same time.

- When a LOW level is applied to \overline{OE} pin, all the LED outputs are enabled.
- When a HIGH level is applied to \overline{OE} pin, all the LED outputs are high-impedance.

The \overline{OE} pin can be used as a synchronization signal to switch on/off several PCA9955B devices at the same time when LED drive output state is set fully ON (LDRx = 01 in LEDOUTx register) in these devices. This requires an external clock reference that provides blinking period and the duty cycle.

16-channel Fm+ I²C-bus 57 mA constant current LED driver

The $\overline{\text{OE}}$ pin can also be used as an external dimming control signal. The frequency of the external clock must be high enough not to be seen by the human eye, and the duty cycle value determines the brightness of the LEDs.

Remark: Do not use \overline{OE} as an external blinking control signal when internal global blinking is selected (DMBLNK = 1, MODE2 register) since it will result in an undefined blinking pattern. Do not use \overline{OE} as an external dimming control signal when internal global dimming is selected (DMBLNK = 0, MODE2 register) since it will result in an undefined dimming pattern.

7.5 Power-on reset

When power is applied to V_{DD} , an internal power-on reset holds the PCA9955B in a reset condition until V_{DD} has reached V_{POR} . At this point, the reset condition is released and the PCA9955B registers and I^2C -bus state machine are initialized to their default states (all zeroes) causing all the channels to be deselected. Thereafter, V_{DD} must be pulled lower than 1 V and stay LOW for longer than 20 μ s. The device will reset itself, and allow 2 ms for the device to fully wake up.

7.6 Hardware reset recovery

When a reset of PCA9955B is activated using an active LOW input on the RESET pin, a reset pulse width of 2.5 µs minimum is required. The maximum wait time after RESET pin is released is 1.5 ms.

7.7 Software reset

The Software Reset Call (SWRST Call) allows all the devices in the I²C-bus to be reset to the power-up state value through a specific formatted I²C-bus command. To be performed correctly, it implies that the I²C-bus is functional and that there is no device hanging the bus.

The maximum wait time after software reset is 1 ms.


The SWRST Call function is defined as the following:

- 1. A START command is sent by the I²C-bus master.
- 2. The reserved General Call address '0000 000' with the R/W bit set to '0' (write) is sent by the I²C-bus master.
- 3. The PCA9955B device(s) acknowledge(s) after seeing the General Call address '0000 0000' (00h) only. If the R/W bit is set to '1' (read), no acknowledge is returned to the I²C-bus master.
- 4. Once the General Call address has been sent and acknowledged, the master sends 1 byte with 1 specific value (SWRST data byte 1):
- 5. Byte 1 = 06h: the PCA9955B acknowledges this value only. If byte 1 is not equal to 06h, the PCA9955B does not acknowledge it.

If more than 1 byte of data is sent, the PCA9955B does not acknowledge any more.

 Once the correct byte (SWRST data byte 1) has been sent and correctly acknowledged, the master sends a STOP condition to end the SWRST function: the PCA9955B then resets to the default value (power-up value) and is ready to be addressed again within the specified bus free time (t_{BUF}).

16-channel Fm+ I²C-bus 57 mA constant current LED driver



The I²C-bus master must interpret a non-acknowledge from the PCA9955B (at any time) as a 'SWRST Call Abort'. The PCA9955B does not initiate a reset of its registers. This happens only when the format of the SWRST Call sequence is not correct.

7.8 Individual brightness control with group dimming/blinking

A 31.25 kHz fixed frequency signal with programmable duty cycle (8 bits, 256 steps) is used to control individually the brightness for each LED.

On top of this signal, one of the following signals can be superimposed (this signal can be applied to the 16 LED outputs LED0 to LED15).

- A lower 122 Hz fixed frequency signal with programmable duty cycle (8 bits, 256 steps) is used to provide a global brightness control.
- A programmable frequency signal from 15 Hz to every 16.8 seconds (8 bits, 256 steps) with programmable duty cycle (8 bits, 256 steps) is used to provide a global blinking control.




Figure 14. Brightness + Group Dimming signals


16-channel Fm+ I²C-bus 57 mA constant current LED driver

8 Characteristics of the I²C-bus

The I²C-bus is for 2-way, 2-line communication between different ICs or modules. The two lines are a serial data line (SDA) and a serial clock line (SCL). Both lines must be connected to a positive supply via a pull-up resistor when connected to the output stages of a device. Data transfer may be initiated only when the bus is not busy.


8.1 Bit transfer

One data bit is transferred during each clock pulse. The data on the SDA line must remain stable during the HIGH period of the clock pulse as changes in the data line at this time will be interpreted as control signals (see Figure 15).




8.1.1 START and STOP conditions

Both data and clock lines remain HIGH when the bus is not busy. A HIGH-to-LOW transition of the data line while the clock is HIGH is defined as the START condition (S). A LOW-to-HIGH transition of the data line while the clock is HIGH is defined as the STOP condition (P) (see Figure 16).



8.2 System configuration

A device generating a message is a 'transmitter'; a device receiving is the 'receiver'. The device that controls the message is the 'master' and the devices which are controlled by the master are the 'slaves' (see Figure 17).



PCA9955B

All information provided in this document is subject to legal disclaimers.

© 2024 NXP B.V. All rights reserved.


16-channel Fm+ I²C-bus 57 mA constant current LED driver

8.3 Acknowledge

The number of data bytes transferred between the START and the STOP conditions from transmitter to receiver is not limited. Each byte of eight bits is followed by one acknowledge bit. The acknowledge bit is a HIGH level put on the bus by the transmitter, whereas the master generates an extra acknowledge related clock pulse.


A slave receiver which is addressed must generate an acknowledge after the reception of each byte. Also a master must generate an acknowledge after the reception of each byte that has been clocked out of the slave transmitter. The device that acknowledges has to pull down the SDA line during the acknowledge clock pulse, so that the SDA line is stable LOW during the HIGH period of the acknowledge related clock pulse; set-up time and hold time must be taken into account.


A master receiver must signal an end of data to the transmitter by not generating an acknowledge on the last byte that has been clocked out of the slave. In this event, the transmitter must leave the data line HIGH to enable the master to generate a STOP condition.



16-channel Fm+ I²C-bus 57 mA constant current LED driver

9 Bus transactions







1. Al1, Al0 = 00. See Table 6 for Auto-Increment options


Remark: Care should be taken to load the appropriate value here in the Al1 and Al0 bits of the MODE1 register for programming the part with the required Auto-Increment options

Figure 20. Write to all registers using the Auto-Increment feature



16-channel Fm+ I²C-bus 57 mA constant current LED driver






Remark: A read operation can be done without doing a write operation before it. In this case, the data sent out is from the register pointed to by the control register (written to during the last write operation) with the Auto-Increment options in the MODE1 register (written to during the last write operation)

Figure 23. Read of registers

16-channel Fm+ I²C-bus 57 mA constant current LED driver




- 2. ALLCALL bit in MODE1 register is previously set to 1 for this example
- 3. OCH bit in MODE2 register is previously set to 1 for this example

Figure 24. LED All Call I²C-bus address programming and LED All Call sequence example

16-channel Fm+ I²C-bus 57 mA constant current LED driver

10 Application design-in information



10.1 Thermal considerations

Figure 25. Typical application

Since the PCA9955B device integrates 16 linear current sources, thermal considerations should be taken into account to prevent overheating, which can cause the device to go into thermal shutdown.

Perhaps the major contributor for device's overheating is the LED forward voltage mismatch. This is because it can cause significant voltage differences between the LED strings of the same type (for example, 2 V to 3 V), which ultimately translates into higher power dissipation in the device. The voltage drop across the LED channels of the device is given by the difference between the supply voltage and the LED forward voltage of each LED string. Reducing this to a minimum (for example, 0.8 V) helps to keep the power dissipation down. Therefore LEDs binning is recommended to minimize LED voltage forward variation and reduce power dissipation in the device.

16-channel Fm+ I²C-bus 57 mA constant current LED driver

In order to ensure that the device will not go into thermal shutdown when operating under certain application conditions, its junction temperature (T_j) should be calculated to ensure that is below the overtemperature threshold limit (130 °C). The T_j of the device depends on the ambient temperature (T_{amb}) , device's total power dissipation (P_{tot}) , and thermal resistance.

The device junction temperature can be calculated by using the following equation:

$$T_i = T_{amb} + R_{th(i-a)} \times P_{tot}$$
(6)

where:

T_i = junction temperature

 T_{amb} = ambient temperature

 $R_{th(i-a)}$ = junction to ambient thermal resistance

 P_{tot} = (device) total power dissipation

An example of this calculation is show below:

Conditions:

```
\begin{split} T_{amb} &= 50 \text{ °C} \\ R_{th(j-a)} &= 39 \text{ °C/W (per JEDEC 51 standard for multilayer PCB)} \\ I_{LED} &= 30 \text{ mA / channel} \\ I_{DD(max)} &= 20 \text{ mA} \\ V_{DD} &= 5 \text{ V} \\ \text{LEDs per channel} &= 5 \text{ LEDs / channel} \\ \text{LED } V_{F(typ)} &= 3 \text{ V per LED (15 V total for 5 LEDs in series)} \\ \text{LED } V_F \text{ mismatch} &= 0.2 \text{ V per LED (1 V total for 5 LEDs in series)} \\ V_{reg(drv)} &= 0.8 \text{ V (This will be present only in the LED string with the highest LED forward voltage.)} \\ V_{sup} &= \text{LED } V_{F(typ)} + \text{LED } V_F \text{ mismatch} + V_{reg(drv)} &= 15 \text{ V} + 1 \text{ V} + 0.8 \text{ V} = 16.8 \text{ V} \end{split}
```

P_{tot} calculation:

```
\begin{split} &P_{tot} = IC\_power + LED \ drivers\_power; \\ &IC\_power = (I_{DD} \times V_{DD}) + (SDA\_V_{OL} \times I_{OL}) \\ &IC\_power = (0.02 \ A \times 5 \ V) + (0.4 \ V \times 0.03 \ A) = 0.112 \ W \\ &LED \ drivers\_power = [(16 - 1) \times (I_{LED}) \times (LED \ V_F \ mismatch + V_{reg(drv)})] + (I_{LED} \times V_{reg(drv)}) \\ &LED \ drivers\_power = [15 \times 0.03 \ A \times (1 \ V + 0.8 \ V)] + (0.03 \ A \times 0.8 \ V) = 0.834 \ W \\ &P_{tot} = 0.112 \ W + 0.834 \ W = 0.946 \ W \end{split}
```

T_i calculation:

```
T_j = T_{amb} + R_{th(j-a)} \times P_{tot}

T_i = 50 \text{ °C} + (39 \text{ °C/W} \times 0.946 \text{ W}) = 86.894 \text{ °C}
```

This confirms that the junction temperature is below the minimum overtemperature threshold of 130 °C, which ensures the device will not go into thermal shutdown under these conditions.

It is important to mention that the value of the thermal resistance junction-to-ambient ($R_{th(j-a)}$) strongly depends in the PCB design. Therefore, the thermal pad of the device should be attached to a big enough PCB copper area to ensure proper thermal dissipation (similar to JEDEC 51 standard). Several thermal vias in the PCB thermal pad should be used as well to increase the effectiveness of the heat dissipation (for example, 15 thermal vias). The thermal vias should be distributed evenly in the PCB thermal pad.

Finally, it is important to point out that this calculation should be taken as a reference only and therefore evaluations should still be performed under the application environment and conditions to confirm proper system operation.

PCA9955E

16-channel Fm+ I²C-bus 57 mA constant current LED driver

11 Limiting values

Table 31. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

| Symbol | Parameter | Conditions | Min | Max | Unit |
|-----------------------|--------------------------------|--|-----------------------|-------|------|
| V_{DD} | supply voltage | | -0.5 | +6.0 | V |
| V _{I/O} | voltage on an input/output pin | | V _{SS} - 0.5 | 5.5 | V |
| V _{drv(LED)} | LED driver voltage | | V _{SS} - 0.5 | 20 | V |
| I _{O(LEDn)} | output current on pin LEDn | | - | 65 | mA |
| I _{SS} | ground supply current | | - | 1.0 | А |
| P _{tot} | total power dissipation | T _{amb} = 25 °C | - | 2.56 | W |
| | | T _{amb} = 85 °C | - | 1.03 | W |
| | | T _{amb} = 105 °C | - | 0.513 | W |
| T _{stg} | storage temperature | | -65 | +150 | °C |
| T _{amb} | ambient temperature | operating for non AEC- Q100 or AEC-Q100 | -40 | +105 | °C |
| Tj | junction temperature | | -40 | +125 | °C |

16-channel Fm+ I²C-bus 57 mA constant current LED driver

12 Thermal characteristics

Table 32. Thermal characteristics

| Symbol | Parameter | Conditions | | Тур | Unit |
|---------------|---|------------|-----|-----|------|
| $R_{th(j-a)}$ | thermal resistance from junction to ambient | HTSSOP28 | [1] | 39 | °C/W |

^[1] Per JEDEC 51 standard for multilayer PCB and Wind Speed (m/s) = 0.

16-channel Fm+ I²C-bus 57 mA constant current LED driver

13 Static characteristics

Table 33. Static characteristics

 V_{DD} = 3 V to 5.5 V; V_{SS} = 0 V; T_{amb} = -40 °C to +105 °C; unless otherwise specified.

| Symbol | Parameter | Conditions | | Min | Typ ^[1] | Max | Unit |
|-----------------------|--------------------------------|---|--------|--------------------|--------------------|---------------------|------|
| Supply | | | | | | | |
| V_{DD} | supply voltage | | | 3 | - | 5.5 | V |
| I _{DD} | supply current | on pin V _{DD} ; operating mode; f _{SCL} = 1 MHz | | | | | 1 |
| | | R_{ext} = 2 k Ω ; LED[15:0] = off; IREFx = 00h | | - | 11 | 12 | mA |
| | | R_{ext} = 1 k Ω ; LED[15:0] = off; IREFx = 00h | | - | 13 | 14 | mA |
| | | R_{ext} = 2 k Ω ; LED[15:0] = on; IREFx = FFh | | - | 15 | 19 | mA |
| | | R_{ext} = 1 kΩ; LED[15:0] = on; IREFx = FFh | | - | 17 | 21 | mA |
| I _{stb} | standby current | on pin V_{DD} ; no load; f_{SCL} = 0 Hz; MODE1[4] = 1; V_{I} = V_{DD} | | | | | |
| | | V _{DD} = 3.3 V | | - | 170 | 600 | μA |
| | | V _{DD} = 5.5 V | | - | 170 | 700 | μA |
| V _{POR} | power-on reset voltage | no load; V _I = V _{DD} or V _{SS} | | - | 2 | - | V |
| V _{PDR} | power-down reset voltage | no load; V _I = V _{DD} or V _{SS} | [2][3] | - | 1 | - | V |
| Input SC | L; input/output SDA | | | | | | |
| V _{IL} | LOW-level input voltage | | | -0.5 | - | +0.3V _{DD} | V |
| V _{IH} | HIGH-level input voltage | | | 0.7V _{DD} | - | 5.5 | V |
| I _{OL} | LOW-level output current | V _{OL} = 0.4 V; V _{DD} = 3 V | | 20 | - | - | mA |
| | | V _{OL} = 0.4 V; V _{DD} = 5 V | | 30 | - | - | mA |
| IL | leakage current | $V_I = V_{DD}$ or V_{SS} | | -1 | - | +1 | μΑ |
| C _i | input capacitance | V _I = V _{SS} | | - | 6 | 10 | pF |
| Current of | controlled outputs (LED[15:0]) | ' | | I | | 1 | |
| I _{O(LEDn)} | output current on pin LEDn | $V_{O} = 0.8 \text{ V}$; IREFx = 80h; $R_{ext} = 1 \text{ k}\Omega$ | | 25 | - | 30 | mA |
| | | $V_O = 0.8 \text{ V}$; IREFx = FFh; $R_{ext} = 1 \text{ k}\Omega$ | [3] | 50 | - | 60 | mA |
| ΔI _O | output current variation | V_{DD} = 3.0 V; T_{amb} = 25 °C; V_{O} = 0.8 V; IREFx = 80h; R_{ext} = 1 kΩ; guaranteed by design | | | | | |
| | | between bits (different ICs, same channel) | [4] | - | - | ±6 | % |
| | | between bits (2 channels, same IC) | [5] | - | - | ±4 | % |
| V _{reg(drv)} | driver regulation voltage | minimum regulation voltage; IREFx = FFh; R_{ext} = 1 k Ω | | 0.8 | 1 | 20 | V |

16-channel Fm+ I²C-bus 57 mA constant current LED driver

Table 33. Static characteristics...continued

 V_{DD} = 3 V to 5.5 V; V_{SS} = 0 V; T_{amb} = -40 °C to +105 °C; unless otherwise specified.

| Symbol | Parameter | Conditions | | Min | Typ ^[1] | Max | Unit |
|----------------------|----------------------------|---|-----|--------------------|--------------------|---------------------|------|
| I _{L(off)} | off-state leakage current | V _O = 20 V | | - | - | 1 | μΑ |
| V_{trip} | trip voltage | short LED protection; Error flag will trip during verification test if $V_O \ge V_{trip}$; $R_{ext} = 1 \text{ k}\Omega$ | | 2.7 | 2.85 | - | V |
| OE input | , RESET input | · | ' | | | | - |
| V _{IL} | LOW-level input voltage | | | -0.5 | - | +0.3V _{DD} | V |
| V _{IH} | HIGH-level input voltage | | | 0.7V _{DD} | - | 5.5 | V |
| ILI | input leakage current | | | -1 | - | +1 | μΑ |
| Ci | input capacitance | | [3] | - | 3.7 | 5 | pF |
| Address | inputs AD2, AD1, AD0 | · | ' | | | | |
| VI | input voltage | voltage on an input pin | | -0.5 | - | 5.5 | V |
| I _{LI} | input leakage current | | | -1 | - | +1 | μΑ |
| C _i | input capacitance | | [3] | - | 3.7 | 5 | pF |
| Overtem | perature protection | | • | • | • | • | |
| T _{th(otp)} | overtemperature protection | rising | [3] | 130 | - | 150 | °C |
| | threshold temperature | hysteresis | [3] | 15 | - | 30 | °C |
| | | | | | | | |

- Typical limits at V_{DD} = 3.3 V, T_{amb} = 25 °C.
- V_{DD} must be lowered to 1 V in order to reset part.
- Value not tested in production, but guaranteed by design and characterization.
- Part-to-part mismatch is calculated:

Part-to-part mismatch is calculated:
$$\Delta\% = \left(\frac{\binom{IO(LED0)^{+I}O(LED1)^{+...+I}O(LED14)^{+I}O(LED15)}{16} - idealoutputcurrent}{idealoutputcurrent} \right) \times 100$$

where 'ideal output current' = 28.68 mA (R_{ext} = 1 k Ω , IREFx = 80h).

Channel-to-channel mismatch is calculated:

$$\Delta\% = \left(\frac{I_{O(LEDn)}(\text{where n = 0 to 15})}{\left(\frac{I_{O(LED0)}+I_{O(LED1}+...+I_{O(LED14)}+I_{O(LED15)}}{16}\right)} - 1\right) \times 100$$

16-channel Fm+ I²C-bus 57 mA constant current LED driver

14 Dynamic characteristics

Table 34. Dynamic characteristics

| Symbol | Parameter | Conditions | | Standard- mode I ² C-bus | | Fast-mode I ² C-bus | | Fast-mode Plus I ² C-bus | | Unit |
|---------------------|---|------------|--------|--|------|---------------------------------------|-----|--|------|------|
| | | | | Min | Max | Min | Max | Min | Max | |
| f _{SCL} | SCL clock frequency | | | 0 | 100 | 0 | 400 | 0 | 1000 | kHz |
| t _{BUF} | bus free time between a STOP and START condition | | | 4.7 | - | 1.3 | - | 0.5 | - | μs |
| t _{HD;STA} | hold time (repeated) START condition | | | 4.0 | - | 0.6 | - | 0.26 | - | μs |
| t _{SU;STA} | set-up time for a repeated START condition | | | 4.7 | - | 0.6 | - | 0.26 | - | μs |
| t _{su;sto} | set-up time for STOP condition | | | 4.0 | - | 0.6 | - | 0.26 | - | μs |
| t _{HD;DAT} | data hold time | | | 0 | - | 0 | - | 0 | - | ns |
| t _{VD;ACK} | data valid acknowledge time | | [1] | 0.3 | 3.45 | 0.1 | 0.9 | 0.05 | 0.45 | μs |
| t _{VD;DAT} | data valid time | | [2] | 0.3 | 3.45 | 0.1 | 0.9 | 0.05 | 0.45 | μs |
| t _{SU;DAT} | data set-up time | | | 250 | - | 100 | - | 50 | - | ns |
| t _{LOW} | LOW period of the SCL clock | | | 4.7 | - | 1.3 | - | 0.5 | - | μs |
| t _{HIGH} | HIGH period of the SCL clock | | | 4.0 | - | 0.6 | - | 0.26 | - | μs |
| t _f | fall time of both SDA and SCL signals | | [3][4] | - | 300 | 20 + 0.1C _b ^[5] | 300 | - | 120 | ns |
| t _r | rise time of both SDA and SCL signals | | | - | 1000 | 20 + 0.1C _b ^[5] | 300 | - | 120 | ns |
| t _{SP} | pulse width of spikes that must be suppressed by the input filter | | [6] | - | 50 | - | 50 | - | 50 | ns |
| t _{w(rst)} | reset pulse width | | | 2.5 | - | 2.5 | - | 2.5 | - | μs |

^[1] t_{VD:ACK} = time for Acknowledgement signal from SCL LOW to SDA (out) LOW.

^[2] t_{VD;DAT} = minimum time for SDA data out to be valid following SCL LOW.


^[3] A master device must internally provide a hold time of at least 300 ns for the SDA signal (refer to the V_{IL} of the SCL signal) in order to bridge the undefined region of SCL's falling edge.

^[4] The maximum t_f for the SDA and SCL bus lines is specified at 300 ns. The maximum fall time (t_f) for the SDA output stage is specified at 250 ns. This allows series protection resistors to be connected between the SDA and the SCL pins and the SDA/SCL bus lines without exceeding the maximum specified t_f.

^[5] C_b = total capacitance of one bus line in pF.


^[6] Input filters on the SDA and SCL inputs suppress noise spikes less than 50 ns.

16-channel Fm+ I²C-bus 57 mA constant current LED driver



16-channel Fm+ I²C-bus 57 mA constant current LED driver

Test information



R_L = Load resistor for LEDn


C_L = Load capacitance includes jig and probe capacitance

 R_T = Termination resistance should be equal to the output impedance Z_0 of the pulse generators

Figure 28. Test circuitry for switching times

16-channel Fm+ I²C-bus 57 mA constant current LED driver

16 Package outline



16-channel Fm+ I²C-bus 57 mA constant current LED driver

17 Handling information

All input and output pins are protected against ElectroStatic Discharge (ESD) under normal handling. When handling ensure that the appropriate precautions are taken as described in *JESD625-A* or equivalent standards.

16-channel Fm+ I²C-bus 57 mA constant current LED driver

18 Soldering of SMD packages

This text provides a very brief insight into a complex technology. A more in-depth account of soldering ICs can be found in Application Note *AN10365 "Surface mount reflow soldering description"*.

18.1 Introduction to soldering

Soldering is one of the most common methods through which packages are attached to Printed Circuit Boards (PCBs), to form electrical circuits. The soldered joint provides both the mechanical and the electrical connection. There is no single soldering method that is ideal for all IC packages. Wave soldering is often preferred when through-hole and Surface Mount Devices (SMDs) are mixed on one printed wiring board; however, it is not suitable for fine pitch SMDs. Reflow soldering is ideal for the small pitches and high densities that come with increased miniaturization.

18.2 Wave and reflow soldering

Wave soldering is a joining technology in which the joints are made by solder coming from a standing wave of liquid solder. The wave soldering process is suitable for the following:

- Through-hole components
- · Leaded or leadless SMDs, which are glued to the surface of the printed circuit board

Not all SMDs can be wave soldered. Packages with solder balls, and some leadless packages which have solder lands underneath the body, cannot be wave soldered. Also, leaded SMDs with leads having a pitch smaller than ~0.6 mm cannot be wave soldered, due to an increased probability of bridging.

The reflow soldering process involves applying solder paste to a board, followed by component placement and exposure to a temperature profile. Leaded packages, packages with solder balls, and leadless packages are all reflow solderable.

Key characteristics in both wave and reflow soldering are:

- · Board specifications, including the board finish, solder masks and vias
- · Package footprints, including solder thieves and orientation
- The moisture sensitivity level of the packages
- · Package placement
- · Inspection and repair
- · Lead-free soldering versus SnPb soldering

18.3 Wave soldering

Key characteristics in wave soldering are:

- Process issues, such as application of adhesive and flux, clinching of leads, board transport, the solder wave parameters, and the time during which components are exposed to the wave
- Solder bath specifications, including temperature and impurities

18.4 Reflow soldering

Key characteristics in reflow soldering are:

- Lead-free versus SnPb soldering; note that a lead-free reflow process usually leads to higher minimum peak temperatures (see <u>Figure 30</u>) than a SnPb process, thus reducing the process window
- Solder paste printing issues including smearing, release, and adjusting the process window for a mix of large and small components on one board

PCA9955E

16-channel Fm+ I²C-bus 57 mA constant current LED driver

Reflow temperature profile; this profile includes preheat, reflow (in which the board is heated to the peak
temperature) and cooling down. It is imperative that the peak temperature is high enough for the solder to
make reliable solder joints (a solder paste characteristic). In addition, the peak temperature must be low
enough that the packages and/or boards are not damaged. The peak temperature of the package depends on
package thickness and volume and is classified in accordance with <u>Table 35</u> and <u>Table 36</u>

Table 35. SnPb eutectic process (from J-STD-020D)


| Package thickness (mm) | Package reflow temperature (°C) | | | | |
|------------------------|---------------------------------|-------|--|--|--|
| | Volume (mm³) | | | | |
| | < 350 | ≥ 350 | | | |
| < 2.5 | 235 | 220 | | | |
| ≥ 2.5 | 220 | 220 | | | |

Table 36. Lead-free process (from J-STD-020D)

| Package thickness (mm) | Package reflow temperature (°C) | | | | | |
|------------------------|---------------------------------|-------------|--------|--|--|--|
| | Volume (mm³) | | | | | |
| | < 350 | 350 to 2000 | > 2000 | | | |
| < 1.6 | 260 | 260 | 260 | | | |
| 1.6 to 2.5 | 260 | 250 | 245 | | | |
| > 2.5 | 250 | 245 | 245 | | | |

Moisture sensitivity precautions, as indicated on the packing, must be respected at all times.


Studies have shown that small packages reach higher temperatures during reflow soldering, see Figure 30.



For further information on temperature profiles, refer to Application Note AN10365 "Surface mount reflow soldering description".

16-channel Fm+ I²C-bus 57 mA constant current LED driver

19 Soldering: PCB footprints



16-channel Fm+ I²C-bus 57 mA constant current LED driver

20 Abbreviations

Table 37. Abbreviations

| Acronym | Description |
|----------------------|--|
| ACK | Acknowledge |
| CDM | Charged-Device Model |
| DAC | Digital-to-Analog Converter |
| DUT | Device Under Test |
| ESD | ElectroStatic Discharge |
| FET | Field-Effect Transistor |
| НВМ | Human Body Model |
| I ² C-bus | Inter-Integrated Circuit bus |
| LED | Light Emitting Diode |
| LSB | Least Significant Bit |
| MCU | MicroController Unit |
| MSB | Most Significant Bit |
| NMOS | Negative-channel Metal-Oxide Semiconductor |
| PCB | Printed-Circuit Board |
| PMOS | Positive-channel Metal-Oxide Semiconductor |
| PWM | Pulse Width Modulation |
| RGB | Red/Green/Blue |
| RGBA | Red/Green/Blue/Amber |
| SMBus | System Management Bus |

16-channel Fm+ I²C-bus 57 mA constant current LED driver

21 Revision history

Table 38. Revision history

| Document ID | Release date | Description |
|----------------|-------------------|---|
| PCA9955B v.2.3 | 27 September 2024 | <u>Section 2</u> : Added part information |
| PCA9955B v.2.2 | 10 June 2020 | <u>Section 2, Section 7.3.14.1, Section 7.3.15</u> : Added clarification regarding size of R _{ext} at which the LED open/short detection no longer works |
| PCA9955B v.2.1 | 2 May 2017 | Extended operating temperature range up to 105 °C |
| PCA9955B v.2 | 20 November 2015 | Corrected Figure 1 Table 3: Corrected description for RESET pin Corrected Figure 25; added Figure note 3 |
| PCA9955B v.1 | 22 June 2015 | Product data sheet |

16-channel Fm+ I²C-bus 57 mA constant current LED driver

Legal information

Data sheet status

| Document status ^{[1][2]} | Product status ^[3] | Definition |
|-----------------------------------|-------------------------------|---|
| Objective [short] data sheet | Development | This document contains data from the objective specification for product development. |
| Preliminary [short] data sheet | Qualification | This document contains data from the preliminary specification. |
| Product [short] data sheet | Production | This document contains the product specification. |

- [1] Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions".
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL https://www.nxp.com.

Definitions

Draft — A draft status on a document indicates that the content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included in a draft version of a document and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between NXP Semiconductors and its customer, unless NXP Semiconductors and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the NXP Semiconductors product is deemed to offer functions and qualities beyond those described in the Product data sheet.

Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. NXP Semiconductors takes no responsibility for the content in this document if provided by an information source outside of NXP Semiconductors.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of NXP Semiconductors.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors and its suppliers accept no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at https://www.nxp.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

PCA9955B

All information provided in this document is subject to legal disclaimers.

© 2024 NXP B.V. All rights reserved.

16-channel Fm+ I²C-bus 57 mA constant current LED driver

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Suitability for use in non-automotive qualified products — Unless this document expressly states that this specific NXP Semiconductors product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. NXP Semiconductors accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without NXP Semiconductors' warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond NXP Semiconductors' specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies NXP Semiconductors for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond NXP Semiconductors' standard warranty and NXP Semiconductors' product specifications.

HTML publications — An HTML version, if available, of this document is provided as a courtesy. Definitive information is contained in the applicable document in PDF format. If there is a discrepancy between the HTML document and the PDF document, the PDF document has priority.

Translations — A non-English (translated) version of a document, including the legal information in that document, is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

Security — Customer understands that all NXP products may be subject to unidentified vulnerabilities or may support established security standards or specifications with known limitations. Customer is responsible for the design and operation of its applications and products throughout their lifecycles to reduce the effect of these vulnerabilities on customer's applications and products. Customer's responsibility also extends to other open and/or proprietary technologies supported by NXP products for use in customer's applications. NXP accepts no liability for any vulnerability. Customer should regularly check security updates from NXP and follow up appropriately. Customer shall select products with security features that best meet rules, regulations, and standards of the intended application and make the ultimate design decisions regarding its products and is solely responsible for compliance with all legal, regulatory, and security related requirements concerning its products, regardless of any information or support that may be provided by NXP.

NXP has a Product Security Incident Response Team (PSIRT) (reachable at PSIRT@nxp.com) that manages the investigation, reporting, and solution release to security vulnerabilities of NXP products.

NXP B.V. — NXP B.V. is not an operating company and it does not distribute or sell products.

Trademarks

Notice: All referenced brands, product names, service names, and trademarks are the property of their respective owners.

NXP — wordmark and logo are trademarks of NXP B.V.

I2C-bus — logo is a trademark of NXP B.V.

16-channel Fm+ I²C-bus 57 mA constant current LED driver

Tables

| Tab. 1. Tab. 2. Tab. 3. | Ordering information | Tab. 19. | GRAD_MODE_SEL[0:1] - Gradation mode select register for channel 15 to channel 0 (address 38h, 39h) bit description | 25 |
|-------------------------------|---|----------|--|----|
| Tab. 3. | Quinary input pad connection | Tab. 20. | GRAD_GRP_SEL[0:3] - Gradation group | 23 |
| Tab. 5. | I2C-bus slave address | 1ab. 20. | select register for channel 15 to channel | |
| тар. 5. Тар. 6. | | | • | |
| | Auto-Increment options | | 0 (address 3Ah, 3Bh, 3Ch, 3Dh) bit | 26 |
| Tab. 7. | Register summary | Tab 21 | description | 20 |
| Tab. 8. | MODE1 - Mode register 1 (address 00h) bit description18 | Tab. 21. | GRAD_CNTL - Gradation control register for group 3 to group 0 (address 3Eh) bit | |
| Tab. 9. | MODE2 - Mode register 2 (address 01h) bit | | description | 26 |
| | description18 | Tab. 22. | OFFSET - LEDn output delay offset | |
| Tab. 10. | LEDOUT0 to LEDOUT3 - LED driver output | | register (address 3Fh) bit description | 29 |
| | state registers (address 02h to 05h) bit | Tab. 23. | SUBADR1 to SUBADR3 - I2C-bus | |
| | description20 | | subaddress registers 1 to 3 (address 40h to | |
| Tab. 11. | GRPPWM - Group brightness control | | 42h) bit description | 30 |
| | register (address 06h) bit description21 | Tab. 24. | ALLCALLADR - LED All Call I2C- | |
| Tab. 12. | GRPFREQ - Group frequency register | | bus address register (address 43h) bit | |
| | (address 07h) bit description21 | | description | 31 |
| Tab. 13. | PWM0 to PWM15 - PWM registers 0 to 15 | Tab. 25. | PWMALL - brightness control for all | |
| | (address 08h to 17h) bit description21 | | LEDn outputs register (address 44h) bit | |
| Tab. 14. | IREF0 to IREF15 - LED output gain | | description | 31 |
| | control registers (address 18h to 27h) bit | Tab. 26. | IREFALL - Output gain control for all LED | |
| | description22 | | outputs (address 45h) bit description | 31 |
| Tab. 15. | RAMP_RATE_GRP[0:3] - Ramp enable | Tab. 27. | EFLAG0 to EFLAG3 - Error flag registers | |
| | and rate control registers (address 28h, | | (address 46h to 49h) bit description | 34 |
| | 2Ch, 30h, 34h) for each group bit | Tab. 28. | ERRx bit description | 34 |
| | description24 | Tab. 29. | Open-circuit detection | 35 |
| Tab. 16. | STEP_TIME_GRP[0:3] - Step time control | Tab. 30. | Short-circuit detection | 35 |
| | registers (address 29h, 2Dh, 31h, 35h) for | Tab. 31. | Limiting values | 45 |
| | each group bit description24 | Tab. 32. | Thermal characteristics | |
| Tab. 17. | HOLD_CNTL_GRP[0:3] - Hold ON and | Tab. 33. | Static characteristics | 47 |
| | OFF enable and time control registers | Tab. 34. | Dynamic characteristics | 49 |
| | (address 2Ah, 2Eh, 32h, 36h) for each | Tab. 35. | SnPb eutectic process (from J-STD-020D) | 55 |
| | group bit description24 | Tab. 36. | Lead-free process (from J-STD-020D) | |
| Tab. 18. | IREF_GRP[0:3] - Final and hold ON output | Tab. 37. | Abbreviations | |
| | gain setting registers (address 2Bh, 2Fh, | Tab. 38. | Revision history | |
| | 33h, 37h) for each group bit description25 | | - | |

16-channel Fm+ I²C-bus 57 mA constant current LED driver

Figures

| Block diagram of PCA9955B6 | Fig. 19. | Write to a specific register | 40 |
|---|--|--|--------------------------------|
| | Fig. 20. | Write to all registers using the Auto- | |
| | | Increment feature | 40 |
| | Fig. 21. | Multiple writes to Individual Brightness | |
| Linear and exponential adjustment curves 19 | | registers only using the Auto-Increment | |
| Gradation timing23 | | feature | 40 |
| Ramp calculation example 127 | Fig. 22. | Read all registers using the Auto-Increment | |
| Ramp calculation example 228 | | feature | 41 |
| | Fig. 23. | Read of registers | 41 |
| | Fig. 24. | | |
| Maximum ILED versus Rext32 | | and LED All Call sequence example | 42 |
| IO(target) versus IREFx value with Rext = 1 | Fig. 25. | | |
| | Fig. 26. | | |
| IO(target) versus IREFx value with Rext = 2 | Fig. 27. | I2C-bus timing diagram | |
| kΩ33 | Fig. 28. | Test circuitry for switching times | 51 |
| SWRST Call37 | Fig. 29. | Package outline SOT1172-3 (HTSSOP28) | |
| Brightness + Group Dimming signals37 | Fig. 30. | Temperature profiles for large and small | |
| Bit transfer38 | | components | 55 |
| Definition of START and STOP conditions 38 | Fig. 31. | | |
| | • | reflow soldering | 56 |
| Acknowledgement on the I2C-bus | | - | |
| | Pin configuration for HTSSOP28 7 PCA9955B slave address 13 Control register 14 Linear and exponential adjustment curves 19 Gradation timing 23 Ramp calculation example 1 27 Ramp calculation example 2 28 Gradation output waveform in single shot or continuous mode 29 Maximum ILED versus Rext 32 IO(target) versus IREFx value with Rext = 1 k Ω 33 IO(target) versus IREFx value with Rext = 2 k Ω 33 SWRST Call 37 Brightness + Group Dimming signals 37 Bit transfer 38 Definition of START and STOP conditions 38 System configuration 38 | Pin configuration for HTSSOP287Fig. 20.PCA9955B slave address13Control register14Fig. 21.Linear and exponential adjustment curves19Gradation timing23Ramp calculation example 127Fig. 22.Ramp calculation example 228Gradation output waveform in single shotFig. 23.or continuous mode29Fig. 24.Maximum ILED versus Rext32IO(target) versus IREFx value with Rext = 1Fig. 25.kΩ33Fig. 26.IO(target) versus IREFx value with Rext = 2Fig. 27.kΩ33Fig. 28.SWRST Call37Fig. 29.Brightness + Group Dimming signals37Fig. 30.Bit transfer38Fig. 31.Definition of START and STOP conditions38Fig. 31. | Pin configuration for HTSSOP28 |

16-channel Fm+ I²C-bus 57 mA constant current LED driver

Contents

| 1 | General description | 1 | 7.3.14.1 | Adjusting output current | 32 |
|---------|--|----|----------|--|----|
| 2 | Features and benefits | | 7.3.15 | LED error detection | |
| 3 | Applications | | 7.3.15.1 | Open-circuit detection principle | 34 |
| 4 | Ordering information | 5 | 7.3.15.2 | Short-circuit detection principle | 35 |
| 4.1 | Ordering options | | 7.3.16 | Overtemperature protection | |
| 5 | Block diagram | 6 | 7.4 | Active LOW output enable input | 35 |
| 6 | Pinning information | 7 | 7.5 | Power-on reset | |
| 6.1 | Pinning | 7 | 7.6 | Hardware reset recovery | 36 |
| 6.2 | Pin description | 7 | 7.7 | Software reset | 36 |
| 7 | Functional description | | 7.8 | Individual brightness control with group | |
| 7.1 | Device addresses | 9 | | dimming/blinking | 37 |
| 7.1.1 | Regular I2C-bus slave address | 9 | 8 | Characteristics of the I2C-bus | |
| 7.1.2 | LED All Call I2C-bus address | 13 | 8.1 | Bit transfer | 38 |
| 7.1.3 | LED Sub Call I2C-bus addresses | 14 | 8.1.1 | START and STOP conditions | 38 |
| 7.2 | Control register | 14 | 8.2 | System configuration | 38 |
| 7.3 | Register definitions | 15 | 8.3 | Acknowledge | |
| 7.3.1 | MODE1 — Mode register 1 | | 9 | Bus transactions | 40 |
| 7.3.2 | MODE2 — Mode register 2 | 18 | 10 | Application design-in information | 43 |
| 7.3.3 | LEDOUT0 to LEDOUT3, LED driver output | | 10.1 | Thermal considerations | 43 |
| | state | 20 | 11 | Limiting values | 4 |
| 7.3.4 | GRPPWM, group duty cycle control | 21 | 12 | Thermal characteristics | 46 |
| 7.3.5 | GRPFREQ, group frequency | 21 | 13 | Static characteristics | 47 |
| 7.3.6 | PWM0 to PWM15, individual brightness | | 14 | Dynamic characteristics | 49 |
| | control | 21 | 15 | Test information | 51 |
| 7.3.7 | IREF0 to IREF15, LED output current value | | 16 | Package outline | 52 |
| | registers | 22 | 17 | Handling information | 53 |
| 7.3.8 | Gradation control | 23 | 18 | Soldering of SMD packages | 54 |
| 7.3.8.1 | RAMP_RATE_GRP0 to RAMP_RATE_ | | 18.1 | Introduction to soldering | 54 |
| | GRP3, ramp rate control registers | 24 | 18.2 | Wave and reflow soldering | |
| 7.3.8.2 | STEP_TIME_GRP0 to STEP_TIME_GRP3, | | 18.3 | Wave soldering | |
| | step time control registers | 24 | 18.4 | Reflow soldering | |
| 7.3.8.3 | HOLD_CNTL_GRP0 to HOLD_CNTL_ | | 19 | Soldering: PCB footprints | |
| | GRP3, hold ON and OFF control registers | 24 | 20 | Abbreviations | |
| 7.3.8.4 | IREF_GRP0 to IREF_GRP3, output gain | | 21 | Revision history | |
| | control | 25 | | Legal information | 59 |
| 7.3.8.5 | GRAD_MODE_SEL0 to GRAD_MODE_ | | | | |
| | SEL1, Gradation mode select registers | 25 | | | |
| 7.3.8.6 | GRAD_GRP_SEL0 to GRAD_GRP_SEL3, | | | | |
| | Gradation group select registers | | | | |
| 7.3.8.7 | GRAD_CNTL, Gradation control register | 26 | | | |
| 7.3.8.8 | Ramp control — equation and calculation | | | | |
| | example | 27 | | | |
| 7.3.9 | OFFSET — LEDn output delay offset | | | | |
| | register | 29 | | | |
| 7.3.10 | LED Sub Call I2C-bus addresses for | | | | |
| | PCA9955B | 30 | | | |
| 7.3.11 | ALLCALLADR, LED All Call I2C-bus | | | | |
| | address | 31 | | | |
| 7.3.12 | PWMALL — brightness control for all LEDn | | | | |
| | outputs | 31 | | | |
| 7.3.13 | IREFALL register: output current value for | | | | |
| | all LED outputs | | | | |
| 7.3.14 | LED driver constant current outputs | 31 | | | |

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.